

## \* TEXAS INSTRUMENTS Bill of Materials

TIDA-00324 - POL Multiphase (3-phase), 120A Power Reference Design

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
1	1	!PCB		Printed Circuit Board	Any	PMP9738			
2	3	C1, C2, C3	470uF	CAP, AL, 470uF, 35V, +/-20%, TH	Rubycon	35ZL470MEFC10X20		10x20	
3	4	C4, C5, C6, C7	0.1uF	CAP, CERM, 0.1uF, 50V, +/-20%, X7R, 0402	TDK	C1005X7R1H104M		0402	
4	1	C8	1uF	CAP, CERM, 1uF, 10V, +/-10%, X5R, 0402	MuRata	GRM155R61A105KE15D		0402	
5	10	C9, C10, C11, C12, C13, C14, C15, C16, C17, C18	470uF	CAP, AL, 470uF, 2.5V, +/-20%, 9 ohm, SMD	Panasonic	EEFSX0E471ER		7.3x1.8x4.3mm	
6	10	C19, C20, C21, C22, C23, C24, C25, C26, C27, C28	100uF	CAP, CERM, 100uF, 6.3V, +/- 20%, X5R, 1210	Kemet	C1210C107M9PACTU		1210	
7	2	C29, C31	10uF	CAP, CERM, 10uF, 25V, +/-20%, X7R, 1210	TDK	C3225X7R1E106M		1210	
8	1	C30	1uF	CAP, CERM, 1uF, 25V, +/-10%, X7R, 0603	MuRata	GRM188R71E105KA12D		0603	
9	1	C32	15pF	CAP, CERM, 15pF, 50V, +/-5%, C0G/NP0, 0402	MuRata	GRM1555C1H150JA01D		0402	
10	1	C41	4700pF	CAP, CERM, 4700pF, 100V, +/- 10%, X7R, 0603	AVX	06031C472KAT2A		0603	
11	1	C42	1000pF	CAP, CERM, 1000pF, 50V, +/- 10%, X7R, 0402	TDK	C1005X7R1H102K		0402	
12	4	C43, C44, C45, C48	1uF	CAP, CERM, 1uF, 25V, +/-10%, X5R, 0603	TDK	C1608X5R1E105K080A C		0603	
13	1	C46	47pF	CAP, CERM, 47pF, 50V, +/-5%, C0G/NP0, 0402	MuRata	GRM1555C1H470JA01D		0402	
14	1	C47	2200pF	CAP, CERM, 2200pF, 50V, +/- 10%, X7R, 0603	MuRata	GRM188R71H222KA01D		0603	
15	1	C49	0.33uF	CAP, CERM, 0.33uF, 6.3V, +/-	MuRata	GRM155R60J334KE01D		0402	
16	2	C50, C51	4.7uF	CAP, CERM, 4.7uF, 10V, +/-20%, X5R, 0402	MuRata	GRM155R61A475M		0402	
17	1	C52	2200pF	CAP, CERM, 2200pF, 50V, +/- 10%, X7R, 0402	TDK	C1005X7R1H222K		0402	
18	3	C100, C200, C300	1000pF	CAP, CERM, 1000pF, 25V, +/-5%, C0G/NP0, 0402	TDK	C1005C0G1E102J		0402	
19	15	C101, C102, C103, C104, C105, C201, C202, C203, C204, C205, C301, C302, C303, C304, C305	10uF	CAP, CERM, 10uF, 25V, +/-10%, X7R, 1206	MuRata	GRM31CR71E106KA12L		1206	
20	3	C106, C206, C306	3300pF	CAP, CERM, 3300pF, 50V, +/- 10%, X7R, 0402	TDK	C1005X7R1H332K		0402	

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
21	3	C110, C210, C310	0.1uF	CAP, CERM, 0.1uF, 25V, +/-5%,	Kemet	C0603C104J3RACTU		0603	
22	3	C111, C211, C311	10uF	CAP, CERM, 10uF, 6.3V, +/-20%,	Kemet	C0603C106M9PACTU		0603	
23	3	C112, C212, C312	0.1uF	CAP, CERM, 0.1uF, 16V, +/-10%,	MuRata	GRM155R61C104KA88D		0402	
24	3	C113, C213, C313	1500pF	CAP, CERM, 1500pF, 100V, +/-	AVX	08051C152KAT2A		0805	
25	2	D1, D3	30V	Diode, Schottky, 30V, 0.5A, SOD-	ON Semiconductor	MBR0530T1G		SOD-123	
26	1	D2	30V	Diode, Schottky, 30V, 0.2A, SOD-	Diodes Inc.	BAT54WS-7-F		SOD-323	
27	1	D4	Red	LED, Red, SMD	Lite-On	LTST-C170KRKT		LED_0805	
28	4	H1, H2, H3, H4		Machine Screw, Round, #4-40 x	B&F Fastener Supply	NY PMS 440 0025 PH		Screw	
29	4	H5, H6, H7, H8		Standoff, Hex, 0.5"L #4-40 Nylon	Keystone	1902C		Standoff	
30	4	H9, H10, H11, H12		Bumpon, Hemisphere, 0.44 X	3M	SJ-5303 (CLEAR)		Transparent	
31	4	J1, J2, J6, J8	GSLU-70	Lug, Solderless, #2 - #8 AWG,	ILSCO	GSLU-70		1.55 x 0.50 inch	
32	2	J3, J47	PEC02SAAN	Header, Male 2-pin, 100mil	Sullins	PEC02SAAN		0.100 inch x 2	
33	3	J4, J9, J45		Terminal Block, 6A, 3.5mm Pitch,	On-Shore Technology	ED555/2DS		7.0x8.2x6.5mm	
34	1	J41		Header (shrouded), 100mil, 5x2,	TE Connectivity	5103308-1		5x2 Shrouded	
35	2	J42, J46	PEC05DAAN	Header, Male 2x5-pin, 100mil	Sullins	PEC05DAAN		0.100 inch x 5 X	
36	1	J43	1x3	Header, TH, 100mil, 1x3, Gold	Sullins Connector Solu			PBC03SAAN	
37	1	J44	PEC03SAAN	Header, Male 3-pin, 100mil	Sullins	PEC03SAAN		0.100 inch x 3	
38	1	L1	6.8 uH	Inductor, SMT, yyA, zzmilliohm	TDK	SLF7032T-xxx		0.276 sq inch	
39	3	L100, L200, L300	210 uH	Inductor, Low-Profile, High-Current		FP1308R3-R21		2525/5050	-
40	2	LBL1. LBL41		Thermal Transfer Printable Labels,	Brady	THT-14-423-10		PCB Label	-
41	1	Q1	25V	MOSFET, N-CH, 25V, 40A, SON	Texas Instruments	CSD16556Q5B		SON 5x6mm	
42	3	R2, R4, R7	0.003	RES, 0.003 ohm, 1%, 1W, 2512	CTS Resistor	73M1R003F		2512	
43	1	R5	8.06k	RES, 8.06k ohm, 1%, 0.063W,	Vishay-Dale	CRCW04028K06FKED		0402	-
44	4	R8, R51, R52, R53	10.0k	RES, 10.0k ohm, 1%, 0.063W,	Vishay-Dale	CRCW040210K0FKED		0402	
45	1	R9	402	RES, 402 ohm, 1%, 0.063W, 0402		CRCW0402402RFKED		0402	
46	1	R10	200k	RES, 200k ohm, 1%, 0.063W,	Vishay-Dale	CRCW0402200KFKED		0402	
47	1	R11	1.00k	RES, 1.00k ohm, 1%, 0.063W,	Vishay-Dale	CRCW04021K00FKED		0402	-
48	1	R13	0.002	RES, 0.002 ohm, 1%, 2W, 2512	Stackpole Electronics I			2512	
49	1	R14	330	RES, 330 ohm, 5%, 0.063W, 0402	<u> </u>	CRCW0402330RJNED		0402	
50	2	R15, R16	49.9	RES, 49.9 ohm, 1%, 0.063W,	Vishay-Dale	CRCW040249R9FKED		0402	
51	6	R17, R18, R19, R20, R22,	1.00Meg	RES, 1.00Meg ohm, 1%, 0.063W,	Vishay-Dale	CRCW04021M00FKED		0402	
52	1	R21	51	RES, 51 ohm, 5%, 0.063W, 0402	Vishay-Dale	CRCW040251R0JNED		0402	
53	1	R24	261k	RES, 261k ohm, 1%, 0.063W,	Vishay-Dale	CRCW0402261KFKED		0402	
54	1	R25	294k	RES, 294k ohm, 1%, 0.063W,	Vishay-Dale	CRCW0402294KFKED		0402	-
55	1	R44	402k	RES, 402k ohm, 1%, 0.063W,	Vishay-Dale	CRCW0402402KFKED		0402	
56	1	R45	16.5k	RES, 16.5k ohm, 1%, 0.063W,	Vishay-Dale	CRCW040216K5FKED		0402	
57	2	R46, R49	9.31k	RES, 9.31k ohm, 1%, 0.063W,	Vishay-Dale	CRCW04029K31FKED		0402	
58	1	R47	14.0k	RES, 14.0k ohm, 1%, 0.063W,	Vishay-Dale	CRCW040214K0FKED		0402	
59	1	R48	13.7k	RES, 13.7k ohm, 1%, 0.063W,	Vishay-Dale	CRCW040213K7FKED		0402	
60	5	R55, R56, R57, R60, R62	20.0k	RES, 20.0k ohm, 1%, 0.063W,	Vishay-Dale	CRCW040220K0FKED		0402	
61	2	R58, R61	150k	RES, 150k ohm, 1%, 0.063W,	Vishay-Dale	CRCW0402150KFKED		0402	
62	1	R63	39.2k	RES, 39.2k ohm, 1%, 0.063W,	Vishay-Dale	CRCW040239K2FKED		0402	
63	7	R64, R65, R66, R71, R81,	100	RES, 100 ohm, 5%, 0.063W, 0402		CRCW0402100RJNED		0402	
64	1	R67	100k	RES, 100k ohm, 1%, 0.063W,	Vishay-Dale	CRCW0402100KFKED		0402	
65	1	R68	6.81k	RES, 6.81k ohm, 1%, 0.063W,	Vishay-Dale	CRCW04026K81FKED		0402	
66	1	R69	2.43k	RES, 2.43k ohm, 1%, 0.063W,	Vishay-Dale	CRCW04022K43FKED		0402	
67	1	R70	121k	RES, 121k ohm, 1%, 0.063W,	Vishay-Dale	CRCW0402121KFKED		0402	
68	2	R72, R73	10	RES, 10 ohm, 5%, 0.063W, 0402	Vishay-Dale	CRCW040210R0JNED		0402	-
00	1	R74	1.0	RES, 1.0 ohm, 5%, 0.063W, 0402		CRCW04021R00JNED		0402	

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
70	3	R100, R200, R300	0	RES, 0 ohm, 5%, 0.063W, 0402	Yageo America	RC0402JR-070RL		0402	
71	3	R110, R210, R310	2.2	RES, 2.2 ohm, 5%, 0.063W, 0402	Vishay-Dale	CRCW04022R20JNED		0402	
72	3	R113, R213, R313	1.0	RES, 1.0 ohm, 5%, 0.5W, 1206	Bourns	CRM1206-JW-1R0ELF		1206	
73	2	TH1, TH2		Thru Hole, 15 mil, plated					
74	4	TP1, TP3, TP4, TP6	5000	Test Point, Red, Thru Hole Color	Keystone	5000		0.100 x 0.100	
75	3	TP2, TP5, TP7	5001	Test Point, Black, Thru Hole Color	Keystone	5001		0.100 x 0.100	
76	1	TP8	131-4244-00	Adaptor, 3.5-mm probe clip (or	Tektronix	131-4244-00		0.200 inch	
77	3	TP100, TP200, TP300	SMT	Test Point, Miniature, SMT	Keystone	5015		Testpoint_Keyst	
78	1	TP301	5016	Test Point, SM, 0.150 x 0.090	Keystone	5016		0.185 x 0.135	
79	1	U1	TLC555CD	IC, Timer, Low-Power CMOS	TI	TLC555CD		SO8	
80	1	U2	UCC37324D	IC, Dual 4-A High Speed Low-	TI	UCC37324D		SO-8	
81	1	U3		Buck Adjustable Regulator with 3.1	Texas Instruments	TPS62110RSAR		RSA0016B	
82	1	U41		3-Phase, D-CAP+ Step-Down	Texas Instruments	TPS53631RSB		RSB0040E	
83	1	U42		Cap-Free, NMOS, 250mA Low	Texas Instruments	TPS73233DBV		DBV0005A	
84	3	U100, U200, U300		Synchronous Buck NexFET Power	Texas Instruments	CSD95372BQ5M		DQP0012A	
85	0	FID1, FID2, FID3		Fiducial mark. There is nothing to	N/A	N/A		Fiducial	

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, Is GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.