


Wireless MCU RF




VDDS / VDDIO / VDDR Options		
Reference Designator	CC2755R10	CC2755P10 CC2755P20
C101	DNM	3.9 pF
C102	DNM	3.9 pF
C111	DNM	3.9 pF
C115	DNM	3.9 pF
C117	DNM	3.9 pF
C121	DNM	3.9 pF
R93	0 ohm	BLM03AX241SN1

RF Frontend Filter Options		
Reference Designator	CC2755R10	CC2755P10 CC2755P20
C33	0.8 pF	0.8 pF
L34	1.1 nH	1.2 nH
L33	3.4 nH	3.3 nH
C34	1.2 pF	1.6 pF
L35	0 ohm	3.3 nH
C109	DNM	0.9 pF
CR10	TPD1E0B04D	DNM



Title: LP-EM-CC2755P20		 TEXAS INSTRUMENTS	
Drawn: RGW/RdS		PN: MCU176	
Checked: Team Reviewed			
Size: A3		Rev: B	
		Sheet: 1 of 4	
Date: Thursday, August 06, 2026			

BoosterPack Headers and Peripherals




NOTE:
R72 and R73 are DNM.
As default, I2S interface is connected to BoosterPack Header pins BP.31 and BP.32.
To connect CAN0 interface, remove R72 and R73 and mount R74 and R75.


5V and 3V headers



External flash




Buttons



Title:	LP-EM-CC2755P20	TEXAS INSTRUMENTS
Drawn:	RGW/RdS	PN: MCU176
Checked:	Team Reviewed	
Size:	A3	Rev: B
Date:	Thursday, August 06, 2020	
	Sheet:	2 of 4

XDS110 Debugger Interface




Title: LP-EM-CC2755P20		 TEXAS INSTRUMENTS
Drawn: RGW/RdS	PN: MCU176	
Checked: Team Reviewed		
Size: A3	Rev: B	Sheet: 3 of 4
Date: Thursday, August 06, 2020		

Mechanical


Jumpers for P2 LED headers



Mounting Holes



Standoffs



Labels




Fiducials



PCB



Shield



Title: LP-EM-CC2755P20		TEXAS INSTRUMENTS
Drawn: RGW/RdS		
Checked: Team Reviewed		PN: MCU176
Size: A3	Rev: B	Sheet: 4 of 4
Date: Thursday, August 06, 2020		