

## PMP10121 REV B Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1	1	47uF	EEUED2W470	Panasonic	CAP, AL, 47 $\mu$ F, 450 V, +/- 20%, 0.609529 ohm, TH	18x31.5
C2, C3	2	0.22uF	B32922C3224K	EPCOS Inc	CAP, Film, 0.22 $\mu$ F, 630 V, +/- 10%, TH	B32922_12.5mm
C4	1	1000pF	GRM31B5C2J102JW01L	MuRata	CAP, CERM, 1000 pF, 630 V, +/- 5%, C0G/NP0, 1206	1206
C5	1	470uF	EKZN350ELL471MJ20S	Chemi-Con	CAP, AL, 470 $\mu$ F, 35 V, +/- 20%, 0.028 ohm, TH	D10xL20mm
C6	1	220uF	EKZN350ELL221MH15D	Chemi-Con	CAP, AL, 220 $\mu$ F, 35 V, +/- 20%, 0.059 ohm, TH	D8xL15mm
C7	1	DNP	Used in BOM report	Used in BOM report	CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference]	Used in PnP output and some BOM reports
C8	1	33uF	EEE-FC1V330P	Panasonic	CAP, AL, 33 $\mu$ F, 35 V, +/- 20%, 0.4 ohm, SMD	SMT Radial E
C9	1	22pF	GRM1885C1H220JA01D	MuRata	CAP, CERM, 22 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C10	1	0.01uF	GRM216R71H103KA01D	MuRata	CAP, CERM, 0.01 $\mu$ F, 50 V, +/- 10%, X7R, 0805	0805
C11	1	DNP	C0603C100J5GACTU	Kemet	CAP, CERM, 10 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C12	1	0.047uF	C1608X7R1H473K	TDK	CAP, CERM, 0.047 $\mu$ F, 50 V, +/- 10%, X7R, 0603	0603
C13	1	0.1uF	GRM21BR71H104KA01L	MuRata	CAP, CERM, 0.1 $\mu$ F, 50 V, +/- 10%, X7R, 0805	0805
C14	1	100pF	C0603C101J5GAC	Kemet	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C15	1	1000pF	C1608C0G1H102J	TDK	CAP, CERM, 1000 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
D1	1	420V	GBU8J-BP	Micro Commercial Component	Diode, Switching-Bridge, 420 V, 8 A, TH	GBU
D2	1	1000V	RS1MB-13-F	Diodes Inc.	Diode, P-N, 1000 V, 1 A, SMB	SMB
D3	1	10CTQ150S PBF	10CTQ150SPBF	Used in BOM report	Diode, Schottky, xxV, xxA, [PackageReference]	Used in PnP output and some BOM reports
D4	1	200V	BAS21-7-F	Diodes Inc.	Diode, Switching, 200 V, 0.2 A, SOT-23	SOT-23
F1	1		37211600001	Littelfuse	Fuse, 1.6 A, 250 V, TH	TR5 fuse 8.5mm DIA
L1	1	330uH	MSS1210-334KE	Coilcraft	Inductor, Shielded, Ferrite, 330 $\mu$ H, 1.7 A, 0.317 ohm, SMD	Inductor, 12.3x10x12.3mm
L2	1	10mH	744823210	Würth Elektronik	Coupled inductor, 10 mH, 2 A, 0.125 ohm, +/- 30%, TH	13x22x17.5mm
Q1	1	710V	STB11N65M5	STMicroelectronics	MOSFET, N-CH, 710 V, 9 A, DDPAK	DDPAK
Q2	1	60 V	MMBT2907A	Fairchild Semiconductor	Transistor, PNP, 60 V, 0.8 A, SOT-23	SOT-23
Q3, Q4	2	40 V	MMBT3904	Fairchild Semiconductor	Transistor, NPN, 40 V, 0.2 A, SOT-23	SOT-23
R1, R5, R6	3	1.0Meg	CRCW08051M00JNEA	Vishay-Dale	RES, 1.0 M, 5%, 0.125 W, 0805	0805
R2	1	33	CRCW201033R0JNEF	Vishay-Dale	RES, 33, 5%, 0.75 W, 2010	2010
R3, R4	2	220k	CRCW2010220KFKEF	Vishay-Dale	RES, 220 k, 1%, 0.75 W, 2010	2010
R7	1	22	CRCW080522R0JNEA	Vishay-Dale	RES, 22, 5%, 0.125 W, 0805	0805
R8	1	49.9	CRCW060349R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.1 W, 0603	0603
R9, R10	2	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
R11	1	0	CRCW08050000Z0EA	Vishay-Dale	RES, 0, 5%, 0.125 W, 0805	0805
R12	1	147k	CRCW0603147KFKEA	Vishay-Dale	RES, 147 k, 1%, 0.1 W, 0603	0603
R13	1	49.9k	CRCW060349K9FKEA	Vishay-Dale	RES, 49.9 k, 1%, 0.1 W, 0603	0603
R14	1	1.43k	CRCW06031K43FKEA	Vishay-Dale	RES, 1.43 k, 1%, 0.1 W, 0603	0603
R15	1	150k	CRCW0603150KFKEA	Vishay-Dale	RES, 150 k, 1%, 0.1 W, 0603	0603
R16	1	0.27ohm	Used in BOM report	Used in BOM report	RES, xxx ohm, x%, xW, [PackageReference]	1210
R17	1	34.8k	CRCW060334K8FKEA	Vishay-Dale	RES, 34.8 k, 1%, 0.1 W, 0603	0603
R18	1	3.01k	CRCW06033K01FKEA	Vishay-Dale	RES, 3.01 k, 1%, 0.1 W, 0603	0603
RT1	1	1 ohm	B57237S109M	EPCOS Inc	Thermistor NTC, 1 ohm, 20%, 15x7mm	15x7mm
RV1	1	275V	S10K275E2	EPCOS Inc	Varistor 275V RMS 10MM Radial, TH	10mm Radial
T1	1	400 uH	750315220	Würth Elektronik	Transformer, 400 uH, TH	TH, 24x29.84mm

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
TP1, TP2, TP3, TP4	4	Double	1503-2	Keystone	Terminal, Turret, TH, Double	Keystone1503-2
TP6	1	Red	5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
TP8	1	Black	5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
U1	1		UCC28600D	Texas Instruments	Quasi-Resonant Flyback Green-Mode Controller with Current Control, 99 % Duty Cycle, -40 to +105 degC, 8-pin SOIC (D), Green (RoHS & no Sb/Br)	D0008A
U2	1		LMV431AIMFX/NOPB	Texas Instruments	Low-Voltage (1.24V) Adjustable Precision Shunt Regulators, 3-pin SOT-23, Pb-Free	MF03A

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.