🐺 Texas Instruments

Bill of Materials

TI DESIGNS

TIDA-00856

ltem	Designator	Qty	Value	Part Number	Manufacturer	Description	PackageReference
1	!PCB	1		AIP041	Any	Printed Circuit Board	
2	C1	1	3900pF	GRM155R71H392KA01D	MuRata	CAP, CERM, 3900 pF, 50 V, +/- 10%, X7R, 0402	0402
3	C2	1	1000pF	GRM155R61A102KA01D	MuRata	CAP, CERM, 1000 pF, 10 V, +/- 10%, X5R, 0402	0402
4	C3, C7	2	0.1uF	GRM188R71E104KA01D	MuRata	CAP, CERM, 0.1 µF, 25 V, +/- 10%, X7R, 0603	0603
5	C4, C9, C10	3	1uF	GRM155R71C104JA88D	Murata Electronics	CAP CER 0.1UF 16V 5% X7R 0402	0402
					North America		
6	C5	1	1000pF	GRM31B5C2J102JW01L	MuRata	CAP, CERM, 1000 pF, 630 V, +/- 5%, C0G/NP0, 1206	1206
7	C6	1	0.047uF	GRM32DR72J473KW01L	MuRata	CAP, CERM, 0.047 µF, 630 V, +/- 10%, X7R, 1210	1210
8	C8	1	10uF	GRM188R61E106MA73	MuRata	CAP, CERM, 10 µF, 25 V, +/- 20%, X5R, 0603	0603
9	C11, C17	2	10uF	0805YD106MAT2A	AVX	CAP, CERM, 10uF, 16V, +/-20%, X5R, 0805	0805
10	C12	1	1000pF	GRM155R60J102KA01D	MuRata	CAP, CERM, 1000pF, 6.3V, +/-10%, X5R, 0402	0402
11	C13	1	22pF	C0805C220KBRACTU	Kemet	CAP, CERM, 22 pF, 630 V, +/- 10%, X7R, 0805_140	0805
12	C14, C15	2	10pF	GRM1555C1H100JA01D	MuRata	CAP, CERM, 10pF, 50V, +/-5%, C0G/NP0, 0402	0402
13	C18		0.01uF	GRM155R71C103KA01D	MuRata	CAP, CERM, 0.01 µF, 16 V, +/- 10%, X7R, 0402	0402
14	C18		6800pF	GRM155R71E682KA01D	MuRata	CAP, CERM, 6800 pF, 25 V, +/- 10%, X7R, 0402	0402
15	C20, C24, C26		0.1uF	C1005X5R0J104K	TDK	CAP, CERM, 0.1uF, 6.3V, +/-10%, X5R, 0402	0402
16	C21	-	8200pF	GRM155R71C822KA01D	MuRata	CAP, CERM, 8200 pF, 16 V, +/- 10%, X7R, 0402	0402
17	C22, C25		0.22uF	GRM155C80J224KE01D	MuRata	CAP, CERM, 0.22uF, 6.3V, +/-10%, X6S, 0402	0402
18	C23		0.47uF	C0603C474K8RACTU	Kemet	CAP, CERM, 0.47uF, 10V, +/-10%, X7R, 0603	0603
19	D1		350V	MMBD3004S-7-F	Diodes Inc.	Diode, Switching, 350 V, 0.225 A, SOT-23	SOT-23
20	D2	1	5.6V	MMSZ5232B-7-F	Diodes Inc.	Diode, Zener, 5.6V, 500 mW, SOD-123	SOD-123
21	D3, D4	2		LTST-C190KGKT	Lite-On	LED, Green, SMD	SMD
22	FID1, FID2, FID3	3		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	N/A
23	H1, H2, H3, H4	4	Black	SJ61A2	3M	Bumpon, Hemisphere, 0.375 X 0.235, Black	0.375 X 0.235, Black
24	J1	1		897-43-005-00-100001	Mill-Max	Connector, USB Mini B	
25	J2	1		691214310002	Wurth Elektronik eiSos	Terminal Block, 2x1, 3.81mm, 24-16 AWG, 10A, 300VAC, TH	2x1, 3.81mm
26	J3	1		1725656	Phoenix Contact	Header, 2 Pos, 6A, 63V, TH	2 Pos, TH
27	J4	1		LPPB061NGCN-RC	Sullins Connector Solutions	Receptacle, 50mil, 6x1, R/A, TH	50mil, 6x1, TH
28	JP1	1	Gold	5-146261-1	TE Connectivity	Header, 100mil, 2x1, Gold, TH	100mil, 2x1, Gold, TH
29	JP2, JP3, JP4	3	Tin	5-146278-3	TE Connectivity	Header, 100mil, 3x1, Tin, TH	100mil, 3x1, Tin, TH
30	Q1		600V	BSS127 H6327		MOSFET, N-CH, 600 V, 0.021 A, SOT-23	SOT-23
31	R1	1	90.9k	CRCW040290K9FKED	Vishay-Dale	RES, 90.9 k, 1%, 0.063 W, 0402	0402
32	R2	1	49.9k	CRCW040249K9FKED	Vishay-Dale	RES, 49.9 k, 1%, 0.063 W, 0402	0402
33	R3, R5, R14, R28	4	10k	CRCW040210K0JNED	Vishay-Dale	RES, 10 k, 5%, 0.063 W, 0402, RES, 10 k, 5%, 0.063 W, 0402, RES,	0402
						10k ohm, 5%, 0.063W, 0402, RES, 10 k, 5%, 0.063 W, 0402	
34	R4	1	220	CRCW0402220RJNED	Vishay-Dale	RES, 220, 5%, 0.063 W, 0402	0402
35	R6	1	100	CRCW0402100RFKED	Vishay-Dale	RES, 100 ohm, 1%, 0.063W, 0402	0402
36	R7	1	3.3k	CRCW04023K30JNED	Vishay-Dale	RES, 3.3k ohm, 5%, 0.063W, 0402	0402

Item	Designator	Qty	Value	Part Number	Manufacturer	Description	PackageReference
37	R8	1	1.4k	CRCW04021K40FKED	Vishay-Dale	RES, 1.40k ohm, 1%, 0.063W, 0402	0402
38	R9	1	1M	CRCW08051M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.125 W, 0805	0805
39	R10, R24	2	750k	RT0805BRD07750KL	Yageo America	RES, 750 k, 0.1%, 0.125 W, 0805	0805
40	R11, R25	2	1.24M	CRCW08051M24FKEA	Vishay-Dale	RES, 1.24 M, 1%, 0.125 W, 0805	0805
41	R12	1	1M	CRCW04021M00JNED	Vishay-Dale	RES, 1.0Meg ohm, 5%, 0.063W, 0402	0402
42	R13, R15	2	511	CRCW0402511RFKED	Vishay-Dale	RES, 511 ohm, 1%, 0.063W, 0402	0402
43	R16, R17	2	33	CRCW040233R0JNED	Vishay-Dale	RES, 33 ohm, 5%, 0.063W, 0402	0402
44	R18	1	392	CRCW0402392RFKED	Vishay-Dale	RES, 392, 1%, 0.063 W, 0402	0402
45	R19	1	9.76k	CRCW04029K76FKED	Vishay-Dale	RES, 9.76k ohm, 1%, 0.063W, 0402	0402
46	R20	1	0	RC0402JR-070RL	Yageo America	RES, 0, 5%, 0.063 W, 0402	0402
47	R21	1	69.8k	CRCW040269K8FKED	Vishay-Dale	RES, 69.8 k, 1%, 0.063 W, 0402	0402
48	R23	1	1.05M	CRCW08051M05FKEA	Vishay-Dale	RES, 1.05 M, 1%, 0.125 W, 0805	0805
49	R26	1	5.11k	CRCW04025K11FKED	Vishay-Dale	RES, 5.11 k, 1%, 0.063 W, 0402	0402
50	R27, R29	2	5.1k	CRCW08055K10JNEA	Vishay-Dale	RES, 5.1 k, 5%, 0.125 W, 0805	0805
51	SH-JP1, SH-JP2, SH-JP3,	4	Black	2SN-BK-G	Samtec	Shunt, 2mm, Gold plated, Black	2mm, Gold plated,
	SH-JP4						Black
52	SW1, SW2	2		TL1015AF160QG	E-Switch	Switch, Tactile, SPST-NO, 0.05A, 12V, SMT	SMT
53	SW3, SW4	2		CL-SB-22B-02T	Copal Electronics	Switch, Slide, DPDT, 0.2A, GULL, 12V, SMD	SMD
54	T1	1	7uH	ATB322515-0110	TDK	Transformer, Xenon Flash, 7uH, SMT	SMD
55	TP1	1	Orange	5013	Keystone	Test Point, Multipurpose, Orange, TH	Orange
56	TP2, TP3	2	Black	5011	Keystone	Test Point, Multipurpose, Black, TH	Black
57	U1	1		TPD4E004DRY	Texas Instruments	4-CHANNEL ESD-PROTECTION ARRAY FOR HIGH-SPEED DATA	Texas Instruments
						INTERFACES, DRY006A	
58	U2	1		DRV2700RGP	Texas Instruments	Piezo Driver with Integrated Boost Converter, RGP0020D	Texas Instruments
59	U3	1		OPA2376AIYZD	Texas Instruments	Low-Noise, Low Quiescent Current, Precision Operational Amplifier e-	Texas Instruments
						trim Series	
60	U4	1		TLV70033DCKR	Texas Instruments	Single Output LDO, 200 mA, Fixed 3.3 V Output, 2 to 5.5 V Input, with	Texas Instruments
61	U5	1		MSP430F5510IRGZ	Texas Instruments	Mixed Signal MicroController, RGZ0048A	Texas Instruments
62	Y1	1		ABM8G-12.000MHZ-B4Y-T	Abracon Corportation	CRYSTAL 12.000MHZ 10PF SMD	SMD

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2015, Texas Instruments Incorporated