

## TEXAS INSTRUMENTS Bill of Materials TI DESIGNS

	0.	Princer	Walna	Port Provideling		Manufacturer	All amounts Doub	DCD Facility int	Nere
Item	Qty	Reference	Value	Part Description	Manufacturer	Part Number	Alternate Part	PCB Footprint	Note
1	1	!PCB	TIDA-00646	Printed Circuit Board	Any	TIDA-00646			
2	1	A1		PCB Antenna. There is nothing to buy or mount.	N/A	ANTENNA_HELICAL		Top and Bottom layers	
3	1	BT1		Battery Holder, Nylon, CR2, SMT	Keystone	1010			
4	1	C1	1200 μF, 10 V, +/- 20%, TH	CAP, AL, 1200 μF, 10 V, +/- 20%, TH	Panasonic	EEUFM1A122	WE 860 080 275 017	Thru hole	
	2	C2, C3		CAP, CERM, 2.2 μF, 6.3 V, +/- 20%, X5R, 0402	MuRata	GRM155R60J225ME15D			
5			2.2 μF, 6.3 V				WE 885012105007	0402	DNP
6	1		10 μF, 10 V, +/- 20%, X5R	CAP, CERM, 10 μF, 10 V, +/- 20%, X5R, 0603	MuRata	GRM188R61A106ME69		0603	
7	13	C5, C41, C42, C43, C131, C221, C342, C343, C351, C441, C451, C481, C482	1 ' ' '	CAP, CERM, 0.1 μF, 25 V, +/- 10%, X5R, 0402	MuRata	GRM155R61E104KA87D	WE 885012205037	0402	
8	2			CAP, CERM, 3.6 pF, 50 V, +/- 5%, C0G/NP0, 0402	MuRata	GRM1555C1H3R6CA01		0402	
9	1	C12	2.7 pF, 50 V, +/- 5%, C0G/NP0	CAP, CERM, 2.7 pF, 50 V, +/- 5%, C0G/NP0, 0402	MuRata	GRM1555C1H2R7CA01		0402	
10	1	C13	6.2 pF, 50 V, +/- 5%, C0G/NP0	CAP, CERM, 6.2 pF, 50 V, +/- 5%, C0G/NP0, 0402	MuRata	GRM1555C1H6R2CA01		0402	
	1	C14		CAP, CERM, 3.3 pF, 50 V, +/- 5%, C0G/NP0, 0402	MuRata	GRM1555C1H3R3CA01			
11			3.3 pF, 50 V, +/- 5%, C0G/NP0			D	WE 885012005052	0402	
12	2	C15, C21	100 pF, 50 V, +/- 5%, C0G/NP0	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0402	MuRata	GRM1555C1H101JA01D	WE 885012005061	0402	
	1	C16		CAP, CERM, 1 pF, 50 V, +/- 5%, C0G/NP0, 0402	MuRata	GRM1555C1H1R0CA01			
13			1 pF, 50 V, +/- 5%, C0G/NP0			D	WE 885012005049	0402	
14	6	C46, C48, C61, C62, C461, C471	12 pF, 50 V, +/- 5%, C0G/NP0	CAP, CERM, 12 pF, 50 V, +/- 5%, C0G/NP0, 0402	MuRata	GRM1555C1H120JA01D	WE	0402	
15	2	C47, C231	1 μF, 10 V, +/- 10%, X5R	CAP, CERM, 1 μF, 10 V, +/- 10%, X5R, 0402	MuRata	GRM155R61A105KE15D	WE 885012105012	0402	
	3	C50, C51, C52		CAP, CERM, 1000 pF, 50 V, +/- 10%, X5R, 0402	MuRata	GRM155R61H102KA01D			
16			1000 pF, 50 V, +/- 10%, X5R				WE 885012205061	0402	
17	2	C331, C341	22 μF, 6.3 V, +/- 20%, X5R	CAP, CERM, 22 μF, 6.3 V, +/- 20%, X5R, 0603	MuRata	GRM188R60J226MEA0J	WE	0603	
18	1	D1	LED, GREEN, 0805	LED, Green, SMD	Lite-On / Wuerth Elektronik	LTST-C170KRKT	WE 150080GS75000	0805	
19	3	FID1, FID2, FID3		Fiducial mark. There is nothing to buy or mount.	N/A	N/A		N/A	
	2	H1, H4		Machine Screw, Round, #4-40 x 1/4, Nylon, Philips	B&F Fastener Supply	NY PMS 440 0025 PH			
20				panhead					
21	1	J1	3-pin Header	Header, TH, 100mil, 3x1, Gold plated, 230 mil above	Samtec/Wuerth Elektronik	TSW-103-07-G-S	WE 613 003 111 21	Handar 100mil 2nd TH	
21	1	J3	3-piii Headei	insulator Header, TH, 100mil, 4x1, Gold plated, 230 mil above	Samtec/Wuerth Elektronik	TSW-104-07-G-S	WE 013 003 111 21	Header, 100mil, 3x1, TH	
22	·		4-pin Header	insulator			WE 613 004 111 21	Header, 100mil, 4x1, TH	
22	3	J4, J5, J13	10 pin 1 27mm 2vE Hooder	Header, 1.27mm, 5x2, SMT	GradConn/Wuerth Elektronik		WE 624 240 240 24	Handan Forell Fug	DND 15 1 142
23		10	10-pin, 1.27mm, 2x5 Header	0.4.0.4.0.4.1.1.1.1.1.1.1.1.1.1.1.1.1.1.	1:14 7 1 1 1 7 7 7	025B00	WE 621 310 210 21	Header, 50mil, 5x2	DNP J5 and J13
	1	J6		Connector, SMA, Vertical, Thru hole w/SMT center pin	Lighthorse Technologies / TE	SASF546-P26-X1			
24			Antenna SMA connector		connectivity		5-1814832-1	SMA, 5-pin	
25	5	J9, J11, J15, J16, J17	DNP	Header, 50mil, 4x1, Gold, TH	Preci-Dip	850-10-004-10-001101		Header, 50mil, 4x1, TH	DNP
26	1	J12	2-pin Header	Header, 100mil, 2x1, TH	Mill-Max	800-10-002-10-001000	WE 613 002 111 21	Header, 100mil, 2x1, TH	DNP
27	1	J14	DNP	Header, 50mil, 3x1, Gold, TH	Mill-Max	850-10-003-10-001000		Header, 50mil, 3x1	DNP
28	1	J21	DNP	Header, 50mil, 5x1, Gold, TH	Sullins Connector Solutions	GRPB051VWVN-RC		Header, 50mil, 5x1	DNP
	1	L1		Inductor, Shielded, Ferrite, 2.2 µH, 0.8 A, 0.23 ohm,	MuRata	LQM21PN2R2NGC			
29			DNP	SMD			WE 74479775222A	0805	DNP
30	1	L11	18 nH, 0.37 A, 0.27 ohm	Inductor, Wirewound, 18 nH, 0.37 A, 0.27 ohm, SMD	MuRata	LQW15AN18NJ00D	WE 744765118A	0402	
21	2	L12, L21	7.5 nH, 0.57 A, 0.13 ohm	Inductor, Wirewound, 7.5 nH, 0.57 A, 0.13 ohm, SMD	MuKata	LQW15AN7N5G00D	WE 744765075A	0403	
31	2	L13, L14	6.8 nH, 0.7 A, 0.09 ohm	Inductor, Wirewound, 6.8 nH, 0.7 A, 0.09 ohm, SMD	MuRata	LQW15AN6N8G00D	WE 744765075A WE 744765068A	0402 0402	
	2	L13, L14	12 nH, 0.5 A, 0.14 ohm		MuRata	LQW 15AN6N8G00D	WE 744765068A WE 744765112A		
33	1	L331	12 mi, 0.0 A, 0.14 0mi	Inductor, Wirewound, 12 nn, 0.5 A, 0.14 onm, SMD Inductor, Multilayer, Ferrite, 6.8 µH, 0.11 A, 0.25 ohm,		MLZ2012N6R8LT000	WE /44/03112A	0402	
34	'		LOD AMILY 1/2 high 1/24	SMD	TDK		WE 74479777268	0805	
35	1	LCD1	LCD 4-MUX, 1/3 bias, 4 x24 Segments	BTL002 4COM LCD		BTL002		DIP28	
36	4	R11, R12, R22, R24	0 Ohm, 5%, 0.063 W	RES, 0, 5%, 0.063 W, 0402	Vishay-Dale	CRCW04020000Z0ED		0402	
37	1		47 k, 5%, 0.1 W	RES, 47 k, 5%, 0.1 W, 0603	Vishay-Dale	CRCW060347K0JNEA		0603	
38	1	R23	200 ohm, 5%, 0.1W	RES, 200 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW0603200RJNEA		0603	DNP
39	1	R351	100 k, 1%, 0.1 W	RES, 100 k, 1%, 0.1 W, 0402	Panasonic	ERJ-2RKF1003X		0402	
40	1	TP1	DNP	Test Point, Miniature, SMT	Keystone	5015		SMT	DNP

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
41	2	TP2, TP3	DNP	TEST POINT SLOTTED .118", TH	Keystone	1040			DNP
42	1	U1		Buck Step Down Regulator with 1.9 to 3.9 V Input and 2.1 V Output, -40 to 85 degC, 6-Pin SON (DRY), Green (RoHS & no Sb/Br)		TPS62730DRYR			DNP
43	1	U4	MSP430FR4133IPM	16-bit Ultra-Low-Power MCU	Texas Instruments	MSP430FR4133IPM		LQFP	
44	1	U5		Sub-1 GHz and 2.4 GHz Multi-standard RF IC Family, RGZ0048A	Texas Instruments	CC1310F128RGZR		QFN	
45	1	Y1		Crystal, 32.768 KHz, 12.5 pF, SMD	Epson	FC-135 32.7680KA-A3		3215	
46	1	Y2		Crystal, 24 MHz, 9 pF, SMD	Epson	TSX-3225		3225	
47	1	Y3		Crystal, 32.768kHz, 12.5pF, SMD	Micro Crystal AG	MS3V-T1R 32.768KHZ +/-			

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.