


- 1) USB Differential Pairs - 90 Ohm
(A) XDS_D_P and XDS_D_N
(B) USB_D_P (GPIO42) and USB_D_N (GPIO43)
- 2) ADC Differential pair Impedance Matching - 50 Ohm
(A) HSEC_ADC even pins should match with HSEC_ADC + 1 pin(ie ADC-C2 should match with ADC-C3)
(B) MCU_ADC even pins should match with MCU_ADC + 1 pin(ie MCU_ADC-A0 should match with MCU_ADC-A1)
- 3) ETHERCAT Differential pairs - 100 Ohm
(A) TD_P and TD_N
(B) RD_P and RD_N
- 4) CLK Paths - 50 Ohm
(A) F28P65x_25MHz_CLK
(B) PHY0_25MHz_CLK and PHY1_25MHz_CLK



Revision History				
Rev	ECN #	Approved Date	Approved by	Notes
E1	N/A	N/A	N/A	Initial



Power to the MCU is either supported by the USB-C on the left or the HSEC 180 pin.


Texas Instruments and/or its licensors do not warrant the accuracy or completeness of this specification or any information contained therein. Texas Instruments and/or its licensors do not warrant that this design will meet the specifications, will be suitable for your application or fit for any particular purpose, or will operate in an implementation. Texas Instruments and/or its licensors do not warrant that the design is production worthy. You should completely validate and test your design implementation to confirm the system functionality for your application.

Orderable: TMDSCNCD28P65X	Designed for: Public Release	Mod. Date: 10/5/2022
TID #: N/A	Project Title: F28P65X Control Card	
Number: MCU114	Rev: E1	Sheet Title:
SVN Rev: 73e91ac938d78e4362d0f066e00b544e04507b	File: MCU114E1_CoverSheet.SchDoc	Sheet: 1 of 11
Drawn By: Uttam Reddy Pailla	Size: B	
Engineer: Uttam Reddy Pailla	Contact: http://www.ti.com/support	



Ext. V_REF Selection	
S7 (SEL 2)	ADC_REF
1	HSEC_ADC-VREFHI
0	ADC_3V0_REF (DEFAULT)


S7 (SEL 1)	S5 (SEL 1)	S5 (SEL 2)	C2000 ADC V_REF	DESCRIPTION
1	1	1	Int. V_REF	NC - No reference input
0	0	0	Ext. V_REF	ADC_REF




ADC_A0A1_P and ADC_A0A1_N make a differential pair using channels A0 and A1 respectively.





If you wish to use A0 or A1 independently the "_P" refers to the first ADC channel (For example A0 in "ADC_A0A1"). Additionally the "_N" refers to the second channel. (A1 in "ADC_A0A1").

NOTE: C6 and C4 are not differential pairs



Texas Instruments and/or its licensors do not warrant the accuracy or completeness of this specification or any information contained therein. Texas Instruments and/or its licensors do not warrant that this design will meet the specifications, will be suitable for your application or fit for any particular purpose, or will operate in an implementation. Texas Instruments and/or its licensors do not warrant that the design is production worthy. You should completely validate and test your design implementation to confirm the system functionality for your application.

Orderable: TMDSCNCD28P65X	Designed for: Public Release	Mod. Date: 10/4/2022	 TEXAS INSTRUMENTS http://www.ti.com © Texas Instruments, 2022
TID #: N/A	Project Title: F28P65X Control Card		
Number: MCU114	Rev: E1	Sheet Title:	
SVN Rev: 73e91ac938d78e4362d0f06600b544a34507b		Sheet: 4 of 11	
Drawn By: Uttam Reddy Paila	File: MCU114E1_ADC_SchDoc		
Engineer: Uttam Reddy Paila	Contact: http://www.ti.com/support		Size: B





Switch Truth Table		
MCU_GPIO44 STATUS	DESCRIPTION	USB_MODE
1 (HIGH)	UB_CC1 & USB_CC2 are pulled up	Host mode
0 (LOW)	UB_CC1 & USB_CC2 are strongly pulled down	Device mode (DEFAULT)


NOTE: USB VBUS_5V0, PFLT & EPEN do not have a specific mux position in this device.

In this controlCARD, a standard GPIO is used to detect changes to these signals.

USB- Type C Connector - XDS110




LDO_5V0_3V3




(Cold Side)

USB Isolated Power



(Hot Side)

Power Selection Switch



NOTE: for TYPE C, the USB2.0 OTG device is referred as a Dual Role Port (DRP)

DRP can function either as a USB host or USB peripheral, the selection choice depends on the channel configuration (CC1/CC2).

1. USB host (DFP) - Use pull-up resistors on CC1/CC2 ; Provides Vbus to the attached peripheral
2. USB peripheral (UFP) -Use pull-down resistors on CC1/CC2 ; monitors Vbus to establish a data connection and/or power on board circuits

~~FID1~~ ~~FID2~~ ~~FID3~~ ~~FID4~~ ~~FID5~~ ~~FID6~~

PCB Number: MCU114
PCB Rev: E1



PCB
LOGO
Texas Instruments

PCB
LOGO
FCC disclaimer

PCB
LOGO
WEEE logo

PCB
LOGO
ETHERCAT LABEL

Variant/Label Table

Variant/Label Table	
Variant	Label Text
001	TMDSCNCD28P65X - 20MHz CLK
002	TMDSCNCD28P65X - 25MHz CLK

PCB Label

THT-14-423-10
Size: 0.65" x 0.20 "

ZZ1

Label Assembly Note

Label Assembly Note
This Assembly Note is for PCB labels only

ZZ2

Assembly Note

These assemblies are ESD sensitive, ESD precautions shall be observed.

ZZ3

Assembly Note

These assemblies must be clean and free from flux and all contaminants. Use of no clean flux is not acceptable.

ZZ4

Assembly Note

These assemblies must comply with workmanship standards IPC-A-610 Class 2, unless otherwise specified.

Orderable: TMDSCNCD28P65X	Designed for: Public Release	Mod. Date: 9/29/2022
TID #: N/A	Project Title: F28P65X Control Card	
Number: MCU114	Rev: E1	Sheet Title:
SVN Rev: 570116fc99fa7a2f210ce1828c2b244dd86cd02	Doc ID: 28P65X002	Sheet: 11 of 11
Drawn by: Uttam Reddy Paila	File: MCU114E1_EVM_Hardware_SchDoc	Size: B
Engineer: Uttam Reddy Paila	Contact: http://www.ti.com/support	



<http://www.ti.com>
© Texas Instruments 2022

Texas Instruments and/or its licensors do not warrant the accuracy or completeness of this specification or any information contained therein. Texas Instruments and/or its licensors do not warrant that this design will meet the specifications, will be suitable for your application or fit for any particular purpose, or will operate in an implementation. Texas Instruments and/or its licensors do not warrant that the design is production worthy. You should completely validate and test your design implementation to confirm the system functionality for your application.