Filename:
 Pro3009.tmp

 Variant:
 001

 Generated:
 3/11/2017 6:00:04 PM

 TID #:
 N/A



## PMP20566 REV A Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	IPCB1	1		PMP20566	Any	Printed Circuit Board	
2	C1, C2	2	10uF	GRM31CR71E106KA12L	MuRata	CAP, CERM, 10 µF, 25 V, +/- 10%, X7R, 1206	1206
3	C3, C4	2	0.1uF	885012206071	Wurth Elektronik	CAP, CERM, 0.1 µF, 25 V, +/- 10%, X7R, 0603	0603
4	C5	1	220uF	EEE-TP1V221AP	Panasonic	CAP, AL, 220 µF, 35 V, +/- 20%, 0.15 ohm, AEC-Q200 Grade 1, SMD	SMT Radial G
5	C6, C7	2	47uF	GRM32ER71A476KE15L	MuRata	CAP, CERM, 47 μF, 10 V, +/- 10%, X7R, 1210	1210
6	C8	1	150uF	6TPE150MAPB	Panasonic	CAP, Tantalum Polymer, 150 µF, 6.3 V, +/- 20%, 0.025 ohm, 3.5x1.9x2.8mm SMD	3.5x1.9x2.8mm
7	C9	1	1300pF	04025C132KAT2A	AVX	CAP, CERM, 1300 pF, 50 V, +/- 10%, X7R, 0402	0402
8	C10	1	0.068uF	GRM155R71C683KA88D	MuRata	CAP, CERM, 0.068 µF, 16 V, +/- 10%, X7R, 0402	0402
9	C11	1	150pF	GRM1555C1H151JA01D	MuRata	CAP, CERM, 150 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
10	D1	1	30V	MBRA130LT3G	ON Semiconductor	Diode, Schottky, 30 V, 1 A, SMA	SMA
11	J1, J2	2		39357-0002	Molex	Terminal Block, 3.5 mm, 2x1, Tin, TH	Terminal Block, 3.5 mm, 2x1, TH
12	L1	1	22uH	DR125-220-R	Coiltronics	Inductor, Shielded Drum Core, Ferrite, 22 µH, 3.7 A, 0.0396 ohm, SMD	DR125
13	R1	1	215k	CRCW0402215KFKED	Vishay-Dale	RES, 215 k, 1%, 0.063 W, 0402	0402
14	R2	1	51.1	CRCW040251R1FKED	Vishay-Dale	RES, 51.1, 1%, 0.063 W, 0402	0402
15	R3	1	31.6k	CRCW040231K6FKED	Vishay-Dale	RES, 31.6 k, 1%, 0.063 W, 0402	0402
16	R4	1	6.34k	CRCW04026K34FKED	Vishay-Dale	RES, 6.34 k, 1%, 0.063 W, 0402	0402
17	R5	1	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
18	R6	1	158k	CRCW0402158KFKED	Vishay-Dale	RES, 158 k, 1%, 0.063 W, 0402	0402
19	R7	1	1.87k	CRCW04021K87FKED	Vishay-Dale	RES, 1.87 k, 1%, 0.063 W, 0402	0402
20	TP1	1		TP105-01-09	Components Corporation	Test Point, Miniature, White, TH	Test-Point, Dia 100mil, TH
21	TP2	1		5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
22	TP3	1		5003	Keystone	Test Point, Miniature, Orange, TH	Orange Miniature Testpoint
23	TP4	1		5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
24	U1	1		TPS54335ADDAR	Texas Instruments	4.5- to 28-V Input, 3-A Output, Synchronous SWIFT Step-Down DC-DC Converter, DDA0008E (SOIC-8)	DDA0008E
25	FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your noncompliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products <a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation modules, and samples (<a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated