Filename: ProB6C7.tmp

Variant: 001

Generated: 5/23/2017 10:52:37 AM

TID #: N/A



## PMP20686 REV B Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1	1	150uF	ESMQ451VSN151MQ25S	Chemi-Con	CAP, AL, 150 μF, 450 V, +/- 20%, TH	25.4x25mm
2	C2	1	47uF	EEU-FC2A470	Panasonic	CAP, AL, 47 µF, 100 V, +/- 20%, 0.24 ohm, AEC-Q200 Grade 2, TH	D10xL20mm
3	C3	1	1uF	CGA5L2X7R2A105K160AA	TDK	CAP, CERM, 1 µF, 100 V, +/- 10%, X7R, AEC-Q200 Grade 1, 1206	1206
4	C4	1	0.22uF	ECQ-U2A224ML	Panasonic	CAP, Film, 0.22 μF, 275 V, +/- 20%, TH	17.5x8x17.5mm
5	C5	1	10uF	GRM21BR6YA106KE43L	MuRata	CAP, CERM, 10 µF, 35 V, +/- 10%, X5R, 0805	0805
6	C6	1	0.1uF	ECQ-E4104JF	Panasonic	CAP, Film, 0.1 µF, 400 V, +/- 5%, TH	12x6.3mm
7	C7	1	0.1uF	GRM155R61H104ME14D	MuRata	CAP, CERM, 0.1 µF, 50 V, +/- 20%, X5R, 0402	0402
8	C8	1	0.022uF	GRM155R61C223KA01D	MuRata	CAP, CERM, 0.022 µF, 16 V, +/- 10%, X5R, 0402	0402
9	C9	1	150uF	EEU-FR1E151B	Panasonic	CAP, AL, 150 μF, 25 V, +/- 20%, TH	D6.3xL11.2mm
10	D1	1	600V	Z4DGP406L-HF	Comchip Technology	Diode, P-N-Bridge, 600 V, 4 A, Z4-D	Z4-D
11	D2	1	600V	MURS360T3G	ON Semiconductor	Diode, Ultrafast, 600 V, 3 A, SMC	SMC
12	D3	1	100V	MMSD4148T1G	ON Semiconductor	Diode, Switching, 100 V, 0.2 A, SOD-123	SOD-123
13	D4	1	100V	MMDL914-TP	Micro Commercial	Diode, Switching, 100 V, 0.2 A, SOD-323	SOD-323
					Components	3, 11 , 1 , 1	
14	D5	1	100V	MURA110T3G	ON Semiconductor	Diode, Ultrafast, 100 V, 2 A, SMA	SMA
15	F1	1		0443003.DR	Littelfuse	Fuse, 3 A, 250VAC/VDC, SMD	FUSE
							10.1x3.12x3.13mm
16	L1	1	330uH	MSS1278-334KLB	Coilcraft	Inductor, Shielded Drum Core, Ferrite, 330 µH, 1 A, 0.49 ohm, SMD	MSS1278
17	L2	1	680uH	744732681	Wurth Elektronik	Inductor, SOD-123F, Ferrite, 680 µH, 0.42 A, 2.2 ohm, TH	D9.0xL8.0mm
18	Q2	1	650V	IPL60R299CP	Infineon Technologies	MOSFET, N-CH, 650 V, 11.1 A, PG-VSON-4	PG-VSON-4
19	R2, R3	2	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
20	R4	1	15.0k	CRCW040215K0FKED	Vishay-Dale	RES, 15.0 k, 1%, 0.063 W, 0402	0402
21	R5	1	1.15k	CRCW04021K15FKED	Vishay-Dale	RES, 1.15 k, 1%, 0.063 W, 0402	0402
22	R6	1	110k	CRCW0402110KFKED	Vishay-Dale	RES, 110 k, 1%, 0.063 W, 0402	0402
23	R7	1	7.68k	CRCW04027K68FKED	Vishay-Dale	RES, 7.68 k, 1%, 0.063 W, 0402	0402
24	R9, R10	2	0.56	ERJ-8RQFR56V	Panasonic	RES, 0.56, 1%, 0.25 W, 1206	1206
25	R11	1	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
26	T1	1	180uH	RLTI-1213	Renco Electronics	Coupled inductor, 180 µH, A, 0.13 ohm, TH	18.288x17.018mm
27	TP1, TP2	2	White	5012	Keystone	Test Point, Multipurpose, White, TH	White Multipurpose
	<i>'</i>				,,,,,,		Testpoint
28	TP3	1		5010	Keystone	Test Point, Multipurpose, Red, TH	Red Multipurpose
					,	,,,	Testpoint
29	TP4	1		5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose
					,	,,,	Testpoint
30	TP5	1	Red	5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature
					,		Testpoint
31	TP6	1	Black	5001	Keystone	Test Point, TH, Miniature, Black	Keystone5001
32	U1	1		UCC28730DR	Texas Instruments	Constant-Voltage Constant-Current Flyback Controller With PSR and	D0007A
						Wake-Up Monitoring, D0007A (SOIC-7)	
33	U2	1		UCC28880D	Texas Instruments		D0007A
			1				
34	R1	0	69.8k	CRCW060369K8FKEA	Vishay-Dale	RES, 69.8 k, 1%, 0.1 W, 0603	0603
35	R8	0	115k	CRCW0402115KFKED	Vishay-Dale	RES, 115 k, 1%, 0.063 W, 0402	0402
36	R12	0	2.00k	CRCW06032K00FKEA	Vishay-Dale	RES, 2.00 k, 1%, 0.1 W, 0603	0603
- 00		J		JOHO T. OGOGEROOF REAL	. iona, baio	1126, 2.00 11, 170, 0.1 11, 0000	

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products <a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation modules, and samples (<a href="http://www.ti.com/sc/docs/sampterms.htm">http://www.ti.com/sc/docs/sampterms.htm</a>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated