Filename: PMP11773RevB - BoM.xls

Variant: None

Generated: 12/9/2015 3:46:13 PM TID #: <Parameter TID not found>



PMP11773 REV B Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C4, C7, C11, C16,	5	1uF	GRM188R71E105KA12D	MuRata	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0603	0603
	C20						
2	C5	1	100uF	EEHZA1H101P	Panasonic	CAP, Polymer Hybrid, 100 µF, 50 V, +/- 20%, 28 ohm, 10x10 SMD	10x10
3	C6, C8, C21	3	0.1uF	GCM188R71H104KA57D	MuRata	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603
4	C9, C10	2	100uF	EEHZA1E101XP	Panasonic	CAP, Polymer Hybrid, 100 µF, 25 V, +/- 20%, 30 ohm, 6.3x7.7 SMD	6.3x7.7
5	C15	1	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
6	C17	1	0.022uF	GRM188R71H223KA01D	MuRata	CAP, CERM, 0.022 µF, 50 V, +/- 10%, X7R, 0603	0603
7	C18	1	2.2uF	GRM188R71A225KE15D	MuRata	CAP, CERM, 2.2 µF, 10 V, +/- 10%, X7R, 0603	0603
8	D1, D4	2	50V	SS5P5	Vishay-Semiconductor	Diode, Schottky, 50 V, 5 A, TO-277A	TO-277A
9	J1, J2, J3, J4	4	Double	1502-2	Keystone	Terminal, Turret, TH, Double	Keystone1502-2
10	L1	1	15uH	MSS1278-153MLB	Coilcraft	Inductor, Shielded Drum Core, Ferrite, 15 µH, 4.9 A, 0.03 ohm, SMD	MSS1278
11	Q1, Q2	2	40V	SIR836DP-T1-GE3	Vishay-Siliconix	MOSFET, N-CH, 40 V, 21 A, PowerPAK SO-8	PowerPAK SO-8
12	R1	1	75.0k	CRCW060375K0FKEA	Vishay-Dale	RES, 75.0 k, 1%, 0.1 W, 0603	0603
13	R2	1	1.00Meg	CRCW06031M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.1 W, 0603	0603
14	R3	1	29.4k	CRCW060329K4FKEA	Vishay-Dale	RES, 29.4 k, 1%, 0.1 W, 0603	0603
15	R4	1	75.0	CRCW060375R0FKEA	Vishay-Dale	RES, 75.0, 1%, 0.1 W, 0603	0603
16	R5, R10, R11	3	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
17	R7	1	18.2k	CRCW060318K2FKEA	Vishay-Dale	RES, 18.2 k, 1%, 0.1 W, 0603	0603
18	R8	1	8.45k	CRCW06038K45FKEA	Vishay-Dale	RES, 8.45 k, 1%, 0.1 W, 0603	0603
19	R9	1	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
20	R12	1	49.9	CRCW060349R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.1 W, 0603	0603
21	R13	1	0.03	CSRN2010FK30L0	Stackpole Electronics Inc	RES, 0.03, 1%, 1 W, 2010	2010
22	TP1	1	Black	5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature
							Testpoint
23	TP4, TP5, TP6	3	White	5002	Keystone	Test Point, Miniature, White, TH	White Miniature
							Testpoint
24	U1	1		LM25118Q1MHX/NOPB	Texas Instruments	Wide Voltage Range Buck-Boost Controller, PWP0020A	PWP0020A

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated