PMP30189 REV B Bill of Materials



Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1, C2, C3, C4, C5		10uF	C3225X7R1H106M250AC	TDK	CAP, CERM, 10 µF, 50 V, +/- 20%, X7R, 1210	1210
C6		1uF	GRM31MR71H105KA88L	MuRata	CAP, CERM, 1 µF, 50 V, +/- 10%, X7R, 1206	1206
C7		4.7uF	GRM21BR71C475KA73L	MuRata	CAP, CERM, 4.7 µF, 16 V, +/- 10%, X7R, 0805	0805
C8		100pF	06035A101FAT2A	AVX	CAP, CERM, 100pF, 50V, +/-1%, C0G/NP0, 0603	0603
C9		0.47uF	GRM188R71E474KA12D	MuRata	CAP, CERM, 0.47uF, 25V, +/-10%, X7R, 0603	0603
C10		27pF	C0603C270J5GACTU	Kemet	CAP, CERM, 27 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C11		6800pF	C0603C682J5RACTU	Kemet	CAP, CERM, 6800 pF, 50 V, +/- 5%, X7R, 0603	0603
C12, C13		470uF	50ZLH470M12.5X20	Rubycon	CAP, AL, 470 µF, 50 V, +/- 20%, 0.027 ohm, TH	12.5x20mm
C14, C15, C21		1uF	08055C105KAT2A	AVX	CAP, CERM, 1 µF, 50 V, +/- 10%, X7R, 0805	0805
C16		0.1uF	08055C104JAT2A	AVX	CAP, CERM, 0.1uF, 50V, +/-5%, X7R, 0805	0805
C17		820pF	GRM188R72A821KA01D	MuRata	CAP, CERM, 820 pF, 100 V, +/- 10%, X7R, 0603	0603
C18		820pF	GRM1885C1H821JA01D	MuRata	CAP, CERM, 820 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C19, C23		1uF	C1608X7R1C105K080AC	TDK	CAP, CERM, 1 µF, 16 V, +/- 10%, X7R, 0603	0603
C20		0.39uF	GRM188R71C394KA88D	MuRata	CAP, CERM, 0.39 µF, 16 V, +/- 10%, X7R, 0603	0603
C22		100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100pF, 50V, +/-5%, C0G/NP0, 0603	0603
C24, C25, C26		0.01uF	06031C103JAT2A	AVX	CAP, CERM, 0.01 µF, 100 V, +/- 5%, X7R, 0603	0603
D1		DFLS1100-7	DFLS1100-7	Diodes Inc.	Diode, Schottky, 100 V, 1A, PowerDI123	PowerDI123
D2		PDS760Q-13	PDS760Q-13	Diodes Inc.	Diode, Schottky, 60 V, 7 A, PowerDI5	PowerDI5
D3		7.5V	MM3Z7V5B	Fairchild Semiconductor	Diode, Zener, 7.5 V, 200 mW, SOD-323F	SOD-323F
D4, D5, D6		BAS21	BAS21-TP	Micro Commercial Components	Diode, P-N, 200V, 200A, SOT-23	SOT-23
GND1, TP2	2	DASZI	5001	·		Black Miniature
GND1, 1P2			5001	Keystone	Test Point, Miniature, Black, TH	Testpoint
H1	1		573300D00010G	Aavid	Heatsink, DDPAK/TO-263, SMT	Heatsink, DDPAk
J1, J2	2		1732720	Phoenix Contact	Terminal Block, 2x1, 7.62mm, TH	15.21x18x12.8mm
J3, J4	2		800-10-002-10-001000	Mill-Max	Header, 100mil, 2x1, TH	Header, 2x1, 100mil,
			000-10-002-10-001000			TH
J5, J8	2		39357-0002	Molex	Terminal Block, 3.5 mm, 2x1, Tin, TH	Terminal Block, 3.5 mm, 2x1, TH
J6	1		39357-0003	Molex	Terminal Block, 3.5 mm, 3x1, Tin, TH	Terminal Block, 3.5 mm, 3x1, TH
J7	1		800-10-003-10-001000	Mill-Max	Header, 100mil, 3x1, TH	Header, 3x1, 100mil,
L1	1	7uH	7443630700	Wurth Elektronik	Inductor, Shielded Drum Core, Mn-Zn, 7 µH, 21 A, 0.005608 ohm, SMD	
Q1, Q2, Q3	3	CSD18533Q5A	CSD18533Q5A	Texas Instruments	MOSFET, N-CH, 60 V, 100 A, DQJ0008A (VSONP-8)	DQJ0008A
Q4		MMBT3904	MMBT3904LT1G	ON Semiconductor	Transistor, NPN, 40 V, 0.2 A, SOT-23	SOT-23
Q5, Q6	2	2N7002-7-F	2N7002-7-F	Diodes Inc.	MOSFET, N-CH, 60 V, 0.17 A, SOT-23	SOT-23
R1		3.24	CRCW06033R24FKEA	Vishay-Dale	RES, 3.24 ohm, 1%, 0.1W, 0603	0603
R2, R23, R24, R29		100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R3		4.87k	RC0603FR-074K87L	Yageo America	RES, 4.87 k, 1%, 0.1 W, 0603	0603
R4, R8		2.21	RC0805FR-072R21L	Yageo America	RES, 2.21, 1%, 0.125 W, 0805	0805
R5		294k	RC0603FR-07294KL	Yageo America	RES, 294 k, 1%, 0.1 W, 0603	0603
R6		158k	RC0603FR-07158KL	Yageo America	RES, 158 k, 1%, 0.1 W, 0603	0603
R7		1.21	CRCW08051R21FKEA	Vishay-Dale	RES, 1.21 ohm, 1%, 0.125W, 0805	0805
R9		1.65k	RC0603FR-071K65L	Yageo America	RES, 1.65 k, 1%, 0.1 W, 0603	0603
R10		49.9k	RC0603FR-0749K9L	Yageo America	RES, 49.9 k, 1%, 0.1 W, 0603	0603
R11		33.2k	RC0603FR-0733K2L	Yageo America	RES, 33.2 k, 1%, 0.1 W, 0603	0603
R12, R13, R27		47.5k	RC0603FR-0747K5L	Yageo America	RES, 47.5 k, 1%, 0.1 W, 0603	0603
R14, R18, R21		100	RC0603FR-07100RL	Yageo America	RES, 100, 1%, 0.1 W, 0603	0603

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R15	1	49.9	RC0603FR-0749R9L	Yageo America	RES, 49.9, 1%, 0.1 W, 0603	0603
R16, R17	2	0.009	PRL1632-R009-F-T1	Susumu Co Ltd	RES, 0.009, 1%, 1 W, 0612	0612
R19	1	6.81k	RC0603FR-076K81L	Yageo America	RES, 6.81 k, 1%, 0.1 W, 0603	0603
R20, R22, R25	3	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R26	1	10.5k	RC0603FR-0710K5L	Yageo America	RES, 10.5 k, 1%, 0.1 W, 0603	0603
R28	1	1.58k	RC0603FR-071K58L	Yageo America	RES, 1.58 k, 1%, 0.1 W, 0603	0603
SW1	1		5002	Keystone	Test Point, Miniature, White, TH	White Miniature Testpoint
TP1, TP3, TP4	3		5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
U1	1	LM5117QPMH/NOPB	LM5117QPMH/NOPB	Texas Instruments	Wide Input Range Synchronous Buck Controller with Analog Current Monitor, PWP0020A (TSSOP-20)	PWP0020A
U2	1	TL431AIDBZR	TL431AIDBZR	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A
U3	1	LM2903VQDR	LM2903VQDR	Texas Instruments	Dual Comparator, D0008A	D0008A

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated