

4 Bill of Materials, Board Layout, and Schematics

Table 2. Bill of Materials

-001 bq24725A	-002 bq24735	RefDes	Value	Description	Size	Part Number	MFR
1	1	C1	2.2 µF	Capacitor, Ceramic, 25V, X7R, 10%	1210	Std	Std
6	6	C2, C3, C4, C5, C6, C7	10 μF	Capacitor, Ceramic, 25V, X7R, 10%	1206	Std	Std
6	6	C8, C14, C15, C16, C17, C19	0.1 μF	Capacitor, Ceramic, 25V, X7R, 10%	603	Std	Std
4	4	C9, C10, C20, C25	1 μF	Capacitor, Ceramic, 25V, X7R, 10%	603	Std	Std
3	3	C11, C12, C27	0.01 μF	Capacitor, Ceramic, 25V, X7R, 10%	603	Std	Std
0	0	C13, C18, C24	Open	Capacitor, Ceramic, 25V, X7R, 10%	603	Std	Std
1	1	C21	0.047 μF	Capacitor, Ceramic, 25V, X7R, 10%	603	Std	Std
1	1	C22	100 pF	Capacitor, Ceramic, 25V, X7R, 10%	603	Std	Std
1	1	C23	2200 pF	Capacitor, Ceramic, 25V, X7R, 10%	603	Std	Std
1	1	C26	1000 pF	Capacitor, Ceramic, 25V, X7R, 10%	603	Std	Std
1	1	D1	BAT54-V-G	Diode, Schottky, 200-mA, 30-V	SOT23	BAT54-V-G	Vishay-Liteon
1	1	D2	BAT54C-V-G	Diode, Dual Schottky, 200-mA, 30-V	SOT23	BAT54C-V-G	Vishay-Liteon
1	1	J1	ED120/2DS	Terminal Block, 2-pin, 15-A, 5.1mm	0.40 x 0.35 inch	ED120/2DS	OST
1	1	J2	ED120/3DS	Terminal Block, 3-pin, 15-A, 5.1mm	0.60 x 0.35 inch	ED120/3DS	OST
2	2	J3. J4	ED555/3DS	Terminal Block, 3-pin, 6-A, 3.5mm	0.41 x 0.25 inch	ED555/3DS	OST
1	1	JP1	PEC02SAAN	Header, Male 2-pin, 100mil spacing,	0.100 inch x 2	PEC02SAAN	Sullins
1	1	SH1	929950-00	Shorting jumpers, 2-pin, 100mil spacing,		929950-00	3M/ESD
1	1	L1	4.7 µH	Inductor, SMT	0.255 x 0.270 inch	IHLP2525CZER4R7M01	Vishay
3	3	Q1, Q2, Q3	CSD17307Q5A	MOSFET, NChan, 30V, 14A, 9.5millohm	PWRPAK S0-8	CSD17307Q5A	Texas Instruments
2	2	Q4, Q5	CSD17308Q3A	MOSFET, NChan, 30V, 13A, 9.4millohm	PWRPAK 1212	CSD17308Q3A	Texas Instruments
1	1	Q6	BSS138W-7-F	MOSFET, Nch, 50V, 200mA,	SOT-323	BSS138W-7-F	Diodes
2	2	R1, R2	0.01	Resistor, Chip, 1/2W, 1% 150PPM Resistor, Chip, 1W, 1% 75 PPM	1206	PMR18EZPFU10L0 WSLP1206R0100FEA	Rohm Vishay/Dale
1	1	R3	0	Resistor, Chip, 1/16W, 5%	603	Std	Std
1	1	R5	20	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	1	R4	7.5	Resistor, Chip, 1/16W, 1%	603	Std	Std
2	2	R6, R7	3.9	Resistor, Chip, 0.5W, 5%	1210	Std	Std
3	3	R8, R9, R13	4.02k	Resistor, Chip, 1/10W, 1%	603	Std	Std
0	0	R10, R11	Open	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	1	R12	1.00M	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	1	R14	66.5k	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	1	R15	430k	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	1	R16	10.0	Resistor, Chip, 1/4W, 1%	1206	Std	Std
3	3	R17, R18, R19	10.0k	Resistor, Chip, 1/16W, 1%	603	Std	Std



Table 2. Bill of Materials (continued)

-001 bq24725A	-002 bq24735	RefDes	Value	Description	Size	Part Number	MFR
1	1	R20	100k	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	1	R21	12.1k	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	1	R22	316k	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	1	R23	3.01M	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	1	R24	10	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	1	TP1	131-4244-00	Adaptor, 3.5-mm probe clip (or 131-5031-00)	0.200 inch	131-4244-00	Tektronix
11	11	TP2, TP3, TP4, TP5, TP6, TP7, TP8, TP9, TP10, TP11, TP12		Test Point, White, Thru Hole Color Keyed	0.100 x 0.100 inch	5002	Keystone
1	1	TP13	GND	Test Point, Black, Thru Hole Color Keyed	0.100 x 0.100 inch	5001	Keystone
0	0	TP14, 15, 16, 17, 18					
4	4			6-32 NYL nuts		NY HN 632	Building Fasteners
4	4	ST1,ST2,ST3,ST4	4816	STANDOFF M/F HEX 6-32 NYL .500"	sf_thvt_325_rnd	4816	Keystone
1	0	U1	bq24725ARGR	IC, SMBus Charge Controller with NMOS Selector		bq24725ARGR	TI
0	1	U1	bq24735RGR	IC, SMBus Charge Controller with NMOS Selector		bq24735RGR	TI
1	1	_		Label	1.25 x 0.25 inch	THT-13-457-10	Brady
1	1	_	HPA710	2.5x2.5inch 4 layer 2oz. PCB	2.5x2.5inch	PCB	Any

Notes: 1. These assemblies are ESD sensitive, ESD precautions shall be observed.

- 2. These assemblies must be clean and free from flux and all contaminants.
- 3. Use of no clean flux is not acceptable.
- 4. Ref designators marked with an asterisk (***) cannot be substituted. All other components can be substituted with equivalent MFG's components.
- 5. Install label after final wash. Text shall be 8 pt font. Text shall be per Table 1.

Table 1.

Assembly Number	Text		
HPA710-001	bq24725AEVM-710		
HPA710-002	bq24735EVM-710		

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.