PMP20660 REV A Bill of Materials



Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
!PCBA1	1		LM5175EVM-HP PCB	Used in BOM report	LM5175EVM-HP PCB	N/A
C1	1	470uF	EMVH500ADA471MMH0S	Nippon Chemi-Con	CAP, Al Electrolytic, 470uF, 50V, +/-%, 0.15Ohm ESR, 125C, SMT	18x16.5mm
C2, C3, C4, C5	4	10uF	GRM32ER71H106KA12L	MuRata	CAP, CERM, 10 µF, 50 V, +/- 10%, X7R, 1210	1210
C6, C7, C8, C9,	6	22uF	GRM32ER71C226ME18L	MuRata	CAP, CERM, 22 µF, 16 V, +/- 20%, X7R, 1210	1210
C10, C11						
C12	1	1uF	GRM219R71E105KA88D	MuRata	CAP, CERM, 1 μF, 25 V, +/- 10%, X7R, 0805	0805
C13, C14, Cx1,	4	330uF	16SVP330M	Sanyo	CAP, OS-CON, 330 µF, 16 V, +/- 20%, 0.016 ohm, 10x10.3 SMD	10x10.3
Cx2						
C15	1	47pF	GRM1885C1H470JA01D	MuRata	CAP, CERM, 47pF, 50V, +/-5%, C0G/NP0, 0603	0603L
C16	1	4.7uF	GRM21BR71C475KA73L	MuRata	CAP, CERM, 4.7 μF, 16 V, +/- 10%, X7R, 0805	0805
C17, C21	2	0.1uF	GRM188R72A104KA35D	MuRata	CAP, CERM, 0.1uF, 100V, +/-10%, X7R, 0603	0603
C18, C19, C24,	4	0.22uF	GRM188R71E224KA88D	MuRata	CAP, CERM, 0.22 μF, 25 V, +/- 10%, X7R, 0603	0603
C25					, , , , , , , , , , , , , , , , , , , ,	
C20, C28, C29,	4	100pF	GRM1885C2A101JA01D	MuRata	CAP, CERM, 100pF, 100V, +/-5%, C0G/NP0, 0603	0603L
C30					, , , , , , , , , , , , , , , , , , , ,	
C22, C27	2	0.022uF	C0603C223K5RACTU	Kemet	CAP, CERM, 0.022uF, 50V, +/-10%, X7R, 0603	0603
C23	1	0.022uF	GRM188R71H223KA01D	MuRata	CAP, CERM, 0.022 µF, 50 V, +/- 10%, X7R, 0603	0603
D1, D2	2	70V	B170-13-F	Diodes Inc.	Diode, Schottky, 70 V, 1 A, SMA	SMA
D3, D4, D5	3	60V	PMEG6010CEJ,115	NXP Semiconductor	Diode, Schottky, 60 V, 1 A, SOD-323F	SOD-323F
Dx1, Dx2		8.2V	MMSZ5237BS-7-F	Diodes Inc.	Diode, Zener, 8.2 V, 200 mW, SOD-323	SOD-323
Dx3	1	75V	LL4148-13	Diodes Inc.	Diode, Standard, 75V, 150mA, MINI-MELF	MINI-MELF
H1, H2, H3, H4	4	707	NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
J1, J2, J3, J4	4		108-0740-001	Emerson Network Power	Standard Banana Jack, Uninsulated, 15A	Banana Jack
L1	1	1.5uH	IHLP6767GZER1R5M01	Vishay Dale	Inductor, Molded, Shielded, 1.5uH, 42Arms, 65Asat, 1.88mOhm, SMT	Dariaria dadk
LBL1	1	1.0011	THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x
	'		1111 14 420 10	Brady	11101111al 11al10101 1 1111able Eabold, 0.000 W X 0.200 11 10,000 per foll	0.200"W
Q1, Q2, Q3	3	60V	BSC028N06NS	Infineon Technologies	MOSFET, N-CH, 60 V, 100 A, PG-TDSON-8	PG-TDSON-8
Q5, Q6, Q7, Q8	4	25V	CSD16414Q5	Texas Instruments	MOSFET, N-CH, 25 V, 100 A, VSON-CLIP-8	DQH0008A
Qx1	1	60V	2N7002BK,215	NXP USA	MOSFET, N-CH, 60V, 350mA, 1.6 Ohm @ 10Vgs, SOT-23	SOT-23-3
R1a, R1b	2	0.01	RL7520WT-R010-F	Susumu Co Ltd	RES, 0.01, 1%, 2 W, 3008	3008
R2, R3, R4, R5,	10	0.01	RC0603JR-070RL	Yageo America	RES, 0 ohm, 5%, 0.1W, 0603	0603L
R15, R17, R24,	10	ľ	TO COCCOUNT OF CITE	rages / interior	1123, 0 01111, 070, 0.1777, 0000	00002
R25, R26, R27						
R6, R8	2	100	RC0603FR-07100RL	Yageo America	RES, 100 ohm, 1%, 0.1W, 0603	0603L
R7a, R7b	2	0.006	WSHM28186L000FEA	Vishay Dale	RES, 0.006 ohm, 1%, 7W, 2818	2818
R9, R11	2	10.0	RC0603FR-0710RL	Yageo America	RES, 10.0 ohm, 1%, 0.1W, 0603	0603L
R10, R23	2	10.0k	RC0603FR-0710KL	Yageo America	RES, 10.0k ohm, 1%, 0.1W, 0603	0603L
R13	1	287k	CRCW0603287KFKEA	Vishay-Dale	RES, 287 k, 1%, 0.1 W, 0603	0603
R14	1	280k	RC0603FR-07280KL	Yageo America	RES, 280k ohm, 1%, 0.1W, 0603	0603L
R16, R21	2	10.0	CRCW060310R0FKEA	Vishay-Dale	RES, 10.0, 1%, 0.1 W, 0603	0603
R18	1	10.0 107k	CRCW0603107KFKEA	Vishay-Dale	RES, 107 k, 1%, 0.1 W, 0603	0603
R19		93.1k	RC0603FR-0793K1L	Yageo America	RES, 93.1 k, 1%, 0.1 W, 0603	0603
R20	1	100k	RC0603FR-07100KL	Yageo America	RES, 100 k, 1%, 0.1 W, 0603	0603
R22	1	20.0k	RC0603FR-0720KL	Yageo America	RES, 20.0k ohm, 1%, 0.1W, 0603	0603L
Rx1a, Rx1b	2	0.47	RL73K3AR47J	TE	RES, 0.47 ohm, 5%, 1W, 2512	2512
Rx2	1	1.00Meg	CRCW06031M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.1 W, 0603	0603
Rx3	1	1.00Meg	CRCW06031M00FKEA	Vishay-Dale Vishay-Dale	RES, 1.00 M, 1%, 0.1 W, 0603 RES, 150, 1%, 0.1 W, 0603	0603
S1, S2, S3	3	130	CJS-1201TA	Copal Electronics	Slide SW, SPDT 0.1A 50VDC	SW, 3.1x2.5x6 mm
01, 02, 00	ა		000-12011A	Copal Electronics Page 1		OVV, J. IAZ.DAU IIIIII

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
TP1, TP3	2	Red	5005	Keystone	Test Point, Compact, Red, TH	Red Compact
						Testpoint
TP2, TP4	2	Black	5006	Keystone	Test Point, Compact, Black, TH	Black Compact
						Testpoint
TP5	1	PGOOD	5007	Keystone	Test Point, Compact, White, TH	White Compact
						Testpoint
TP6, TP7	2	White	5007	Keystone	Test Point, Compact, White, TH	White Compact
						Testpoint
U1	1		LM5175PWPR	Texas Instruments	42V Wide VIN 4-Switch Synchronous Buck-Boost Controller, PWP0028F	PWP0028F
C26	0	47pF	GRM1885C1H470JA01D	MuRata	CAP, CERM, 47pF, 50V, +/-5%, C0G/NP0, 0603	0603L
FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
Q4	0	60V	BSC028N06NS	Infineon Technologies	MOSFET, N-CH, 60 V, 100 A, PG-TDSON-8	PG-TDSON-8
R12	0	0	RC0603JR-070RL	Yageo America	RES, 0 ohm, 5%, 0.1W, 0603	0603L

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated