Variant: 001 Generated: 12/21/2017 7:33:05 AM TID #: TIDA-01570

TIDA-01570 REV E1 Bill of Materials



Item #	Designator	Quantity	Value	alua Datiliumhar Manufaalurar Provinter			
1	PCB1		value	PartNumber TIDA-01570	Manufacturer Any	Description Printed Circuit Board	PackageReferen
2	A1	1		N/A	Used in BOM report		eg: 0603, used in
3	C1	1	0.47uF	JMK105B7474KVHF	Taiyo Yuden	CAP, CERM, 0.47 µF, 6.3 V, +/- 10%, X7R, 0402	PnP report 0402
4	C2	1	10uF	EEE-FK1H100UR	Panasonic	CAP, AL, 10 µF, 50 V, +/- 20%, 1.52 ohm, AEC-Q200 Grade 2, SMD	SMT Radial C
5	C3, C6	2	10uF	GRM32ER71H106MA12 C1210C104K5RACTU	MuRata	CAP, CERM, 10 µF, 50 V, +/- 20%, X7R, 1210 CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 1210	1210
6	C4, C7 C5, C8	2	0.1uF 0.01uF	C0805C103K5RACTU	Kemet Kemet	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 1210 CAP, CERM, 0.01 µF, 50 V, +/- 10%, X7R, 0805	1210 0805
8	C9, C15, C18,	10	0.1uF	0402YC104KAT2A	AVX	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0402	0402
	C24, C31, C59, C60, C63, C64, C69						
9	C10, C11, C12	3	22uF	C3225X7R1C226K250AC	TDK	CAP, CERM, 22 µF, 16 V, +/- 10%, X7R, 1210	1210
10 11	C13 C14, C17, C23,	1	4.7uF 1.0µF	CGA4J1X7R1E475K125AC CL05B105KQ5NQNC	TDK Samsung Electro-Mechanics	CAP, CERM, 4.7 µF, 25 V,+/- 10%, X7R, AEC-Q200 Grade 1, 0805 CAP CER 1UF 6.3V 10% X7R 0402	0805 0402 (1005 Metric)
	C33, C45, C47	0	1.001		America, Inc		0402 (1003 Metric)
12	C16, C22, C30, C34, C36, C38, C39, C41, C49,	10	10uF	CL21B106KOQNNNE	Samsung Electro-Mechanics	CAP, CERM, 10 µF, 16 V, +/- 10%, X7R, 0805	0805
13	C76 C19, C20, C21, C26, C27	5	22uF	GCM21BD70J226ME36L	MuRata	CAP, CERM, 22 uF, 6.3 V, +/- 20%, X7T, AEC-Q200 Grade 1, 0805	0805
14	C25	1	10uF	GCM21BR71A106KE22L	MuRata	CAP, CERM, 10 µF, 10 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0805	0805
15 16	C28, C29 C32	2	0.01uF 22uF	GRM155R71C103KA01D GRM21BZ71A226ME15L	MuRata MuRata	CAP, CERM, 0.01uF, 16V, +/-10%, X7R, 0402 CAP, CERM, 22 uF, 10 V, +/- 20%, X7R, 0805	0402 0805
17	C35, C37, C40, C42, C43, C44, C50, C51, C54, C55, C57, C58, C61	13	0.22uF	GCM155R71C224KE02D	MuRata	CAP, CERM, 0.22 μF, 16 V,+/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402
18	C46, C48, C72, C74	4	4.7pF	GJM1555C1H4R7BB01D	MuRata	CAP, CERM, 4.7 pF, 50 V, +/- 2%, C0G/NP0, 0402	0402
19	C52 C53 C56	1	0.22uF	GCM155R71C224KE02 GCM188R70.I225KE22D	MuRata	CAP, CERM, 0.22 uF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
20 21	C53, C56 C62	1	2.2uF 2200pF	GCM188R70J225KE22D UMK105B7222KV-F	MuRata Taiyo Yuden	CAP, CERM, 2.2 uF, 6.3 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603 Cap, Cer-X7R, 2200pF, 50V, 10%, 0402	0603 0402 (1005 Metric
22	C65	1	0.1uF	C1005X5R1A104K050BA	TDK	CAP, CERM, 0.1 µF, 10 V, +/- 10%, X5R, 0402	0402
23 24	C66, C68 C67, C71	2	1uF 4700pF	GRM155R6YA105ME11D GCM188R71H472KA37D	MuRata MuRata	CAP, CERM, 1 µF, 35 V, +/- 20%, X5R, 0402 CAP, CERM, 4700 pF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0402 0603
25	C70	1	4.7uF	GRM32ER71H475KA88L	MuRata	CAP, CERM, 4.7 uF, 50 V, +/- 10%, X7R, 1210	1210
26	C73	1	0.01uF	GRM188R71H103KA01D C0603C334K4RACTU	MuRata	CAP, CERM, 0.01 uF, 50 V, +/- 10%, X7R, 0603	0603
27 28	C75 D1	1	0.33uF 40V	C0603C334K4RACTU BAT165E6327HTSA1	Kemet Infineon Technologies	CAP, CERM, 0.33 uF, 16 V, +/- 10%, X7R, 0603 Diode, Schottky, 40 V, 0.75 A, AEC-Q101, SOD-323	0603 SOD-323
29	D2	1	26V	SMBJ26A-13-F	Diodes Inc.	Diode, TVS, Uni, 26 V, 600 W, SMB	SMB
30 31	D3 D4	1	Red Green	SML-P12UTT86 SML-P12PTT86	Rohm Rohm	LED, Red, SMD LED, Green, SMD	LED, 1x.2x.6mm
32	D4 D5	1	14V	SMBJ14A-13-F	Diodes Inc.	Diode, TVS, Uni, 14 V, 600 W, SMB	LED, 1x.2x.6mm SMB
33	H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
34	H5, H6, H7, H8 J1, J5, J7	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
35 36	J1, J5, J7 J2, J3	3		1727010 TSW-103-07-G-S	Phoenix Contact Samtec	Conn Term Block, 2POS, 3.81mm, TH Header, 100mil, 3x1, Gold, TH	2POS Terminal Bl 3x1 Header
37	J4	1		TSW-105-09-G-D	Samtec	Header, 2.54mm, 5x2, Gold, TH	Header, 2.54mm,
38	J6	1		QSH-030-01-L-D-A	Samtec	Receptacle, 0.5 mm, 30x2, Gold, TH	TH Receptacle, 0.5 m 30x2, TH
39	L2, L3	2	470nH	DFE252012PD-R47M	MuRata Toko	Inductor, Shielded, 470 nH, 4.7 A, 0.021 ohm, SMD	1008
40	L4	1	1uH	DFE252012PD-1R0M	MuRata Toko	Inductor, Shielded, 1 uH, 3.8 A, 0.035 ohm, AEC-Q200 Grade 1, SMD	1008
41	L5, L6, L7, L8, L9, I 10	6	120 ohm	BLM18KG121TH1D	MuRata	Ferrite Bead, 120 ohm @ 100 MHz, 1.9 A, 0603	0603
42	L100	1	2.2uH	XAL5030-222MEB	Coilcraft	Inductor, Shielded, Composite, 2.2 uH, 9.2 A, 0.01 ohm, SMD	5.3x31.x5.5mm
43 44	R1, R3 R2	2	10k 2.2k	CRCW040210K0JNED CRCW04022K20JNED	Vishay-Dale	RES, 10k ohm, 5%, 0.063W, 0402 RES, 2.2 k, 5%, 0.063 W, 0402	0402
44	R4	1	220	CRCW0402220RJNED	Vishay-Dale Vishay-Dale	RES, 220, 5%, 0.063 W, 0402	0402
46	R6, R7, R8, R9, R15, R16, R18, R20, R21, R24, R25, R33, R35, R36, R38, R39, R40, R59, R60, R61, R62, R63, R64, R65, R66, R67, R73, R76, R77, R78, R79, Dec Dec	34	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0 ohm, 5%, 0.063W, 0402	0402
47	R82, R83, R85 R10	1	12.1k	CRCW040212K1FKED	Vishay-Dale	RES, 12.1 k, 1%, 0.063 W, 0402	0402
48 49	R11, R12 R13, R14, R23,	2	3.3k 10k	CRCW04023K30JNED CRCW040210K0JNED	Vishay-Dale	RES, 3.3 k, 5%, 0.063 W, 0402 RES, 10 k, 5%, 0.063 W, 0402	0402
	R26, R31, R37, R41, R48, R49, R50, R57, R58, R74, R75, R80, R81, R84				Vishay-Dale		
50 51	R17 R19	1	48.7k 1.0k	CRCW040248K7FKED RC0603JR-071KL	Vishay-Dale Yageo America	RES, 48.7 k, 1%, 0.063 W, 0402 RES, 1.0 k, 5%, 0.1 W, 0603	0402 0603
52	R22	1	2.43k	CRCW04022K43FKED	Vishay-Dale	RES, 2.43 k, 1%, 0.063 W, 0402	0402
53 54	R29 R42, R44, R45, R47	1 4	4.7k 4.7k	CRCW04024K70JNED CRCW06034K70JNEA	Vishay-Dale Vishay-Dale	RES, 4.7 k, 5%, 0.063 W, 0402 RES, 4.7 k, 5%, 0.1 W, 0603	0402 0603
55 56	R51 R52, R55, R69, R71	4	47.5k 61.9	CRCW040247K5FKED CRCW040261R9FKED CRCW040233R2FKED	Vishay-Dale Vishay-Dale	RES, 47.5 k, 1%, 0.063 W, 0402 RES, 61.9, 1%, 0.063 W, 0402	0402 0402
57 58	R53, R54, R56 R68	3	33.2 3.0k	CRCW040233R2FKED CRCW04023K00JNED	Vishay-Dale Vishay-Dale	RES, 33.2, 1%, 0.063 W, 0402 RES, 3.0 k, 5%, 0.063 W, 0402	0402 0402
59	R70	1	33k	CRCW040233K0JNED	Vishay-Dale	RES, 33 k, 5%, 0.063 W, 0402	0402
60	S3, S4	2		SKRKAEE010	Alps	Switch, Tactile, 12v, 50mA, Vertical, SMD	2.9x2x3.9mm SME
61	TP1 U1	1		5001 LM536253QRNLRQ1	Keystone	Test Point, Miniature, Black, TH 2.5/3.5A, 36 V Synchronous, 2.1MHz, Automotive Step Down DC-DC	Black Miniature Testpoint RNL0022A
62 63	U1 U2	1		LM536253QRNLRQ1	Texas Instruments Texas Instruments	2.5/3.5A, 36 V Synchronous, 2.1MHz, Automotive Step Down DC-DC Converter, RNL0022A (VQFN-HR-22) Boost and Dual Buck Regulators With Diagnostic Functions, RHB0032N	RNL0022A RHB0032N
64	U2 U3	1		TPS7A5201QRGRRQ1	Texas Instruments	VQFN-32) TPS7A5201RTKT, RTK0020C (VQFNP-20)	RTK0020C
65	U4	1		X1642BIGABL	Texas Instruments	Single-Chip 77- and 79-GHz FMCW Radar Sensor, ABL0161B (FCBGA- 161)	ABL0161B
66	U5	1		TCAN1042GVDRQ1	Texas Instruments	Automotive Fault Protected CAN Transceiver With Flexible Data-Rate, D0008A (SOIC-8)	D0008A
67	U6	1		MX25R1635FZUIH0	Macronix International Co., LTD	ULTRA LOW POWER, 16M-BIT [x 1/x 2/x 4] CMOS MXSMIO (SERIAL MULTI I/O) FLASH MEMORY, SON-8	SON-8
68 69	U7	1		TCAN4550RGYRQ1 CX3225SA40000D0PTWCC	Texas Instruments	CAN-FD Controller with Integrated Transceiver, RGY0020A (VQFN-20)	RGY0020A
	Y3, Y4 FID1, FID2, FID3,	0		N/A	Kyocera N/A	Crystal, 40 MHz, 8pF, SMD Fiducial mark. There is nothing to buy or mount.	3.2x2.5mm Fiducial
70							
70	FID4, FID5, FID6	c	0	000000000000000000000000000000000000000	Mahari Dala	DEC 0 shar 5% 0.0000M 0400	0.400
	FID4, FID5, FID6 R5, R30, R72 R43, R46	0	0 4.7k	CRCW04020000Z0ED CRCW06034K70JNEA	Vishay-Dale Vishay-Dale	RES, 0 ohm, 5%, 0.063W, 0402 RES, 4.7 k, 5%, 0.1 W, 0603	0402

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your noncompliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/stdterms.htm), evaluation

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated