Filename: PMP30439 Rev_B-BOM.xls

Variant: None

Generated: 11/27/2018 3:18:24 PM TID #: <Parameter TID not found>

TEXAS INSTRUMENTS

PMP30439 REV B Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1	1	100uF	400KXW100MEFC16X30	Rubycon	CAP, AL, 100 μF, 400 V, +/- 20%, TH	RCAP, 16x30mm
2	C2	1	10uF	200CFX10MEFC10X16	Rubycon	CAP, AL, 10 μF, 200 V, +/- 20%, TH	10x16mm
3	C3	1	560pF	C0603C561J5GACTU	Kemet	CAP, CERM, 560 pF, 50 V,+/- 5%, C0G/NP0, 0603	0603
4	C4	1	1uF	885012206052	Wurth Elektronik	CAP, CERM, 1 µF, 16 V,+/- 10%, X7R, 0603	0603
5	C5	1	DNP	DNP	DNP	DNP	0603
6	D1	1	400V	ES1G-13-F	Diodes Inc.	Diode, Superfast Rectifier, 400 V, 1 A, SMA	SMA
7	J1	1		ED555/2DS	On-Shore Technology	Terminal Block, 3.5mm Pitch, 2x1, TH	7.0x8.2x6.5mm
8	L1	1	8.2mH	MSS1210-825KE	Coilcraft	Inductor, Shielded, Ferrite, 8.2 mH, 0.35 A, 6.2 ohm, SMD	12.3x10x12.3mm
9	Q1	1	FDD5N50NZTM	FDD5N50NZTM	ON Semiconductor	MOSFET, N-CH, 500 V, 4 A, DPAK	DPAK
10	R1, R4	2	150k	RC0603FR-07150KL	Yageo America	RES, 150 k, 1%, 0.1 W, 0603	0603
11	R2, R3	2	10.0	RC0603FR-0710RL	Yageo America	RES, 10.0, 1%, 0.1 W, 0603	0603
12	R5	1	3.01	RC0805FR-073R01L	Yageo America	RES, 3.01, 1%, 0.125 W, 0805	0805
13	R6	1	13.0	CRCW080513R0FKEA	Vishay-Dale	RES, 13.0, 1%, 0.125 W, 0805	0805
14	TP1, TP2, TP4	3		5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature
							Testpoint
15	TP3, TP8	2		5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature
							Testpoint
16	TP5, TP7	2		5003	Keystone	Test Point, Miniature, Orange, TH	Orange Miniature
							Testpoint
17	TP6	1		5002	Keystone	Test Point, Miniature, White, TH	White Miniature
							Testpoint
18	U1	1	LM3445MM	LM3445MM	Texas Instruments	Triac Dimmable Offline LED Driver, PowerWise, 10-pin MSOP	MUB10A

"DNP" = do not populate

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2019, Texas Instruments Incorporated