

Addressing challenges in data-center power delivery with 800 VDC architectures



Jeff Morroni



Given rapid growth in the server and artificial intelligence (AI) markets, the amount of energy required per rack is increasing from 100kW to over 1MW. This increase requires designers to fundamentally reimagine the entire data center's power delivery path, from the grid to the gates of processors.

While 48V infrastructures were “the next big challenge” just a few years ago, using 48V distribution with a 1MW rack would require almost 450lbs of copper to maintain distribution losses – an unsustainable amount in both weight and cost. Today, TI's power-management and sensing technology can enable DC architectures as high as 800V. That's why we're working with NVIDIA on a 800 VDC distribution ecosystem to help further scale computing performance and power delivery.

800V_{DC} distribution

800 VDC distribution and power conversion is the heart of future AI data center power delivery architectures. Technologies such as [gallium nitride \(GaN\)](#) enable power density and conversion efficiency in these systems.

Furthermore, enabling safe operation of 800 VDC systems requires voltage sensing, protection and safety isolation. An 800 VDC system architecture needs products and technologies such as solid-state relays, 800V hot swaps, high-accuracy battery monitors for battery backup units and central battery units, isolated gate drivers, isolated current sensors and voltage sensors.

This type of system architecture can deliver high-reliability, energy-efficient power distribution across data centers.

The next generation of AI processors

Beyond 800 VDC distribution, improving power density and thermal management at the 48V and processor power levels requires additional innovations. Fundamentally, while power requirements are increasing, racks and trays are not getting bigger. The power solutions must evolve to become denser and more efficient.

TI's 100V mid-voltage GaN technology helps support the 48V trend toward higher efficiency and density, enabling greater integration, higher efficiency, and smaller overall solution size. Our integrated GaN solutions simplify previously more complex, higher-density and higher-efficiency intermediate bus-converter architectures.

Processing the >1,000A required in today's systems demands high-frequency multiphase processor power. TI's high-performance bipolar complementary metal-oxide semiconductor (CMOS) double-diffused MOS (DMOS) power process enables less multiphase processor power. In this regard, TI is also working closely with NVIDIA to define next-generation multiphase solution requirements to support >1MW rack trends.

Conclusion

As technologies evolve and demands grow more complex, TI's collaboration with NVIDIA is positioned to deliver integrated, high-performance solutions for tomorrow's systems, combining world-class energy and AI expertise to drive real, transformative progress.

Additional resources

- Learn more about our [data center and enterprise computing](#).
- Watch our "[Powering data centers: From the grid to the gate](#)" video.
- Check out Nvidia's blog post, "[NVIDIA 800 VDC Architecture Will Power the Next Generation of AI Factories](#)."

Trademarks

All trademarks are the property of their respective owners.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025