

TPS22962EVM-079 10A Load Switch IC

The TPS22962EVM-079 evaluation module (EVM) allows the user to connect power to and control the 8-pin SON package load switch. Parameters such as the On-resistance, output rise time and output discharge resistance can be easily evaluated. [Table 1](#) lists a short description of the load switch performance specifications; refer to the datasheet [SLVSCN3](#) for more details

Table 1. TPS22962 Slew Rate, Output Current Rating, Enable, and Output Discharge Options

| EVM | Device | Slew Rate Typical $V_{BIAS} = 5V$ | VIN (V) | Max. Continuous Current | Enable (ON Pin) | Quick Output Discharge |
|------------|----------|--------------------------------------|---------|-------------------------|-----------------|------------------------|
| HVL079-003 | TPS22962 | 2663 μs | 5 | 10A | Active High | Yes |

Contents

| | | |
|---|-------------------------------|----|
| 1 | Description | 2 |
| 2 | Electrical Performance | 2 |
| 3 | Schematic | 2 |
| 4 | Layout | 3 |
| 5 | Operation | 6 |
| 6 | Test Configurations | 7 |
| 7 | Bill of Materials (BOM) | 10 |

List of Figures

| | | |
|---|---|---|
| 1 | TPS22962EVM-079 Schematic | 2 |
| 2 | TPS22962EVM-079 Top Assembly | 3 |
| 3 | TPS22962EVM-079 Top Layout | 4 |
| 4 | TPS22962EVM-079 Bottom Layout | 5 |
| 5 | R_{ON} Setup | 7 |
| 6 | Slew Rate Setup | 8 |
| 7 | TPS22962 V_{out} t_R Example ($V_{BIAS} = 5V$, $V_{IN} = 5V$, $R_L = 10\Omega$) | 9 |

List of Tables

| | | |
|---|---|----|
| 1 | TPS22962 Slew Rate, Output Current Rating, Enable, and Output Discharge Options | 1 |
| 2 | Bill of Materials | 10 |

1 Description

The TPS22962EVM is a two sided PCB containing the TPS22962 load switch device. The VIN and VOUT connections to the device and the PCB layout routing are capable of handling high continuous currents and provide a low resistance pathway into and out of the device under test. Test point connections allow the EVM User to control the device with user defined test conditions and make accurate RON measurements.

1.1 Features

- VIN input voltage range: 0.8V to 5.5V.
- VBIAS voltage range: 2.5 to 5.5V
- EVM allows access to the VIN, VOUT and ON pin of the TPS22962 Load Switch Device.
- On board CIN and COUT capacitors.
- 10A max continuous current.

2 Electrical Performance

Refer to the datasheet [SLVSCN3](#) for detailed electrical characteristics of the TPS22962.

3 Schematic




Figure 1. TPS22962EVM-079 Schematic

4 Layout




Figure 2. TPS22962EVM-079 Top Assembly




Figure 3. TPS22962EVM-079 Top Layout




Figure 4. TPS22962EVM-079 Bottom Layout

4.1 Setup

This section describes the jumpers and connectors on the EVM as well as how to properly connect, set up, and use the EVM.

4.1.1 J1 – Input Connection

This is the connection for the leads from the input source. Connect the positive lead to J1-1 (+) terminal and the negative lead to J1-2 (–) terminal (GND). TP1 is also available for connecting to the input.

J1 Connector is rated for currents of 15A, use the J1 input connection point when operating the EVM in the High current mode ($I_{IN} > 3A$).

4.1.2 J2 – Output Connection

This is the connection for the output of the EVM. Connect the positive lead to J2-2 (+) terminal and the negative lead to J2-1 (–) terminal (GND). TP5 is also available for connecting to the output.

J2 Connector is rated for currents of 15A, use the J2 input connection point when operating the EVM in the High current mode ($I_{OUT} > 3A$).

4.1.3 JP3 – ON

This is the enable input for the device. A shorting jumper must be installed on JP3 in either the High or Low Position. The TPS22962 is active High. ON must not be left floating. An external enable source can be applied to the EVM by removing the shunt and connecting a signal to TP6. Refer to the datasheet for proper ON and OFF voltage level settings. A switching signal may also be used and connected at this point.

4.1.4 TP2 – VIN Sense, TP3 – VOUT Sense

These two connections are used when very accurate measurements of the input or output are required. R_{ON} measurements should be made using these sense connections when measuring the voltage drop from VIN to VOUT and then calculating the resistance.

4.1.5 TP4 - VBIAS

This connection to the device is used for applying VBIAS voltage, VBIAS voltage range is from 2.5V to 5.5V, VBIAS voltage must be applied for the device to operate.

4.1.6 JP1 Input Capacitor

During normal operation a shorting jumper is placed on JP1 this connects C1 capacitor from the input of the device to ground. Refer to the Applications Section of the Datasheet for additional information on selecting the input capacitor.

4.1.7 JP2 – Output Capacitor

During normal operation a shorting jumper is placed on JP2 this connects C2 capacitor from the output of the device to ground. Refer to the Applications Section of the Datasheet for additional information on selecting the output capacitor.

4.1.8 TP7/TP8/TP9 – GND

These are connections to GND.

5 Operation

Connect the positive input of the VIN power supply to VIN at J1-1 for currents greater than 3A, or connect the positive input of the VIN power supply to VIN at TP1 for currents less than 3A. Connect the negative lead of the power supply to GND at J1-2. The input voltage range of the TPS22962EVM-079 is 0.8V to 5.5V.

The VBIAS voltage range of the TPS22962EVM-079 is 2.5V to 5.5V. Connect the positive input of the VBIAS power supply to VBIAS at TP4. Connect the negative lead of the V_{BIAS} power supply to GND at TP7, TP8 or TP9.

External output loads can be applied to the switch by connecting between J2-2 VOUT and J2-1 GND for currents greater than 3A. For currents less than 3A, connect the output load between TP5 and GND (TP7, TP8 or TP9). The TPS22962EVM-079 is rated for a maximum continuous current of 10A. Configure JP3 as required. JP3 must be installed for proper operation. When the ON pin is asserted high, the output of the TPS22962 will be enabled.

6 Test Configurations

6.1 On-Resistance (R_{ON}) Test Setup

Figure 5 shows a typical setup for measuring On-Resistance. The voltage drop across the switch is measured using the sense connections then divided by the current into the load yielding the R_{ON} resistance.




Figure 5. R_{ON} Setup

6.2 Slew Rate Test Setup

Figure 6 shows a test setup for measuring the Slew Rate of the Load Switch. Controlling the ON pin of the switch with a signal source and then measuring the VOUT with a scope shows the switches ability to have a controlled VOUT ramp.




Figure 6. Slew Rate Setup

6.3 VOUT Slew Rate Examples




Figure 7. TPS22962 Vout t_R Example ($V_{BIAS} = 5V$, $V_{IN} = 5V$, $R_L = 10\Omega$)

7 Bill of Materials (BOM)
Table 2. Bill of Materials

| Designator | Quantity | Value | Description | Package Reference | Part Number | Manufacturer | Alternate | |
|-------------------------|----------|-----------|--|------------------------------|--------------------|-----------------------------|--------------|----------|
| | | | | | | | Part Number | Manufac. |
| !PCB | 1 | | Printed Circuit Board | | HVL079 | Any | - | - |
| C1 | 1 | 1uF | CAP, CERM, 1uF, 16V, +/-10%, X5R, 0603 | 0603 | C0603C105K4PACTU | Kemet | | |
| C2 | 1 | 0.1uF | CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603 | 0603 | GCM188R71H104KA57B | MuRata | | |
| C3 | 1 | 0.01uF | CAP, CERM, 0.01uF, 50V, +/-5%, X7R, 0603 | 0603 | C0603C103J5RACTU | Kemet | | |
| FID1, FID2, FID3 | 3 | | Fiducial mark. There is nothing to buy or mount. | Fiducial | N/A | N/A | | |
| J1, J2 | 2 | ED120/2DS | Terminal Block, 2-pin, 15-A, 5.1mm | 0.40 x 0.35 inch | ED120/2DS | OST | | |
| JP1, JP2 | 2 | | Header, 100mil, 2x1, Tin plated, TH | Header, 2 PIN, 100mil, Tin | PEC02SAAN | Sullins Connector Solutions | | |
| JP3 | 1 | | Header, 100mil, 3x1, Tin plated, TH | Header, 3 PIN, 100mil, Tin | PEC03SAAN | Sullins Connector Solutions | | |
| LBL1 | 1 | | Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll | PCB Label 0.650"H x 0.200"W | THT-14-423-10 | Brady | | |
| SH-JP1, SH-JP2, SH-JP3 | 3 | 1x2 | Shunt, 100mil, Gold plated, Black | Shunt | 969102-0000-DA | 3M | SNT-100-BK-G | Samtec |
| TP1, TP2, TP3, TP4, TP5 | 5 | Red | Test Point, Multipurpose, Red, TH | Red Multipurpose Testpoint | 5010 | Keystone | | |
| TP6 | 1 | Yellow | Test Point, Compact, Yellow, TH | Yellow Compact Testpoint | 5009 | Keystone | | |
| TP7, TP8, TP9 | 3 | Black | Test Point, Multipurpose, Black, TH | Black Multipurpose Testpoint | 5011 | Keystone | | |
| U1 | 1 | | IC, Ultra- Low On Resistance, 6A Single Chan-Load SW with Controlled Turn-On | DNY0008A | TPS22962DNY | Texas Instruments | | None |

Note: Unless otherwise noted in the Alternate Part Number and/or Alternate Manufacturer columns, all parts may be substituted with equivalents.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

| | |
|------------------------------|--|
| Audio | www.ti.com/audio |
| Amplifiers | amplifier.ti.com |
| Data Converters | dataconverter.ti.com |
| DLP® Products | www.dlp.com |
| DSP | dsp.ti.com |
| Clocks and Timers | www.ti.com/clocks |
| Interface | interface.ti.com |
| Logic | logic.ti.com |
| Power Mgmt | power.ti.com |
| Microcontrollers | microcontroller.ti.com |
| RFID | www.ti-rfid.com |
| OMAP Applications Processors | www.ti.com/omap |
| Wireless Connectivity | www.ti.com/wirelessconnectivity |

Applications

| | |
|-------------------------------|--|
| Automotive and Transportation | www.ti.com/automotive |
| Communications and Telecom | www.ti.com/communications |
| Computers and Peripherals | www.ti.com/computers |
| Consumer Electronics | www.ti.com/consumer-apps |
| Energy and Lighting | www.ti.com/energy |
| Industrial | www.ti.com/industrial |
| Medical | www.ti.com/medical |
| Security | www.ti.com/security |
| Space, Avionics and Defense | www.ti.com/space-avionics-defense |
| Video and Imaging | www.ti.com/video |

TI E2E Community

e2e.ti.com