

AN-1724 LM5015 Isolated Two-Switch DC-DC Regulator Evaluation Board

1 Introduction

The LM5015 Isolated DC-DC regulator evaluation board provides a low cost and fully functional DC-DC regulator without employing any discrete power MOSFET. The evaluation board can be configured as either an Isolated Two-Switch Forward DC-DC Regulator, or an Isolated Two-Switch Flyback DC-DC Regulator. The factory default configuration of the evaluation board is forward topology. The forward converter configuration will produce about 2% higher efficiency and lower output ripple voltage than the flyback. Whereas, the Flyback configuration costs slightly less. Suggestion to reconfigure the evaluation board as an Isolated Two-Switch Flyback DC-DC Regulator is provided at the end of this document.

For detailed features and technical information of the LM5015 device, see the *LM5015 High Voltage Monolithic Two-Switch Forward DC-DC Regulator Data Sheet* (SNVS538). For non-isolated applications, see the *AN-1725 LM5015 Non-Isolated Two-Switch DCDC Regulator Evaluation Board User's Guide* (SNVA292).

The evaluation board features:

- Input Voltage: 36V to 72VIsolated Output Voltage: 5V
- Output Current: 0A minimum, 2.5A nominal, and 3A maximum
- Input UVLO Threshold: 34V nominal
- Measured Efficiency: 86% (V_{IN} = 48V, I_{OUT} = 2.5A)
- Switching Frequency: 300 kHz
- Ability to Synchronize to External Clock
- Ability to Be Remote Controlled (Enable/Disable)
- Two Layer PC Board and Top Side Component Placement
- Configurable as Either a Forward (Factory Default) or a Flyback Regulator
- Board Size (WxLxH): 2.5 in. x 3.5 in. x 0.63 in






Figure 1. Evaluation Board Layout

2 Board Connections/Start-up

Figure 1 shows the PC board layout. The input connections are made to connectors J1 (high potential) and J2 (input return). The load is connected between connectors J3 (5V) and J4 (5V return). Ensure the wires are adequately sized for the intended load current.

A DC power supply capable of at least 75V and 0.5A is recommended as the input power source for the evaluation board. Use the output over-voltage and over-current limit features of the DC power supply to protect the board against damage by errant connections.

A resistive load is optimal, but an appropriate electronic load is acceptable. The maximum load current is 3A. Exceeding this current will cause the LM5015 to enter cycle-by-cycle peak current limit mode, and the output voltage will fall below the regulated 5V. Current limit mode is triggered whenever the primary switch current exceeds 1.2A (nominal).

During the first power up, the load should be kept reasonably low (<0.1A). Before start-up, a voltmeter should be connected to the input terminals, and to the output terminals. The load current should be monitored with an ammeter or a current probe. It is recommended that the input voltage be increased gradually.

Before the input voltage reach about 34V, which is the evaluation board's Under Voltage Lock-Out (VULO) threshold preset with R9 and R10, there should be no output voltage, and the input current should be lower than 10 mA. Otherwise, remove power immediately and verify if the input polarity is reversed.

When the input voltage is increased to 36V, the output voltage should be established at 5V nominal. If that indicates correctly, increase the input voltage gradually to 72V maximum and the output voltage should be regulated at 5V $\pm 1.5\%$ over the entire input voltage range from 36V to 72V. Otherwise, remove power and check if the connection is correct.

Once the proper setup has been established, full load can be applied. A final check of efficiency is suggested to confirm that the unit is operating properly. Efficiency significantly lower than 80% at full load indicates a problem.



The evaluation board can be synchronized to an external clock of faster than the board's native oscillator frequency, which is twice the switching frequency F_{SW} . Note that the LM5015 oscillator uses a divide-by-2 circuit and the actually switching frequency is half the oscillator frequency set by R2. Since the evaluation board's switching frequency is 300 kHz, the external clock should be faster than 600 kHz. The external clock signal should feed into the plated via hole of the SYNC port, referenced to the AGND node. Refer to the LM5015 datasheet for the requirement of the external clock signal for successful synchronization.

The evaluation board can be remote controlled for enabling and disabling. The control port on the PC board is the plated via hole dedicated to EN node. The remote control signal should be referenced to the AGND node. Refer to the LM5015 datasheet for detailed information of remote control.

3 Isolated Two-Switch Forward DC-DC Regulator

Figure 2 shows the schematic of the evaluation board in a default configuration of a Two-Switch Forward DC-DC regulator. The two MOSFET switches are integrated in the LM5015, and the regulator is implemented without using any discrete power MOSFET. A transformer winding between pins 4 and 5 of T1 is used to produce 10V Vcc for the LM5015, thus blocking the internal LDO regulator during normal operation and improving efficiency. Refer to Figure 6 for the schematic of optional Isolated Two-Switch Flyback DC-DC Regulator.




Figure 2. Schematic of Isolated Two Forward DC-DC Regulator (Factory Default)

4 Board Layout and Probing

The following should be kept in mind when the board is powered:

- The LM5015, and the diodes D3 and D4 will be hot to the touch when operating at high input voltage and/or high load current.
- Use CAUTION when probing the circuit at high input voltages. 72 volts is enough to produce shocks and sparks.
- At maximum load current (3A), the wire size and length used to connect the load become important.
 Ensure there is not a significant voltage drop along the wires.



5 Typical Performance Characteristics

Figure 3 shows the overall efficiency of the evaluation board in the Two-Switch Forward configuration.





Figure 3. Evaluation Board Efficiency vs Input Voltage vs Load

Figure 4 shows key voltage waveforms at switch nodes HO and LO under full load (2.5A) and mid input voltage (48V).




Horizontal Resolution: 0.5 µs/div Trace 1: The HO pin voltage. 20V/div Trace 2: The LO pin voltage. 20V/div

Operating condition: Vin = 48V, Vout = 5V, lout = 2.5A

Figure 4. Key Voltage Waveforms at the HO and LO Pins



Figure 5 shows the input ripple current and output ripple voltage full load (2.5A) and mid input voltage (48V).



Horizontal Resolution: 2 µs/div

Trace 1: The output voltage ripples (ac coupled). 50 mV/div Trace 2: The input current ripples (ac coupled). 100 mA/div Operating condition: Vin = 48V, Vout = 5V, lout = 2.5A

Figure 5. Input Ripple Current and Output Ripple Voltage

6 Schematic of Isolated Two-Switch Flyback DC-DC Regulator

Figure 6 shows the schematic to reconfigure the evaluation board as an Isolated Two-Switch Flyback DC-DC regulator. Refer to the changes in BOM at the end of this article. Note that the use of dual-diode D3 herein is owing to the D3 footprint on the PC board. Only the high side of the dual-diode D3 is used in Flyback configuration, and the low side diode is always reverse biased during normal operation.





Figure 6. Schematic of Isolated Two-Switch Flyback DC-DC Regulator Configuration




Evaluation Board PCB www.ti.com

7 Evaluation Board PCB



SILKSCREEN (PLACE) LAYER AS VIEWED FROM TOP

Figure 7. Sikscreen




TOP (COMPONENT) LAYER AS VIEWED FROM TOP

Figure 8. Top Layer



www.ti.com Bill of Materials (BOM)



BOTTOM (SOLDER) LAYER AS VIEWED FROM TOP

Figure 9. Bottom Layer

8 Bill of Materials (BOM)

Table 1. Isolated Two-Switch Forward DC-DC Regulator (Factory Default)

Item	Part Number	Description	Value
PCB	551012884-003 REV C	LM5015 Two-Switch Forward ISOLATED	
C1	NU	DO NOT INSTALL	
C2	HMK325BJ225KN-T	CAPACITOR, CER, CC1210, TAIYO YUDEN	2.2 μF, 100V
C3	HMK325BJ225KN-T	CAPACITOR, CER, CC1210, TAIYO YUDEN	2.2 μF, 100V
C4	C3216X7R2A104K	CAPACITOR, CER, CC1206, TDK	0.1 μF, 100V
C5	C1608X7R1H103K	CAPACITOR, CER, CC0603, TDK	0.01 μF, 50V
C6	C0603C151J5GACTU	CAPACITOR, CER, CC0603, KEMET	150 pF, 50V
C7	C0603C104K5RACTU	CAPACITOR, CER, CC0603, KEMET	0.1 μF, 50V
C8	ECJ-1VB1E105K	CAPACITOR, CER, CC0603, PANASONIC-ECG	1μF, 25V
C9	GRM188R71E224KA88D	CAPACITOR, CER, CC0603, MURATA	0.22 μF, 25V
C10	APXA6R3ARA151MH70G	CAPACITOR, AL ELEC, NIPPON CHEMI-CON	150 μF, 6.3V
C11	LMK212BJ106KD-T	CAPACITOR, CER, CC0805, TAIYO YUDEN	10 μF, 10V
C12	LMK212BJ106KD-T	CAPACITOR, CER, CC0805, TAIYO YUDEN	10 μF, 10V
C13	NU	DO NOT INSTALL	
C14	C0805C103K5RAC	CAPACITOR, CER, CC0805, KEMET	0.01 μF, 50V
C15	C0805C333K5RAC	CAPACITOR, CER, CC0805, KEMET	0.033 μF, 50V
C16	C4532X7R3D222K	CAPACITOR, CER, CC1812, TDK	2.2 nF, 2 kV
D1	CMHD4448	DIODE, SOD-123, CENTRAL	75V, 250 mA
D2	CMHD4448	DIODE, SOD-123, CENTRAL	75V, 250 mA
D3	CMPD2838E	DIODE, DUAL, SOT-23, CENTRAL	75V, 200 mA
D4	CMSH2-40	DIODE, SCHOTTKY, SMB, CENTRAL	40V, 2A



Bill of Materials (BOM) www.ti.com

Table 1. Isolated Two-Switch Forward DC-DC Regulator (Factory Default) (continued)

Item	Part Number	Description	Value
D5	CMSH2-40	DIODE, SCHOTTKY, SMB, CENTRAL	40V, 2A
L1	LPS4012-185MLB	INDUCTOR, COILCRAFT	1.8 µH,
L2	SRU1048-100Y	INDUCTOR, BOURNS	10 μH, 3.7A
R1	CRCW120610R0J	RESISTOR, 1206	10 Ω
R2	CRCW06032002F	RESISTOR, 0603	20k
R3	CRCW120610R0J	RESISTOR, 1206	10 Ω
R4	CRCW08052432F	RESISTOR, 0805	24.3k
R5	CRCW08058061F	RESISTOR, 0805	8.06K
R6	NU	DO NOT INSTALL	
R7	NU	DO NOT INSTALL	
R8	CRCW08055900F	RESISTOR, 0805	590 Ω
R9	CRCW08052743F	RESISTOR, 0805	274k
R10	CRCW06031002F	RESISTOR, 0603	10k
T1-A	CA2983-CL	FORWARD TRANSFORMER, COILCRAFT	OPTION 1
T1-B	PA2194NL	FORWARD TRANSFORMER, PULSE	OPTION 2
U1	LM5015	2-SW FWD REG, TSSOP-14EP, Texas Instruments	
U2	PS2811-1-M	OPTO-COUPLER, NEC	
U3	LMV431	REFERENCE, SOT23-3, Texas Instruments	

Table 2. Bill of Materials (BOM) Changes to Configure the Evaluation Board as an Isolated Two-Switch Flyback DC-DC Regulator With 5V 2.5A Output

Item	Part Number	Description	Value
D4	CMDH3-40L	DIODE, SCHOTTKY, SMC, CENTRAL	40V, 3A
D5	NU	DO NOT INSTALL	
L1	CRCW120624R9J	RESISTOR, 1206	24.9 Ω
L2	SHORT	AWG 24 BUS WIRE	0 Ω
T1-A	GA3372-AL	FLBACK TRANSFORMER, COILCRAFT	OPTION 1
T1-B	PA2367NL	FLYBACK TRANSFORMER, PULSE	OPTION 2

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products Applications

Audio www.ti.com/audio Automotive and Transportation www.ti.com/automotive Communications and Telecom **Amplifiers** amplifier.ti.com www.ti.com/communications **Data Converters** dataconverter.ti.com Computers and Peripherals www.ti.com/computers **DLP® Products** www.dlp.com Consumer Electronics www.ti.com/consumer-apps

DSP **Energy and Lighting** dsp.ti.com www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical logic.ti.com Logic Security www.ti.com/security

Power Mgmt power.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Microcontrollers <u>microcontroller.ti.com</u> Video and Imaging <u>www.ti.com/video</u>

RFID www.ti-rfid.com

OMAP Applications Processors www.ti.com/omap TI E2E Community e2e.ti.com

Wireless Connectivity <u>www.ti.com/wirelessconnectivity</u>