TI Designs: TIDA-01470

PCM1864 Based Linear Microphone Board Reference Design



Description

The PCM1864 Linear Microphone Board (LMB) is a low-cost, easy-to-use reference design for applications that require clear spoken audio, such as voice triggering and speech recognition. This TID uses microphone array to capture voice signal and converts it to digital stream that can be used by DSP system to extract clear audio from noisy environments.

Resources

TIDA-01470 Design Folder
PCM1864 Product Folder
TIDEP-0077 Product Folder
TIDEP-0088 Product Folder




ASK Our E2E Experts

Features


- Uses PCM1864 (4-ch Audio ADC) to Interface With Four Microphone Arrays to Extract Clear Speaker Voice From Noisy Environments
- Energy-Sense Notification for Signal Presence and Loss—Can Be Central Part of Low-Power, High-Performance Audio Solution
- Offers Complete System Reference Design Using Microphone Array, Texas Instruments[™] Provided Software, and Evaluation Module

Applications

- Interface-to-Cloud-Based Voice Recognition for Voice-Activated Digital Assistant Applications
- Interface-to-Cloud-Based Voice Recognition for Smart Home Applications
- Local (Limited Dictionary) Voice Recognition for Voice-Based Appliances Control
- Voice and Speech Applications (Such as Video Conferencing)



Copyright © 2017, Texas Instruments Incorporated





An IMPORTANT NOTICE at the end of this TI reference design addresses authorized use, intellectual property matters and other important disclaimers and information.



System Description www.ti.com

1 System Description


This TI Design uses TI hardware and sophisticated field-proven software algorithms to obtain clear speech and audio from noisy environments. This Linear Microphone Board provides the streaming of multiple data inputs to the processor, which implements a beamforming algorithm to form a virtual directional microphone that points at the direction of the speaker or the desired audio source and then amplifies the speech signal from the desired direction, which attenuates all signals from all other directions.

The PCM1864 device is a highly flexible audio front end that supports input levels from small-mV microphone inputs to 2.1-VRMS line inputs without external resistor dividers. Without requiring a 5-V supply or an external programmable-gain amplifier, smaller, smarter products are feasible at reduced cost.

2 System Overview

2.1 Block Diagram

Figure 1 shows the TIDA01454 block diagram.



Copyright © 2017, Texas Instruments Incorporated

Figure 1. TIDA-01470 Block Diagram

2.2 Highlighted Products

2.2.1 PCM1864

The PCM1864 device is a highly integrated, high performance audio analog-to-digital converter (ADC) with four mono ADC channels and 103-dB SNR. It is a software controlled device with integrated PLL that provides audio master clocks for the entire system. PCM186x supports EnergySense, which allows easy-to-implement power-down and wake-up scenarios to meet the European Ecodesign Directive.

See the PCM1864 product folder for a full description of this device.



3 Getting Started Hardware and Software

3.1 Hardware and Software Setup

3.1.1 Linear Microphone Board as Standalone Unit

See Table 1, Table 2, Table 3, and Table 4 to configure and test the Linear Microphone Board to interface as a standalone unit.

Table 1. Linear Microphone Board Power Connection

| LMB | C5517 | Description |
|-----------|----------|-------------|
| DPS_Pin16 | J10_Pin9 | LMB_3.3V |
| DSP_Pin17 | J10_Pin5 | GND |

Table 2. Linear Microphone Board Jumper Settings

| Pin | Parameter | Description |
|-----|-----------|-------------|
| J2 | ON | Master mode |
| J6 | ON | MIC BIAS |

Table 3. Linear Microphone Board Interface With C5517 EVM (Mic 1 and 2)

| СМВ | C5518 EVM | Description |
|------------------|------------------------|-----------------|
| DPS_Pin15 (SCL) | J14_Pin16 | LMB_I2C-SCL |
| DPS_Pin18 (SDA) | J14_Pin20 | LMB_I2C-SDA |
| DSP_Pin4 (BCLK) | J27_Pin3 (no jumper) | LMB bit clock |
| DSP_Pin6 (LRCK) | J27_Pin4 (no jumper) | LMB frame clock |
| DSP_Pin8 (DATA1) | J30_Pin2 (no jumper) | LMB Data1 |
| _ | J29_Pin1-3 (jumper on) | _ |
| _ | J29_Pin2-4 (jumper on) | _ |
| _ | J30_Pin1-3 (jumper on) | _ |

Table 4. Linear Microphone Board Interface With C5517 EM (Mic 3 and 4)

| СМВ | C5517 EVM | Description |
|-------------------|---------------------|-------------|
| IS2_Pin3 (BCLK) | J31_Pin3 | Bit clock |
| IS2_Pin5 (LRCK) | J31_Pin2 | Frame clock |
| DSP_Pin12 (DATA3) | J31_Pin1 | LMB Data3 |
| _ | UART_EN (no jumper) | _ |



After the hardware setup is complete, each PCM1864 device must be configured as listed in the following code snippet to set up the operation mode, sampling frequency, PLL clock reference, and more by using the I²C interface.

Device U1 can be configured by using device address 0x94 to run in master mode with the following register writes.

```
0x94 0x00 0x00 // Change to Page 0
0x94 0x01 0x40 // PGA CH1_L to 32dB
0x94 0x02 0x40 // PGA CH1_R to 32dB
0x94 0x03 0x40 // PGA CH2_L to 32dB
0x94 0x04 0x40 // PGA CH2_R to 32dB
0x94 0x05 0x86 // Enable SMOOTH PGA Change; Independent Link PGA;
0x94 0x06 0x41 // Polarity: Normal, Channel: VINL1[SE]
0x94 0x07 0x41 // Polarity: Normal, Channel: VINR1[SE]
0x94 0x08 0x44 // Polarity: Normal, Channel: VINL3[SE]
0x94 0x09 0x44 // Polarity: Normal, Channel: VINR3[SE]
0x94 0x0A 0x00 // Secondary ADC Input: No Selection
0x94 0x0B 0x0C // TX WLEN: 16 bit; FMT: I2S format
0x94 0x10 0x03 // GPIO0_FUNC - SCK Out; GPIO0_POL - Normal
0x94 0x11 0x50 // GPIO3_FUNC - DOUT2; GPIO3_POL - Normal
0x94 0x12 0x04 // GPIOO_DIR - GPIOO - Output
0x94 0x13 0x40 // GPIO3_DIR - GPIO3 - Output
0x94 0x20 0x3E // MST_MODE: Master; CLKDET_EN: Disable
0x94 0x21 0x02 // XTAL to DSP1 Divide value = 1/3
0x94 0x22 0x05 // XTAL to DSP2 Divide value = 1/6
0x94 0x23 0x0B // XTAL to ADC Divide value = 1/12
0x94 0x25 0x17 // PLL to SCK Divide value = 1/24
0x94 0x26 0x03 // PLL to BCK Divide value = 1/4
0x94 \ 0x29 \ 0x03 \ // \ P \ Divide value = 1/4
0x94 0x2A 0x00 // R Divide value = 1
0x94 0x2B 0x10 // J Divide value = 16
0x94 0x28 0x01 // PLL_REF_CLK = SCK; PLL_EN=Enable
0x94 0x29 0x03 // PLL to BCK Divide value = 1/4
0x94 0x29 0x03 // PLL to BCK Divide value = 1/4
0x94 0x29 0x03 // PLL to BCK Divide value = 1/4
0x94 0x29 0x03 // PLL to BCK Divide value = 1/4
0x94 0x2A 0x00 // R Divide value = 1
```

3.1.2 Linear Microphone Board With TMDSEVM5517 Evaluation Module

To configure and test the Linear Microphone Board by interfacing with the 66AK2Gx or C5517 EVM, see *Audio Pre-Processing Reference Design for Voice-Based Applications* and *K2G-Based Voice Recognition Audio System Design Guide*.



www.ti.com Testing and Results

4 Testing and Results

Testing the Linear Microphone Board to validate the device configuration and proper microphone bias can be achieved by:

- Ensuring the BIASA LED is ON once the devices are configured
- Evaluating the digital data stream from thePCM1864 device

Figure 2 shows the FFT plot for the DOUT data streaming using the an AP2722 device when playing a 1-kHz monotone.




Figure 2. FFT Plot



Testing and Results www.ti.com

Figure 3 shows the LRCK and I²S data stream on DOUT1 and DOUT2 on the PCM1864 device in time domain.




Figure 3. I²S Plot



www.ti.com Design Files

5 Design Files

5.1 Schematics

To download the schematics, see the design files at TIDA-01470.

5.2 Bill of Materials

To download the bill of materials (BOM), see the design files at TIDA-01470.

5.3 PCB Layout Recommendations

5.3.1 Layout Prints

To download the layer plots, see the design files at TIDA-01470.

5.4 Altium Project

To download the Altium project files, see the design files at TIDA-01470.

5.5 Gerber Files

To download the Gerber files, see the design files at TIDA-01470.

5.6 Assembly Drawings

To download the assembly drawings, see the design files at TIDA-01470.

6 Software Files

To download the software files, see the design files at TIDA-01470.

7 Trademarks

Texas Instruments is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated