

# CLC001,CLC012,DS92LV1021A,DS92LV1212A

*Hundreds of Megabits @ Hundreds of Meters: Extending the Transmission  
Length for LVDS*



Literature Number: SNLA204

# Technology Edge

## Hundreds of Megabits @ Hundreds of Meters: Extending the Transmission Length for LVDS

Davor Glisic, Applications Engineer

Low-Voltage Differential Signaling (LVDS) is becoming the preferred differential interface standard as it delivers high data rates while consuming significantly less power than competing technologies. LVDS technology allows products to address applications with data rates of hundreds of Mbps in many market segments wherever the need for robust transmission of signals at high speed and low power exists.

The ability to integrate this technology into system-level ICs such as SerDes (Serializer/Deserializer) products means that LVDS interface technology is used for applications in every design that transfers data from chip-to-chip, card-to-card, shelf-to-shelf, rack-to-rack, or box-to-box. The typical transmission distances range from several inches (chip-to-chip) to several meters for an LVDS SerDes serial link driving a cable between racks. However, many systems now require the ability to extend this transmission distance to support cable lengths greater than 100 meters. This extended cable length offers some unique design challenges to the system design engineer. This design idea shows how the range of LVDS can be extended to meet these criteria by utilizing a high-speed serial digital interface (SDI) adaptive cable equalizer and cable driver products.

### System-to-System Transmission

Serial cabling systems often use coaxial or twisted pair cables. All cable types provide significant attenuation of a signal which depends on both data rate (frequency) and the cable length.

Low-voltage differential signals are not exempt from cable attenuation and, as a result, can only travel limited distance.

Systems employing LVDS devices without any signal conditioning features can typically achieve transmission distances of several meters. Those employing LVDS ICs with driver pre-emphasis and receiver equalization can reach 15- to 20-meter distances. Systems that use LVDS interface devices but are required to transmit data across long distances (from several tens of meters to even hundreds of meters) must employ devices specifically designed to drive long transmission lines to work in conjunction with the LVDS devices. Figure 1 is an example of a communication channel in such a system.




Figure 1: Example of a communication channel employing LVDS 10-bit SerDes and SDI cable driver/equalizer combo to transmit data over coaxial cable

This channel consists of National's 10-bit SerDes (DS92LV1021A and DS92LV1212A) pair and SDI cable driver / equalizer combo (CLC001 and CLC012). The SerDes pair reduces system cost by reducing connector and cable size, and brings LVDS benefits such as exceptional noise immunity, low power, minimal EMI, relaxed decoupling requirements, and simple termination scheme.

The SDI cable driver / receiver combo works to overcome signal attenuation caused by long cables. The key device for the task is the CLC012 which is a high-value solution for equalizing data transmitted over cable. The equalizer automatically

compensates for losses of any length of cable from zero meters to lengths that attenuate the signal by 40 dB at 200 MHz. This corresponds to 300 meters of high quality coax cable (such as Belden 8281) or 120 meters of Category 5 UTP (unshielded twisted pair). The equalizer reconstructs serial digital data received from the transmission line (cable) by attempting to match the inverse of the cable loss characteristic and adapting to cable length.

Figure 2 is a block diagram of a communication channel that employs LVDS 10-bit SerDes and SDI cable driver / equalizer combo to move data across twisted pair (TP) cables. The only difference between this channel and the channel in Figure 1 (besides different cable) is in resistor values of R1 through R6. These resistors were experimentally determined; they adjust signals for optimal equalization.




Figure 2: Example of a communication channel employing LVDS 10-bit SerDes and SDI cable driver/equalizer combo to transmit data over twisted pair cable

### Experimental Results

Both circuits illustrated in Figures 1 and 2 were constructed using evaluation kits of the respective devices and tested using a bit-error rate tester. Both circuits exhibited operation without errors. The input was a 10-bit wide pseudo random bit stream (PRBS-15) latched in by a 40 MHz clock ( $DS92LV1021A T_{CLK}$ ). The equivalent data rate transmitted through the cables was 480 Mbps.

Note that the circuits utilize AC coupling capacitors to isolate CLC012 PECL output levels from the DS92LV1212A receiver which expects LVDS levels. The configuration works well for the DC-balanced data. However, DC-unbalanced data would require DC coupling between the CLC012 and an LVDS receiver. A PECL-to-LVDS interface needs an attenuation resistor network. The attenuation network slows down signal edges significantly and reduces maximum data rate.

### Optimization Tips

The following list provides optimization tips for a channel that employs LVDS SerDes and SDI devices to transmit data over long distances.

1. Provide proper load for the CLC001 while matching the impedance of the cable.
2. Use CLC001  $R_{REF}$  and R1 through R6 resistors to adjust signals traveling through the cable for optimal cable equalization and proper cable termination.
3. Provide proper load for the CLC012 while matching impedance of the interconnect to the LVDS receiver.
4. Follow best PCB layout practices – see respective device datasheets for detailed information.
5. Use cables with individually shielded conductor pairs for minimal cross-talk.
6. Use controlled impedance connectors rated for gigabit operation.

### Conclusion

The two example circuits illustrate how system designers can benefit from LVDS SerDes devices even when their systems require transmission distances ranging from a few tens of meters to two hundreds or more meters. The circuits were constructed using evaluation kits of the respective devices and tested with coaxial and twisted pair cables and have demonstrated error-free operation.

For more information visit the [LVDS](#), and [Serial Digital Interface](#) Featured communities.

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
OMAP Mobile Processors	<a href="http://www.ti.com/omap">www.ti.com/omap</a>
Wireless Connectivity	<a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a>

### Applications

Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Transportation and Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2011, Texas Instruments Incorporated