


A


DESIGN CROSS SECTION CHART
TOTAL THICKNESS 1.6 MM



* SURFACE - AIR 0 MM
L1 TOP CONDUCTOR - COPPER 0.035 MM
* DIELECTRIC - FR-4 0.175 MM
L2 CONDUCTOR - COPPER 0.035 MM
* DIELECTRIC - FR-4 1.11 MM
L3 CONDUCTOR - COPPER 0.035 MM
* DIELECTRIC - FR-4 0.175 MM
L4 BOTTOM CONDUCTOR - COPPER 0.035 MM
* SURFACE - AIR 0 MM

B

C



DRILL CHART: TOP to BOTTOM				
ALL UNITS ARE IN MILLIMETERS				
FIGURE	FINISHED_SIZE	DRILLED_SIZE	PLATED	QTY
•	0.2	-	PLATED	437
▪	0.7	-	PLATED	4
••	1.05	-	PLATED	3
■	1.25	-	PLATED	4

D

	TEXAS INSTRUMENTS	
	DRILL	CC2745R10-CS-EVM Rev. A
	DATE: 2026-02-26	

Texas Instruments (TI) and/or its licensors do not warrant the accuracy or completeness of this specification or any information contained therein. TI and/or its licensors do not warrant this design will meet the specifications, will be suitable for your application or fit for any particular purpose, or will operate in an implementation. TI and/or its licensors do not warrant that the design is production worthy. You should completely validate and test your design implementation to confirm the system functionality for your application.

A

B

C

D

DESIGN INFORMATION		
MIN. TRACK WIDTH:	0.15 mm	
MIN. CLEARANCE:	0.15 mm	
MIN. VIA PAD SIZE:	0.40 mm	
MINIMUM ANNULAR RING 0.05mm (2MIL) EXTERNAL PER IPC-D-275 CLASS 2 LEVEL C REGISTRATION TOLERANCES: METAL +/-150 um, HOLES +/-80 um HOLE SIZE TOLERANCE (UNLESS OTHERWISE SPECIFIED): +/-80 um		
MATERIAL:		
☐ FR-4	☒ FR-4 High Tg	☐ OTHER _____
THICKNESS:	☒ 1.6mm +/-10%	☐ OTHER _____
TOLERANCE:	☒ ANSI IPC-6012 TYPE 3 CLASS 2	☐ OTHER +/- _____
BOW & TWIST:	☒ ANSI IPC-6012 TYPE 3 CLASS 2	☐ OTHER +/- _____
DRILLING:		
REFERENCE:	☐ AS SHOWN	☒ NC_DRILL FILES
PTH COPPER THICKNESS:	☒ 20-30 um	☐ OTHER _____
BOARD FINISH:		
SILKSCREEN:	☒ TOP	☒ BOTTOM
SILKSCREEN COLOR:	☒ WHITE	☐ OTHER _____
SILKSCREEN RESIST COLOR:	☐ GREEN	☒ OTHER RED
	☒ MATTE	☐ SEMI-GLOSS
SURFACE FINISH:	☒ IMMERSION GOLD (ENIG)	☐ ENEPIG
☐ IMM. TIN/SILVER OR EQUIV	☐ OTHER _____	
ARRAY/PANEL:	☐ CUT AND TRIM PER M1 BOARD OUTLINE	☐ N.C. ROUTE
	☒ V. SCORE	
CERTIFICATION:	MATERIALS AND WORKMANSHIP FOR ALL PCBs TO MEET OR EXCEED THE REQUIREMENTS OF:	
	☒ ANSI IPC-A-600F CLASS	-> ☐ 1 ☒ 2 ☐ 3
	☒ RoHS	☐ OTHER PER ORDER
ALL BOARDS MUST MEET OR EXCEED UL94-V0 REQUIREMENTS.		
PCB MUST BEAR THE UL94V-0 UL REG. MATERIAL ID NUMBER: BOTTOM LAYER		
ADDITIONAL REQUIREMENTS:		
MICROSECTION: ☐ YES		
BARE BOARD ELEC. TEST: ☒ NONE ☐ REQUIRED ☐ PER ORDER		
☐ XX MIL VIAS REQUIRE NON-CONDUCTIVE FILL AND PLANARIZE		
☐ XX MIL VIAS REQUIRE CONDUCTIVE FILL AND PLANARIZE		
☐ OUTER XX MIL VIAS REQUIRE 50 OHM SINGLE-ENDED IMPEDANCE		
☐ LAYER 2 & 3 (INNER LAYERS) XX MIL WIDE, XX MIL SPACE		
☐ TRACES REQUIRE 100 OHM DIFFERENTIAL IMPEDANCE		
TITLE: CC2745R10-CS-EVM		
PROJECT NUMBER: MCU204		
FILE NAME: cc2745r10-cs-evm.brd		
DESIGNER: HG	DATE: 2026-02-28	REVISION: A
SCALE: 1.00		ALLEGRO DESIGNER VERSION: 24.1