



Functional Safety FIT Rate, Failure Mode Distribution TPS7B67xx-Q1

450-mA High-Voltage Ultra-Low IQ Low-Dropout Regulator

Functional Block Diagrams



Failure Rate Mission Profile (1)	Per 10 ⁹ Hours (FIT)
Total FIT Rate	20
Die FIT Rate	7
Package FIT Rate	13

Failure Modes	Failure Mode Distribution (%)
V _{OUT} high (following V _{IN})	15%
V _{OUT} not in specification – voltage or timing	60%
V _{OUT} low (no output)	15%
RESET false trigger, fails to trigger	5%
Short circuit any two pins	5%

(1) Failure Rate, Mission Profile and Failure Mode Distribution

The failure rate and mission profile information comes from the Reliability data handbook IEC TR 62380 using the reliability modeling for Integrated circuits.

Mission Profile Automotive Control IEC TR 62380

Power dissipation 800mW

Climate type: World-wide Table 8 IEC TR 62380

Package factor lambda 3 Table 17b IEC TR 62380

Substrate Material: FR4

EOS FIT rate assumed = 0

The failure mode distribution estimation comes from the combination of common failure modes listed in standards such as IEC 61508 and ISO 26262, the ratio of sub-circuit function size and complexity and from best engineering judgment. The failure rates listed reflect random failure events and do not include failures due to misuse or over stress.

TPS7B67xx-Q1 are catalog product and not compliant to ISO-26262 standards.