



DESIGN CROSS SECTION CHART
TOTAL THICKNESS 1.6 MM (+0.16/-0.16)

TOTAL PREPREG 0.18 MM (+0.03/-0.01)

TOTAL PREPREG 0.18 MM (+0.03/-0.01)

FR-4: Er = 4.3 (+/- 0.3)



DRILL CHART: TOP to BOTTOM					
ALL UNITS ARE IN MILLIMETERS					
FIGURE	FINISHED_SIZE	DRILLED_SIZE	ROTATION	PLATED	QTY
•	0.2	-	-	PLATED	933
⊕	1.05	-	-	PLATED	6
⊗	1.05	-	-	PLATED	64
◬	3.2	-	-	PLATED	4
▯	1.4x0.6	-	90.000	PLATED	2
▯	1.5x0.6	-	90.000	PLATED	2

	TEXAS INSTRUMENTS
DRILL	BP-CC140xP-9-SKY Rev. E2
	DATE: 2026-09-23

DESIGN INFORMATION

MIN. TRACK WIDTH: 0.15 mm
MIN. CLEARANCE: 0.15 mm
MIN. VIA PAD SIZE: 0.40 mm

MINIMUM ANNULAR RING 0.05mm (2MIL) EXTERNAL
PER IPC-D-275 CLASS 2 LEVEL C
REGISTRATION TOLERANCES: METAL +/-150 um, HOLES +/-80 um
HOLE SIZE TOLERANCE (UNLESS OTHERWISE SPECIFIED): +/-80 um

MATERIAL:
[X] FR-4 [ ] FR-4 High Tg [ ] OTHER _____
THICKNESS: [X] 1.6mm +/-10% [ ] OTHER _____
TOLERANCE: [X] ANSI IPC-6012 TYPE 3 CLASS 2
[ ] OTHER +/- _____
BOW & TWIST: [X] ANSI IPC-6012 TYPE 3 CLASS 2
[ ] OTHER +/- _____

DRILLING:
REFERENCE: [ ] AS SHOWN [X] NC_DRILL FILES
PTH COPPER THICKNESS: [X] 20-30 um [ ] OTHER _____

BOARD FINISH:
SILKSCREEN: [X] TOP [X] BOTTOM
SILKSCREEN COLOR: [X] WHITE [ ] OTHER _____
SILKSCREEN RESIST COLOR: [ ] GREEN [X] OTHER RED
[ ] MATTE [ ] SEMI-GLOSS

SURFACE FINISH: [X] IMMERSION GOLD (ENIG) [ ] ENEPIG
[ ] IMM. TIN/SILVER OR EQUIV [ ] OTHER _____

ARRAY/PANEL: [ ] CUT AND TRIM PER M1 BOARD OUTLINE
[ ] N.C. ROUTE [X] V. SCORE

CERTIFICATION: MATERIALS AND WORKMANSHIP FOR ALL PCBS TO MEET OR EXCEED THE REQUIREMENTS OF:
[X] ANSI IPC-A-600F CLASS -> [ ] 1 [X] 2 [ ] 3
[X] RoHS [ ] OTHER PER ORDER

ALL BOARDS MUST MEET OR EXCEED UL94-VO REQUIREMENTS.
PCB MUST BEAR THE UL94V-O UL REG. MATERIAL ID NUMBER: BOTTOM LAYER
ADDITIONAL REQUIREMENTS:
MICROSECTION: [ ] YES
BARE BOARD ELEC. TEST: [X] NONE [ ] REQUIRED [ ] PER ORDER
[ ] XX MIL VIAS REQUIRE NON-CONDUCTIVE FILL AND PLANARIZE
[ ] XX MIL VIAS REQUIRE CONDUCTIVE FILL AND PLANARIZE
[ ] OUTER XX MIL VIAS REQUIRE 50 OHM SINGLE-ENDED IMPEDANCE
[ ] LAYER 2 & 3 (INNER LAYERS) XX MIL WIDE, XX MIL SPACE TRACES REQUIRE 100 OHM DIFFERENTIAL IMPEDANCE

TEXAS INSTRUMENTS

TITLE: BP-CC140xP-9-SKY

PROJECT NUMBER:

FILE NAME: BP-CC140xP-9-SKY.brd

DESIGNER:	DATE:	REVISION:
RGW	2026-09-23	E2
SCALE: 1.00	ALLEGRO DESIGNER VERSION: 24.1	

Texas Instruments (TI) and/or its licensors do not warrant the accuracy or completeness of this specification or any information contained therein. TI and/or its licensors do not warrant this design will meet the specifications, will be suitable for your application or fit for any particular purpose, or will operate in an implementation. TI and/or its licensors do not warrant that the design is production worthy. You should completely validate and test your design implementation to confirm the system functionality for your application.