


- NOTES: UNLESS OTHERWISE SPECIFIED:
1. MATERIAL: 6061-T6 ALUMINUM
 2. LIGHT BEADBLAST EXTERIOR SURFACES ONLY (MATTE FINISH); MASK INTERNAL FEATURES AND THREADING TO ENSURE TOLERANCES ARE HELD.
 3. FINISH: ANOPLATE ANOBLACK EC PROCESS. ALTERNATE BLACK ANODIZING PROCESSES NOT CONSIDERED AN EQUIVALENT

© COPYRIGHT 2013 TEXAS INSTRUMENTS
UNPUBLISHED, ALL RIGHTS RESERVED

REVISIONS			
REV	DESCRIPTION	DATE	BY
A	ECO #2136196 - INITIAL RELEASE	9/20/13	RDR



SECTION A-A

		UNLESS OTHERWISE SPECIFIED <ul style="list-style-type: none">● DIMENSIONS ARE IN MILLIMETERS● TOLERANCES: ANGLES ±1° 2 PLACE DECIMALS ±0.25 1 PLACE DECIMALS ±0.50● DIMENSIONAL LIMITS APPLY BEFORE PROCESSES● INTERPRET DIMENSIONS IN ACCORDANCE WITH ASME Y14.5M-1994● REMOVE ALL BURRS AND SHARP EDGES● PARENTHETICAL INFO FOR REF ONLY	DWN R ROWE	DATE 9/8/2013	 TEXAS INSTRUMENTS			
			Engr		LAMP FOCUS RING			
			CQE/QA					
			CM					
			Apprvd					
NEXT ASSY		USED ON	SIZE B		DWG NO 2513383	REV A		
APPLICATION			SCALE 5:1			SHEET 1 OF 1		