


NOTES: UNLESS OTHERWISE SPECIFIED:

1. MATERIAL: SOFT ELECTROFORMED NICKEL
2. BI-LEVEL PARTS 127 UM THICK GENERALLY REDUCED TO 25UM THICK AROUND CENTRAL SLIT.
3. SECOND LEVEL EDGES STEPPED BACK FROM FIRST LEVEL SLIT EDGETS BY ~60UM.
4. BLACKEN BOTH SIDES OF PART

© COPYRIGHT 2013 TEXAS INSTRUMENTS
UNPUBLISHED, ALL RIGHTS RESERVED

REVISIONS			
REV	DESCRIPTION	DATE	BY
A	INITIAL RELEASE	3/3/2014	RDR



A

B

C


D

A

B

C

D

		UNLESS OTHERWISE SPECIFIED <ul style="list-style-type: none">● DIMENSIONS ARE IN MILLIMETERS● TOLERANCES: ANGLES ±1° 2 PLACE DECIMALS ±0.25 1 PLACE DECIMALS ±0.50● DIMENSIONAL LIMITS APPLY BEFORE PROCESSES● INTERPRET DIMENSIONS IN ACCORDANCE WITH ASME Y14.5M-1994● REMOVE ALL BURRS AND SHARP EDGES● PARENTHETICAL INFO FOR REF ONLY	DWN	DATE	 TEXAS INSTRUMENTS				
			Engr		SLIT DISK, .010MM				
			CQE/QA						
			CM						
					SIZE	DWG NO			REV
					B	2513431			A
					SCALE 10:1				SHEET 1 OF 1

SW-2010a