




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PMP41037_Power REV: E1	SUN REV: Not in version control
LAYER NAME = Top Overlay	TID #: PMP41037	
PLOT NAME = Top Overlay	GENERATED : 4/18/2023 3:31:43 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PMP41037_Power REV: E1	SUN REV: Not in version control
LAYER NAME = Top Solder	TID #: PMP41037	
PLOT NAME = Top Solder Mask	GENERATED : 4/18/2023 3:31:43 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PMP41037_Power REV: E1	SVN REV: Not in version control
LAYER NAME = Top Layer	TID #: PMP41037	
PLOT NAME = Top Layer	GENERATED : 4/18/2023 3:31:44 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PMP41037_Power REV: E1	SUN REV: Not in version control
LAYER NAME =	TID #: PMP41037	
PLOT NAME = Signal 1	GENERATED : 4/18/2023 3:31:44 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PMP41037_Power REV: E1	SUN REV: Not in version control
LAYER NAME =	TID #: PMP41037	
PLOT NAME = Signal 2	GENERATED : 4/18/2023 3:31:44 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PMP41037_Power REV: E1	SUN REV: Not in version control
LAYER NAME = Bottom Layer	TID #: PMP41037	
PLOT NAME = Bottom Layer	GENERATED : 4/18/2023 3:31:45 PM	TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PMP41037_Power REV: E1	SUN REV: Not in version control
LAYER NAME = Bottom Solder	TID #: PMP41037	
PLOT NAME = Bottom Solder Mask	GENERATED : 4/18/2023 3:31:45 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PMP41037_Power REV: E1	SUN REV: Not in version control
LAYER NAME = Bottom Overlay	TID #: PMP41037	
PLOT NAME = Bottom Overlay	GENERATED : 4/18/2023 3:31:45 PM	TEXAS INSTRUMENTS



Symbol	Quantity	Finished Hole Size	Plated	Hole Type	Drill Layer Pair	Hole Tolerance
D	385	11.81mil (0.300mm)	PTH	Round	Top Layer - Bottom Layer	+3.94mil/-0.00mil
C	116	16.00mil (0.406mm)	PTH	Round	Top Layer - Bottom Layer	
O	54	27.56mil (0.700mm)	PTH	Round	Top Layer - Bottom Layer	
X	2	31.50mil (0.800mm)	PTH	Round	Top Layer - Bottom Layer	
□	12	33.47mil (0.850mm)	PTH	Round	Top Layer - Bottom Layer	
⊕	8	39.37mil (1.000mm)	PTH	Round	Top Layer - Bottom Layer	
B	10	40.16mil (1.020mm)	PTH	Round	Top Layer - Bottom Layer	
◇	4	41.34mil (1.050mm)	PTH	Round	Top Layer - Bottom Layer	
☆	3	43.31mil (1.100mm)	PTH	Round	Top Layer - Bottom Layer	
A	2	55.12mil (1.400mm)	PTH	Round	Top Layer - Bottom Layer	
⊙	2	59.06mil (1.500mm)	PTH	Round	Top Layer - Bottom Layer	
⊗	4	63.00mil (1.600mm)	PTH	Round	Top Layer - Bottom Layer	
⊗	2	98.43mil (2.500mm)	PTH	Round	Top Layer - Bottom Layer	
□	2	254.00mil (6.452mm)	PTH	Round	Top Layer - Bottom Layer	
⊕	2	47.24mil (1.200mm)	PTH	Rectangle	Top Layer - Bottom Layer	
▼	2	62.99mil (1.600mm)	PTH	Rectangle	Top Layer - Bottom Layer	
☆	2	62.99mil (1.600mm)	PTH	Rectangle	Top Layer - Bottom Layer	
⊗	2	62.99mil (1.600mm)	PTH	Rectangle	Top Layer - Bottom Layer	
614 Total						

Slot definitions : Routed Path Length = Calculated from tool start centre position to tool end centre position.
Hole Length = Routed Path Length + Tool Size = Slot length as defined in the PCB layout

ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PMP41037_Power REV: E1	SUN REV: Not in version control
LAYER NAME = Drill Drawing	TID #: PMP41037	
PLOT NAME = Drill Drawing	GENERATED : 4/18/2023 3:31:46 PM	TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PMP41037_Power REV: E1	SUN REV: Not in version control
LAYER NAME = M2 Board Dimensions	TID #: PMP41037	
PLOT NAME = Board Dimensions	GENERATED : 4/18/2023 3:31:47 PM	TEXAS INSTRUMENTS