

NOTES: UNLESS OTHERWISE SPECIFIED:

1. MATERIAL : 5052-H32 ALUMINUM OR ENGINEERING APPROVED EQUIVALENT
2. FINISH: BLACK ANODIZED
3. TOLERANCE APPLIES AFTER FINISH
4. REMOVE ALL BURRS AND SHARP EDGES
5. BAG & TAG WITH PART NUMBER AND REVISION

© COPYRIGHT 2014 TEXAS INSTRUMENTS
UNPUBLISHED, ALL RIGHTS RESERVED

REVISIONS			
REV	DESCRIPTION	DATE	BY
A	INITIAL DRAWING RELEASE	4/26/17	JCC
B	REDESIGNED FLANGE	7/10/17	JCC
C	PUNCH ADDED TO TOP SURFACE	8/23/17	JCC

D

C

B




A

D

C

B

A



UNLESS OTHERWISE SPECIFIED

- DIMENSIONS ARE IN MILLIMETERS
- TOLERANCES: ANGLES $\pm 1^\circ$
2 PLACE DECIMALS ± 0.25
1 PLACE DECIMALS ± 0.50
- DIMENSIONAL LIMITS APPLY BEFORE PROCESSES
- INTERPRET DIMENSIONS IN ACCORDANCE WITH ASME Y14.5M-1994
- REMOVE ALL BURRS AND SHARP EDGES
- PARENTHETICAL INFO FOR REF ONLY

DWN Justin Chambliss	DATE 4/13/2017
Engr Steve Smith	2/20/2017
CQE/QA	
CM	
Apprvd	



P33 EVM COMPONENT HEATSINK

SIZE	DWG NO	REV
B	P33-EVM-CHIP-HEATSINK	C
SCALE 1:1		SHEET 1 OF 2

D

C

B


A

D

C



B

A



Ø3.50 THRU

R3.00
ALL FILETS



R0.650

