


These schematics are provided for reference only. For any designs based on these schematics always contact National Semiconductor Corporation BEFORE initiating PCB manufacturing and ask for your design to be reviewed. Copyright (c) 2004 National Semiconductor Corporation. All Rights Reserved. Unpublished rights reserved under the copyright laws of the United States of America, other countries and international treaties. These schematics are provided without fee. Permission to use, copy, store, modify, disclose, transmit or distribute the schematics is granted, provided that this copyright notice must appear in any copy, modification, disclosure, transmission or distribution of the schematics. National Semiconductor Corporation retains all ownership, copyright, trade secret and proprietary rights in the schematics. THESE SCHEMATICS HAVE BEEN PROVIDED "AS IS", WITHOUT EXPRESS OR IMPLIED WARRANTY INCLUDING, WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR USE AND NON-INFRINGEMENT.

Note: For Reference Only



Revision Updated:

- Rev A - Initial draft.
- Rev B
 - Change of LEDs.
 - Pin 28 to LED_LINK
 - Pin 27 to LED_SPEED
 - Pin 26 to LED_ACT/COL
- Rev C
 - Connect jack's LEDs to SPEED and ACT
- Rev D
 - Change DP83848 pinouts to reflect July 04 datasheet.
 - Default is MII mode
 - Use Pulse H1102 as reference magnetic
 - Default is PHYAD = 1
 - AN_EN, AN0, AN1 have internal pull-ups
 - Default is Auto-MDIX enable
- Rev E
 - Changed RBIAS resistor to 4.87K (1%)
 - Added 2.2K pull-ups to reserved pins (20, 21)
 - Changed resistor value for pull-ups/pull-downs to 2.2K
 - Added 33 ohm in series with MII signal lines
 - Updated pinouts to reflect March 05 datasheet

Title			Motorola MCF5282/NSC DP83848 App. Note
Size	Document Number	Rev	E
C	CID Working Draft		
Date:	Thursday, March 31, 2005	Sheet	2 of 2