


Notes:

- 1) Refer to BOM for stuffing options.
- 2) Observe polarity on diodes and capacitors.

REVISIONS				
REV.	REV.	DESCRIPTION	DATE	APPROVED



APPLICATION Secondary CONTRACT NO.

Secondary Side		APPLICATION	CONTRACT NO.	DWN: www.WSTSCORP.com	7/14	TEXAS INSTRUMENTS				
USED ON		NEXT ASSY.		CHK:						
				P.E.:		TITLE: ASSEMBLY DRAWING, C2000 BI-DIRECTIONAL DC-DC				
		UNLESS OTHERWISE SPECIFIED		DES.ENG.:						
		1. TOLERANCES:		P.C.:						
		LINEAR = : 0.26 (.010)		Q.C.:						
		ANGULAR = : 0.50 °		C.M.:						
		2. ALL DIMENSIONS ARE IN MM (INCHES).		REL:						
MATERIAL: SEE NOTE FINISH: SEE NOTE		3. INTERPRET DRAWING IN ACCORDANCE WITH DOD-STD-100.		MFG:		SIZE	CAGE CODE NO.	DRAWING NO.	REV:	
				ENG.MGR:		C		BI-DIR DC-DC	D	
				OTHER:						
DO NOT SCALE DRAWING				OTHER:		SCALE: 1:1		SHEET 2 OF 2		