Filename: BOM-TPS92314 Dimmable\_RevA(230VAC).xls

Variant: 230VAC

Generated: 20/11/2012 16:54:22

SVN path: \$URL::

SVN rev: \$Rev:: \$

## **TPS92314-DIM**

D	0	Description	Manuelantuman	Downthia and
Designator		Description	Manufacturer	PartNumber
C1	1	CAP FILM 0.15uF 630VDC RADIAL	Panasonic	ECW-F6104JL
C2	1	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	MuRata	GCM188R71H104KA57B
C3	1	CAP, Film, 0.033uF, 630V, +/-10%, TH	EPCOS Inc	B32921C3333K
C4	1	CAP, Film, 0.033uF, 630VDC, 20%, Radial	Vishay BC Components	
C5, C7	2	CAP, CERM, 10uF, 50V, +/-10%, X7R, 1210	America	GRM32ER71H106KA12L
C6	1	CAP ALUM 680UF 35V 20% RADIAL	Panasonic Electronic Components	EEU-FM1V681
C8	1	CAP, CERM, 2200pF, 250VAC, X1Y1, TH	Murata Electronics North America	DE1E3KX222MA4BL01
C9	1	CAP, CERM, 4.7uF, 16V, +/-10%, X7R, 0805	MuRata	GRM21BR71C475KA73L
CN1, CN2	2	Conn Term Block, 2POS, 5.08mm PCB	Phoenix Contact	1715721
D1, D3, D6	3	Diode, Ultrafast, 600V, 1A, SMA, Diode, Ultrafast, 400V, 1A, SMA, Diode, Ultrafast, 600V, 1A, SMA	Diodes Inc	US1J-13-F
D2	1	Diode, Switching-Bridge, 600V, 0.5A, MiniDip	Diodes Inc	RH06-T
D4	1	Diode, TVS, 250V, 400W, SMA	Littelfuse Inc	SMAJ250A
D5	1	Diode, Scottky 3A 100V SMB	STMicroelectronics	STPS2H100AY
D7	1	Diode, Zener, 36V, 500mW, SOD-123	Vishay-Semiconductor	MMSZ4715-V
D8	1	Diode 150V, 0.2A, 50nS, SOD-123	Diodes Inc	BAV20W-7-F
D9	1	Zener Diodes Diode Zener Single 4.7V 1% 250mW	NXP	BZX84-A4V7,215
D10	1	Diode, Schottky, 30V, 0.2A, SOD-323	ON Semiconductor	BAT54HT1G
D11	1	Diode, Ultrafast, 100V, 0.15A, SOD-123	Diodes Inc.	1N4148W-7-F
D12	1	Diode, Zener, 3V, 200mW, SOD-323	Diodes Inc.	MMSZ5225BS-7-F
D13	1	Diode, Ultrafast, 75V, 0.25A, SOD-323	Central Semiconductor	CMDD4448TR
F1	1	Fuse Slow 250VAC 500mA AXIAL	Littelfuse Inc	0875.500MXEP
J1, J2, J3, J4	4	Jumper Wire, 300mil spacing, Orange, pkg of 200	3M	923345-03-C
L1	1	Inductor, Drum Ferrite 3.3mH 0.15A, 11ohm, TH1	Sumida	RCH895NP-332K
L2	1	Inductor, Drum Ferrite 1.5mH 0.21A, 3ohm, TH1	Sumida	RCH895NP-152K
LED+1, LED-1, TP1, TP3	4	Terminal, Turret, TH, Double	Keystone	1502-2
Q1	1	STMICROELECTRONICS - STD1NK60-1 - MOSFET, N CH, 600V, 1A, IPAK	STMicroelectronics	STD1NK60-1
Q2	1	MOSFET N-CH, 2.5A, 800V, 4.5ohm, 19nC	STMicroelectronics	STD3NK80Z-1
R1, R7	2	NA	NA	NA
R2	1	RES, 220 ohm, 1%, 0.25W, 1206	Yageo America	RC1206FR-07220RL
R3	1	RES, 100 ohm, 5%, 1W, Axial	Panasonic Electronic Components	ERG-1SJ101
R4, R5, R12	3	RES, 2.10Meg ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW08052M10FKEA
R6	1	RES, 1.00k ohm, 1%, 0.25W, 1206	Vishay-Dale	CRCW12061K00FKEA
R8	1	RES, 0 ohm, 5%, 0.125W, 0805	Vishay-Dale	CRCW08050000Z0EA
R9	1	RES, 42.2k ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW080542K2FKEA
R10	1	RES, 127k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603127KFKEA
R11	1	RES, 20.0 ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW080520R0FKEA
R13	1	RES, 27k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060327K0JNEA
R14	1	RES, 90.9k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060390K9FKEA
R15	1	RES, 3.65Meg ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW08053M65FKEA
R16	1	RES, 1.00k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06031K00FKEA
R17	1	RES, 10.2k ohm, 1%, 0.1W, 0603	Yageo America	RC0603FR-0710K2L
R18	1	RES, 3.00 ohm, 1%, 0.25W, 1206	Yageo America	RC1206FR-073RL
R19	1	RES, 26.7 ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW080526R7FKEA

Designator	Quantity	Description	Manufacturer	PartNumber
R20	1	RES, 1.10k ohm, 1%, 0.1W, 0603	Yageo America	RC0603FR-071K1L
R21	1	RES, 13.3k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060313K3FKEA
R22, R23	2	RES, 10.0k ohm, 1%, 0.1W, 0603	Yageo America	RC0603FR-0710KL
T1	1	Transformer EE-16	Wurth	750341087
TP2	1	Test Point, SMT, Miniature	Keystone Electronics	5015
U1	1	Off-Line Primary Side Sensing with PFC	TI	TPS92314A
U2	1	TRANS NPN 30V 100MA DUAL SOT143B	NXP Semiconductors	BCV61B,235
VDR1	1	Varistor, 300VAC, 385VDC, 30J, 7mm, Radial	EPCOS Inc	S07K300E2

## Notes:

Substitutions made according to Alternate PartNumber must meet datasheet parameters, not just the Description specified.

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

## Products Applications

Audio www.ti.com/audio Automotive and Transportation www.ti.com/automotive Communications and Telecom **Amplifiers** amplifier.ti.com www.ti.com/communications **Data Converters** dataconverter.ti.com Computers and Peripherals www.ti.com/computers **DLP® Products** www.dlp.com Consumer Electronics www.ti.com/consumer-apps

DSP **Energy and Lighting** dsp.ti.com www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical logic.ti.com Logic Security www.ti.com/security

Power Mgmt power.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Microcontrollers <u>microcontroller.ti.com</u> Video and Imaging <u>www.ti.com/video</u>

RFID <u>www.ti-rfid.com</u>

OMAP Applications Processors <a href="www.ti.com/omap">www.ti.com/omap</a> TI E2E Community <a href="e2e.ti.com">e2e.ti.com</a>

Wireless Connectivity <u>www.ti.com/wirelessconnectivity</u>