


TAPE AND REEL INFORMATION



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
M0G3505QDGS28RQ1	VSSOP	DGS	28	5000	330.0	16.4	5.5	7.4	1.45	8.0	16.0	Q1
M0G3505QDGS32RQ1	VSSOP	DGS	32	5000	330.0	16.4	5.65	8.4	1.45	8.0	16.0	Q1
M0G3505QPMRQ1	LQFP	PM	64	1000	330.0	24.4	13.0	13.0	2.1	16.0	24.0	Q2
M0G3505QPTRQ1	LQFP	PT	48	1000	330.0	16.4	9.6	9.6	1.9	12.0	16.0	Q2
M0G3505QRGZRQ1	VQFN	RGZ	48	3000	330.0	16.4	7.3	7.3	1.1	12.0	16.0	Q2
M0G3505QRHBRQ1	VQFN	RHB	32	3000	330.0	12.4	5.3	5.3	1.1	8.0	12.0	Q2
M0G3506QDGS28RQ1	VSSOP	DGS	28	5000	330.0	16.4	5.5	7.4	1.45	8.0	16.0	Q1
M0G3506QDGS32RQ1	VSSOP	DGS	32	5000	330.0	16.4	5.65	8.4	1.45	8.0	16.0	Q1
M0G3506QPMRQ1	LQFP	PM	64	1000	330.0	24.4	13.0	13.0	2.1	16.0	24.0	Q2
M0G3506QPTRQ1	LQFP	PT	48	1000	330.0	16.4	9.6	9.6	1.9	12.0	16.0	Q2
M0G3506QRGZRQ1	VQFN	RGZ	48	3000	330.0	16.4	7.3	7.3	1.1	12.0	16.0	Q2
M0G3506QRHBRQ1	VQFN	RHB	32	3000	330.0	12.4	5.3	5.3	1.1	8.0	12.0	Q2
M0G3507QDGS28RQ1	VSSOP	DGS	28	5000	330.0	16.4	5.5	7.4	1.45	8.0	16.0	Q1
M0G3507QDGS32RQ1	VSSOP	DGS	32	5000	330.0	16.4	5.65	8.4	1.45	8.0	16.0	Q1
M0G3507QPMRQ1	LQFP	PM	64	1000	330.0	24.4	13.0	13.0	2.1	16.0	24.0	Q2
M0G3507QPTRQ1	LQFP	PT	48	1000	330.0	16.4	9.6	9.6	1.9	12.0	16.0	Q2

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
M0G3507QRGZRQ1	VQFN	RGZ	48	3000	330.0	16.4	7.3	7.3	1.1	12.0	16.0	Q2
M0G3507QRHBRQ1	VQFN	RHB	32	3000	330.0	12.4	5.3	5.3	1.1	8.0	12.0	Q2

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
M0G3505QDGS28RQ1	VSSOP	DGS	28	5000	353.0	353.0	32.0
M0G3505QDGS32RQ1	VSSOP	DGS	32	5000	353.0	353.0	32.0
M0G3505QPMRQ1	LQFP	PM	64	1000	336.6	336.6	41.3
M0G3505QPTRQ1	LQFP	PT	48	1000	336.6	336.6	31.8
M0G3505QRGZRQ1	VQFN	RGZ	48	3000	367.0	367.0	35.0
M0G3505QRHBRQ1	VQFN	RHB	32	3000	367.0	367.0	35.0
M0G3506QDGS28RQ1	VSSOP	DGS	28	5000	353.0	353.0	32.0
M0G3506QDGS32RQ1	VSSOP	DGS	32	5000	353.0	353.0	32.0
M0G3506QPMRQ1	LQFP	PM	64	1000	336.6	336.6	41.3
M0G3506QPTRQ1	LQFP	PT	48	1000	336.6	336.6	31.8
M0G3506QRGZRQ1	VQFN	RGZ	48	3000	367.0	367.0	35.0
M0G3506QRHBRQ1	VQFN	RHB	32	3000	367.0	367.0	35.0
M0G3507QDGS28RQ1	VSSOP	DGS	28	5000	353.0	353.0	32.0
M0G3507QDGS32RQ1	VSSOP	DGS	32	5000	353.0	353.0	32.0
M0G3507QPMRQ1	LQFP	PM	64	1000	336.6	336.6	41.3
M0G3507QPTRQ1	LQFP	PT	48	1000	336.6	336.6	31.8
M0G3507QRGZRQ1	VQFN	RGZ	48	3000	367.0	367.0	35.0
M0G3507QRHBRQ1	VQFN	RHB	32	3000	367.0	367.0	35.0