

ESD441W-Q1 Automotive 1-Channel $\pm 30\text{kV}$ Unidirectional ESD Diode in Wettable Flank 0402 Package

1 Features

- IEC 61000-4-2 level 4 ESD protection
 - $\pm 30\text{kV}$ contact discharge
 - $\pm 30\text{kV}$ air gap discharge
- ISO 10605 (150pF, 330 Ω & 330pF, 330 Ω) ESD protection:
 - $\pm 30\text{kV}$ contact discharge
 - $\pm 30\text{kV}$ air gap discharge
- IEC 61000-4-5 surge protection
 - 6A (8/20 μs)
- IO capacitance:
 - 1pF (typical)
- Breakdown voltage: 7V (typical)
- Ultra low leakage current: 50nA (maximum)
- Extremely low ESD clamping voltage
 - 8.2V at 16A TLP
 - R_{DYN} : 0.16 Ω (I/O to GND)
- Low insertion loss: 2GHz (–3dB bandwidth)
- Supports high speed interfaces up to 4Gbps
- Space-saving industry standard 0402 footprint (1.0mm \times 0.6mm)
- Industrial temperature range: -55°C to $+150^{\circ}\text{C}$
- AEC-Q101 Qualified

2 Applications

- End equipment:
 - Vacuum robots
 - Wearables
 - Smart speakers
 - Portable electronics
 - Small appliances
 - Retail automation and payment
 - Laptops and desktops
 - TV and monitors
 - Docking stations
- Interfaces:
 - USB 2.0
 - HDMI™ 1.4 and 2.0
 - DisplayPort™
 - SIM card
 - GPIO

3 Description

The ESD441W-Q1 is a unidirectional ESD protection diode for protecting data lines and other I/O ports. The ESD441W-Q1 is rated to dissipate ESD strikes up to $\pm 30\text{kV}$ per the IEC 61000-4-2 international standard (greater than Level 4).

This device features a 1pF (typical) IO capacitance enabling high-speed interfaces protection for protocols such as USB 2.0. The extremely low dynamic resistance (0.16 Ω) and clamping voltage (8.2V at 16A TLP) is specified for system level protection against transient events.

The 30kV ESD rating and 6A surge provides robust transient protection in a tiny package for protecting 5.5V power rails in portable electronics and other space constrained applications such as wearables.

The ESD441W-Q1 is offered in a wettable flank 0402 package.

Package Information

PART NUMBER	PACKAGE ⁽¹⁾	PACKAGE SIZE ⁽²⁾
ESD441W-Q1	DPY (DFN1006, 2)	1.0mm \times 0.6mm

- (1) For all available packages, see the orderable addendum at the end of the data sheet.
- (2) The package size (length \times width) is a nominal value and includes pins, where applicable.



Functional Block Diagram



Table of Contents

1 Features	1	5.7 Electrical Characteristics.....	5
2 Applications	1	5.8 Typical Characteristics.....	6
3 Description	1	6 Device and Documentation Support	8
4 Pin Configuration and Functions	3	6.1 Documentation Support.....	8
5 Specifications	4	6.2 Receiving Notification of Documentation Updates.....	8
5.1 Absolute Maximum Ratings.....	4	6.3 Support Resources.....	8
5.2 ESD Ratings - AEC Specifications.....	4	6.4 Trademarks.....	8
5.3 ESD Ratings—IEC Specification.....	4	6.5 Electrostatic Discharge Caution.....	8
5.4 ESD Ratings - ISO Specifications.....	4	6.6 Glossary.....	8
5.5 Recommended Operating Conditions.....	4	7 Revision History	8
5.6 Thermal Information.....	5	8 Mechanical, Packaging, and Orderable Information	8

4 Pin Configuration and Functions




Figure 4-1. DPY Package, 2-Pin DFN1006 (Top View)

Table 4-1. Pin Functions

PIN		TYPE ⁽¹⁾	DESCRIPTION
NAME	NO.		
IO	1	I/O	ESD protected channel
GND	2	GND	Ground. Connect to ground.

(1) I = input, O = output, GND = ground

5 Specifications

5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) ⁽¹⁾

		MIN	MAX	UNIT
Peak Pulse ^{(2) (3)}	IEC 61000-4-5 power ($t_p - 8/20\mu s$)		45	W
	IEC 61000-4-5 Current ($t_p - 8/20\mu s$)		6	A
T_A	Ambient Operating Temperature	-55	150	°C
T_{stg}	Storage Temperature	-65	155	°C

- (1) Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute maximum ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If briefly operating outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not sustain damage, but it may not be fully functional. Operating the device in this manner may affect device reliability, functionality, performance, and shorten the device lifetime.
- (2) Voltages are with respect to GND unless otherwise noted.
- (3) Measured at 25°C

5.2 ESD Ratings - AEC Specifications

Parameter		Test Conditions	VALUE	UNIT
$V_{(ESD)}$	Electrostatic discharge	Human body model (HBM), per AEC Q101-001 ⁽¹⁾	±2500	V
		Charged device model (CDM), per AEC Q101-005 ⁽²⁾	±1000	

- (1) JEDEC document JEP155 states that 500V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250V CDM allows safe manufacturing with a standard ESD control process.

5.3 ESD Ratings—IEC Specification

		VALUE	UNIT
$V_{(ESD)}$	Electrostatic discharge	IEC 61000-4-2 contact discharge	±30000
		IEC 61000-4-2 air-gap discharge	±30000

5.4 ESD Ratings - ISO Specifications

Parameter		Test Conditions	VALUE	UNIT
$V_{(ESD)}$	ISO 10605 Electrostatic Discharge	C = 150pF; R = 330Ω	Contact Discharge, all pins	±30000
			Air-gap Discharge, all pins	±30000
		C = 330pF; R = 330Ω	Contact Discharge, all pins	±30000
			Air-gap Discharge, all pins	±30000

5.5 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
V_{IO}	Input pin voltage	Pin 1 to 2	0	5.5	V
T_A	Operating free-air temperature		-55	150	°C

5.6 Thermal Information

THERMAL METRIC ⁽¹⁾		ESD441W-Q1	
		DPY (DFN1006)	
		2 PINS	
			UNIT
$R_{\theta JA}$	Junction-to-ambient thermal resistance	448.9	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	308.6	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	197.5	°C/W
Ψ_{JT}	Junction-to-top characterization parameter	159.4	°C/W
Ψ_{JB}	Junction-to-board characterization parameter	196.6	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	N/A	°C/W

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application note.

5.7 Electrical Characteristics

At $T_A=25^\circ\text{C}$ (unless otherwise noted) ⁽¹⁾

PARAMETER		TEST CONDITION	MIN	TYP	MAX	UNIT
V_{RWM}	Reverse stand-off voltage	$I_{IO} < 100\text{nA}$, across operating temperature range			5.5	V
I_{LEAK}	Reverse leakage current	$V_{IO} = 5.5\text{V}$, IO to GND		1	50	nA
V_{BR}	Break-down voltage	$I_{IO} = 1\text{mA}$, IO to GND	6	7	8	V
V_{FWD}	Forward voltage	$I_{IO} = 1\text{mA}$, GND to IO		0.8		V
V_{CLAMP}	Clamping voltage with TLP ⁽²⁾	$I_{PP} = 1\text{A}$, TLP, IO to GND		7.1		V
		$I_{PP} = 5\text{A}$, TLP, IO to GND		7.3		V
		$I_{PP} = 16\text{A}$, TLP, IO to GND		8.2		V
	Clamping voltage with surge strike ⁽⁴⁾	$I_{PP} = 16\text{A}$, TLP, GND to IO		3.8		V
R_{DYN}	Dynamic resistance ⁽³⁾	IO to GND		0.16		Ω
		GND to IO		0.16		
C_L	Line capacitance	$V_{IO} = 0\text{V}$; $f = 1\text{MHz}$, $V_{pp} = 30\text{mV}$, IO to GND		1		pF

(1) Typical parameters are measured at 25°C

(2) Transition line pulse with 100ns width and 10ns rise and fall time

(3) Extraction of R_{DYN} using least squares fit of TLP characteristics between $I = 10\text{A}$ and $I = 20\text{A}$

(4) Nonrepetitive current pulse 8 to 20 μs exponentially decaying waveform according to IEC 61000-4-5

5.8 Typical Characteristics




Figure 5-1. Positive TLP Curve




Figure 5-2. Negative TLP Curve




Figure 5-3. +8kV Clamped IEC Waveform




Figure 5-4. -8kV Clamped IEC Waveform




Figure 5-5. Bias Voltage vs. Capacitance




Figure 5-6. Temperature vs. Capacitance




Figure 5-7. Temperature vs Leakage Current




Figure 5-8. Insertion Loss

6 Device and Documentation Support

6.1 Documentation Support

6.1.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, [ESD Packaging and Layout Guide](#)
- Texas Instruments, [ESD Layout Guide application reports](#)
- Texas Instruments, [Generic ESD Evaluation Module user's guide](#)
- Texas Instruments, [Picking ESD Diodes for Ultra High-Speed Data Lines application reports](#)
- Texas Instruments, [Reading and Understanding an ESD Protection data sheet](#)

6.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](#). Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

6.3 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

6.4 Trademarks

HDMI™ is a trademark of HDMI Licensing LLC.

DisplayPort™ is a trademark of Video Electronics Standards Association.

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

6.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

6.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

7 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

DATE	REVISION	NOTES
June 2026	*	Initial Release

8 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
ESD441WDPYRQ1	Active	Production	null (null)	10000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	RX

(1) **Status:** For more details on status, see our [product life cycle](#).

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025