

## FEATURES

- Member of the Texas Instruments Widebus™ Family
- Operates From 1.65 V to 3.6 V
- Max  $t_{pd}$  of 4.2 ns at 3.3 V
- $\pm 12$ -mA Output Drive at 3.3 V
- All Outputs Have Equivalent 26- $\Omega$  Series Resistors, So No External Resistors Are Required
- Bus Hold on Data Inputs Eliminates the Need for External Pullup/Pulldown Resistors
- Latch-Up Performance Exceeds 250 mA Per JESD 17
- ESD Protection Exceeds JESD 22
  - 2000-V Human-Body Model (A114-A)
  - 200-V Machine Model (A115-A)

## DESCRIPTION/ORDERING INFORMATION

This 16-bit (dual-octal) noninverting bus transceiver is designed for 1.65-V to 3.6-V  $V_{CC}$  operation.


The SN74ALVCHR16245 is designed for asynchronous communication between data buses. The control-function implementation minimizes external timing requirements.

This device can be used as two 8-bit transceivers or one 16-bit transceiver. It allows data transmission from the A bus to the B bus or from the B bus to the A bus, depending on the logic level at the direction-control (DIR) input. The output-enable ( $\overline{OE}$ ) input can be used to disable the device so that the buses are effectively isolated.

All outputs, which are designed to sink up to 12 mA, include equivalent 26- $\Omega$  series resistors to reduce overshoot and undershoot.

To ensure the high-impedance state during power up or power down,  $\overline{OE}$  should be tied to  $V_{CC}$  through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

Active bus-hold circuitry holds unused or undriven inputs at a valid logic state. Use of pullup or pulldown resistors with the bus-hold circuitry is not recommended.



## ORDERING INFORMATION

| $T_A$         | PACKAGE <sup>(1)</sup> |               | ORDERABLE PART NUMBER | TOP-SIDE MARKING |
|---------------|------------------------|---------------|-----------------------|------------------|
| -40°C to 85°C | SSOP - DL              | Tape and reel | SN74ALVCHR16245LR     | ALVCHR16245      |
|               | TSSOP - DGG            | Tape and reel | SN74ALVCHR16245GR     | ALVCHR16245      |
|               | VFBGA - GQL            | Tape and reel | SN74ALVCHR16245KR     | VR245            |
|               | VFBGA - ZQL (Pb-free)  |               | 74ALVCHR16245ZQLR     |                  |

(1) Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at [www.ti.com/sc/package](http://www.ti.com/sc/package).



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

Widebus is a trademark of Texas Instruments.


# SN74ALVCHR16245

## 16-BIT BUS TRANSCEIVER

### WITH 3-STATE OUTPUTS

SCES064G–DECEMBER 1995–REVISED OCTOBER 2004

**GQL OR ZQL PACKAGE  
(TOP VIEW)**



**TERMINAL ASSIGNMENTS<sup>(1)</sup>**



|          | 1    | 2   | 3               | 4               | 5   | 6                 |
|----------|------|-----|-----------------|-----------------|-----|-------------------|
| <b>A</b> | 1DIR | NC  | NC              | NC              | NC  | 1 $\overline{OE}$ |
| <b>B</b> | 1B2  | 1B1 | GND             | GND             | 1A1 | 1A2               |
| <b>C</b> | 1B4  | 1B3 | V <sub>CC</sub> | V <sub>CC</sub> | 1A3 | 1A4               |
| <b>D</b> | 1B6  | 1B5 | GND             | GND             | 1A5 | 1A6               |
| <b>E</b> | 1B8  | 1B7 |                 |                 | 1A7 | 1A8               |
| <b>F</b> | 2B1  | 2B2 |                 |                 | 2A2 | 2A1               |
| <b>G</b> | 2B3  | 2B4 | GND             | GND             | 2A4 | 2A3               |
| <b>H</b> | 2B5  | 2B6 | V <sub>CC</sub> | V <sub>CC</sub> | 2A6 | 2A5               |
| <b>J</b> | 2B7  | 2B8 | GND             | GND             | 2A8 | 2A7               |
| <b>K</b> | 2DIR | NC  | NC              | NC              | NC  | 2 $\overline{OE}$ |

(1) NC - No internal connection

**FUNCTION TABLE  
(each 8-bit section)**

| INPUTS          |     | OPERATION       |
|-----------------|-----|-----------------|
| $\overline{OE}$ | DIR |                 |
| L               | L   | B data to A bus |
| L               | H   | A data to B bus |
| H               | X   | Isolation       |

### LOGIC DIAGRAM (POSITIVE LOGIC)



Pin numbers shown are for the DGG and DL packages.

### ABSOLUTE MAXIMUM RATINGS<sup>(1)</sup>

over operating free-air temperature range (unless otherwise noted)

|  |  |                                 | MIN  | MAX                   | UNIT |      |
|--|--|---------------------------------|------|-----------------------|------|------|
| V <sub>CC</sub>  | Supply voltage range                     |                                 | -0.5 | 4.6                   | V    |      |
| V <sub>I</sub>   | Input voltage range                      | Except I/O ports <sup>(2)</sup> | -0.5 | 4.6                   | V    |      |
|  |  | I/O ports <sup>(2)(3)</sup>     | -0.5 | V <sub>CC</sub> + 0.5 |      |      |
| V <sub>O</sub>   | Output voltage range <sup>(2)(3)</sup>   |                                 | -0.5 | V <sub>CC</sub> + 0.5 | V    |      |
| I <sub>IK</sub>  | Input clamp current                      | V <sub>I</sub> < 0              |      |                       | -50  | mA   |
| I <sub>OK</sub>  | Output clamp current                     | V <sub>O</sub> < 0              |      |                       | -50  | mA   |
| I <sub>O</sub>   | Continuous output current                |                                 |      |                       | ±50  | mA   |
| Continuous current through each V <sub>CC</sub> or GND |  |                                 |      |                       | ±100 | mA   |
| θ <sub>JA</sub>  | Package thermal impedance <sup>(4)</sup> | DGG package                     |      |                       | 70   | °C/W |
|  |  | DL package                      |      |                       | 63   |      |
|  |  | GQL/ZQL package                 |      |                       | 42   |      |
| T <sub>stg</sub>                                       | Storage temperature range                |                                 | -65  | 150                   | °C   |      |

- (1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The input negative-voltage and output voltage ratings may be exceeded if the input and output current ratings are observed.
- (3) This value is limited to 4.6 V maximum.
- (4) The package thermal impedance is calculated in accordance with JESD 51-7.

**SN74ALVCHR16245**  
**16-BIT BUS TRANSCEIVER**  
**WITH 3-STATE OUTPUTS**

SCES064G–DECEMBER 1995–REVISED OCTOBER 2004

**RECOMMENDED OPERATING CONDITIONS<sup>(1)</sup>**

|                     |                                    |   | MIN                  | MAX                  | UNIT |
|---------------------|------------------------------------|---|----------------------|----------------------|------|
| $V_{CC}$            | Supply voltage                     |   | 1.65                 | 3.6                  | V    |
| $V_{IH}$            | High-level input voltage           | $V_{CC} = 1.65\text{ V to }1.95\text{ V}$ | $0.65 \times V_{CC}$ |                      | V    |
|                     |                                    | $V_{CC} = 2.3\text{ V to }2.7\text{ V}$   | 1.7                  |                      |      |
|                     |                                    | $V_{CC} = 2.7\text{ V to }3.6\text{ V}$   | 2                    |                      |      |
| $V_{IL}$            | Low-level input voltage            | $V_{CC} = 1.65\text{ V to }1.95\text{ V}$ |                      | $0.35 \times V_{CC}$ | V    |
|                     |                                    | $V_{CC} = 2.3\text{ V to }2.7\text{ V}$   |                      | 0.7                  |      |
|                     |                                    | $V_{CC} = 2.7\text{ V to }3.6\text{ V}$   |                      | 0.8                  |      |
| $V_I$               | Input voltage                      |   | 0                    | $V_{CC}$             | V    |
| $V_O$               | Output voltage                     |   | 0                    | $V_{CC}$             | V    |
| $I_{OH}$            | High-level output current          | $V_{CC} = 1.65\text{ V}$                  |                      | -2                   | mA   |
|                     |                                    | $V_{CC} = 2.3\text{ V}$                   |                      | -6                   |      |
|                     |                                    | $V_{CC} = 2.7\text{ V}$                   |                      | -8                   |      |
|                     |                                    | $V_{CC} = 3\text{ V}$                     |                      | -12                  |      |
| $I_{OL}$            | Low-level output current           | $V_{CC} = 1.65\text{ V}$                  |                      | 2                    | mA   |
|                     |                                    | $V_{CC} = 2.3\text{ V}$                   |                      | 6                    |      |
|                     |                                    | $V_{CC} = 2.7\text{ V}$                   |                      | 8                    |      |
|                     |                                    | $V_{CC} = 3\text{ V}$                     |                      | 12                   |      |
| $\Delta t/\Delta v$ | Input transition rise or fall rate |   |                      | 10                   | ns/V |
| $T_A$               | Operating free-air temperature     |   | -40                  | 85                   | °C   |

- (1) All unused control inputs of the device must be held at  $V_{CC}$  or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.

## ELECTRICAL CHARACTERISTICS

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER                      |                | TEST CONDITIONS  | V <sub>CC</sub> | MIN                   | TYP <sup>(1)</sup> | MAX | UNIT |
|--------------------------------|----------------|--|-----------------|-----------------------|--------------------|-----|------|
| V <sub>OH</sub>                |                | I <sub>OH</sub> = -100 µA  | 1.65 V to 3.6 V | V <sub>CC</sub> - 0.2 |                    |     | V    |
|                                |                | I <sub>OH</sub> = -2 mA  | 1.65 V          | 1.2                   |                    |     |      |
|                                |                | I <sub>OH</sub> = -4 mA  | 2.3 V           | 1.9                   |                    |     |      |
|                                |                | I <sub>OH</sub> = -6 mA  | 2.3 V           | 1.7                   |                    |     |      |
|                                |                |  | 3 V             | 2.4                   |                    |     |      |
|                                |                | I <sub>OH</sub> = -8 mA  | 2.7 V           | 2                     |                    |     |      |
|                                |                | I <sub>OH</sub> = -12 mA   | 3 V             | 2                     |                    |     |      |
| V <sub>OL</sub>                |                | I <sub>OL</sub> = 100 µA   | 1.65 V to 3.6 V | 0.2                   |                    |     | V    |
|                                |                | I <sub>OL</sub> = 2 mA   | 1.65 V          | 0.45                  |                    |     |      |
|                                |                | I <sub>OL</sub> = 4 mA   | 2.3 V           | 0.4                   |                    |     |      |
|                                |                | I <sub>OL</sub> = 6 mA   | 2.3 V           | 0.55                  |                    |     |      |
|                                |                |  | 3 V             | 0.55                  |                    |     |      |
|                                |                | I <sub>OL</sub> = 8 mA   | 2.7 V           | 0.6                   |                    |     |      |
|                                |                | I <sub>OL</sub> = 12 mA  | 3 V             | 0.8                   |                    |     |      |
| I <sub>I</sub>                 |                | V <sub>I</sub> = V <sub>CC</sub> or GND                                      | 3.6 V           | ±5                    |                    |     | µA   |
| I <sub>I(hold)</sub>           |                | V <sub>I</sub> = 0.58 V  | 1.65 V          | 25                    |                    |     | µA   |
|                                |                | V <sub>I</sub> = 1.07 V  |                 | -25                   |                    |     |      |
|                                |                | V <sub>I</sub> = 0.7 V   | 2.3 V           | 45                    |                    |     |      |
|                                |                | V <sub>I</sub> = 1.7 V   |                 | -45                   |                    |     |      |
|                                |                | V <sub>I</sub> = 0.8 V   | 3 V             | 75                    |                    |     |      |
|                                |                | V <sub>I</sub> = 2 V   |                 | -75                   |                    |     |      |
|                                |                | V <sub>I</sub> = 0 to 3.6 V <sup>(2)</sup>                                   | 3.6 V           | ±500                  |                    |     |      |
| I <sub>OZ</sub> <sup>(3)</sup> |                | V <sub>O</sub> = V <sub>CC</sub> or GND                                      | 3.6 V           | ±10                   |                    |     | µA   |
| I <sub>CC</sub>                |                | V <sub>I</sub> = V <sub>CC</sub> or GND, I <sub>O</sub> = 0                  | 3.6 V           | 40                    |                    |     | µA   |
| ΔI <sub>CC</sub>               |                | One input at V <sub>CC</sub> - 0.6 V, Other inputs at V <sub>CC</sub> or GND | 3 V to 3.6 V    | 750                   |                    |     | µA   |
| C <sub>i</sub>                 | Control inputs | V <sub>I</sub> = V <sub>CC</sub> or GND                                      | 3.3 V           | 4                     |                    |     | pF   |
| C <sub>io</sub>                | A or B ports   | V <sub>O</sub> = V <sub>CC</sub> or GND                                      | 3.3 V           | 9                     |                    |     | pF   |

(1) All typical values are at V<sub>CC</sub> = 3.3 V, T<sub>A</sub> = 25°C.

(2) This is the bus-hold maximum dynamic current. It is the minimum overdrive current required to switch the input from one state to another.

(3) For I/O ports, the parameter I<sub>OZ</sub> includes the input leakage current.

## SWITCHING CHARACTERISTICS

over recommended operating free-air temperature range (unless otherwise noted) (see Figure 1)

| PARAMETER        | FROM<br>(INPUT)        | TO<br>(OUTPUT) | V <sub>CC</sub> = 1.8 V | V <sub>CC</sub> = 2.5 V<br>± 0.2 V |     | V <sub>CC</sub> = 2.7 V |     | V <sub>CC</sub> = 3.3 V<br>± 0.3 V |     | UNIT |
|------------------|------------------------|----------------|-------------------------|------------------------------------|-----|-------------------------|-----|------------------------------------|-----|------|
|                  |                        |                | TYP                     | MIN                                | MAX | MIN                     | MAX | MIN                                | MAX |      |
| t <sub>pd</sub>  | A or B                 | B or A         | (1)                     | 1                                  | 4.9 | 4.7                     |     | 1                                  | 4.2 | ns   |
| t <sub>en</sub>  | $\overline{\text{OE}}$ | B or A         | (1)                     | 1                                  | 6.8 | 6.7                     |     | 1                                  | 5.6 | ns   |
| t <sub>dis</sub> | $\overline{\text{OE}}$ | B or A         | (1)                     | 1                                  | 6.3 | 5.7                     |     | 1                                  | 5.5 | ns   |

(1) This information was not available at the time of publication.

# SN74ALVCHR16245

## 16-BIT BUS TRANSCEIVER

### WITH 3-STATE OUTPUTS

SCES064G–DECEMBER 1995–REVISED OCTOBER 2004


#### OPERATING CHARACTERISTICS

$T_A = 25^\circ\text{C}$

| PARAMETER |                               |                  | TEST CONDITIONS                         | $V_{CC} = 1.8\text{ V}$ | $V_{CC} = 2.5\text{ V}$ | $V_{CC} = 3.3\text{ V}$ | UNIT |
|-----------|-------------------------------|------------------|---|-------------------------|-------------------------|-------------------------|------|
|           |                               |                  |   | TYP                     | TYP                     | TYP                     |      |
| $C_{pd}$  | Power dissipation capacitance | Outputs enabled  | $C_L = 50\text{ pF}, f = 10\text{ MHz}$ | (1)                     | 24                      | 32                      | pF   |
|           |                               | Outputs disabled |   | (1)                     | 4                       | 5                       |      |

(1) This information was not available at the time of publication.





## PARAMETER MEASUREMENT INFORMATION



LOAD CIRCUIT

| TEST              | S1         |
|-------------------|------------|
| $t_{pd}$          | Open       |
| $t_{PLZ}/t_{PZL}$ | $V_{LOAD}$ |
| $t_{PHZ}/t_{PHL}$ | GND        |

| $V_{CC}$          | INPUT    |               | $V_M$      | $V_{LOAD}$        | $C_L$ | $R_L$        | $V_{\Delta}$ |
|-------------------|----------|---------------|------------|-------------------|-------|--------------|--------------|
|                   | $V_I$    | $t_r/t_f$     |            |                   |       |              |              |
| 1.8 V             | $V_{CC}$ | $\leq 2$ ns   | $V_{CC}/2$ | $2 \times V_{CC}$ | 30 pF | 1 k $\Omega$ | 0.15 V       |
| 2.5 V $\pm$ 0.2 V | $V_{CC}$ | $\leq 2$ ns   | $V_{CC}/2$ | $2 \times V_{CC}$ | 30 pF | 500 $\Omega$ | 0.15 V       |
| 2.7 V             | 2.7 V    | $\leq 2.5$ ns | 1.5 V      | 6 V               | 50 pF | 500 $\Omega$ | 0.3 V        |
| 3.3 V $\pm$ 0.3 V | 2.7 V    | $\leq 2.5$ ns | 1.5 V      | 6 V               | 50 pF | 500 $\Omega$ | 0.3 V        |



- NOTES:
- $C_L$  includes probe and jig capacitance.
  - Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
  - All input pulses are supplied by generators having the following characteristics:  $PRR \leq 10$  MHz,  $Z_O = 50 \Omega$ .
  - The outputs are measured one at a time, with one transition per measurement.
  - $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
  - $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .
  - $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{pd}$ .
  - All parameters and waveforms are not applicable to all devices.

Figure 1. Load Circuit and Voltage Waveforms

## PACKAGING INFORMATION

| Orderable part number             | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-----------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| 74ALVCHR16245GRG4                 | Active        | Production           | TSSOP (DGG)   48 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | ALVCHR16245         |
| 74ALVCHR16245GRG4.B               | Active        | Production           | TSSOP (DGG)   48 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | ALVCHR16245         |
| 74ALVCHR16245LR1G4                | Active        | Production           | SSOP (DL)   48   | 1000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | ALVCHR16245         |
| 74ALVCHR16245LR1G4.B              | Active        | Production           | SSOP (DL)   48   | 1000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | ALVCHR16245         |
| <a href="#">SN74ALVCHR16245GR</a> | Active        | Production           | TSSOP (DGG)   48 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | ALVCHR16245         |
| SN74ALVCHR16245GR.B               | Active        | Production           | TSSOP (DGG)   48 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | ALVCHR16245         |
| <a href="#">SN74ALVCHR16245LR</a> | Active        | Production           | SSOP (DL)   48   | 1000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | ALVCHR16245         |
| SN74ALVCHR16245LR.B               | Active        | Production           | SSOP (DL)   48   | 1000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | ALVCHR16245         |

(1) **Status:** For more details on status, see our [product life cycle](#).

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.



In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device             | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| 74ALVCHR16245GRG4  | TSSOP        | DGG             | 48   | 2000 | 330.0              | 24.4               | 8.6     | 13.0    | 1.8     | 12.0    | 24.0   | Q1            |
| 74ALVCHR16245LR1G4 | SSOP         | DL              | 48   | 1000 | 330.0              | 32.4               | 11.35   | 16.2    | 3.1     | 16.0    | 32.0   | Q1            |
| SN74ALVCHR16245GR  | TSSOP        | DGG             | 48   | 2000 | 330.0              | 24.4               | 8.6     | 13.0    | 1.8     | 12.0    | 24.0   | Q1            |
| SN74ALVCHR16245LR  | SSOP         | DL              | 48   | 1000 | 330.0              | 32.4               | 11.35   | 16.2    | 3.1     | 16.0    | 32.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS




\*All dimensions are nominal


| Device             | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| 74ALVCHR16245GRG4  | TSSOP        | DGG             | 48   | 2000 | 356.0       | 356.0      | 45.0        |
| 74ALVCHR16245LR1G4 | SSOP         | DL              | 48   | 1000 | 356.0       | 356.0      | 53.0        |
| SN74ALVCHR16245GR  | TSSOP        | DGG             | 48   | 2000 | 356.0       | 356.0      | 45.0        |
| SN74ALVCHR16245LR  | SSOP         | DL              | 48   | 1000 | 356.0       | 356.0      | 53.0        |

DL (R-PDSO-G48)

PLASTIC SMALL-OUTLINE PACKAGE



- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).
  - D. Falls within JEDEC MO-118



4214859/B 11/2020

## NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. Reference JEDEC registration MO-153.

# EXAMPLE BOARD LAYOUT



DGG0048A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
SCALE:6X



SOLDER MASK DETAILS

4214859/B 11/2020

NOTES: (continued)


5. Publication IPC-7351 may have alternate designs.
6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

DGG0048A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:6X

4214859/B 11/2020

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

## DGG (R-PDSO-G\*\*)

## PLASTIC SMALL-OUTLINE PACKAGE

48 PINS SHOWN



- NOTES: A. All linear dimensions are in millimeters.  
 B. This drawing is subject to change without notice.  
 C. Body dimensions do not include mold protrusion not to exceed 0,15.  
 D. Falls within JEDEC MO-153



## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025