


1	Startup2				
2	Shutdown				
3	Efficiency 4				
4	Load Regulation				
5	Line Regulation				
6	Cross Regulation				
7	Ripple Voltage				
7	'.1	Positive Output			
7	.2	Negative Output 10			
7	' .3	Input Voltage			
8	Control Loop Frequency Response 12				
9	Load Transients				
ç	9.1	Transient applied at negative VOUT (-VOUT)13			
ç).2	Transient applied at positive VOUT (+VOUT)14			
10		Miscellaneous Waveforms 15			
11		Thermal Image 19			
Тор	olo	pgy:Dual Inverting Buck-Boost (negative and positive output on second winding).			

Device: TPS54360

Unless otherwise mentioned all measurements were done with 24V input voltage and 0.7A output current on each output





1 Startup

The startup waveform is shown in the Figure 1. The input voltage was set at 24V, with 0.7A load at the output on each output. Power supply was connected.




Figure 1



2 Shutdown

The shutdown waveform is shown in the Figure 2. The input voltage was set at 24V, with 0.7A load on each output. Power supply was disconnected.




Figure 2



3 Efficiency

The efficiency is shown in the Figure 3 below. The input voltage was set to 24V. The output currents were modified simultaneous (-IOUT = +IOUT). The discontinuity in the curve reflects the transition from discontinuous to continuous mode.





Figure 3



4 Load Regulation

The load regulation of the output is shown in the Figure 4 below.



Deviation on load of negative rail <100mV, less than 1% Deviation of positive rail around 120mV, roughly 1%



5 Line Regulation

Line regulation at 0.7A output current is shown in Figure 5




Figure 5

Deviation on input voltage is around 20mV, insignificant low.



With the same measurement the full load efficiencies across input voltage were calculated




Figure o

Full load efficiency across input voltage range +90%.



6 Cross Regulation

The output currents were changed separately (0A, 0.2A, 0.4A, 0.7A) Figure 7 shows the effects on the positive output voltage, if the negative output current is varied. The different curves represent the positive output current settings





Figure 7

Figure 8 shows the effects on the negative output voltage, if the positive output current is varied. The different curves represent the negative output current settings.






7 Ripple Voltage

7.1 Positive Output

The output ripple voltage is shown in Figure 9. The image was taken with a 0.7A and 24V at the input.



Output ripple around 100mVpp, so less than 1% of output voltage.



7.2 Negative Output

The negative output ripple voltage is shown in Figure 10. The image was taken with a 0.7A load 24V at the input.




Figure 10

Output ripple around 50mVpp, so less than 1% of output voltage.



7.3 Input Voltage

The input ripple voltage is shown in Figure 11.




Figure 11



8 Control Loop Frequency Response

Figure 12 shows the loop response with 0.7A load and 20V,24V and 28V input.




Table 1 summarizes the results

	001/	041/	001/
	20V	24V	28V
Bandwidth (kHz)	5.65	6.2	6.65
Phasemargin	71 °	72.4°	72.5°
slope (20dB/decade)	-1.2	-1	-1.1
gain margin (dB)	-14.67	-15.7	-16.1
slope (20dB/decade)	-1.44	-2.15	-1.5
freq (kHz)	25.5	29.9	32.1
	Table 1		

The loop was designed for PM>65degs and GM around -15dB;


The bandwidth of 6kHz for the flyback topology is fair, the slope of -1 at Fco is perfect.




9 Load Transients

9.1 Transient applied at negative VOUT (-VOUT)

The Figure 13 shows the response to load transients. The load is switching from 0.35A to 0.7A (50 Hz). Negative VOUT was measured



The Figure 14 shows the response to load transients. The load is switching from 0.35A to 0.7A (50 Hz). Positive VOUT was measured







9.2 Transient applied at positive VOUT (+VOUT)

The Figure 13 shows the response to load transients. The load is switching from **0.36A to 0.87A** (load precision !) (50 Hz). Negative VOUT was measured





Figure 15






Figure 16



10 Miscellaneous Waveforms

Switch node ("SW" to -VOUT)) waveform shown in Figure 17




Figure 17



Switchnode ("SW" to GND measured at the inductor pads) results in the waveform shown in Figure 18.





Figure 18




"Secondary" switchchnode (measured at the inductor pads): the waveform is shown in **Figure 19**. Measured without snubber.





Secondary switchnode (SW2 to +VOUT) the waveform is shown in Figure 20. Applied RC snubber across diode D1 (100Ohm + 470pF in series)



RC snubber deduced voltage stress below 60Vpk



11 Thermal Image

Thermal image is shown in Figure 21. Input voltage was set to 24V and both output currents at full load 700mA for more than 30minutes:




Figure 21

Name	Temperature			
R101	61.3°C			
U1	58.9°C			
D1	59.1°C			
L1	57.5°C			
D2	52.9°C			

Table 2

Thermall stress at the semiconductors is low, dT < 40K

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated