Errata **MSP430G2744 Microcontroller**

Texas Instruments

ABSTRACT

This document describes the known exceptions to the functional specifications (advisories).

Table of Contents

1 Functional Advisories	2
2 Preprogrammed Software Advisories	2
3 Debug Only Advisories	
4 Fixed by Compiler Advisories	
5 Nomenclature, Package Symbolization, and Revision Identification	4
5.1 Device Nomenclature	
5.2 Package Markings	4
5.3 Memory-Mapped Hardware Revision (TLV Structure)	
6 Advisory Descriptions	6
7 Revision History	



1 Functional Advisories

Advisories that affect the device's operation, function, or parametrics.

 \checkmark The check mark indicates that the issue is present in the specified revision.

Errata Number	V V	< < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < < <<
BCL12	1	\checkmark
BCL16	1	\checkmark
CPU45	1	✓
FLASH24	1	\checkmark
FLASH27	1	\checkmark
FLASH36	1	✓
PORT10	1	\checkmark
SYS15	1	✓
TA12	1	\checkmark
TA16	1	1
TA21	1	1
TAB22	1	✓
TB2	1	✓
TB16	1	\checkmark
TB24	1	1
USCI20	1	\checkmark
USCI21	1	1
USCI22	1	✓
USCI23	1	\checkmark
USCI24	1	1
USCI25	1	1
USCI26	1	1
USCI27	1	1
USCI30	1	1
USCI34	1	1
USCI35	1	1
USCI40	1	1
XOSC5	\checkmark	✓

2 Preprogrammed Software Advisories

Advisories that affect factory-programmed software.

 \checkmark The check mark indicates that the issue is present in the specified revision.

The device does not have any errata for this category.

3 Debug Only Advisories

Advisories that affect only debug operation.

 \checkmark The check mark indicates that the issue is present in the specified revision.

Errata Number	Rev J	Rev H
EEM20	1	1



4 Fixed by Compiler Advisories

Advisories that are resolved by compiler workaround. Refer to each advisory for the IDE and compiler versions with a workaround.

 \checkmark The check mark indicates that the issue is present in the specified revision.

Errata Number	Rev J	Rev H	
CPU19	1	1	

Refer to the following MSP430 compiler documentation for more details about the CPU bugs workarounds.

TI MSP430 Compiler Tools (Code Composer Studio IDE)

- MSP430 Optimizing C/C++ Compiler: Check the --silicon_errata option
- MSP430 Assembly Language Tools

MSP430 GNU Compiler (MSP430-GCC)

- MSP430 GCC Options: Check -msilicon-errata= and -msilicon-errata-warn= options
- MSP430 GCC User's Guide

IAR Embedded Workbench

IAR workarounds for msp430 hardware issues



5 Nomenclature, Package Symbolization, and Revision Identification

The revision of the device can be identified by the revision letter on the Package Markings or by the HW_ID located inside the TLV structure of the device.

5.1 Device Nomenclature

To designate the stages in the product development cycle, TI assigns prefixes to the part numbers of all MSP MCU devices. Each MSP MCU commercial family member has one of two prefixes: MSP or XMS. These prefixes represent evolutionary stages of product development from engineering prototypes (XMS) through fully qualified production devices (MSP).

XMS - Experimental device that is not necessarily representative of the final device's electrical specifications

MSP - Fully qualified production device

Support tool naming prefixes:

X: Development-support product that has not yet completed Texas Instruments internal qualification testing.

null: Fully-qualified development-support product.

XMS devices and X development-support tools are shipped against the following disclaimer:


"Developmental product is intended for internal evaluation purposes."

MSP devices have been characterized fully, and the quality and reliability of the device have been demonstrated fully. TI's standard warranty applies.


Predictions show that prototype devices (XMS) have a greater failure rate than the standard production devices. TI recommends that these devices not be used in any production system because their expected end-use failure rate still is undefined. Only qualified production devices are to be used.

TI device nomenclature also includes a suffix with the device family name. This suffix indicates the temperature range, package type, and distribution format.

5.2 Package Markings







5.3 Memory-Mapped Hardware Revision (TLV Structure)

This device does not support reading the hardware revision from memory.

Further guidance on how to locate the TLV structure and read out the HW_ID can be found in the device User's Guide.



6 Advisory Descriptions

BCL12	BCL Module
Category	Functional
Function	Switching RSELx or modifying DCOCTL can cause DCO dead time or a complete DCO stop
Description	After switching RSELx bits (located in register BCSCTL1) from a value of >13 to a value of <12 OR from a value of <12 to a value of >13, the resulting clock delivered by the DCO can stop before the new clock frequency is applied. This dead time is approximately 20 us. In some instances, the DCO may completely stop, requiring a power cycle.
	Furthermore, if all of the RSELx bits in the BSCTL1 register are set, modifying the DCOCTL register to change the DCOx or the MODx bits could also result in DCO dead time or DCO hang up.
Workaround	- When switching RSEL from >13 to <12, use an intermediate frequency step. The intermediate RSEL value should be 13.
	Current DSEL Target DSEL Decommonded Transition Sequence

Current RSEL	Target RSEL	Recommended Transition Sequence
15	14	Switch directly to target RSEL
14 or 15	13	Switch directly to target RSEL
14 or 15	0 to 12	Switch to 13 first, and then to target RSEL (two step sequence)
0 to 13	0 to 12	Switch directly to target RSEL

AND

- When switching RSEL from <12 to >13 it's recommended to set RSEL to its default value first (RSEL = 7) before switching to the desired target frequency.

AND

- In case RSEL is at 15 (highest setting) it's recommended to set RSEL to its default value first (RSEL = 7) before accessing DCOCTL to modify the DCOx and MODx bits. After the DCOCTL register modification the RSEL bits can be manipulated in an additional step.

In the majority of cases switching directly to intermediate RSEL steps as described above will prevent the occurrence of BCL12. However, a more reliable method can be implemented by changing the RSEL bits step by step in order to guarantee safe function without any dead time of the DCO.

Note that the 3-step clock startup sequence consisting of clearing DCOCTL, loading the BCSCTL1 target value, and finally loading the DCOCTL target value as suggested in the in the "TLV Structure" chapter of the MSP430x2xx Family User's Guide is not affected by BCL12 if (and only if) it is executed after a device reset (PUC) prior to any other modifications being made to BCSCTL1 since in this case RSEL still is at its default value of 7. However any further changes to the DCOx and MODx bits will require the consideration of the workaround outlined above.

BCL16	BCL Module
Category	Functional
Function	SMCLK clock source selection from XT1/VLO to DCO

Description	When the MCLK and the SMCLK do not use the DCO, the DCO is off. The DCO does not start if the clock source for SMCLK is changed from XT1/VLO to DCO. As a result, the SMCLK remains high. Note: This is only true for SMCLK. The DCO starts if the clock source of MCLK is set to DCO.
Workaround	Set clock source of MCLK to DCO by either:
	1)setting the selection bits SELMx of BCSCTL2 register to '00' or '01'.
	OR
	2)setting the OFIFG bit of IFG1 register. Note: This triggers the oscillator fault logic that automatically starts the DCO. Reset the OFIFG bit to further use the XT1/VLO.
	For both options, if the XT1/VLO is still required to source MCLK, revert the clock source of MCLK back to XT1/VLO afterwards.
CPU19	CPU Module
CPU19 Category	CPU Module Compiler-Fixed
Category	Compiler-Fixed
Category Function	Compiler-Fixed CPUOFF modification may result in unintentional register read If an instruction that modifies the CPUOFF bit in the Status Register is followed by an instruction with an indirect addressed operand (e.g. MOV @R8, R9, RET, POP, POPM), an unintentional register read operation can occur during the wakeup of the CPU. If the unintentional read occurs to a read sensitive register (e.g. UCB0RXBUF, TAIV), which changes its value or the value of other registers (IFG's), the bug leads to lost interrupts or
Category Function Description	Compiler-Fixed CPUOFF modification may result in unintentional register read If an instruction that modifies the CPUOFF bit in the Status Register is followed by an instruction with an indirect addressed operand (e.g. MOV @R8, R9, RET, POP, POPM), an unintentional register read operation can occur during the wakeup of the CPU. If the unintentional read occurs to a read sensitive register (e.g. UCB0RXBUF, TAIV), which changes its value or the value of other registers (IFG's), the bug leads to lost interrupts or wrong register read values.

Refer to the table below for compiler-specific fix implementation information. Note that compilers implementing the fix may lead to double stack usage when RET/ RETA follows the compiler-inserted NOP.

IDE/Compiler	Version Number	Notes
IAR Embedded Workbench	IAR EW430 v6.20.1 until v6.40	User is required to add the compiler or assembler flag option below hw_workaround=nop_after_lpm
IAR Embedded Workbench	IAR EW430 v6.40 or later	Workaround is automatically enabled
TI MSP430 Compiler Tools (Code Composer Studio)	15.12.0.LTS	User is required to add the compiler or assembler flag option below silicon_errata=CPU19
MSP430 GNU Compiler (MSP430- GCC)	MSP430-GCC 4.9 build 389 or later	User is required to add the compiler or assembler flag option below. -msilicon-errata=cpu19 -msilicon- errata-warn=cpu19 generates a warning in addition



IDE/Compiler	Version Number	Notes
MSP430 GNU Compiler (MSP430- GCC)	MSP430-GCC 5.x build 14 or later	User is required to add the compiler or assembler flag option below. -msilicon-errata=cpu19 -msilicon- errata-warn=cpu19 generates a warning in addition

CPU45	CPU Module
Category	Functional
Function	CPU speed performance limitation
Description	The CPU register contents may become unpredictable during CPU register operations if the device operates at minimum Vcc required for system speed performance above 4.15MHz under certain conditions. This is dependent on voltage and CPU clock (MCLK) frequency and duty-cycle.
Workaround	With respect to the system speed performance above 4.15MHz versus minimum required Vcc
	1. Increase Vcc by 200mV for DCO calibrated frequencies when sourced to MCLK OR
	Use internally divided clock for MCLK (BCSCTL2.DIVMx > 00)
	3. Use external clock with 50% positive duty cycle when sourced to MCLK
	OR 4. Reduce LFXT1 (used in HF mode) or external clock frequency by 20% when sourced to MCLK OR
	5. Reduce DCO speed by 20% when DCO is sourced to MCLK
EEM20	EEM Module
Category	Debug
Function	Debugger might clear interrupt flags
Description	During debugging read-sensitive interrupt flags might be cleared as soon as the debugger stops. This is valid in both single-stepping and free run modes.
Workaround	None.
FLASH24	FLASH Module
Category	Functional
Function	Write or erase emergency exit can cause failures
Description	 When a flash write or erase is abruptly terminated, the following flash accesses by the CPU may be unreliable resulting in erroneous code execution. The abrupt termination can be the result of one the following events: 1) The flash controller clock is configured to be sourced by an external crystal. An oscillator fault occurs thus stopping this clock abruptly. or 2) The Emergency Exit bit (EMEX in FCTL3) when set forces a write or an erase

	operation to be terminated before normal completion. or 3) The Enable Emergency Interrupt Exit bit (EEIEX in FCTL1) when set with GIE=1 can lead to an interrupt causing an emergency exit during a Flash operation.
Workaround	1) Use the internal DCO as the flash controller clock provided from MCLK or SMCLK.
	or 2) After setting EMEX = 1, wait for a sufficient amount of time before Flash is accessed again.
	or 3) No Workaround. Do not use EEIEX bit.
FLASH27	FLASH Module
Category	Functional
Function	EEI feature can disrupt segment erase
Description	When a flash segment erase operation is active with EEI feature selected (EEI=1 in FLCTL1) and GIE=0, the following can occur:
	An interrupt event causes the flash erase to be stopped, and the flash controller expects an RETI to resume the erase. Because GIE=0, interrupts are not serviced and RETI will never happen.
Workaround	1) Do not set bit EEI=1 when GIE = 0.
	or, 2) Force an RETI instruction during the erase operation during the check for BUSY=1 (FCLTL3).
	Sample code:
	MOV R5, 0(R5) ; Dummy write, erase segment LOOP: BIT #BUSY, &FCTL3 ; test busy bit JMP SUB_RETI ; Force RETI instruction JNZ LOOP ; loop while BUSY=1
	SUB_RETI: PUSH SR RETI
FLASH36	FLASH Module
Category	Functional
Function	Flash content may degrade due to aborted page erases
Description	If a page erase is aborted by EEIEX, the flash page containing the last instruction before erase operation will start to degrade. This effect is incremental and, after repetitions, may lead to corrupted flash content.
Workaround	- Use the EEI (interrupted erasing) feature instead of EEIEX (abort erasing).
	or - A PSA checksum can be calculated over affected flash page using the marginal read mode (marginal 0). If PSA sum differs from expected PSA value the affected flash page has to be reprogrammed. or
	 Start flash erasing from RAM and limit system frequency to <1MHz (to ensure 6-us delay



after EEIEX). If the last instruction before erasing is located in RAM, flash cell degradation does not occur.

PORT10	PORT Module							
Category	Functional							
Function	Pull-up/down resistor selection when module pin function is selected							
Description	When the pull-up/down resistor for a certain port pin is enabled (PxREN.y=1) and the module port pin function is selected (PxSEL.y=1), the pull-up/down resistor configuration of this pin is controlled by the respective module output signal (Module X OUT) instead of the port output register (PxOUT.y).							
Workaround	None. Do not set PxSEL.y and PxREN.y at the same time.							
SYS15	SYS Module							
Category	Functional							
Function	LPM3 and LPM4 currents exceed specified limits							
Description	LPM3 and LPM4 currents may exceed specified limits if the SMCLK source is switched from DCO to VLO or LFXT1 just before the instruction to enter LPM3 or LPM4 mode.							
Workaround	After clock switching, a delay of at least four new clock cycles (VLO or LFXT1) must be implemented to complete the clock synchronization before going into LPM3 or LPM4.							
TA12	TA Module							
Category	Functional							
Function	Interrupt is lost (slow ACLK)							
Description	Timer_A counter is running with slow clock (external TACLK or ACLK)compared to MCLK. The compare mode is selected for the capture/compare channel and the CCRx register is incremented by one with the occurring compare interrupt (if TAR = CCRx). Due to the fast MCLK the CCRx register increment (CCRx = CCRx+1) happens before the Timer_A counter has incremented again. Therefore the next compare interrupt should happen at once with the next Timer_A counter increment (if TAR = CCRx + 1). This interrupt gets lost.							
Workaround	Switch capture/compare mode to capture mode before the CCRx register increment. Switch back to compare mode afterwards.							
TA16	TA Module							
Category	Functional							
Function	First increment of TAR erroneous when $IDx > 00$							
Description	The first increment of TAR after any timer clear event (POR/TACLR) happens immediately following the first positive edge of the selected clock source (INCLK, SMCLK, ACLK or TACLK). This is independent of the clock input divider settings (ID0, ID1). All following TAR increments are performed correctly with the selected IDx settings.							
Workaround	None							



TA21	TA Module					
Category	Functional					
Function	TAIFG Flag is erroneously set after Timer A restarts in Up Mode					
Description	In Up Mode, the TAIFG flag should only be set when the timer counts from TACCR0 to zero. However, if the Timer A is stopped at TAR = TACCR0, then cleared (TAR=0) by setting the TACLR bit, and finally restarted in Up Mode, the next rising edge of the TACLK will erroneously set the TAIFG flag.					
	Timer Clock Timer Set TAIFG Set TACCR0 CCIFG Set TACCR0 CCIFG Stopped restarted					
Workaround	None.					
TAB22	TAB Module					
Category	Functional					
Function	Timer_A/Timer_B register modification after Watchdog Timer PUC					
Description	Unwanted modification of the Timer_A/Timer_B registers TACTL/TBCTL and TAIV/TBIV can occur when a PUC is generated by the Watchdog Timer(WDT) in Watchdog mode and any Timer_A/Timer_B counter register TACCRx/TBCCRx is incremented/ decremented (Timer_A/Timer_B does not need to be running).					
Workaround	Initialize TACTL/TBCTL register after the reset occurs using a MOV instruction (BIS/BIC may not fully initialize the register). TAIV/TBIV is automatically cleared following this initialization.					
	Example code:					
	MOV.W #VAL, &TACTL					
	or MOV.W #VAL, &TBCTL					
	Where, VAL=0, if Timer is not used in application otherwise, user defined per desired function.					
TB2	TB Module					
Category	Functional					
Function	Interrupt is lost (slow ACLK)					
Description	Timer_B counter is running with slow clock (external TBCLK or ACLK) compared to MCLK. The compare mode is selected for the capture/compare channel and the CCRx register is incremented by 1 with the occurring compare interrupt (if TBR = CCRx). Due to the fast MCLK, the CCRx register increment (CCRx = CCRx + 1) happens before the Timer_B counter has incremented again. Therefore, the next compare interrupt should					



	happen at once with the next Timer_B counter increment (if TBR = CCRx + 1). This interrupt is lost.						
Workaround	Switch capture/compare mode to capture mode before the CCRx register increment. Switch back to compare mode afterward.						
TB16	TB Module						
Category	Functional						
Function	First increment of TBR erroneous when $IDx > 00$						
Description	The first increment of TBR after any timer clear event (POR/TBCLR) happens immediately following the first positive edge of the selected clock source (INCLK, SMCLK, ACLK, or TBCLK). This is independent of the clock input divider settings (ID0, ID1). All following TBR increments are performed correctly with the selected IDx settings.						
Workaround	None						
TB24	TB Module						
Category	Functional						
Function	TBIFG Flag is erroneously set after Timer B restarts in Up Mode						
Description	In Up Mode, the TBIFG flag should only be set when the timer resets from TBCCR0 to zero. However, if the Timer B is stopped at TBR = TBCCR0, then cleared (TBR=0) by setting the TBCLR bit, and finally restarted in Up Mode, the next rising edge of the TBCLK will erroneously set the TBIFG flag.						
	Timer Clock Timer CCR0-1 / SCR0 / 0h / 1h / SS / CCR0-1 / CCR0 / 0h Set TBIFG / SS / CCR0-1 / CCR0 / 0h Set TBIFG / SS /						
Workaround	None.						
USCI20	USCI Module						
Category	Functional						
Function	I2C Mode Multi-master transmitter issue						
Description	When configured for I2C master-transmitter mode, and used in a multi-master environment, the USCI module can cause unpredictable bus behavior if all of the following four conditions are true:						
	1 - Two masters are generating SCL And 2 - The slave is stretching the SCL low phase of an ACK period while outputting NACK on SDA And 3 - The slave drives ACK on SDA after the USCI has already released SCL, and then the						

	SCL bus line gets released And 4 - The transmit buffer has not been loaded before the other master continues communication by driving SCL low					
	The USCI will remain in the SCL high phase until the transmit buffer is written. After the transmit buffer has been written, the USCI will interfere with the current bus activity and may cause unpredictable bus behavior.					
Workaround	1 - Ensure that slave doesn't stretch the SCL low phase of an ACK period Or 2 - Ensure that the transmit buffer is loaded in time Or 3 - Do not use the multi-master transmitter mode					
USCI21	USCI Module					
Category	Functional					
Function	UART IrDA receive filter					
Description	The IrDA receive filter can be used to filter pulses with length UCAIRRXFL configured in UCAXIRRCTL register. If UCIRRXFE is set the IrDA receive decoder may filter out pulses longer than the configured filter length depending on frequency of BRCLK. This is resulting in framing errors or corrupted data on the receiver side.					
Workaround	Depending on the used baud rate and the configured filter length a maximum frequency for BRCLK needs to be set to avoid this issue:					
	For baud rates equal and higher than 115.000 the maximum allowed BRCLK frequency is equal to the max specified system frequency.					
	Filter Length + 64 Baud Rate x 16					

Max BRCLK = $\frac{\text{Filter Length + 64}}{2} \times \frac{\text{Baud Rate \times 16}}{3 \times 10^6}$



Baud Rate	Filter Length UCIRRXFL (dec)	Max BRCLK (MHz)		
	64	3.28		
	32	2.46		
	16	2.05		
9600	8	1.84		
9000	4	1.74		
	2	1.69		
	1	1.66		
	0	1.64		
	64	6.55		
	32	4.92		
	16	4.1		
19200	8	3.69		
19200	4	3.48		
	2	3.38		
	1	3.33		
	0	3.28		
	64	13.11		
	32	9.83		
	16	8.19		
38400	8	7.37		
30400	4	6.96		
	2	6.76		
	1	6.66		
	0	6.55		
	64	19.11		
	32	14.34		
	16	11.95		
56000	8	10.75		
50000	4	10.15		
	2	9.86		
	1	9.71		
	0	9.56		

USCI22	USCI Module							
Category	Functional							
Function	I2C Master Receiver with 10-bit slave addressing							
Description	Unexpected behavior of the USCI_B can occur when configured in I2C master receive mode with 10-bit slave addressing under the following conditions:							
	 The USCI sends first byte of slave address, the slave sends an ACK and when second address byte is sent, the slave sends a NACK. Master sends a repeat start condition (If UCTXSTT=1). The first address byte following the repeated start is acknowledged. 							
	However, the second address byte is not sent, instead the Master incorrectly starts to receive data and sets UCBxRXIFG=1.							
Workaround	Do not use repeated start condition instead set the stop condition UCTXSTP=1 in the NACK ISR prior to the following start condition (USTXSTT=1).							
USCI23	USCI Module							
Category	Functional							
Function	UART transmit mode with automatic baud rate detection							

Description	Erroneous behavior of the USCI_A can occur when configured in UART transmit mode with automatic baud rate detection. During transmission if a "Transmit break" is initiated (UCTXBRK=1), the USCI_A will not deliver a stop bit of logic high, instead, it will send a logic low during the subsequent synch period.							
Workaround	1) Follow User's Guide instructions for transmitting a break/synch field following UCSWRST=1. Or, 2) Set UCTXBRK=1 before an active transmission, i.e. check for bit UCBUSY=0 and then set UCTXBRK=1.							
USCI24	USCI Module							
Category	Functional							
Function	Incorrect baud rate information during UART automatic baud rate detection mode							
Description	Erroneous behavior of the USCI_A can occur when configured in UART mode with automatic baud rate detection. After automatic baud rate measurement is complete, the UART updates UCAxBR0 and UCAxBR1. Under Oversampling mode (UCOS16=1), for baud rates that should result in UCAxBRx=0x0002, the UART incorrectly reports it as UCAxBRx=0x5555.							
Workaround	When break/synch is detected following the automatic baud rate detection, the flag UCBRK flag is set to 1. Check if UCAxBRx=0x5555 and correct it to 0x0002.							
USCI25	USCI Module							
Category	Functional							
Function	TXIFG is not reset when NACK is received in I2C mode							
Description	When the USCI_B module is configured as an I2C master transmitter the TXIFG is not reset after a NACK is received if the master is configured to send a restart (UCTXSTT=1 & UCTXSTP=0).							
Workaround	Reset TXIFG in software within the NACKIFG interrupt service routine							
USCI26	USCI Module							
Category	Functional							
Function	Tbuf parameter violation in I2C multi-master mode							
	The parameter violation in 20 multi-master mode							
Description	In multi-master I2C systems the timing parameter Tbuf (bus free time between a stop condition and the following start) is not guaranteed to match the I2C specification of 4.7us in standard mode and 1.3us in fast mode. If the UCTXSTT bit is set during a running I2C transaction, the USCI module waits and issues the start condition on bus release causing the violation to occur. Note: It is recommended to check if UCBBUSY bit is cleared before setting UCTXSTT=1.							
Description Workaround	In multi-master I2C systems the timing parameter Tbuf (bus free time between a stop condition and the following start) is not guaranteed to match the I2C specification of 4.7us in standard mode and 1.3us in fast mode. If the UCTXSTT bit is set during a running I2C transaction, the USCI module waits and issues the start condition on bus release causing the violation to occur.							
	In multi-master I2C systems the timing parameter Tbuf (bus free time between a stop condition and the following start) is not guaranteed to match the I2C specification of 4.7us in standard mode and 1.3us in fast mode. If the UCTXSTT bit is set during a running I2C transaction, the USCI module waits and issues the start condition on bus release causing the violation to occur. Note: It is recommended to check if UCBBUSY bit is cleared before setting UCTXSTT=1.							



Function	Timing of USCI I2C interrupts may cause device reset due to automatic clear of an IFG.
Description	When certain USCI I2C interrupt flags (IFG) are set and an automatic flag-clearing event on the I2C bus occurs, the program counter may become corrupted. This will only happen when the IFG is cleared within a critical time window (~6 CPU clock cycles) after a USCI interrupt request occurs and before the interrupt servicing is initiated. The affected interrupts are UCBxTXIFG, UCSTPIFG, UCSTTIFG and UCNACKIFG.
	The automatic flag-clearing scenarios are described in the following situations: (1) A pending UCBxTXIFG interrupt request is cleared on the falling SCL clock edge following a NACK. (2) A pending UCSTPIFG, UCSTTIFG, or UCNACKIFG interrupt request is cleared by a following Start condition.
Workaround	 (1) Polling the affected flags instead of enabling the interrupts. or (2) Ensuring the above mentioned flag-clearing events occur after a time delay of 6 CPU clock cycles has elapsed since the interrupt request occurred and was accepted.
USCI30	USCI Module
Category	Functional
Function	I2C mode master receiver / slave receiver
Description	When the USCI I2C module is configured as a receiver (master or slave), it performs a double-buffered receive operation. In a transaction of two bytes, once the first byte is moved from the receive shift register to the receive buffer the byte is acknowledged and the state machine allows the reception of the next byte.
	If the receive buffer has not been cleared of its contents by reading the UCBxRXBUF register while the 7th bit of the following data byte is being received, an error condition may occur on the I2C bus. Depending on the USCI configuration the following may occur:
	 If the USCI is configured as an I2C master receiver, an unintentional repeated start condition can be triggered or the master switches into an idle state (I2C communication aborted). The reception of the current data byte is not successful in this case. If the USCI is configured as I2C slave receiver, the slave can switch to an idle state stalling I2C communication. The reception of the current data byte is not successful in this case. The USCI I2C state machine will notify the master of the aborted reception with a NACK.
	Note that the error condition described above occurs only within a limited window of the 7th bit of the current byte being received. If the receive buffer is read outside of this window (before or after), then the error condition will not occur.
Workaround	a) The error condition can be avoided altogether by servicing the UCBxRXIFG in a timely manner. This can be done by (a) servicing the interrupt and ensuring UCBxRXBUF is read promptly or (b) Using the DMA to automatically read bytes from receive buffer upon UCBxRXIFG being set.
	OR
	b) In case the receive buffer cannot be read out in time, test the I2C clock line before the UCBxRXBUF is read out to ensure that the critical window has elapsed. This is done by checking if the clock line low status indicator bit UCSCLLOW is set for atleast three USCI bit clock cycles i.e. 3 X t(BitClock)

bit clock cycles i.e. 3 X t(BitClock).

Note that the last byte of the transaction must be read directly from UCBxRXBUF. For all other bytes follow the workaround:

Code flow for workaround

(1) Enter RX ISR for reading receiving bytes
(2) Check if UCSCLLOW.UCBxSTAT == 1
(3) If no, repeat step 2 until set
(4) If yes, repeat step 2 for a time period > 3 x t (BitClock) where t (BitClock) = 1/ f
(BitClock)
(5) If window of 3 x t(BitClock) cycles has elapsed, it is safe to read UCBxRXBUF



IFG2 &= ~UCB0TXIFG; // Clear USCI_B0 TX int flag __bic_SR_register_on_exit(CPUOFF); // Exit LPM0 } }

	}						
USCI35	USCI Module						
Category	Functional						
Function	Violation of setup and hold times for (repeated) start in I2C master mode						
Description	In I2C master mode, the setup and hold times for a (repeated) START, $t_{SU,STA}$ and $t_{HD,STA}$ respectively, can be violated if SCL clock frequency is greater than 50kHz in standard mode (100kbps). As a result, a slave can receive incorrect data or the I2C bus can be stalled due to clock stretching by the slave.						
Workaround	If using repeated start, ensure SCL clock frequencies is < 50kHz in I2C standard mode (100 kbps).						
USCI40	USCI Module						
Category	Functional						
Function	SPI Slave Transmit with clock phase select = 1						
Description	In SPI slave mode with clock phase select set to 1 (UCAxCTLW0.UCCKPH=1), after the first TX byte, all following bytes are shifted by one bit with shift direction dependent on UCMSB. This is due to the internal shift register getting pre-loaded asynchronously when writing to the USCIA TXBUF register. TX data in the internal buffer is shifted by one bit after the RX data is received.						
Workaround	Reinitialize TXBUF before using SPI and after each transmission. If transmit data needs to be repeated with the next transmission, then write back previously read value:						
	CRATADOF - CCRATADOF,						
XOSC5	XOSC Module						
Category	Functional						
Function	LF crystal failures may not be properly detected by the oscillator fault circuitry						
Description	The oscillator fault error detection of the LFXT1 oscillator in low frequency mode (XTS = 0) may not work reliably causing a failing crystal to go undetected by the CPU, i.e. OFIFG will not be set.						
Workaround	None						



7 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes	from	October	9,	2019	to	Мау	11,	2021

Changes from October 9, 2019 to May 11, 2021		Page
•	Changed the document format and structure; updated the numbering format for tables, figures, and cro	oss
	references throughout the document	<mark>6</mark>

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated