









SN74HC4851-Q1

SCLS554D - JANUARY 2004 - REVISED JUNE 2024

# SN74HC4851-Q1 Automotive 8-Channel Analog Multiplexer/Demultiplexer With Injection-Current Effect Control

#### 1 Features

- Qualified for automotive applications
- Injection-current cross coupling <1mV/mA (see Section 8.1 in Application Information)
- Low crosstalk between switches
- Terminal compatible with CD74HC4051, SN74LV4051A, and CD4051B devices
- 2V to 5.5V V<sub>CC</sub> operation
- Latch-up performance exceeds 100mA per JESD 78, class II

## 2 Applications

- Analog and digital multiplexing and demultiplexing
- Diagnostics and monitoring
- **Zonal Architecture**
- Body control modules
- Battery management systems (BMS)
- **HVAC** control module
- Automotive head unit
- **Telematics**
- On-board (OBC) and wireless charging

## 3 Description


eight-channel CMOS analog multiplexer/ demultiplexer is terminal compatible with the function of the '4051 device, and features injection-current effect control, which has excellent value in automotive applications where voltages in excess of normal supply voltages are common.

The injection-current effect control allows signals at disabled analog input channels to exceed the supply voltage without affecting the signal of the enabled analog channel. This feature eliminates the need for external diode/resistor networks typically used to keep the analog channel signals within the supply-voltage range.

#### **Package Information**

PART NUMBER	PACKAGE <sup>(1)</sup>	PACKAGE SIZE <sup>(2)</sup>
SN74HC4851-Q1	PW (TSSOP, 16)	5mm × 6.4mm

- For more information, see Section 11 (1)
- (2)The package size (length × width) is a nominal value and includes pins, where applicable.




Logic Diagram (Positive Logic)



## **Table of Contents**

1 Features	1	7.1 Functional Block Diagram	9
2 Applications	1	8 Application and Implementation	10
3 Description		8.1 Application Information	10
4 Pin Configuration and Functions		9 Device and Documentation Support	12
5 Specifications	3	9.1 Receiving Notification of Documentation Updates.	
5.1 Absolute Maximum Ratings	3	9.2 Support Resources	12
5.2 Thermal Information: SN74HC485x-Q1	3		
5.3 Recommended Operating Conditions	4	9.4 Electrostatic Discharge Caution	12
5.4 Electrical Characteristics	5	9.5 Glossary	
5.5 Timing Characteristics	6	10 Revision History	
5.6 Injection Current Coupling	6	11 Mechanical, Packaging, and Orderable	
6 Parameter Measurement Information			12
7 Detailed Description			

# **4 Pin Configuration and Functions**



NC - No internal connection

Figure 4-1. SN74HC4851-Q1 PW Package, 16-Pin TSSOP (Top View)

Inputs On Channel INH С Α Υx L L Y0 Н Y1 Y2 L Н Υ3 Н Y4 Н Y5 Н Н Y6 Н Н Н Υ7 Н Χ Χ Χ None

Table 4-1. Function Table



## **5 Specifications**

## 5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)(1) (2)

		MIN	MAX	UNIT
V <sub>CC</sub>	Supply voltage	-0.5	6	V
V <sub>SEL</sub> or V <sub>EN</sub>	Logic control input pin voltage (EN, A0, A1, A2)	-0.5	V <sub>CC</sub> +0.5V	V
V <sub>S</sub> or V <sub>D</sub>	Source or drain voltage (Sx, D)	-0.5	V <sub>CC</sub> +0.5V	V
I <sub>IK</sub>	Input clamp current (V <sub>I</sub> < 0 or V <sub>I</sub> > V <sub>CC</sub> )	-20	20	mA
I <sub>IOK</sub>	I/O diode current (V <sub>IO</sub> < 0 or V <sub>IO</sub> > V <sub>CC</sub> )	-20	20	mA
I <sub>T</sub>	Switch through current (V <sub>IO</sub> = 0 to V <sub>CC</sub> )	-25	25	mA
I <sub>GND</sub>	Continuous current through V <sub>CC</sub> or GND	-50	50	mA
T <sub>stg</sub>	Storage temperature	-65	150	°C
TJ	Junction temperature		150	J

<sup>(1)</sup> Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute maximum ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If briefly operating outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not sustain damage, but it may not be fully functional. Operating the device in this manner may affect device reliability, functionality, performance, and shorten the device lifetime.

(2) The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

### 5.2 Thermal Information: SN74HC485x-Q1

		SN74HC485x-Q1	
	THERMAL METRIC(1)	PW (TSSOP)	UNIT
		PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	139.6	°C/W

 For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.



## **5.3 Recommended Operating Conditions**

over operating free-air temperature range (unless otherwise noted)

	.gg. (		MIN NOM	MAX	UNIT	
V <sub>CC</sub>	Supply voltage		2	5.5	V	
		2V	1.5			
		2.5V	2.1			
$V_{IH}$	Input logic high	3.3V	2.3		V	
		4.5V	3.15			
		5.5V	4.2			
		2V	0	0.5		
$V_{IL}$		2.5V	0	0.7	V	
	Input logic low	3.3V	0	8.0		
		4.5V	0	0.95		
		5.5V	0	1.05		
V <sub>SEL</sub> or V <sub>EN</sub>	Logic control input pin voltage (EN, A0, A1, A2)		0	V <sub>CC</sub>	V	
V <sub>S</sub> or V <sub>D</sub>	Signal path input/output voltage (source or drain pin) (Sx, D)		0	V <sub>CC</sub>	V	
		V <sub>CC</sub> = 2V		1000		
		V <sub>CC</sub> = 3V		800		
Δt/Δv	Input transition rise or fall time	V <sub>CC</sub> = 3.3V		700	ns	
		V <sub>CC</sub> = 4.5V		500		
	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$		400			
T <sub>A</sub>	Ambient temperature		-40	125	°C	



## **5.4 Electrical Characteristics**

At specified  $V_{CC} \pm 10\%$ 

Typical values measured at nominal  $V_{\text{CC}}$ .

				Operating free-air temperature (T <sub>A</sub> )									
PA	RAMETER	TEST CONDITIONS	Vcc	25°C		–40°	°C to 85	°C	–40°	C to 12	5°C	UNIT	
				MIN TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX		
			2V	500	650			670			700		
D	On-state switch	$V_S = 0V \text{ to } V_{CC}$	3V	215	280			320			360	Ω	
R <sub>ON</sub>	resistance	$I_{SD} = 0.5 \text{mA}$	3.3V	210	270			305			345	1 12	
			4.5V	160	210			240			270		
	On-state		2V	4	13			18			23		
	switch resistance	$V_S = V_{CC} / 2$	3V	2	10			12			16		
$\Delta_{RON}$	matching	$I_{SD} = 0.5 \text{mA}$	3.3V	2	9			12			16	Ω	
	between inputs		4.5V	2	9			12			16		
l <sub>l</sub>	Control input current	V <sub>I</sub> = V <sub>CC</sub> or GND	5V		±0.1			±0.1			±1	μA	
one channel  Off-state switch leakage current (common	switch	Switch Off			±0.1			±0.5			±1	μА	
	switch leakage current	$V_{\text{INH}} = V_{\text{IH}}$ $V_{\text{D}} = V_{\text{CC}} / \text{GND}$ $V_{\text{S}} = \text{GND} / V_{\text{CC}}$	5V		±0.2			±2			±4	μА	
I <sub>S(ON)</sub>	Channel on- state leakage current	Switch Off $V_{INH}=V_{IL}$ $V_{D}=V_{CC} / GND$ $V_{S}=GND / V_{CC}$	5V		±0.1			±0.5			±1	μA	
I <sub>DD</sub>	V <sub>CC</sub> supply current	Logic inputs = 0V or V <sub>CC</sub>	5V		2			20			40	μA	
C <sub>IC</sub>	Control input capacitance	A, B, C, INH		3.5	10			10			10	pF	
C <sub>IS</sub>	Common terminal capacitance	Switch off		22	40			40			40	pF	
C <sub>OS</sub>	Switch terminal capacitance	Switch off		6.7	15			15			15	pF	
	Power	No Load	3.3V	32									
$C_{PD}$	Dissipation Capacitance	$t_r = t_f = 1$ ns f = 1MHz	5V	37								pF	



## 5.5 Timing Characteristics

At specified  $V_{CC}\,\pm 10\%$ 

Typical values measured at nominal V<sub>CC</sub>.

				Operating free-air temperature (T <sub>A</sub> )										
	PARAMETER	TEST CONDITIONS	V <sub>CC</sub>	25°C			-40°	C to 8	5°C	-40°	C to 12	5°C	UNIT	
				MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX		
SWITCH	HING CHARACTERIST	TCS <sup>(1)</sup>				•								
			2V		19.5	30			34			37		
	Dranagation dalay	C <sub>L</sub> = 50pF	3V		12	17.5			19.5			21.5		
t <sub>PD</sub>	Propagation delay	Sx to D, D to Sx	3.3V		11	16.5			18.5			20.5	ns	
			5.5V		8.6	14			15			16		
	Transition-time between inputs	$R_L = 10k\Omega$ , $C_L = 50pF$ Ax to D, Ax to Sx	2V		44	94			103			103		
			3V		30	63			67			67		
t <sub>TRAN</sub>			3.3V		23	51			54			54	ns	
			5.5V		18	43			46			46	1	
			2V			95			105			115		
	Turnon-time from	$R_L = 10k\Omega$ , $C_L = 50pF$	3V			90			100			110		
t <sub>ON(EN)</sub>	enable	EN to D, EN to Sx	3.3V			85			95			105	ns	
			5V			80			90			100		
			2V			95			105			115		
	Turnoff time from	$R_L = 10k\Omega$ , $C_L = 50pF$	3V	90		90	100				110			
t <sub>OFF(EN)</sub>	enable	EN to D, EN to Sx	3.3V			85			95			105	ns	
			5.5V			80			90			100		

<sup>(1)</sup>  $t_{PLH}/t_{PHL} = t_{PD}$  propagation delay time,  $t_{PZH}/t_{PZL} = t_{ON(EN)}$  enable delay time,  $t_{PHZ}/t_{PLZ} = t_{OFF(EN)}$  disable delay time,  $t_{PLH}/t_{PHL}$  Channel select =  $t_{TRAN}$ 

## 5.6 Injection Current Coupling

At specified  $V_{CC} \pm 10\%$ 

Typical values measured at nominal  $V_{CC}$  and  $T_A = 25$ °C.

	PARAMETER	V	TEST CO	NDITIONS	-40°C		UNIT	
	PARAMETER	V <sub>CC</sub>	V <sub>CC</sub> TEST CONDITIONS			TYP	MAX	UNII
INJECTION	N CURRENT COUPLING							
		3.3V		I < 1mA		0.05	1	
		5V	$R_S \le 3.9 k\Omega$	I <sub>INJ</sub> ≤ 1mA		0.1	1	
		3.3V		I <sub>INJ</sub> ≤ 10mA		0.345	5	
۸۱/	Maximum shift of output voltage	5V				0.067	5	mV
ΔV <sub>OUT</sub>	of enabled analog input <sup>(1)</sup>	3.3V		I <sub>INJ</sub> ≤ 1mA		0.05	2	IIIV
		5V	B < 2010	I <sub>INJ</sub> = IIIIA		0.11	2	
		3.3V	R <sub>S</sub> ≤ 20kΩ	1 40··· A		0.05	20	
		5V	1	I <sub>INJ</sub> ≤ 10mA		0.024	20	

(1)  $I_{INJ}$  = total current injected into all disabled channels



## **6 Parameter Measurement Information**




Figure 6-1. On-State-Resistance Test Circuit




Figure 6-2. Maximum Off-Channel Leakage Current, Any One Channel, Test Setup




Figure 6-3. Maximum Off-Channel Leakage Current, Common Channel, Test Setup




Figure 6-4. Maximum On-Channel Leakage Current, Channel To Channel, Test Setup






Figure 6-5. Propagation Delays, Channel Select to Analog Out



† Includes all probe and jig capacitance

Figure 6-6. Propagation-Delay Test Setup, Channel Select to Analog Out



† Includes all probe and jig capacitance

Figure 6-8. Propagation-Delay Test Setup, Analog In to Analog Out




Figure 6-9. Propagation Delays, Enable to Analog Out




Figure 6-10. Propagation-Delay Test Setup, Enable to Analog Out




Figure 6-11. Power-Dissipation Capacitance Test Setup



## 7 Detailed Description

## 7.1 Functional Block Diagram




Figure 7-1. Logic Diagram (Positive Logic)



## 8 Application and Implementation

#### **Note**

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

## 8.1 Application Information




Figure 8-1. Injection-Current Coupling Specification




Figure 8-2. Alternate Solution Requires 32 Passive Components and One Extra 6-V Regulator to Suppress Injection Current Into a Standard 'HC4051 Multiplexer

Product Folder Links: SN74HC4851-Q1






Figure 8-3. Solution by Applying the 'HC4851 Multiplexer




Figure 8-4. Diagram of Bipolar Coupling Mechanism (Appears if  $V_{\text{IN}}$  Exceeds  $V_{\text{CC}}$ , Driving Injection Current Into the Substrate)



## 9 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

#### 9.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

#### 9.2 Support Resources

TI E2E<sup>™</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 9.3 Trademarks

TI E2E<sup>™</sup> is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

## 9.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 9.5 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.

### **10 Revision History**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

С	hanges from Revision C (October 2012) to Revision D (June 2024)	Page
•	Updated the numbering format for tables, figures, and cross-references throughout the document	1
•	Changed VCC ABS Max from 7V to 6V	3
•	Changed RθJA	3
•	Recommended supply changed from 6V to 5.5V and all test conditions using 6V were removed	4
•	Changed ttran, tON, tOFF parameters	6
	-	

## 11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical packaging and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser based versions of this data sheet, refer to the left hand navigation.

Product Folder Links: SN74HC4851-Q1

www.ti.com 1-May-2024

#### PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
							(6)				
SN74HC4851QDRG4Q1	NRND	SOIC	D	16	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	HC4851Q	
SN74HC4851QDRQ1	NRND	SOIC	D	16	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	HC4851Q	
SN74HC4851QPWRG4Q1	NRND	TSSOP	PW	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	HC4851Q	
SN74HC4851QPWRQ1	ACTIVE	TSSOP	PW	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	HC4851Q	Samples

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

## **PACKAGE OPTION ADDENDUM**

www.ti.com 1-May-2024

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF SN74HC4851-Q1:

Catalog: SN74HC4851

NOTE: Qualified Version Definitions:

Catalog - Tl's standard catalog product

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 10-Jan-2024

## TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74HC4851QPWRG4Q1	TSSOP	PW	16	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
SN74HC4851QPWRQ1	TSSOP	PW	16	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1

www.ti.com 10-Jan-2024



### \*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74HC4851QPWRG4Q1	TSSOP	PW	16	2000	367.0	367.0	35.0
SN74HC4851QPWRQ1	TSSOP	PW	16	2000	356.0	356.0	35.0

# D (R-PDS0-G16)

## PLASTIC SMALL OUTLINE



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AC.





SMALL OUTLINE PACKAGE



#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153.



SMALL OUTLINE PACKAGE



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated