

# SN751177, SN751178 Dual Differential Drivers and Receivers

## 1 Features

- Meet or exceed the requirements of ANSI standards TIA/EIA-422-B and TIA/EIA-485-A and ITU recommendations V.10 and V.11
- Designed for multipoint bus transmission on long bus lines in noise environments
- Driver positive- and negative-current limiting
- Thermal shutdown protection
- Driver 3-state outputs
- Receiver common-mode input voltage range of  $-12\text{V}$  to  $12\text{V}$
- Receiver input sensitivity:  $\pm 200\text{mV}$
- Receiver hysteresis:  $50\text{mV}$  typical
- Receiver input impedance:  $12\text{ k}\Omega$  minimum
- Receiver 3-state outputs (SN751177 only)
- Operate from single  $5\text{V}$  supply

## 2 Applications

- [Motor Drives](#)
- [Factory Automation](#)
- [Building Automation](#)

## 3 Description

The SN751177 and SN751178 dual differential drivers and receivers are monolithic integrated circuits that are designed for balanced multipoint bus transmission at rates up to 10 Mbits. The devices are designed to improve the performance of full-duplex data communications over long bus lines and meet ANSI Standards TIA/EIA-422-B and TIA/EIA-485-A and ITU Recommendations V.10 and V.11.

The SN751177 and SN751178 driver outputs provide limiting for both positive and negative currents and thermal-shutdown protection from line-fault conditions on the transmission bus line.

The receiver features high input impedance of at least  $12\text{ k}\Omega$ , an input sensitivity of  $\pm 200\text{mV}$  over a common-mode input voltage range of  $-12\text{V}$  to  $12\text{V}$ , and typical input hysteresis of  $50\text{mV}$ . Fail-safe design makes sure the receiver inputs are open, the receiver outputs are always high.



The SN751177 and SN751178 are characterized for operation from  $-20^\circ\text{C}$  to  $85^\circ\text{C}$ .

### Package Information

PART NUMBER	PACKAGE <sup>(1)</sup>	PACKAGE SIZE <sup>(2)</sup>
SN751177	PDIP (N, 16)	19.3mm × 9.4mm
SN751178	SO (NS, 16)	10.2mm × 7.8mm

(1) For more information, see [Section 10](#).

(2) The package size (length × width) is a nominal value and includes pins, where applicable.




<sup>†</sup> These symbols are in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.



## Table of Contents


<b>1 Features</b> .....	1	7.1 Device Functional Modes.....	11
<b>2 Applications</b> .....	1	<b>8 Device and Documentation Support</b> .....	13
<b>3 Description</b> .....	1	8.1 Documentation Support.....	13
<b>4 Pin Configuration and Functions</b> .....	3	8.2 Receiving Notification of Documentation Updates....	13
<b>5 Specifications</b> .....	5	8.3 Support Resources.....	13
5.1 Absolute Maximum Ratings.....	5	8.4 Trademarks.....	13
5.2 Thermal Information.....	5	8.5 Electrostatic Discharge Caution.....	13
5.3 Recommended Operating Conditions.....	5	8.6 Glossary.....	13
5.4 Driver Sections.....	6	<b>9 Revision History</b> .....	13
5.5 Receiver Sections.....	7	<b>10 Mechanical, Packaging, and Orderable Information</b> .....	13
<b>6 Parameter Measurement Information</b> .....	8		
<b>7 Detailed Description</b> .....	11		

## 4 Pin Configuration and Functions



**Figure 4-1. SN751177: N or NS Package  
(Top View)**

NAME	PIN		TYPE	DESCRIPTION
	PDIP	SO		
1A	2	2	I	RS422 differential input (non-inverting) to receiver 1
2A	6	6	I	RS422 differential input (non-inverting) to receiver 2
1B	1	1	I	RS422 differential input (inverting) to receiver 1
2B	7	7	I	RS422 differential input (inverting) to receiver 2
1D	15	15	I	Logic data input to RS422 driver 1
2D	9	9	I	Logic data input to RS422 driver 2
DE	12	12	I	Driver enable (active high)
GND	8	8	—	Device ground pin
1R	3	3	O	Logic data output of RS422 receiver 1
2R	5	5	O	Logic data output of RS422 receiver 2
RE	4	4	I	Receiver enable pin (active low)
V <sub>CC</sub>	16	16	—	Power supply
1Y	14	14	O	RS-422 differential (non-inverting) driver output 1
2Y	10	10	O	RS-422 differential (non-inverting) driver output 2
1Z	13	13	O	RS-422 differential (inverting) driver output 1
2Z	11	11	O	RS-422 differential (inverting) driver output 2



**Figure 4-2. SN751178: N or NS Package (Top View)**

NAME	PIN		TYPE	DESCRIPTION
	PDIP	SO		
1A	2	2	I	RS422 differential input (non-inverting) to receiver 1
2A	6	6	I	RS422 differential input (non-inverting) to receiver 2
1B	1	1	I	RS422 differential input (inverting) to receiver 1
2B	7	7	I	RS422 differential input (inverting) to receiver 2
1D	15	15	I	Logic data input to RS422 driver 1
2D	9	9	I	Logic data input to RS422 driver 2
1DE	4	4	I	Driver 1 enable (active high)
2DE	12	12	I	Driver 2 enable (active high)
GND	8	8	—	Device ground
1R	3	3	O	Logic data output of RS422 receiver 1
2R	5	5	O	Logic data output of RS422 receiver 2
V <sub>CC</sub>	16	16	—	Power supply
1Y	14	14	O	RS-422 differential (non-inverting) driver output 1
2Y	10	10	O	RS-422 differential (non-inverting) driver output 2
1Z	13	13	O	RS-422 differential (non inverting) driver output 1
2Z	11	11	O	RS-422 differential (non inverting) driver output 2

## 5 Specifications

### 5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

		MIN	MAX	UNIT
V <sub>CC</sub>	Supply voltage, (see note <sup>(2)</sup> )		7	V
V <sub>I</sub>	Input voltage, (DE, $\overline{RE}$ , and D inputs)		7	V
V <sub>I</sub>	Receiver input voltage range, (A or B inputs)	-25	25	V
V <sub>ID</sub>	Receiver differential input voltage range, (see note <sup>(3)</sup> )	-25	25	V
V <sub>O</sub>	Driver output voltage range	-10	15	V
I <sub>OL</sub>	Receiver low-level output current		50	mA
T <sub>stg</sub>	Storage temperature range	-65	150	°C
	Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds		260	°C

- (1) Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) All voltage values, except differential input voltage, are with respect to the network ground terminal.
- (3) Differential input voltage is measured at the noninverting terminal with respect to the inverting terminal.

### 5.2 Thermal Information

THERMAL METRIC <sup>(1)</sup>		N	NS	UNIT
		16-PINS	16-PINS	
R <sub>θJA</sub>	Junction-to-ambient thermal resistance <sup>(2)</sup>	60.6	88.5	°C/W
R <sub>θJC(top)</sub>	Junction-to-case (top) thermal resistance	48.1	46.2	°C/W
R <sub>θJB</sub>	Junction-to-board thermal resistance	40.6	50.7	°C/W
Ψ <sub>JT</sub>	Junction-to-top characterization parameter	27.5	13.5	°C/W
Ψ <sub>JB</sub>	Junction-to-board characterization parameter	40.3	50.3	°C/W
R <sub>θJC(bot)</sub>	Junction-to-case (bottom) thermal resistance	N/A	N/A	°C/W

- (1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC package thermal metrics](#) application report.
- (2) The package thermal impedance is calculated in accordance with JEDEC 51, except for through-hole packages, which use a trace length of zero.

### 5.3 Recommended Operating Conditions

		MIN	NOM	MAX	UNIT
Supply voltage, V <sub>CC</sub>		4.75	5	5.25	V
High-level input voltage, V <sub>IH</sub>	DE, $\overline{RE}$ , and D inputs	2			V
Low-level input voltage, V <sub>IL</sub>				0.8	V
Common-mode output voltage, V <sub>OC</sub>	Driver	-7 <sup>(1)</sup>		12	V
High-level output current, I <sub>OH</sub>				-60	mA
Low-level output current, I <sub>OL</sub>				60	mA
Common-mode input voltage, V <sub>IC</sub>				±12	V
Differential input voltage, V <sub>ID</sub>	Receiver			±12	V
High-level output current, I <sub>OH</sub>				-400	μA
Low-level output current, I <sub>OL</sub>				16	mA
Operating free-air temperature, T <sub>A</sub>			-20		85

- (1) The algebraic convention, where the less positive (more negative) limit is designated as minimum, is used in this data sheet for common-mode output and threshold voltage levels only.

## 5.4 Driver Sections

### 5.4.1 Electrical Characteristics

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

PARAMETER		TEST CONDITIONS			MIN	TYP <sup>(1)</sup>	MAX	UNIT
$V_{IK}$	Input clamp voltage	$I_I = -18\text{mA}$					-1.5	V
$V_{OH}$	High-level output voltage	$V_{IH} = 2\text{V}$ ,	$V_{IL} = 0.8\text{V}$ ,	$I_{OH} = -33\text{mA}$		3.7		V
$V_{OL}$	Low-level output voltage	$V_{IH} = 2\text{V}$ ,	$V_{IL} = 0.8\text{V}$ ,	$I_{OH} = 33\text{mA}$		1.1		V
$ V_{OD1} $	Differential output voltage	$I_O = 0$			1.5		6	V
$ V_{OD2} $	Differential output voltage	$R_L = 100\Omega$ ,	See <a href="#">Figure 6-1</a>		2 or 1/2 $V_{OD1}$ <sup>(2)</sup>			V
		$R_L = 54\Omega$ ,	See <a href="#">Figure 6-1</a>		1.5		5	
$V_{OD3}$	Differential output voltage	See <a href="#">Note 4</a>			1.5		5	V
$\Delta V_{OD} $	Change in magnitude of differential output voltage (see <a href="#">Note 5</a> )						$\pm 0.2$	V
$V_{OC}$	Common-mode output voltage	$R_L = 54\Omega$ or $100\Omega$ ,		See <a href="#">Figure 6-1</a>	-1 <sup>(3)</sup>		3	V
$\Delta V_{OC} $	Change in magnitude of common-mode output voltage (see <a href="#">Note 5</a> )						$\pm 0.2$	V
$I_O$	Output current with power off	$V_{CC} = 0$ ,		$V_O = -7\text{V}$ to $12\text{V}$			$\pm 100$	$\mu\text{A}$
$I_{OZ}$	High-impedance-state output current	$V_O = -7\text{V}$ to $12\text{V}$					$\pm 100$	$\mu\text{A}$
$I_{IH}$	High-level input current	$V_{IH} = 2.7\text{V}$					20	$\mu\text{A}$
$I_{IL}$	Low-level input current	$V_{IL} = 0.4\text{V}$					-100	$\mu\text{A}$
		$V_O = -7\text{V}$					-250	
$I_{OS}$	Short-circuit output current (see <a href="#">Note 6</a> )	$V_O = V_{CC}$					250	mA
		$V_O = 12\text{V}$					250	
$I_{CC}$	Supply current	No load	Outputs enabled			80	110	mA
			Outputs disabled			50	80	

(1) All typical values are at  $V_{CC} = 5\text{V}$  and  $T_A = 25^\circ\text{C}$ .

(2) The minimum  $V_{OD2}$  with a  $100\Omega$  load is either  $1/2 V_{OD1}$  or  $2\text{V}$ , whichever is greater.

(3) The algebraic convention, where the less positive (more negative) limit is designated as minimum, is used in this data sheet for common-mode output and threshold voltage levels only.

(4) See TIA/EIA-485-A [Figure 6-3.5](#), Test Termination Measurement 2

(5)  $\Delta|V_{OD}|$  and  $\Delta|V_{OC}|$  are the changes in magnitude of  $V_{OD}$  and  $V_{OC}$ , respectively, that occur when the input is changed from a high level to a low level.

(6) Not more than one output should be shorted at a time, and the duration of the short circuit should not exceed one second.

### 5.4.2 Switching Characteristics

at  $V_{CC} = 5\text{V}$ ,  $C_L = 50\text{pF}$ ,  $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		MIN	TYP	MAX	UNIT
$t_{d(OD)}$	Differential output delay time	$R_L = 54\Omega$ ,	See <a href="#">Figure 6-3</a>		20	25	ns
$t_{t(OD)}$	Differential output transition time				27	35	ns
$t_{PLH}$	Propagation delay time, low- to high-level output	$R_L = 27\Omega$ ,	See <a href="#">Figure 6-4</a>		20	25	ns
$t_{PHL}$	Propagation delay time, high- to low-level output				20	25	ns
$t_{PZH}$	Output enable time to high level	$R_L = 110\Omega$ ,	See <a href="#">Figure 6-5</a>		80	120	ns
$t_{PZL}$	Output enable time to low level	$R_L = 110\Omega$ ,	See <a href="#">Figure 6-6</a>		40	60	ns
$t_{PHZ}$	Output disable time from high level	$R_L = 110\Omega$ ,	See <a href="#">Figure 6-5</a>		90	120	ns
$t_{PLZ}$	Output disable time from low level	$R_L = 110\Omega$ ,	See <a href="#">Figure 6-6</a>		30	45	ns

### 5.4.3 Symbol Equivalents

DATA-SHEET PARAMETER	TIA/EIA-422-B	TIA/EIA-485-A
$ V_{OD1} $	$V_O$	$V_O$
$ V_{OD2} $	$V_t (R_L = 100\Omega)$	$V_t (R_L = 54\Omega)$
$ V_{OD3} $		$V_t$ (Test Termination Measurement 2)
$\Delta V_{OD} $	$  V_t  -  \bar{V}_t  $	$  V_t  -  \bar{V}_t  $
$V_{OC}$	$ V_{OS} $	$ V_{OS} $
$\Delta V_{OC} $	$ V_{OS} - \bar{V}_{OS} $	$ V_{OS} - \bar{V}_{OS} $
$I_{OS}$	$ I_{sa} ,  I_{sb} $	
$I_O$	$ I_{xa} ,  I_{xb} $	$I_{ia}, I_{ib}$

## 5.5 Receiver Sections

### 5.5.1 Electrical Characteristics

over recommended ranges of common-mode input voltage, supply voltage, and operating free-air temperature (unless otherwise noted)

PARAMETER			TEST CONDITIONS		MIN	TYP <sup>(1)</sup>	MAX	UNIT
$V_{IT+}$	Positive-going input threshold voltage		$V_O = 2.7V,$	$I_O = -0.4mA$			0.2	V
$V_{IT-}$	Negative-going input threshold voltage		$V_O = 0.5V,$	$I_O = 16mA$	-0.2 <sup>(2)</sup>			V
$V_{hys}$	Input hysteresis voltage ( $V_{IT+} - V_{IT-}$ )					50		mV
$V_{IK}$	Enable clamp voltage	SN751177	$I_I = -18mA$				-1.5	V
$V_{OH}$	High-level output voltage		$V_{ID} = 200mV,$	$I_{OH} = -400\mu A$	2.7			V
$V_{OL}$	Low-level output voltage		$V_{ID} = -200mV$	$I_{OL} = 8mA$			0.45	V
				$I_{OL} = 16mA$			0.5	
$I_{OZ}$	High-impedance-state output current	SN751177	$V_O = 0.4V$ to $2.4V$				$\pm 20$	$\mu A$
$I_I$	Line input current (see Note 7)		Other input at 0V	$V_I = 12V$			1	mA
				$V_I = -7V$			-0.8	
$I_{IH}$	High-level enable input current	SN751177	$V_{IH} = 2.7V$				20	$\mu A$
$I_{IL}$	Low-level enable input current	SN751177	$V_{IL} = 0.4V$				-100	$\mu A$
$I_{OS}$	Short-circuit output current (see Note 6)				-15		-85	$\mu A$
$I_{CC}$	Supply current		No load,	outputs enabled		80	110	mA
$r_i$	Input resistance				12			k $\Omega$

(1) All typical values are at  $V_{CC} = 5V$  and  $T_A = 25^\circ C$ .

(2) The algebraic convention, where the less positive (more negative) limit is designated as minimum, is used in this data sheet for common-mode output and threshold voltage levels only.

(3) Not more than one output should be shorted at a time, and the duration of the short circuit should not exceed one second.

(4) Refer to ANSI Standards TIA/EIA-422-B, TIA/EIA-423-A, and TIA/EIA-485-A for exact conditions.

### 5.5.2 Switching Characteristics

at  $V_{CC} = 5V, C_L = 15pF, T_A = 25^\circ C$

PARAMETER			TEST CONDITIONS		MIN	TYP	MAX	UNIT
$t_{PLH}$	Propagation delay time, low- to high-level output		$V_{ID} = -1.5V$ to $1.5V,$	See Figure 6-7		20	35	ns
$t_{PHL}$	Propagation delay time, high- to low-level output					22	35	ns
$t_{PZH}$	Output enable time to high level	SN751177	See Figure 6-8			17	25	ns
$t_{PZL}$	Output enable time to low level					20	27	ns
$t_{PHZ}$	Output disable time from high level					25	40	ns
$t_{PLZ}$	Output disable time from low level					30	40	ns

## 6 Parameter Measurement Information




Figure 6-1. Driver Test Circuit,  $v_{OD}$  And  $v_{OC}$






Figure 6-2. Receiver Test Circuit,  $v_{OH}$  And  $v_{OL}$




TEST CIRCUIT




VOLTAGE WAVEFORMS

- A.  $C_L$  includes probe and jig capacitance.
- B. The pulse generator has the following characteristics:  $PRR \leq 1\text{MHz}$ , 50% duty cycle,  $Z_O = 50\Omega$ ,  $t_r \leq 6\text{ns}$ ,  $t_f \leq 6\text{ns}$ .

Figure 6-3. Driver Differential Output-Delay and Transition-Time Test Circuit and Voltage Waveforms



TEST CIRCUIT




VOLTAGE WAVEFORMS


- A.  $C_L$  includes probe and jig capacitance.
- B. The pulse generator has the following characteristics:  $PRR \leq 1\text{MHz}$ , 50% duty cycle,  $Z_O = 50\Omega$ ,  $t_r \leq 6\text{ns}$ ,  $t_f \leq 6\text{ns}$ .

Figure 6-4. Driver Propagation-Time Test Circuit and Voltage Waveforms






TEST CIRCUIT




VOLTAGE WAVEFORMS

- A.  $C_L$  includes probe and jig capacitance.
- B. The pulse generator has the following characteristics:  $PRR \leq 1\text{MHz}$ , 50% duty cycle,  $Z_O = 50\Omega$ ,  $t_r \leq 6\text{ns}$ ,  $t_f \leq 6\text{ns}$ .

Figure 6-5. Driver Enable- and Disable-Time Test Circuit and Voltage Waveforms




TEST CIRCUIT




VOLTAGE WAVEFORMS

- A.  $C_L$  includes probe and jig capacitance.
- B. The pulse generator has the following characteristics:  $PRR \leq 1\text{MHz}$ , 50% duty cycle,  $Z_O = 50\Omega$ ,  $t_r \leq 6\text{ns}$ ,  $t_f \leq 6\text{ns}$ .

Figure 6-6. Driver Enable- and Disable-Time Test Circuit and Voltage Waveforms



TEST CIRCUIT




VOLTAGE WAVEFORMS

- A.  $C_L$  includes probe and jig capacitance.
- B. The pulse generator has the following characteristics:  $PRR \leq 1\text{MHz}$ , 50% duty cycle,  $Z_O = 50\Omega$ ,  $t_r \leq 6\text{ns}$ ,  $t_f \leq 6\text{ns}$ .


Figure 6-7. Receiver Propagation-Time Test Circuit and Voltage Waveforms

SN751177, SN751178

SLLS059E – FEBRUARY 1990 – REVISED FEBRUARY 2024



TEST CIRCUIT



VOLTAGE WAVEFORMS

- A.  $C_L$  includes probe and jig capacitance.
- B. The pulse generator has the following characteristics:  $\text{PRR} \leq 1\text{MHz}$ , 50% duty cycle,  $Z_O = 50\Omega$ ,  $t_r \leq 6\text{ns}$ ,  $t_f \leq 6\text{ns}$ .

Figure 6-8. Receiver Output Enable- and Disable-Time Test Circuit and Voltage Waveforms

## 7 Detailed Description

### 7.1 Device Functional Modes

Table 7-1. SN751177, SN751178 Functional Table (Each Driver)

INPUT D <sup>(1)</sup>	ENABLE DE	OUTPUTS	
		Y	Z
H	H	H	L
L	H	L	H
X	L	Z	Z

(1) H = high level, L = low level, X = irrelevant, Z = high impedance (off)

Table 7-2. SN751177 Functional Table (Each Receiver)


DIFFERENTIAL INPUTS A – B	ENABLE RE	OUTPUT R <sup>(1)</sup>
$V_{ID} \geq 0.2V$	L	H
$-0.2V < V_{ID} < 0.2V$	L	?
$V_{ID} \leq -0.2V$	L	L
X	H	Z
Open	L	H

(1) H = high level, L = low level, ? = indeterminate, X = irrelevant, Z = high impedance (off)

Table 7-3. SN751178 Functional Table (Each Receiver)


DIFFERENTIAL INPUTS A – B	OUTPUT R <sup>(1)</sup>
$V_{ID} \geq 0.2V$	H
$-0.2V < V_{ID} < 0.2V$	?
$V_{ID} \leq -0.2V$	L

(1) H = high level, L = low level, ? = indeterminate



A. All resistor values are nominal.

Figure 7-1. Schematics of Inputs



A. All resistor values are nominal.

**Figure 7-2. Schematics of Outputs**

## 8 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

### 8.1 Documentation Support

### 8.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](http://ti.com). Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 8.3 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 8.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.  
All trademarks are the property of their respective owners.

### 8.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 8.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 9 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision D (May 1999) to Revision E (February 2024)	Page
• Changed the numbering format for tables, figures, and cross-references throughout the document.....	1

## 10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

**PACKAGING INFORMATION**

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
SN751177N	ACTIVE	PDIP	N	16	25	RoHS & Green	NIPDAU	N / A for Pkg Type	-20 to 85	SN751177N	<a href="#">Samples</a>
SN751177NSR	ACTIVE	SO	NS	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-20 to 85	SN751177	<a href="#">Samples</a>
SN751177NSRE4	ACTIVE	SO	NS	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-20 to 85	SN751177	<a href="#">Samples</a>
SN751178N	ACTIVE	PDIP	N	16	25	RoHS & Green	NIPDAU	N / A for Pkg Type	-20 to 85	SN751178N	<a href="#">Samples</a>
SN751178NSR	ACTIVE	SO	NS	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-20 to 85	SN751178	<a href="#">Samples</a>

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBsolete:** TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

**Green:** TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**TAPE AND REEL INFORMATION**

**QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE**


\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN751177NSR	SO	NS	16	2000	330.0	16.4	8.2	10.5	2.5	12.0	16.0	Q1
SN751178NSR	SO	NS	16	2000	330.0	16.4	8.45	10.55	2.5	12.0	16.2	Q1



**TAPE AND REEL BOX DIMENSIONS**



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN751177NSR	SO	NS	16	2000	356.0	356.0	35.0
SN751178NSR	SO	NS	16	2000	356.0	356.0	35.0

**TUBE**


\*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (μm)	B (mm)
SN751177N	N	PDIP	16	25	506	13.97	11230	4.32
SN751177N	N	PDIP	16	25	506	13.97	11230	4.32
SN751178N	N	PDIP	16	25	506	13.97	11230	4.32
SN751178N	N	PDIP	16	25	506	13.97	11230	4.32




# PACKAGE OUTLINE

## NS0016A

### SOP - 2.00 mm max height

SOP



4220735/A 12/2021

#### NOTES:



- All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- This drawing is subject to change without notice.
- This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
- This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.

# EXAMPLE BOARD LAYOUT

NS0016A

SOP - 2.00 mm max height

SOP



SOLDER MASK DETAILS

4220735/A 12/2021

NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.


6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

NS0016A

SOP - 2.00 mm max height

SOP



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:7X

4220735/A 12/2021

NOTES: (continued)


7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

## MECHANICAL DATA

**NS (R-PDSO-G\*\*)**

**PLASTIC SMALL-OUTLINE PACKAGE**

**14-PINS SHOWN**




- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

N (R-PDIP-T\*\*)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
  - The 20 pin end lead shoulder width is a vendor option, either half or full width.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2024, Texas Instruments Incorporated