







SCHS026E - NOVEMBER 1998 - REVISED AUGUST 2024

**CD4016B** 

# **CD4016B Types CMOS Quad Bilateral Switch**

#### 1 Features

- 20V digital or ± 10V peak-to-peak switching
- 280Ω typical on-state resistance for 15V operation
- Switch on-state resistance matched to within  $10\Omega$ typ over 15V signal-input range
- High on/off output-voltage ratio: 65dB typ at  $f_{is} = 10kHz$ ,  $R_L = 10k\Omega$
- High degree of linearity: <0.5% distortion typ at f  $_{is}$ = 1kHz, V  $_{is}$ = 5V $_{p-p}$ , V  $_{DD}$  -V  $_{SS}$   $\square$  10V, R  $_{L}$  =  $10k\Omega$
- Extremely low off-state switch leakage resulting in very low offset current and high effective offstate resistance: 100pA typ. at V <sub>DD</sub> -V <sub>SS</sub> =18V,  $T_A=25^{\circ}C$
- Extremely high control input impedance (control circuit isolated from signal circuit: 10  $^{12}\,\Omega$  typ.
- Low crosstalk between switches: -50dB typ at f is = 0.9MHz,  $R_{\perp} = 1k\Omega$
- Matched control-input to signal-output capacitance: Reduces output signal transients
- Frequency response, switch on = 40MHz (typical)
- 100% tested for guiescent current at 20V
- Maximum control input current of 1µA at 18V over full package temperature range; 100nA at 18V at 25°C
- 5V, 10V, and 15V parametric ratings

#### 2 Applications

- Analog signal switching/multiplexing signal gating
- Modulator squelch control
- Demodulator chopper
- Commutating switch
- Digital signal switching/multiplexing
- CMOS logic implementation
- Analog-to-digital and digital-to-analog conversion
- Digital control of frequency, impedance, phase, and analog-signal gain

#### 3 Description

For transmission or multiplexing of analog or digital signals high-voltage types (20V rating).

CD4016B B Series types are quad bilateral switches intended for the transmission or multiplexing of analog or digital signals. Each of the four independent bilateral switches has a single control signal input which simultaneously biases both the p and n device in a given switch on or off.

The CD4016B B Series types are supplied in 14lead hermetic dual-in-line ceramic packages (F3A suffix), 14-lead dual-in-line plastic packages (E suffix), 14-lead small-outline packages (M, MT, M96, and NSR suffixes), and 14-lead thin shrink small-outline packages (PW and PWR suffixes).


#### **Package Information**


PART NUMBER	N (PDIP, 14) 19.3mm × 9.4		
CD4016B	N (PDIP, 14)	19.3mm × 9.4mm	
CD4010B	D (SOIC, 14)	8.65mm × 6mm	

- For more information, see Section 8.
- The package size (length × width) is a nominal value and includes pins, where applicable.



# Terminal Assignment





Schematic Diagram - 1 of 4 Identical Sections



# **Table of Contents**

1 Features1	4.5 Electrical Characteristics5
2 Applications1	
3 Description1	
4 Specifications4	
	6 Device and Documentation Support13
<u> </u>	6.1 Documentation Support13
	7 Revision History13
	8 Mechanical, Packaging, and Orderable Information 13

# 4 Specifications

### 4.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)(1) (2)

, J	,	MIN	MAX	UNIT
V <sub>DD</sub> – V <sub>SS</sub>			20	V
$V_{DD}$	Supply voltage	-0.5	20	V
V <sub>SS</sub>		-20	0.5	V
I <sub>SEL</sub> or I <sub>EN</sub>	Logic control input pin current (EN, Ax, SELx)	-30	30	mA
V <sub>S</sub> or V <sub>D</sub>	Source or drain voltage (Sx, D)	V <sub>SS</sub> -0.5	V <sub>DD</sub> +0.5	V
I <sub>S</sub> or I <sub>D (CONT)</sub>	Source or drain continuous current (Sx, D)	-20	20	mA
TJ	Junction temperature		150	°C
T <sub>stg</sub>	Storage temperature	-65	150	°C

<sup>(1)</sup> Stresses beyond those listed under Absolute Maximum Rating may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Condition. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

# 4.2 ESD Ratings

			VALUE	UNIT
V	Floatrostatic discharge	Human body model (HBM), per ANSI/ESDA/ JEDEC JS-001, all pins <sup>(1)</sup>	±500	
V(ESD)	Electrostatic discharge	Charged device model (CDM), per JEDEC specification JESD22-C101, all pins <sup>(2)</sup>	±1500	V

<sup>(1)</sup> JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

#### 4.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM MAX	UNIT
V <sub>DD</sub> – V <sub>SS</sub> (1)	Power supply voltage differential	3	18	V
$V_{DD}$	Positive power supply voltage	3	18	V
V <sub>S</sub> or V <sub>D</sub>	Signal path input/output voltage (source or drain pin) (Sx, D)	V <sub>SS</sub>	$V_{DD}$	V
V <sub>SEL</sub> or V <sub>EN</sub>	Address or enable pin voltage	0	$V_{DD}$	V
I <sub>S</sub> or I <sub>D (CONT)</sub>	Source or drain continuous current (Sx, D)	-10	10	mA
T <sub>A</sub>	Ambient temperature	<b>–</b> 55	125	°C

(1)  $V_{DD}$  and  $V_{SS}$  can be any value as long as  $3V \le (V_{DD} - V_{SS}) \le 24V$ , and the minimum  $V_{DD}$  is met.

<sup>(2)</sup> All voltages are with respect to ground, unless otherwise specified.

<sup>(2)</sup> JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

### 4.4 Thermal Information

		CD4	CD4016				
	THERMAL METRIC <sup>(1)</sup>	N (PDIP)	D (SOIC)	UNIT			
		14 PINS	14 PINS				
R <sub>θJA</sub>	Junction-to-ambient thermal resistance	93.7	109.7	°C/W			
R <sub>0JC(top)</sub>	Junction-to-case (top) thermal resistance	72.5	69.4	°C/W			
R <sub>0JB</sub>	Junction-to-board thermal resistance	68.0	67.9	°C/W			
$\Psi_{JT}$	Junction-to-top characterization parameter	50.3	25.8	°C/W			
$\Psi_{JB}$	Junction-to-board characterization parameter	67.3	67.1	°C/W			

<sup>(1)</sup> For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

# 4.5 Electrical Characteristics

Over operating free-air temperature range,  $V_{SUPPLY} = \pm 5V$ , and  $R_1 = 100\Omega$ , (unless otherwise noted)<sup>(1)</sup>

	PARAMETER		TEST CONDITIONS	MIN TYP MAX	UNIT
SIGNAL	. INPUTS (V <sub>IS</sub> ) AND OUTPUTS (V	'os)			•
			T <sub>A</sub> = -55°C	5	
			T <sub>A</sub> = -40°C	5	
	$V_{is} = 0 \text{ to } 5V$ $V_{DD} = 5V$	T <sub>A</sub> = 25°C	4.5 6	1	
		TOD ST	T <sub>A</sub> = 85°C	7.5	1
		T <sub>A</sub> = 125°C	7.5	1	
		T <sub>A</sub> = -55°C	6	1	
		T <sub>A</sub> = -40°C	6	1	
	$V_{is} = 0 \text{ to } 10V$ $V_{DD} = 10V$	T <sub>A</sub> = 25°C	5 7	]	
	TOD 101	T <sub>A</sub> = 85°C	15	1	
	Quiescent Device Current		T <sub>A</sub> = 125°C	15	
DD			T <sub>A</sub> = -55°C	7	μA
			T <sub>A</sub> = -40°C	7.2	
		$V_{is} = 0 \text{ to } 15V$ $V_{DD} = 15V$	T <sub>A</sub> = 25°C	6 8	]
		TOD 101	T <sub>A</sub> = 85°C	30	1
			T <sub>A</sub> = 125°C	30	
			T <sub>A</sub> = -55°C	8.5	
		T <sub>A</sub> = -40°C	8.5		
	$V_{is} = 0 \text{ to } 20V$ $V_{DD} = 20V$	T <sub>A</sub> = 25°C	6.5 9		
		100 201	T <sub>A</sub> = 85°C	150	]
			T <sub>A</sub> = 125°C	150	]

Copyright © 2024 Texas Instruments Incorporated

Submit Document Feedback



# 4.5 Electrical Characteristics (continued)

Over operating free-air temperature range,  $V_{SUPPLY} = \pm 5V$ , and  $R_L = 100\Omega$ , (unless otherwise noted)<sup>(1)</sup>

	PARAMETER		TEST CO	ONDITIONS		MIN TY	P MAX	UNIT	
				T <sub>A</sub> = -55°C			600		
			V <sub>DD</sub> = 10V	T <sub>A</sub> = -40°C			610		
			$V_{is} = V_{SS}$ or	T <sub>A</sub> = 25°C		25	0 660		
			$V_{DD}$	T <sub>A</sub> = 85°C			840		
				T <sub>A</sub> = 125°C			960		
				T <sub>A</sub> = -55°C			1870		
			V <sub>DD</sub> = 10V	T <sub>A</sub> = -40°C			1900		
			$V_{is} = 4.75 \text{ to}$	T <sub>A</sub> = 25°C		,	2000		
		to (V <sub>DD</sub> +V <sub>SS</sub> )/2 ,	5.75V	T <sub>A</sub> = 85°C			2380		
	ON Business and Man			T <sub>A</sub> = 125°C			2600		
r <sub>ON</sub>	ON Resistance r <sub>ON</sub> Max	$V_C = V_{DD}$		T <sub>A</sub> = -55°C			360	Ω	
		$RL = 10k\Omega$	V <sub>DD</sub> = 15V	T <sub>A</sub> = -40°C			370		
			$V_{is} = V_{SS}$ or	T <sub>A</sub> = 25°C		20	0 400		
		V	$V_{DD}$	T <sub>A</sub> = 85°C			520		
				T <sub>A</sub> = 125°C			600		
				T <sub>A</sub> = -55°C			775		
			V <sub>DD</sub> = 15V V <sub>is</sub> = 7.25 to	T <sub>A</sub> = -40°C			790		
				T <sub>A</sub> = 25°C			850		
			7.75V	T <sub>A</sub> = 85°C			1080		
				T <sub>A</sub> = 125°C			1230		
	to (V <sub>DD</sub> +V <sub>SS</sub> )/2			$V_{DD} = 5V$ $V_{SS} = 0V$ $T_{A} = 25^{\circ}C$		58	0 7000		
rau		$V_{DD} = 7.5V$ $V_{SS} = -7.5V$	T <sub>A</sub> = 25°C		20	0 280	Ω		
r <sub>ON</sub>	ON Resistance ION Max	ance $r_{ON}$ Max $V_C = V_{DD}$ , $RL = 10k\Omega$	$V_C = V_{DD},$ RL = $10k\Omega$	$V_{DD} = 5V$ $V_{SS} = -5V$	T <sub>A</sub> = 25°C		25	0 580	
			$V_{DD} = 2.5V$ $V_{SS} = -2.5V$	T <sub>A</sub> = 25°C		52	0 30000		
	On the house is here a life and the	D 401-0	$V_{DD} = 5V$			1	5		
$\Delta R_{ON}$	On-state resistance difference between any two switches	$R_L = 10k\Omega$ , $V_C = V_{DD}$	V <sub>DD</sub> = 10V			1	0	Ω	
	,	0 00	V <sub>DD</sub> = 15V				5		
THD	Total Harmonic Distortion	$V_C = V_{DD} = 5V_{DD}$ on 0V), $R_L = 1$	$V_{SS} = -5V, V_{is}$ 0kΩ, $f_{is} = 1$ kHz	s <sub>(p-p)</sub> = 5V (sine v sine wave	wave centered	0.	4	%	
BW	-3-dB cutoff frequency (switch on)	$V_{C} = V_{DD} = 5V_{DD}$ on 0V), $R_{L} = 1$		s(p-p) = 5V (sine v	wave centered	4	0	MHz	
OISO	-50-dB feedthrough frequency (switch off)	$V_C = V_{DD} = 5V_{DD}$ on 0V), $R_L = 1$	$V_{SS} = -5V, V_{is}$ k $\Omega$	s(p-p) = 5V (sine v	wave centered	1.2	5	MHz	
				T <sub>A</sub> = -55°C		-0.1	0.1		
		V <sub>DD</sub> = 18V		T <sub>A</sub> = -40°C		-0.1	0.1		
is	Input/Output Leakage Current V	$V_C = 0V$ $V_{is} = 18V, V_{os}$	= 0V	T <sub>A</sub> = 25°C		0.00	0 0.1	μA	
		$V_{is} = 0V, V_{os} =$		T <sub>A</sub> = 85°C		-1	1		
				T <sub>A</sub> = 125°C		-1	1		
XTALK	-50-dB crosstalk frequency	$V_{\rm C} = V_{\rm DD} = 5V_{\rm DD}$ on 0V), $R_{\rm L} = 1$		s(p-p) = 5V (sine v	wave centered	0.		MHz	



# 4.5 Electrical Characteristics (continued)

Over operating free-air temperature range,  $V_{SUPPLY} = \pm 5V$ , and  $R_L = 100\Omega$ , (unless otherwise noted)<sup>(1)</sup>

	PARAMETER		TEST C	ONDITIONS	MIN	TYP	MAX	UNIT
		$V_C = V_{DD}, V_{SS}$	V <sub>DD</sub> = 5V			40	100	
		= GND V <sub>IS</sub> = Square	V <sub>DD</sub> = 10V			20	40	
t <sub>pd</sub>	Propagation delay	Wave 0 to $V_{DD}$ , $C_L = 50$ pF, $R_L = 200$ k $\Omega$	Wave 0 to V <sub>DD</sub> , C <sub>L</sub> = 50pF, R <sub>L</sub> =			15	30	ns
C <sub>IS</sub>	Input capacitance	V <sub>DD</sub> = 5V, VC =	V <sub>SS</sub> = -5V			4		pF
Cos	Output capacitance	V <sub>DD</sub> = 5V, VC =	= V <sub>SS</sub> = -5V			4		pF
C <sub>IOS</sub>	Feed through	V <sub>DD</sub> = 5V, VC =	= V <sub>SS</sub> = -5V			0.2		pF
				T <sub>A</sub> = -55°C			0.9	
		$ I_{is}  < 10\mu A,$ $V_{is} = V_{SS}, V_{OS}$	V = 5V	T <sub>A</sub> = -40°C			0.9	
$V_{ILC}$	Control input, low voltage (ma	$= V_{DD}$ , and $V_{is}$	$V_{DD} = 10V$	T <sub>A</sub> = 25°C			0.7	V
		$= V_{DD}, V_{OS} = V_{SS}$	V <sub>DD</sub> = 15V	T <sub>A</sub> = 85°C			0.4	
		VSS		T <sub>A</sub> = 125°C			0.4	
			V <sub>DD</sub> = 5V		3.5			V
$V_{IHC}$	Control input, high voltage	See Figure 10	V <sub>DD</sub> = 10V V <sub>DD</sub> = 15V		7			V
					11			V
I <sub>IH</sub>	Input High Lekaage		V <sub>DD</sub> = 18V			0.5	1	μA
I <sub>IL</sub>	Input Low Leakage		V <sub>DD</sub> = 18V		-1	-0.1		μA
	Crosstalk (control input to sign output)	$\begin{array}{c} V_C = 10V\\ \text{(square}\\ \text{wave), } t_r \text{, } t_f = \\ 20\text{ns, } R_L = \\ 10\text{k}\Omega  V_{DD} = \\ 10V \end{array}$	V <sub>DD</sub> = 10V			50		mV
		$t_{r}$ , $t_{f} = 20 \text{ns}$	V <sub>DD</sub> = 5V			35	70	ns
	Turn-on propagation delay	$C_{L} = 50pF,$	V <sub>DD</sub> = 10V			20	40	ns
		$R_L = 1k\Omega$	V <sub>DD</sub> = 15V			15	30	ns
	Maximum control input repetit rate	$\begin{aligned} & V_{IN} = V_{DD},  C_L \\ &= 50pF,  R_L = \\ & 1k\Omega \\ & V_C = 10V \\ & (square wave \\ & centered on \\ & 5V),  t_r,  t_f = \\ & 20ns,  V_{os} = \\ & 1/2V_{os}  at \\ & 1kHz \end{aligned}$	V <sub>DD</sub> = 10V			10		MHz
C <sub>IN</sub>	Input Capacitance		1			5	7.5	pF

Copyright © 2024 Texas Instruments Incorporated

Submit Document Feedback



# 4.5 Electrical Characteristics (continued)

Over operating free-air temperature range,  $V_{SUPPLY} = \pm 5V$ , and  $R_L = 100\Omega$ , (unless otherwise noted)<sup>(1)</sup>

	PARAMETER		TEST CONDITIONS	MIN TYP MAX	UNIT
			T <sub>A</sub> = -55°C	0.25	
			T <sub>A</sub> = -40°C	0.2	
		$V_{DD} = 5V$ $V_{is} = 0V$	T <sub>A</sub> = 25°C	0.2	mA
		V IS	T <sub>A</sub> = 85°C	0.12	
			T <sub>A</sub> = 125°C	0.14	
			T <sub>A</sub> = -55°C	-0.25	
			T <sub>A</sub> = -40°C	-0.2	
		$V_{DD} = 5V$ $V_{is} = 5V$	T <sub>A</sub> = 25°C	-0.2	mA
		VIS OV	T <sub>A</sub> = 85°C	-0.12	
			T <sub>A</sub> = 125°C	-0.14	
			T <sub>A</sub> = -55°C	0.62	
			T <sub>A</sub> = -40°C	0.5	
		$V_{DD} = 10V$ $V_{is} = 0V$	T <sub>A</sub> = 25°C	0.5	mA
		v <sub>is</sub> – 0 v	T <sub>A</sub> = 85°C	0.3	
	Cwitch input current		T <sub>A</sub> = 125°C	0.35	
I <sub>IS</sub>	Switch input current		T <sub>A</sub> = -55°C	-0.62	
			T <sub>A</sub> = -40°C	-0.5	
		$V_{DD} = 10V$ $V_{is} = 10V$	T <sub>A</sub> = 25°C	-0.5	mA
		V IS TO V	T <sub>A</sub> = 85°C	-0.3	
			T <sub>A</sub> = 125°C	-0.35	
			T <sub>A</sub> = -55°C	1.8	
			T <sub>A</sub> = -40°C	1.4	
		$V_{DD} = 15V$ $V_{is} = 0V$	T <sub>A</sub> = 25°C	1.5	mA
		VIS OV	T <sub>A</sub> = 85°C	1	
			T <sub>A</sub> = 125°C	1.1	
			T <sub>A</sub> = -55°C	-1.8	
			T <sub>A</sub> = -40°C	-1.4	
		$V_{DD} = 15V$ $V_{is} = 15V$	T <sub>A</sub> = 25°C	-1.5	mA
		T <sub>IS</sub>	T <sub>A</sub> = 85°C	-1	
			T <sub>A</sub> = 125°C	-1.1	
		$V_{DD} = 5V$ $V_{is} = 0V$		0.4	V
		V <sub>DD</sub> = 5V V <sub>is</sub> = 5V		4.6	V
\ <i>/</i>	Switch output valtees	V <sub>DD</sub> = 10V V <sub>is</sub> = 0V		0.5	V
V <sub>OS</sub>	Switch output voltage	V <sub>DD</sub> = 10V V <sub>is</sub> = 10V		9.5	V
		$V_{DD} = 15V$ $V_{is} = 0V$		1.5	٧
		V <sub>DD</sub> = 15V V <sub>is</sub> = 15V		13.5	V

<sup>(1)</sup> Peak-to-Peak voltage symmetrical about  $(V_{DD}-V_{EE})$  / 2.



# **4.6 Electrical Characteristics**

		TEST CONDIT	IONS		LIMITS AT INDICATED TEMPERATURES (°C)						
CHARACTERISTIC			V 00	V 00					+	+25	
			V <sub>IN</sub> (V)	V <sub>DD</sub> (V)	-55	-40	+85	+125	TYP	MAX	1
			0,5	5	025	0.25	7.5	7.5	0.01	0.25	
Quiescent Device			0,10	10	0.5	0.5	15	15	0.01	0.5	],, <u>,</u>
Current, I <sub>DD</sub>			0,15	15	1	1	30	30	0.01	1	μA
			0,20	20	5	5	150	150	0.02	5	
Signal Inputs (V <sub>is</sub> ) and (	Output (V <sub>os</sub> )							•			
	V <sub>C</sub> =V <sub>DD</sub>	V <sub>is</sub> =V <sub>DD</sub> or V <sub>SS</sub>		10	600	610	840	960	-	660	
On-State	R <sub>L</sub> =10kΩ Returned to	V <sub>is</sub> =4.75 to 5.75V		10	1870	1900	2380	2600	-	2000	Ω
Resistance, r <sub>on</sub> MAX	V <sub>DD</sub> -V <sub>SS</sub>	$V_{is}$ = $V_{DD}$ or $V_{SS}$		15	360	370	520	600	-	400	32
	2	V <sub>is</sub> =7.25 to 7.75V		15	775	790	1080	1230	-	850	
ΔOn-State				5	-	-	-	-	15	-	
Resistance Between	$R_L=10k\Omega$ , $V_C=V_{DD}$			10	-	-	-	-	10	-	Ω
Any 2 Switches, Δr <sub>on</sub>				15	-	-	-	-	5	-	
Total Harmonic	$V_C = V_{DD} = 5V$ , $V_{SS} = -5V$ , $V_{is(p-p)} = 5V$ (Sine wave centered of			on 0V) R <sub>L</sub> = 10kΩ,		_	_	_	0.4		%
Distortion, THD	f <sub>is</sub> = 1kHz sine wave								0.4		70
-3dB Cutoff Frequency (Switch on)	$V_C$ = $V_{DD}$ =5 $V$ , $V_{SS}$ =-5 $V$ , $V_{is(p-p)}$ (Sine wave centered on 0 $V$ ) F			R <sub>L</sub> =1kΩ,	-	-	-	-	40	-	MHz
-50dB Feed-through Frequency (Switch off)	$V_C=V_{SS}=-5V$ , $V_{is(p-p)}=5V$ (Sine wave centered on 0V) $R_L=1$			1 lkΩ	-	-	-	-	1.25	-	MHz
Input/Output	V <sub>C</sub> = 0V										
Leakage Current	$V_{is} = 18V, V_{OS} = 0V;$			18	±0.1	±0.1	±1	±1	10-4	±0.1	μΑ
(Switch off) I <sub>is</sub> MAX	V <sub>is</sub> = 0V, V <sub>OS</sub> = 18V										
-50dB Crosstalk Frequency	$V_{C}(A) = V_{DD} = +5V, V_{C}(I)$	$= +5V$ , $V_{C}(B) = V_{SS} = -5V$ , $V_{is}(A) = 5V_{p-p}$ , $50\Omega$									
	source				_	-	-	-	0.9	-	MHz
	R <sub>L</sub> = 1kΩ										
	R <sub>L</sub> = 200kΩ			5	_	-	_	-	40	100	
Propagation	$V_C = V_{DD}, V_{SS} = GND,$	C <sub>L</sub> = 50pF		10	-	-	-	-	20	40	
Delay (Signal Input to	V <sub>is</sub> = Square Wave 0 to	$V_{DD}$		1-					4-		ns
Signal Output) t <sub>pd</sub>	t <sub>r</sub> , t <sub>f</sub> = 20ns			15	_	-	-	-	15	30	
Capacitance:					_	-	_	-	4	_	
Input, C <sub>is</sub> Output, C <sub>OS</sub>	V <sub>DD</sub> = +5V				_	-	_	-	4	-	pF
Feed-through, C <sub>ios</sub>	V <sub>C</sub> =V <sub>SS</sub> =-5V				_	_	_	_	0.2	_	
Control (V <sub>C</sub> )											
Control Input Low	I <sub>is</sub>  < 10 μΑ								Π		
Voltage, V <sub>ILC</sub> (MAX)	$V_{is} = V_{SS}, V_{OS} = V_{DD}$ ar	and $V_{is} = V_{DD}$ , $V_{OS} = V_{DD}$	$V_{SS}$	5,10, 15	0.9	0.9	0.4	0.4	-	0.7	V
	10 00 00 00	55. 66		5					3	3.5 (Min.)	
Control Input High	See Figure 4-8			10						7 (Min.)	-
Voltage, V <sub>IHC</sub>	Soot igure 10			15						11 (Min.)	1
	Input Current, I <sub>IN</sub> (MAX	Via∏ VDD							Т		
Input Current, I <sub>IN</sub>	$V_{DD} - V_{SS} = 18V$	7 - IS — - DD		18	±0.1	±0.1	±1	±1	±10 <sup>-5</sup>	±0.1	μA
(MAX)	V <sub>CC</sub> □ V <sub>DD</sub> - V <sub>SS</sub>			-							ļ
V <sub>C</sub> = 10V (Sq. Wave)											
Crosstalk (Control	$t_r, t_f = 20 \text{ns}$			10	_	_	_	_	50	_	mV
Input to Signal Output)	$R_L = 10k\Omega$			<del>-</del>							
	Turn-On Propagation D	elav t <sub>r</sub> . t <sub>f</sub> = 20ns		5	_	-	_	_	35	70	
Turn-On Propagation	C <sub>L</sub> = 50pF	-, -, -, -0110		10	_	-	_	_	20	40	ns
Delay	$C_L = \text{SUPF}$ $R_L = 1 \text{k}\Omega$		15	_	-	-	+	15	30	<b>∤</b>	



#### 4.6 Electrical Characteristics (continued)

CHARACTERISTIC	TEST CONDITIONS			LIMITS AT INDICATED TEMPERATURES (°C)						
		V 00	V 00					+25		UNITS
		V <sub>IN</sub> (V)	V <sub>DD</sub> (V)	-55	-40	+85	+125	TYP	MAX	
Repetition Rate	Maximum Control Input Repetition Rate $V_{is} = V_{DD} < V_{SS} = GND, \ R_L = 1 k\Omega \ to \ GND, \ C_L = 10V(Square wave centered on 5V)$ $t_r, \ t_f = 20ns, \ V_{OS} = 1/2 \ V_{OS} \ at \ 1 kHz$	= 50pF, V <sub>C</sub> =	10	-	-	-	_	10	-	MHz
Input Capacitance, C <sub>IN</sub>				-	-	-	_	5	7.5	μF

### 4.7 Typical Characteristics




Figure 4-1. System Settling Time vs Signal Rise/Fall Time




Figure 4-2. System Settling Time vs Signal Voltage




Figure 4-3. System Settling Time vs Signal Voltage





Figure 4-4. On-state Characteristics for 1 of 4 Switches with vDD = +15V,  $v_{SS}$  = 0V.



=+10V,  $v_{SS} = 0V$ .





Figure 4-5. On-state Characteristics for 1 of 4 Switches with v<sub>DD</sub> | Figure 4-6. On-state Characteristics for 1 of 4 Switches with v<sub>DD</sub> = +7.5V,  $v_{SS} = -7.5V$ .

# 4.7 Typical Characteristics (continued)



#### **5 Parameter Measurement Information**




Figure 5-1. Off-state Switch Input or Output Leakage Current Test Circuit.




Figure 5-3. Propagation Delay Time Signal Input (v<sub>IS</sub>) To Signal Output (v<sub>OS</sub>)




Figure 5-2. Test Circuit for Square-wave Response.




Figure 5-4. MAX Control-input Repetition Rate.






Figure 5-5. Switch Threshold Voltage.




Figure 5-6. Turn-On Propagation Delay-control Input.

# 6 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

### **6.1 Documentation Support**

#### 6.1.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

#### 6.1.2 Support Resources

TI E2E™ support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 6.1.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

#### 6.1.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

#### 6.1.5 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.

#### 7 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision D (May 2024) to Revision E (August 2024)	Page
Added Settling Time plots	10
Changes from Revision C (September 2003) to Revision D (May 2024)	Page
Increased IDD max/typ for the lower Temperature cases	5
Changed typical IIH to 0.5µA	5
Changed typical IIL to -0.1µA	

### 8 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Copyright © 2024 Texas Instruments Incorporated

www.ti.com 20-Aug-2024

#### PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
							(6)				
5962-9064001CA	ACTIVE	CDIP	J	14	25	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	5962-9064001CA CD4016BF3A	Samples
CD4016BE	ACTIVE	PDIP	N	14	25	RoHS & Green	NIPDAU	N / A for Pkg Type	-55 to 125	CD4016BE	Samples
CD4016BEE4	ACTIVE	PDIP	N	14	25	RoHS & Green	NIPDAU	N / A for Pkg Type	-55 to 125	CD4016BE	Samples
CD4016BF	ACTIVE	CDIP	J	14	25	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	CD4016BF	Samples
CD4016BF3A	ACTIVE	CDIP	J	14	25	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	5962-9064001CA CD4016BF3A	Samples
CD4016BM	OBSOLETE	SOIC	D	14		TBD	Call TI	Call TI	-55 to 125	CD4016BM	
CD4016BM96	ACTIVE	SOIC	D	14	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	CD4016BM	Samples
CD4016BMT	OBSOLETE	SOIC	D	14		TBD	Call TI	Call TI	-55 to 125	CD4016BM	
CD4016BNSR	NRND	SO	NS	14	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	CD4016B	
CD4016BPW	NRND	TSSOP	PW	14	90	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM016B	
CD4016BPWR	NRND	TSSOP	PW	14	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM016B	

<sup>(1)</sup> The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

**Green:** TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

# PACKAGE OPTION ADDENDUM

www.ti.com 20-Aug-2024

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF CD4016B, CD4016B-MIL:

Catalog : CD4016B

Military: CD4016B-MIL

NOTE: Qualified Version Definitions:

Catalog - TI's standard catalog product

• Military - QML certified for Military and Defense Applications

### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated