

SLVSDJ3D -FEBRUARY 2017-REVISED MARCH 2022

DRV832x 6 to 60-V Three-Phase Smart Gate Driver

1 Features

Texas

INSTRUMENTS

- Triple Half-Bridge Gate Driver
 - Drives 3 High-Side and 3 Low-Side N-Channel MOSFETs (NMOS)
- Smart Gate Drive Architecture
 - Adjustable Slew Rate Control
 - 10-mA to 1-A Peak Source Current
 - 20-mA to 2-A Peak Sink Current
 - Integrated Gate Driver Power Supplies
 - Supports 100% PWM Duty Cycle
 - High-Side Charge Pump
 - Low-Side Linear Regulator
- 6 to 60-V Operating Voltage Range
- Optional Integrated Buck Regulator
 - LMR16006X SIMPLE SWITCHER®
 - 4 to 60-V Operating Voltage Range
 - 0.8 to 60-V, 600-mA Output Capability
- Optional Integrated Triple Current Sense Amplifiers (CSAs)
 - Adjustable Gain (5, 10, 20, 40 V/V)
 - Bidirectional or Unidirectional Support
- SPI and Hardware Interface Available
- 6x, 3x, 1x, and Independent PWM Modes
- Supports 1.8-V, 3.3-V, and 5-V Logic Inputs
- Low-Power Sleep Mode (12 μA)
- Linear Voltage Regulator, 3.3 V, 30 mA
- Compact QFN Packages and Footprints
- Efficient System Design With Power Blocks
- Integrated Protection Features
 - VM Undervoltage Lockout (UVLO)
 - Charge Pump Undervoltage (CPUV)
 - MOSFET Overcurrent Protection (OCP)
 - Gate Driver Fault (GDF)
 - Thermal Warning and Shutdown (OTW/OTSD)
 - Fault Condition Indicator (nFAULT)

2 Applications

- Brushless-DC (BLDC) Motor Modules and PMSM
- Fans, Pumps, and Servo Drives
- E-Bikes, E-Scooters, and E-Mobility
- Cordless Garden and Power Tools, Lawnmowers
- Cordless Vacuum Cleaners
- Drones, Robotics, and RC Toys
- Industrial and Logistics Robots

3 Description

The DRV832x family of devices is an integrated gate driver for three-phase applications. The devices provide three half-bridge gate drivers, each capable of driving high-side and low-side N-channel power MOSFETs. The DRV832x generates the correct gate drive voltages using an integrated charge pump for the high-side MOSFETs and a linear regulator for the low-side MOSFETs. The Smart Gate Drive architecture supports peak gate drive currents up to 1-A source and 2-A. The DRV832x can operate from a single power supply and supports a wide input supply range of 6 to 60 V for the gate driver and 4 to 60 V for the optional buck regulator.


The 6x, 3x, 1x, and independent input PWM modes allow for simple interfacing to controller circuits. The configuration settings for the gate driver and device are highly configurable through the SPI or hardware (H/W) interface. The DRV8323 and DRV8323R devices integrate three low-side current sense amplifiers that allow bidirectional current sensing on all three phases of the drive stage. The DRV8320R and DRV8323R devices integrate a 600-mA buck regulator.

A low-power sleep mode is provided to achieve low quiescent current draw by shutting down most of the internal circuitry. Internal protection functions are provided for undervoltage lockout, charge pump fault, MOSFET overcurrent, MOSFET short circuit, gate driver fault, and overtemperature. Fault conditions are indicated on the nFAULT pin with details through the device registers for SPI device variants.


PART NUMBER	PACKAGE	BODY SIZE (NOM)
DRV8320	WQFN (32)	5.00 mm × 5.00 mm
DRV8320R	VQFN (40)	6.00 mm × 6.00 mm
DRV8323	WQFN (40)	6.00 mm × 6.00 mm
DRV8323R	VQFN (48)	7.00 mm × 7.00 mm

(1) For all available packages, see the orderable addendum at the end of the data sheet.

Simplified Schematic



Copyright © 2017, Texas Instruments Incorporated



TEXAS INSTRUMENTS

www.ti.com

Table of Contents

Features1				
Applications1				
	cription1			
Rev	ision History2			
Dev	ice Comparison Table4			
Pin	Configuration and Functions4			
Spe	cifications11			
7.1	Absolute Maximum Ratings11			
7.2	ESD Ratings11			
7.3	Recommended Operating Conditions12			
7.4	Thermal Information12			
7.5	Electrical Characteristics13			
7.6	SPI Timing Requirements18			
7.7	Typical Characteristics19			
Deta	ailed Description21			
8.1	Overview21			
8.2	Functional Block Diagram22			
8.3	Feature Description			
8.4	Device Functional Modes50			
8.5	Programming51			
	App Des Rev Pin Spe 7.1 7.2 7.3 7.4 7.5 7.6 7.7 Deta 8.1 8.2 8.3 8.4			

	8.6	Register Maps	53
9		ication and Implementation	
	9.1	Application Information	<mark>6</mark> 1
	9.2	Typical Application	<mark>61</mark>
10	Pow	er Supply Recommendations	70
	10.1	BulkCapacitance Sizing	70
11	Layo	out	71
	11.1	Layout Guidelines	71
	11.2	Layout Example	72
12	Devi	ce and Documentation Support	73
	12.1	Device Support	73
	12.2	Documentation Support	73
	12.3	Related Links	73
	12.4	Receiving Notification of Documentation Update	es <mark>74</mark>
	12.5	Community Resources	74
	12.6	Trademarks	74
	12.7	Electrostatic Discharge Caution	74
	12.8	Glossary	74
13	Mec	hanical, Packaging, and Orderable	
		mation	74

4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Cł	Changes from Revision C (August 2018) to Revision D				
•	Added information in the Sleep Mode section on the behavior of GHx and GLx when Enable is pulled low	50			

Changes from Revision B (December 2017) to Revision C Page

•	Changed the Applications1
•	Updated input labels for the INLx and INHx signals in the <i>Layout Example</i> imags
•	Added the DRV835x device options to the image in the Device Nomenclature section

Changes from Revision A (April 2017) to Revision B

•	Changed the low-power sleep mode supply current from the maximum value (20 μ A) to the typical value (12 μ A) in the <i>Features</i>	1
•	Changed the Applications	1
•	Changed the GAIN value from 45 k Ω to 47 k Ω in the test condition of the amplifier gain for the H/W device in the <i>Electrical Characteristics</i> table	15
•	Deleted t _{EN_nSCS} from the SPI Slave Mode Timing Diagram	18
•	Added a note to the Synchronous 1x PWM Mode to define !PWM	31
•	Updated the Auto Offset Calibration section	44
•	Updated the VDs Latched Shutdown and VDs Automatic Retry sections	48
•	Updated the Sleep Mode section	50
•	Changed the address listed in the title for the Gate Drive LS Register section to the correct register address, 0x04	
•	Changed the maximum Q_g value for both trapezoidal and sinusoidal commutation the V_{VM} = 8 V example of the Detailed Design Procedure	63
•	Changed IDRIVEP and IDRIVEN equations in the IDRIVE Configuration section	64
2	Submit Documentation Feedback Copy right© 2017–2022, Texas Instruments Incorp	orated



3

SLVSDJ3D - FEBRUARY 2017 - REVISED MARCH 2022

CI	Changes from Original (February 2017) to Revision A Pag		
•	Changed the test condition for the IBIAS parameter in the Electrical Characteristics table	16	
•	Changed the GHx values in the 3x PWM Mode Truth Table	31	
•	Changed the calibration description and added auto calibration feature description	44	




5 Device Comparison Table

DEVICE		CURRENT SENSE AMPLIFIERS	BUCK REGULATOR ⁽¹⁾	INTERFACE ⁽¹⁾	
	DRV8320H		News	Hardware	
DRV8320	DRV8320S	0	None	SPI	
DRV8320R	DRV8320RH		U	600 m A	Hardware
	DRV8320RS		600 mA	SPI	
DRV8323	DRV8323H	0	Nana	Hardware	
	DRV8323S		None	SPI	
DRV8323R		DRV8323RH	3	600 m A	Hardware
	DRV8323RS		600 mA	SPI	

(1) For more information on the device name and device options, see the *Device Nomenclature* section. For additional details, see the *Architecture for Brushless-DC Gate Drive Systems* application report.

6 Pin Configuration and Functions



Pin Functions-32-Pin DRV8320 Devices

PIN					
NAME	NO.		TYPE ⁽¹⁾	DESCRIPTION	
NAME	DRV8320H	DRV8320S			
AGND	23	23	PWR	Device analog ground. Connect to system ground.	
CPH	1	1	PWR	Charge pump switching node. Connect a X5R or X7R, 47-nF, VM-rated ceramic capacitor between the CPH and CPL pins.	
CPL	32	32	PWR	Charge pump switching node. Connect a X5R or X7R, 47-nF, VM-rated ceramic capacitor between the CPH and CPL pins.	
DVDD	24	24	PWR	3.3-V internal regulator output. Connect a X5R or X7R, 1-µF, 6.3-V ceramic capacitor between the DVDD and AGND pins. This regulator can source up to 30 mA externally.	
ENABLE	22	22	I	Gate driver enable. When this pin is logic low the device goes to a low-power sleep mode. An 8 to 40-µs pulse can be used to reset fault conditions.	
GHA	5	5	0	High-side gate driver output. Connect to the gate of the high-side power MOSFET.	
GHB	12	12	0	High-side gate driver output. Connect to the gate of the high-side power MOSFET.	
GHC	13	13	0	High-side gate driver output. Connect to the gate of the high-side power MOSFET.	

(1) PWR = power, I = input, O = output, NC = no connection, OD = open-drain output

4 Submit Documentation Feedback

Copy right © 2017-2022, Texas Instruments Incorporated

Product Folder Links: DRV8320 DRV8320R DRV8323 DRV8323R




SLVSDJ3D - FEBRUARY 2017-REVISED MARCH 2022

www.ti.com

Pin Functions—32-Pin DRV8320 Devices (continued)

PIN				
NAME NO.		TYPE ⁽¹⁾	DESCRIPTION	
	DRV8320H	DRV8320S		
GLA	7	7	0	Low-side gate driver output. Connect to the gate of the low-side power MOSFET.
GLB	10	10	0	Low-side gate driver output. Connect to the gate of the low-side power MOSFET.
GLC	15	15	0	Low-side gate driver output. Connect to the gate of the low-side power MOSFET.
IDRIVE	19	_	I	Gate drive output current setting. This pin is a 7 level input pin set by an external resistor.
INHA	25	25	I	High-side gate driver control input. This pin controls the output of the high-side gate driver.
INHB	27	27	I	High-side gate driver control input. This pin controls the output of the high-side gate driver.
INHC	29	29	I	High-side gate driver control input. This pin controls the output of the high-side gate driver.
INLA	26	26	I	Low-side gate driver control input. This pin controls the output of the low-side gate driver.
INLB	28	28	I	Low-side gate driver control input. This pin controls the output of the low-side gate driver.
INLC	30	30	I	Low-side gate driver control input. This pin controls the output of the low-side gate driver.
MODE	18	_	I	PWM input mode setting. This pin is a 4 level input pin set by an external resistor.
NC	21	—	NC	No internal connection. This pin can be left floating or connected to system ground.
nFAULT	17	17	OD	Fault indicator output. This pin is pulled logic low during a fault condition and requires an external pullup resistor.
nSCS	—	21	I	Serial chip select. A logic low on this pin enables serial interface communication.
PGND	31	31	PWR	Device power ground. Connect to system ground.
SCLK	—	20	I	Serial clock input. Serial data is shifted out and captured on the corresponding rising and falling edge on this pin.
SDI	—	19	I	Serial data input. Data is captured on the falling edge of the SCLK pin.
SDO	—	18	OD	Serial data output. Data is shifted out on the rising edge of the SCLK pin. This pin requires an external pullup resistor.
SHA	6	6	I	High-side source sense input. Connect to the high-side power MOSFET source.
SHB	11	11	I	High-side source sense input. Connect to the high-side power MOSFET source.
SHC	14	14	I	High-side source sense input. Connect to the high-side power MOSFET source.
SLA	8	8	I	Low-side source sense input. Connect to the low-side power MOSFET source.
SLB	9	9	I	Low-side source sense input. Connect to the low-side power MOSFET source.
SLC	16	16	I	Low-side source sense input. Connect to the low-side power MOSFET source.
VCP	2	2	PWR	Charge pump output. Connect a X5R or X7R, 1-µF, 16-V ceramic capacitor between the VCP and VM pins.
VDRAIN	4	4	I	High-side MOSFET drain sense input. Connect to the common point of the MOSFET drains.
VDS	20	_	I	VDS monitor trip point setting. This pin is a 7 level input pin set by an external resistor.
VM	3	3	PWR	Gate driver power supply input. Connect to the bridge power supply. Connect a X5R or X7R, 0.1-µF, VM-rated ceramic and greater then or equal to 10-uF local capacitance between the VM and PGND pins.
Thermal Pa	d		PWR	Must be connected to ground





Pin Functions—40-Pin DRV8320R Devices

	PIN						
NAME NO.		TYPE ⁽¹⁾	DESCRIPTION				
NAME	DRV8320RH	DRV8320RS					
AGND	26	26	PWR	Device analog ground. Connect to system ground.			
BGND	34	34	PWR	Buck regulator ground. Connect to system ground.			
СВ	35	35	PWR	Buck regulator bootstrap input. Connect a X5R or X7R, 0.1-µF, 16-V, capacitor between the CB and SW pins.			
CPH	3	3	PWR	Charge pump switching node. Connect a X5R or X7R, 47-nF, VM-rated ceramic capacitor between the CPH and CPL pins.			
CPL	2	2	PWR	Charge pump switching node. Connect a X5R or X7R, 47-nF, VM-rated ceramic capacitor between the CPH and CPL pins.			
DVDD	27	27	PWR	ternal regulator output. Connect a X5R or X7R, 1-μF, 6.3-V ceramic capacitor between the DVDD and AGND pins. gulator can source up to 30 mA externally.			
ENABLE	25	25	I	Gate driver enable. When this pin is logic low the device goes to a low-power sleep mode. An 8 to 40-µs low pulse can be used to reset fault conditions.			
FB	40	40	I	Buck feedback input. A resistor divider from the buck post inductor output to this pin sets the buck output voltage.			
GHA	7	7	0	High-side gate driver output. Connect to the gate of the high-side power MOSFET.			
GHB	14	14	0	High-side gate driver output. Connect to the gate of the high-side power MOSFET.			
GHC	15	15	0	High-side gate driver output. Connect to the gate of the high-side power MOSFET.			
GLA	9	9	0	Low-side gate driver output. Connect to the gate of the low-side power MOSFET.			
GLB	12	12	0	Low-side gate driver output. Connect to the gate of the low-side power MOSFET.			
GLC	17	17	0	Low-side gate driver output. Connect to the gate of the low-side power MOSFET.			
GND	19	19	PWR	Device ground. Connect to system ground.			
IDRIVE	22	_	I	Gate drive output current setting. This pin is a 7 level input pin set by an external resistor.			
INHA	28	28	I	High-side gate driver control input. This pin controls the output of the high-side gate driver.			
INHB	30	30	I	High-side gate driver control input. This pin controls the output of the high-side gate driver.			
INHC	32	32	I	High-side gate driver control input. This pin controls the output of the high-side gate driver.			
INLA	29	29	I	Low-side gate driver control input. This pin controls the output of the low-side gate driver.			
INLB	31	31	I	Low-side gate driver control input. This pin controls the output of the low-side gate driver.			
INLC	33	33	I	Low-side gate driver control input. This pin controls the output of the low-side gate driver.			
MODE	21	_	I	PWM input mode setting. This pin is a 4 level input pin set by an external resistor.			
NC	24	_	NC	No internal connection. This pin can be left floating or connected to system ground.			
NC	37	37	NC	No internal connection. This pin can be left floating or connected to system ground.			
nFAULT	20	20	OD	Fault indicator output. This pin is pulled logic low during a fault condition and requires an external pullup resistor.			

(1) PWR = power, I = input, O = output, NC = no connection, OD = open-drain output

SLVSDJ3D - FEBRUARY 2017-REVISED MARCH 2022

DRV8323S RTA Package

40-Pin WQFN With Exposed Thermal Pad


Top View

www.ti.com

Pin Functions-40-Pin DRV8320R Devices (continued)

PIN NO.				
NAME			TYPE ⁽¹⁾	DESCRIPTION
	DRV8320RH	DRV8320RS		
nSCS	_	24	I	Serial chip select. A logic low on this pin enables serial interface communication.
nSHDN	39	39	I	Buck shutdown input. Enable and disable input (high voltage tolerant). Internal pullup current source. Pull lower than 1.25 V to disable. Float to enable. Establish input undervoltage lockout with two resistor divider.
PGND	1	1	PWR	Device power ground. Connect to system ground.
SCLK	_	23	I	Serial clock input. Serial data is shifted out and captured on the corresponding rising and falling edge on this pin.
SDI		22	-	Serial data input. Data is captured on the falling edge of the SCLK pin.
SDO		21	OD	Serial data output. Data is shifted out on the rising edge of the SCLK pin. This pin requires an external pullup resistor.
SHA	8	8	I	High-side source sense input. Connect to the high-side power MOSFET source.
SHB	13	13	-	High-side source sense input. Connect to the high-side power MOSFET source.
SHC	16	16	Ι	High-side source sense input. Connect to the high-side power MOSFET source.
SLA	10	10	Ι	Low-side source sense input. Connect to the low-side power MOSFET source.
SLB	11	11	Ι	Low-side source sense input. Connect to the low-side power MOSFET source.
SLC	18	18	-	Low-side source sense input. Connect to the low-side power MOSFET source.
SW	36	36	0	Buck switch node. Connect this pin to an inductor, diode, and the CB bootstrap capacitor.
VCP	4	4	PWR	Charge pump output. Connect a X5R or X7R, 1-µF, 16-V ceramic capacitor between the VCP and VM pins.
VDRAIN	6	6	Ι	High-side MOSFET drain sense input. Connect to the common point of the MOSFET drains.
VDS	23	_	Ι	VDS monitor trip point setting. This pin is a 7 level input pin set by an external resistor.
VIN	38	38	PWR	Buck regulator power supply input. Place an X5R or X7R, VM-rated ceramic capacitor between the VIN and BGND pins.
VM	10 10 11 11 18 18 36 36 4 4 N 6 6 23 38 38 5 5 5		PWR	Gate driver power supply input. Connect to the bridge power supply. Connect a X5R or X7R, 0.1-µF, VM-rated ceramic and greater then or equal to 10-uF local capacitance between the VM and PGND pins.
Thermal F	Pad		PWR	Must be connected to ground





Pin Functions-40-Pin DRV8323 Devices

	PIN			
NAME	N	0.	TYPE ⁽¹⁾	DESCRIPTION
	DRV8323H	DRV8323S		
AGND	32	32	PWR	Device analog ground. Connect to system ground.
CAL	31	31	I	Amplifier calibration input. Set logic high to internally short amplifier inputs and perform auto offset calibration.
CPH	2	2	PWR	Charge pump switching node. Connect a X5R or X7R, 47-nF, VM-rated ceramic capacitor between the CPH and CPL pins.
(1) PW	R = power, I =	input, O = ou	put, NC	= no connection, OD = open-drain output
Copyrigh	t© 2017–2022,	Texas Instrumen	ts Incorpo	rated Submit Documentation Feedback 7

Copy right © 2017-2022, Texas Instruments Incorporated

Product Folder Links: DRV8320 DRV8320R DRV8323 DRV8323R

Texas Instruments


www.ti.com

Pin Functions—40-Pin DRV8323 Devices (continued)

PIN NO.							
NAME	N	0.	TYPE ⁽¹⁾	DESCRIPTION			
	DRV8323H	DRV8323S					
CPL	1	1	PWR	Charge pump switching node. Connect a X5R or X7R, 47-nF, VM-rated ceramic capacitor between the CPH and CPL pins.			
DVDD	33	33	PWR	R 3.3-V internal regulator output. Connect a X5R or X7R, 1-µF, 6.3-V ceramic capacitor between the DVDD and AGND pins This regulator can source up to 30 mA externally.			
ENABLE	30	30	I	Gate driver enable. When this pin is logic low the device goes to a low-power sleep mode. An 8 to 40-µs low pulse can be used to reset fault conditions.			
gain	29		I	Amplifier gain setting. The pin is a 4 level input pin set by an external resistor.			
GHA	6	6	0	High-side gate driver output. Connect to the gate of the high-side power MOSFET.			
GHB	15	15	0	High-side gate driver output. Connect to the gate of the high-side power MOSFET.			
GHC	16	16	0	High-side gate driver output. Connect to the gate of the high-side power MOSFET.			
GLA	8	8	0	Low-side gate driver output. Connect to the gate of the low-side power MOSFET.			
GLB	13	13	0	Low-side gate driver output. Connect to the gate of the low-side power MOSFET.			
GLC	18	18	0	Low-side gate driver output. Connect to the gate of the low-side power MOSFET.			
DRIVE	27	—	I	Gate drive output current setting. This pin is a 7 level input pin set by an external resistor.			
NHA	34	34	I	High-side gate driver control input. This pin controls the output of the high-side gate driver.			
INHB	36	36	I	High-side gate driver control input. This pin controls the output of the high-side gate driver.			
NHC	38	38	I	High-side gate driver control input. This pin controls the output of the high-side gate driver.			
NLA	35	35	I	Low-side gate driver control input. This pin controls the output of the low-side gate driver.			
NLB	37	37	I	Low-side gate driver control input. This pin controls the output of the low-side gate driver.			
NLC	39	39	I	Low-side gate driver control input. This pin controls the output of the low-side gate driver.			
NODE	26	—	I	PWM input mode setting. This pin is a 4 level input pin set by an external resistor.			
hFAULT	25	25	OD	Fault indicator output. This pin is pulled logic low during a fault condition and requires an external pullup resistor.			
ISCS	_	29	I	Serial chip select. A logic low on this pin enables serial interface communication.			
PGND	40	40	PWR	Device power ground. Connect to system ground.			
SCLK	_	28	I	Serial clock input. Serial data is shifted out and captured on the corresponding rising and falling edge on this pin.			
SDI	_	27	I	Serial data input. Data is captured on the falling edge of the SCLK pin.			
SDO	_	26	OD	Serial data output. Data is shifted out on the rising edge of the SCLK pin. This pin requires an external pullup resistor.			
SHA	7	7	I	High-side source sense input. Connect to the high-side power MOSFET source.			
SHB	14	14	1	High-side source sense input. Connect to the high-side power MOSFET source.			
SHC	17	17	I	High-side source sense input. Connect to the high-side power MOSFET source.			
SNA	10	10	I	Current sense amplifier input. Connect to the low-side of the current shunt resistor.			
SNB	11	11	1	Current sense amplifier input. Connect to the low-side of the current shunt resistor.			
SNC	20	20	1	Current sense amplifier input. Connect to the low-side of the current shunt resistor.			
SOA	23	23	0	Current sense amplifier output.			
SOB	22	22	0	Current sense amplifier output.			
SOC	21	21	0	Current sense amplifier output.			
SPA	9	9	I	Low-side current shunt amplifier input. Connect to the low-side power MOSFET source and high-side of the current shunt resistor.			
SPB	12	12	I	Low-side current shunt amplifier input. Connect to the low-side power MOSFET source and high-side of the current shunt resistor.			
SPC	19	19	I	Low-side current shunt amplifier input. Connect to the low-side power MOSFET source and high-side of the current shunt resistor.			
VCP	3	3	PWR	Charge pump output. Connect a X5R or X7R, 1-µF, 16-V ceramic capacitor between the VCP and VM pins.			
VDRAIN	5	5	I	High-side MOSFET drain sense input. Connect to the common point of the MOSFET drains.			
VDS	28		I	VDS monitor trip point setting. This pin is a 7 level input pin set by an external resistor.			
VM	4	4	PWR	Gate driver power supply input. Connect to the bridge power supply. Connect a X5R or X7R, 0.1-µF, VM-rated ceramic and greater then or equal to 10-uF local capacitance between the VM and PGND pins.			
VREF	24	24	PWR	Current sense amplifier power supply input and reference. Connect a X5R or X7R, 0.1-µF, 6.3-V ceramic capacitor betweer the VREF and AGND pins.			
Thermal P	Pad	•	PWR	Must be connected to ground			

Copy right © 2017-2022, Texas Instruments Incorporated





Pin Functions—48-Pin DRV8323R Devices

	PIN			
NAME	N	0.	TYPE ⁽¹⁾	DESCRIPTION
	DRV8323RH	DRV8323RS		
AGND	35	35	PWR	Device analog ground. Connect to system ground.
BGND	43	43	PWR	Buck regulator ground. Connect to system ground.
CAL	34	34	I	Amplifier calibration input. Set logic high to internally short amplifier inputs and perform auto offset calibration.
СВ	44	44	PWR	Buck regulator bootstrap input. Connect a X5R or X7R, 0.1-µF, 16-V, capacitor between the CB and SW pins.
CPH	4	4	PWR	Charge pump switching node. Connect a X5R or X7R, 47-nF, VM-rated ceramic capacitor between the CPH and CPL pins.
CPL	3	3	PWR	Charge pump switching node. Connect a X5R or X7R, 47-nF, VM-rated ceramic capacitor between the CPH and CPL pins.
DGND	27	27	PWR	Device ground. Connect to system ground.
DVDD	36	36	PWR	3.3-V internal regulator output. Connect a X5R or X7R, 1-µF, 6.3-V ceramic capacitor between the DVDD and AGND pins. This regulator can source up to 30 mA externally.
ENABLE	33	33	I	Gate driver enable. When this pin is logic low the device goes to a low-power sleep mode. An 8 to 40-µs low pulse can be used to reset fault conditions.
FB	1	1	I	Buck feedback input. A resistor divider from the buck post inductor output to this pin sets the buck output voltage.
GAIN	32	_	I	Amplifier gain setting. The pin is a 4 level input pin set by an external resistor.
GHA	8	8	0	High-side gate driver output. Connect to the gate of the high-side power MOSFET.
GHB	17	17	0	High-side gate driver output. Connect to the gate of the high-side power MOSFET.
GHC	18	18	0	High-side gate driver output. Connect to the gate of the high-side power MOSFET.
GLA	10	10	0	Low-side gate driver output. Connect to the gate of the low-side power MOSFET.
GLB	15	15	0	Low-side gate driver output. Connect to the gate of the low-side power MOSFET.
GLC	20	20	0	Low-side gate driver output. Connect to the gate of the low-side power MOSFET.
IDRIVE	30	—	I	Gate drive output current setting. This pin is a 7 level input pin set by an external resistor.
INHA	37	37	I	High-side gate driver control input. This pin controls the output of the high-side gate driver.
INHB	39	39	I	High-side gate driver control input. This pin controls the output of the high-side gate driver.
INHC	41	41	I	High-side gate driver control input. This pin controls the output of the high-side gate driver.
INLA	38	38	-	Low-side gate driver control input. This pin controls the output of the low-side gate driver.
INLB	40	40	-	Low-side gate driver control input. This pin controls the output of the low-side gate driver.
INLC	42	42	-	Low-side gate driver control input. This pin controls the output of the low-side gate driver.
MODE	29		-	PWM input mode setting. This pin is a 4 level input pin set by an external resistor.
NC	46	46	NC	No internal connection. This pin can be left floating or connected to system ground.
nFAULT	28	28	OD	Fault indicator output. This pin is pulled logic low during a fault condition and requires an external pullup resistor.

(1) PWR = power, I = input, O = output, NC = no connection, OD = open-drain output

Copy right © 2017–2022, Texas Instruments Incorporated

DRV8320, DRV8320R DRV8323, DRV8323R SLVSDJ3D –FEBRUARY 2017–REVISED MARCH 2022 Texas Instruments

www.ti.com

Pin Functions—48-Pin DRV8323R Devices (continued)

	PIN			
NAME	N	0.	TYPE ⁽¹⁾	DESCRIPTION
NAWE	DRV8323RH	DRV8323RS		
nSCS	_	32	I	Serial chip select. A logic low on this pin enables serial interface communication.
nSHDN	48	48	I	Buck shutdown input. Enable and disable input (high voltage tolerant). Internal pullup current source. Pull lower than 1.25 V to disable. Float to enable. Establish input undervoltage lockout with two resistor divider.
PGND	2	2	PWR	Device power ground. Connect to system ground.
SCLK	_	31	Ι	Serial clock input. Serial data is shifted out and captured on the corresponding rising and falling edge on this pin.
SDI		30	-	Serial data input. Data is captured on the falling edge of the SCLK pin.
SDO		29	OD	Serial data output. Data is shifted out on the rising edge of the SCLK pin. This pin requires an external pullup resistor.
SHA	9	9	I	High-side source sense input. Connect to the high-side power MOSFET source.
SHB	16	16	I	High-side source sense input. Connect to the high-side power MOSFET source.
SHC	19	19	I	High-side source sense input. Connect to the high-side power MOSFET source.
SNA	12	12	I	Current sense amplifier input. Connect to the low-side of the current shunt resistor.
SNB	13	13	I	Current sense amplifier input. Connect to the low-side of the current shunt resistor.
SNC	22	22	I	Current sense amplifier input. Connect to the low-side of the current shunt resistor.
SOA	25	25	0	Current sense amplifier output.
SOB	24	24	0	Current sense amplifier output.
SOC	23	23	0	Current sense amplifier output.
SPA	11	11	I	Low-side current shunt amplifier input. Connect to the low-side power MOSFET source and high-side of the current shunt resistor.
SPB	14	14	I	Low-side current shunt amplifier input. Connect to the low-side power MOSFET source and high-side of the current shunt resistor.
SPC	21	21	Ι	Low-side current shunt amplifier input. Connect to the low-side power MOSFET source and high-side of the current shunt resistor.
SW	45	45	0	Buck switch node. Connect this pin to an inductor, diode, and the CB bootstrap capacitor.
VCP	5	5	PWR	Charge pump output. Connect a X5R or X7R, 1-µF, 16-V ceramic capacitor between the VCP and VM pins.
VDRAIN	7	7	I	High-side MOSFET drain sense input. Connect to the common point of the MOSFET drains.
VDS	31	_	I	VDS monitor trip point setting. This pin is a 7 level input pin set by an external resistor.
VIN	47	47	PWR	Buck regulator power supply input. Place an X5R or X7R, VM-rated ceramic capacitor between the VIN and BGND pins.
VM	6	6	PWR	Gate driver power supply input. Connect to the bridge power supply. Connect a X5R or X7R, 0.1-µF, VM-rated ceramic and greater then or equal to 10-uF local capacitance between the VM and PGND pins.
VREF	26	26	PWR	Current sense amplifier power supply input and reference. Connect a X5R or X7R, 0.1-µF, 6.3-V ceramic capacitor between the VREF and AGND pins.
Thermal F	Pad	-	PWR	Must be connected to ground

Product Folder Links: DRV8320 DRV8320R DRV8323 DRV8323R



7 Specifications

7.1 Absolute Maximum Ratings

at $T_A = -40^{\circ}C$ to +125°C (unless otherwise noted)⁽¹⁾

	MIN	MAX	UNIT
GATE DRIVER			
Power supply pin voltage (VM)	-0.3	65	V
Voltage differential between ground pins (AGND, BGND, DGND, PGND)	-0.3	0.3	V
MOSFET drain sense pin voltage (VDRAIN)	-0.3	65	V
Charge pump pin voltage (CPH, VCP)	-0.3	V _{VM} + 13.5	V
Charge pump negative-switching pin voltage (CPL)	-0.3	V _{VM}	V
Internal logic regulator pin voltage (DVDD)	-0.3	3.8	V
Digital pin voltage (CAL, ENABLE, GAIN, IDRIVE, INHx, INLx, MODE, nFAULT, nSCS, SCLK, SDI, SDO, VDS)	-0.3	5.75	V
Continuoushigh-side gate drive pin voltage (GHx)	-5 ⁽²⁾	V _{VCP} + 0.5	V
Transient 200-nshigh-side gate drive pin voltage (GHx)	-7	V _{VCP} + 0.5	V
High-side gate drive pin voltage with respect to SHx (GHx)	-0.3	13.5	V
Continuoushigh-side source sense pin voltage (SHx)	-5(2)	V _{VM} + 5	V
Transient 200-ns high-side source sense pin voltage (SHx)	-7	V _{VM} + 7	V
Continuouslow-side gate drive pin voltage (GLx)	-0.5	13.5	V
Gate drive pin source current (GHx, GLx)	Intern	allylimited	А
Gate drive pin sinkcurrent (GHx, GLx)	Intern	allylimited	А
Continuous low-side source sense pin voltage (SLx)	-1	1	V
Transient 200-ns low-side source sense pin voltage (SLx)	-3	3	V
Continuousinput pinvoltage (SNx, SPx)	-1	1	V
Transient 200-ns input pin voltage (SNx, SPx)	-3	3	V
Reference input pin voltage (VREF)	-0.3	5.75	V
output pin voltage (SOx)	-0.3	V _{VREF} + 0.3	V
BUCK REGULATOR			
Power supply pin voltage (VIN)	-0.3	65	V
Shutdown control pin voltage (nSHDN)	-0.3	V _{VIN}	V
Voltage feedbackpin voltage (FB)	-0.3	7	V
Bootstrap pin voltage with respect to SW (CB)	-0.3	7	V
Switching node pin voltage (SW)	-0.3	V _{VIN}	V
Switching node pin voltage less than 30-ns transients (SW)	-2	V _{VIN}	V
DRV832x			
Operating junction temperature, T _J	-40	150	°C
Storage temperature, T _{stg}	-65	150	°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) Continuous high-side gate pin (GHx) and phase node pin voltage (SHx) should be limited to -2 V minimum for an absolute maximum of 65 V on VM. At 60 V and lower, the full specification of -5 V continuous on GHx and SHx is allowable.

7.2 ESD Ratings

			VALUE	UNIT
V _(ESD)	Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾		V
		Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾	±1000	v

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process. Pinslisted as ±2000 V may actually have higher performance.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process. Pinslisted as ±500 V may actually have higher performance.

DRV8320, DRV8320R

SLVSDJ3D -FEBRUARY 2017-REVISED MARCH 2022



www.ti.com

7.3 Recommended Operating Conditions

at $T_A = -40^{\circ}C$ to $+125^{\circ}C$ (unless otherwise noted)

		MIN	MAX	UNIT
GATE DRIVI	ER			
V_{VM}	Powersupply voltage (VM)	6	60	V
Vi	Input voltage (CAL, ENABLE, GAIN, IDRIVE, INHx, INLx, MODE, nSCS, SCLK, SDI, VDS)	0	5.5	V
f _{PWM}	Applied PWM signal (INHx, INLx)	0	200 ⁽¹⁾	kHz
I _{GATE_HS}	High-side average gate drive current (GHx)	0	25 ⁽¹⁾	mA
I _{GATE_LS}	Low-side average gate drive current (GLx)	0	25 ⁽¹⁾	mA
I _{DVDD}	External load current (DVDD)	0	30 ⁽¹⁾	mA
V _{VREF}	Reference voltage input (VREF)	3	5.5	V
I _{SO}	output current (SOx)	0	5	mA
V _{OD}	Open drain pullup voltage (nFAULT, SDO)	0	5.5	V
I _{OD}	Open drain output current (nFAULT, SDO)	0	5	mA
BUCK REGU	JLATOR			
V _{VIN}	Powersupply voltage (VIN)	4	60	V
V _{nSHDN}	Shutdown control input voltage (nSHDN)	0	60	V
DRV832x				
T _A	Operating ambient temperature	-40	125	°C

(1) Power dissipation and thermal limits must be observed

7.4 Thermal Information

			DRV	/832x		
	THERMAL METRIC ⁽¹⁾	RTV (WQFN)	RHA (VQFN)	RTA (WQFN)	RGZ (VQFN)	UNIT
		32 PINS	40 PINS	40 PINS	48 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	32.9	30.1	32.1	26.6	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	15.8	16.7	11	13.9	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	6.8	9.9	7.1	9.2	°C/W
τιΨ	Junction-to-top characterization parameter	0.2	0.5	0.1	0.3	°C/W
ψ_{JB}	Junction-to-board characterization parameter	6.8	9.9	7.1	9.1	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	2.1	2.2	2.1	2	°C/W

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

Copy right © 2017-2022, Texas Instruments Incorporated

7.5 Electrical Characteristics

at $T_A = -40^{\circ}C$ to +125°C, $V_{VM} = 6$ to 60 V (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
POWER SU	PPLIES (DVDD, VCP, VM)					
I _{VM}	VM operating supply current	V _{VM} = 24 V, ENABLE = 3.3 V, INHx/INLx = 0 V		10.5	14	mA
	VM sleep mode supply current	ENABLE = 0 V, V_{VM} = 24 V, T_A = 25°C		12 20 50		
I _{VMQ}	VM sleep mode supply current	ENABLE = 0 V, V_{VM} = 24 V, T_A = 125°C ⁽¹⁾			50	μA
t _{RST} ⁽¹⁾	Reset pulse time	ENABLE = 0 V period to reset faults	8		40	μs
t _{WAKE}	Turnon time	$V_{VM} > V_{UVLO}$, ENABLE = 3.3 V to outputs ready			1	ms
t _{SLEEP}	Turnoff time	ENABLE = 0 V to device sleep mode			1	ms
V _{DVDD}	DVDD regulator voltage	$I_{DVDD} = 0$ to 30 mA	3	3.3	3.6	V
		$V_{VM} = 13 V$, $I_{VCP} = 0$ to 25 mA	8.4	11	12.5	
V	VCP operating voltage	V_{VM} = 10 V, I_{VCP} = 0 to 20 mA	6.3	9	10	V
VCP	with respect to VM	$V_{VM} = 8 V$, $I_{VCP} = 0$ to 15 mA	5.4	7	8	v
		$V_{VM} = 6 V, I_{VCP} = 0 \text{ to } 10 \text{ mA}$	4	5	6	
LOGIC-LEV	EL INPUTS (CAL, ENABLE, INHx, INL)	x, nSCS, SCLK, SDI)				
V _{IL}	Input logic low voltage		0		0.8	V
VIH	Input logic high voltage		1.5		5.5	V
V _{HYS}	Input logic hysteresis			100		mV
IIL	Input logic low current	V _{VIN} = 0 V	-5		5	μA
I _{IH}	Input logic high current	V _{VIN} = 5 V		50	70	μA
R _{PD}	Pulldown resistance	To AGND		100		kΩ
t _{PD}	Propagation delay	INHx/INLx transition to GHx/GLx transition		150		ns
FOUR-LEV	EL H/W INPUTS (GAIN, MODE)					
V _{I1}	Input mode 1 voltage	Tied to AGND		0		V
V _{I2}	Input mode 2 voltage	45 k Ω ± 5% to tied AGND		1.2		V
V _{I3}	Input mode 3 voltage	Hi-Z		2		V
V _{I4}	Input mode 4 voltage	Tied to DVDD		3.3		V
R _{PU}	Pullup resistance	Internal pullup to DVDD		50		kΩ
R _{PD}	Pulldown resistance	Internal pulldown to AGND		84		kΩ
SEVEN-LE	/EL H/W INPUTS (IDRIVE, VDS)					
V _{I1}	Input mode 1 voltage	Tied to AGND		0		V
V _{I2}	Input mode 2 voltage	18 k Ω ± 5% tied to AGND		0.5		V
V _{I3}	Input mode 3 voltage	75 k Ω ± 5% tied to AGND		1.1		V
V ₁₄	Input mode 4 voltage	Hi-Z		1.65		V
V _{I5}	Input mode 5 voltage	$75 \text{ k}\Omega \pm 5\%$ tied to DVDD		2.2		V
V _{I6}	Input mode 6 voltage	18 k Ω ± 5% tied to DVDD		2.8		V
V _{I7}	Input mode 7 voltage	Tied to DVDD		3.3		V
R _{PU}	Pullup resistance	Internal pullup to DVDD		73		kΩ
R _{PD}	Pulldown resistance	Internal pulldown to AGND		73		kΩ
	IN OUTPUTS (nFAULT, SDO)					
V _{OL}	Output logic low voltage	I ₀ = 5 mA			0.1	V
I _{OZ}	Output high impedance leakage	$V_0 = 5 V$	-2		2	μA

(1) Specified by design and characterization data

TEXAS INSTRUMENTS

www.ti.com

Electrical Characteristics (continued)

at $T_A = -40^{\circ}C$ to +125°C, $V_{VM} = 6$ to 60 V (unless otherwise noted)

	PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT	
GATE DRIVE	RS (GHx, GLx)							
			V_{VM} = 13 V, I_{VCP} = 0 to 25 mA	8.4	11	12.5		
V (1) Low-side gate dri	ve voltage	V_{VM} = 10 , I_{VCP} = 0 to 20 mA	6.3	9	10	V		
	with respect to SH		V _{VM} = 8 V, I _{VCP} = 0 to 15 mA	5.4	7	8	v	
			$V_{VM} = 6 V, I_{VCP} = 0 \text{ to } 10 \text{ mA}$	4	5	12.5		
V _{GSL} ⁽¹⁾			V_{VM} = 12 V, I_{VGLS} = 0 to 25 mA	9	11	12	1	
(1)	Low-side date drive	e voltage	V_{VM} = 10 V, I_{VGLS} = 0 to 20 mA	7.5	9	10	.,	
	with respect to PG		V _{VM} = 8 V, I _{VGLS} = 0 to 15 mA	5.5	7	8	V	
			$V_{VM} = 6 V, I_{VGLS} = 0 \text{ to } 10 \text{ mA}$	4	5	6		
			DEAD TIME = 00b		50			
			DEAD_TIME = 01b		100			
t _{nean}		SPI Device	DEAD TIME = 10b		200		ns	
DERD	dead time		DEAD TIME = 11b		400			
		H/W Device			100			
			TDRIVE = 00b		500			
			TDRIVE = 01b		1000			
toour		SPI Device	TDRIVE = 10b		2000		ns	
DRIVE	gate drive time		TDRIVE = 11b		4000			
		H/W Device			4000			
		TI/W Device						
			IDRIVEP_HS or IDRIVEP_LS = 0000b		10			
			IDRIVEP_HS or IDRIVEP_LS = 0001b		30			
			IDRIVEP_HS or IDRIVEP_LS = 0010b		60			
			IDRIVEP_HS or IDRIVEP_LS = 0011b		80			
			IDRIVEP_HS or IDRIVEP_LS = 0100b		120			
			IDRIVEP_HS or IDRIVEP_LS = 0101b		140			
			IDRIVEP_HS or IDRIVEP_LS = 0110b		170			
		SPI Device	IDRIVEP_HS or IDRIVEP_LS = 0111b		190			
			IDRIVEP_HS or IDRIVEP_LS = 1000b		260			
			IDRIVEP_HS or IDRIVEP_LS = 1001b		330		mA	
	Peak source		IDRIVEP_HS or IDRIVEP_LS = 1010b		370			
DRIVEP	gate current		IDRIVEP_HS or IDRIVEP_LS = 1011b		440			
	5		IDRIVEP_HS or IDRIVEP_LS = 1100b		570			
			IDRIVEP_HS or IDRIVEP_LS = 1101b		680			
			IDRIVEP_HS or IDRIVEP_LS = 1110b		820			
			IDRIVEP_HS or IDRIVEP_LS = 1111b		1000			
			IDRIVE = Tied to AGND		10			
			IDRIVE = $18 \text{ k}\Omega \pm 5\%$ tied to AGND		30			
			IDRIVE = 75 k Ω ± 5% tied to AGND		60			
		H/W Device	IDRIVE = Hi-Z		120			
			IDRIVE = 75 k Ω ± 5% tied to DVDD		260			
			IDRIVE = $18 \text{ k}\Omega \pm 5\%$ tied to DVDD		570			
			IDRIVE = Tied to DVDD		1000			

Copy right © 2017-2022, Texas Instruments Incorporated



Electrical Characteristics (continued)

at $T_A = -40^{\circ}C$ to +125°C, $V_{VM} = 6$ to 60 V (unless otherwise noted)

	PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNI		
			IDRIVEN_HS or IDRIVEN_LS = 0000b		20				
			IDRIVEN_HS or IDRIVEN_LS = 0001b						
			IDRIVEN_HS or IDRIVEN_LS = 0010b		120				
			IDRIVEN_HS or IDRIVEN_LS = 0011b		160				
			IDRIVEN HS or IDRIVEN LS = 0100b		240 280				
			IDRIVEN HS or IDRIVEN LS = 0101b						
			IDRIVEN HS or IDRIVEN LS = 0110b		340				
			IDRIVEN HS or IDRIVEN LS = 0111b		380				
		SPI Device	IDRIVEN HS or IDRIVEN LS = 1000b	_	520				
			IDRIVEN HS or IDRIVEN LS = 1000b		660				
				-	740				
	Peaksink		IDRIVEN_HS or IDRIVEN_LS = 1010b		-				
DRIVEN	gate current		IDRIVEN_HS or IDRIVEN_LS = 1011b	_	880		mA		
			IDRIVEN_HS or IDRIVEN_LS = 1100b	_	1140				
			IDRIVEN_HS or IDRIVEN_LS = 1101b		1360				
			IDRIVEN_HS or IDRIVEN_LS = 1110b	_	1640 2000				
			IDRIVEN_HS or IDRIVEN_LS = 1111b						
			IDRIVE = Tied to AGND		20	20 60			
			IDRIVE = 18 k Ω ± 5% tied to AGND						
			IDRIVE = 75 k Ω ± 5% tied to AGND		120				
		H/W Device	IDRIVE = Hi-Z		240				
			IDRIVE = 75 k Ω ± 5% tied to DVDD		520				
			IDRIVE = 18 k Ω ± 5% tied to DVDD		1140				
			IDRIVE = Tied to DVDD		2000				
			Source current after t _{DRIVE}		10				
HOLD	Gate holding currer	t	Sink current after t _{DRIVE}		50		mA		
STRONG	Gate strong pulldov	n current	GHx to SHx and GLx to PGND	2			А		
R _{OFF}	Gate hold off resisto	r	GHx to SHx and GLx to PGND	150			kΩ		
	ENSE AMPLIFIER (SNx,	SOx, SPx, VI	REF)						
	· · ·		CSA GAIN=00b	4.85	5	5.15			
			CSA GAIN=01b	9.7	10	10.3			
		SPI Device	CSA GAIN = 10b	19.4	20	20.6	I		
			CSA GAIN = 11b	38.8	40	41.2			
G _{CSA}	Amplifiergain		GAIN = Tied to AGND	4.85	5		V/V		
				9.7	10				
		H/W Device	GAIN = $47 \text{ k}\Omega \pm 5\%$ tied to AGND	-	-	10.3			
			GAIN = Hi-Z	19.4	20	20.6			
			GAIN = Tied to DVDD	38.8	40	41.2			
			$V_{O_{STEP}} = 0.5 V, G_{CSA} = 5 V/V$	_	150				
tset ⁽¹⁾	Settling time to ±1%)	$V_{O_STEP} = 0.5 V, G_{CSA} = 10 V/V$		300		ns		
-SET	g		$V_{O_STEP} = 0.5 V, G_{VSA} = 20 V/V$	_	600				
			V_{O_STEP} = 0.5 V, G_{CSA} = 40 V/V		1200				
V _{COM}	Common mode in p	ut range		-0.15		0.15	V		
V _{DIFF}	Differential mode in	putrange		-0.3		0.3	V		
V _{OFF}	Input offset error		$V_{SP} = V_{SN} = 0 V$, CAL = 3.3 V, VREF = 3.3 V	-4		4	mV		
V _{DRIFT} ⁽¹⁾	Drift offset		$V_{SP} = V_{SN} = 0 V$		10		μV/°		
	SOx output voltage linear range					V _{VREF}			

Copy right © 2017–2022, Texas Instruments Incorporated

Submit Documentation Feedback 15



Electrical Characteristics (continued)

at $T_A = -40^{\circ}$ C to +125°C, $V_{VM} = 6$ to 60 V (unless otherwise noted)

	PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
			$V_{SP} = V_{SN} = 0 V$, CAL = 3.3 V, VREF_DIV = 0b	V _{VF}	_{REF} - 0.3	;	
V _{BIAS}	SOx output voltage bias	SPI Device	$V_{SP} = V_{SN} = 0 V$, CAL = 3.3 V, VREF_DIV = 1b	V _{VREF} /2			V
	0183	H/W Device	V _{SP} = V _{SN} = 0 V, CAL = 3.3 V	V _{VREF} /2			
I _{BIAS}	SPx/SNx input bias	current	VREF_DIV = 1b			100	μA
V _{SLEW} ⁽¹⁾	SOx output slew rate	Э	60-pFload		10		V/µs
I _{VREF}	VREF input current		V _{VREF} = 5 V		2	3	mA
UGB ⁽¹⁾	Unity gain bandwid	h	60-pFload		1		MHz
PROTECTION	CIRCUITS			-			
			VM falling, UVLO report	5.4	5.6	5.8	
V _{UVLO}	VM undervoltage lo	ckout	VM rising, UVLO recovery	5.6	5.8	6	V
V _{UVLO_HYS}	VM undervoltage hy	/steresis	Rising to falling threshold		200		mV
t _{UVLO_DEG}	VM undervoltage de	eglitch time	VM falling, UVLO report		10		μs
V _{CPUV}	Charge pump unde lockout	rvoltage	VCP falling, CPUV report	V	_{′M} + 2.8		V
M Llink sid	المعام والمالية والمراجع		Positive clamping voltage	15	16.5	18	
V _{GS_CLAMP}	_{IP} High-side gate clamp		Negative clamping voltage	1	-0.7		V
			VDS_LVL = 0000b		0.06		
			VDS_LVL = 0001b		0.13		
			VDS_LVL = 0010b		0.2		
			VDS_LVL = 0011b		0.26		
			VDS_LVL = 0100b		0.31		
		SPI Device	VDS_LVL = 0101b		0.45		
			VDS LVL = 0110b		0.53		
			VDS_LVL = 0111b	0.6			
			VDS LVL = 1000b	0.68			
			VDS_LVL = 1001b	0.75			
			VDS LVL = 1010b		0.94		
V _{VDS_OCP}	V _{DS} overcurrent		VDS_LVL = 1011b		1.13		V
	trip voltage		VDS_LVL = 1100b	1.3			
			VDS LVL = 1101b	1.5			
			VDS LVL = 1110b	1.7			
			 VDS_LVL=1111b		1.88		
			VDS = Tied to AGND		0.06		
			VDS = 18 k $\Omega \pm 5\%$ tied to AGND		0.13		
			VDS = 75 k $\Omega \pm 5\%$ tied to AGND		0.26		
		H/W Device			0.6		
			VDS = 75 k $\Omega \pm 5\%$ tied to DVDD	1.13 1.88			
			VDS = $18 \text{ k}\Omega \pm 5\%$ tied to DVDD				
			VDS = Tied to DVDD	D	isabled		
		L	OCP DEG = 00b		2		
	V_ ond V		OCP DEG=01b		4		
tocp_deg	V _{DS} and V _{SENSE} overcurrent	SPI Device	OCP DEG = 10b		6		μs
001_020	deglitchtime		OCP DEG = 11b	<u> </u>	8		
		H/W Device			4		



Electrical Characteristics (continued)

at $T_A = -40^{\circ}C$ to +125°C,	$V_{VM} = 6$ to 60 V (unless	otherwise noted)

	PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
			SEN_LVL = 00b		0.25		
			SEN_LVL = 01b		0.5		
V _{SEN_OCP}	V _{SENSE} overcurrent trip voltage	SPI Device	SEN_LVL = 10b		0.75		V
	the voltage		SEN_LVL = 11b		1		
		H/W Device			1		
		SPI Device	TRETRY = 0b		4		ms
t _{RETRY}	Overcurrent retry time	SFIDEVICE	TRETRY = 1b		50		μs
une		H/W Device			4		ms
T _{OTW} ⁽¹⁾	Thermal warning te	mperature	Die temperature, TJ	130	150	165	°C
T _{OTSD} ⁽¹⁾	Thermal shutdown t	emperature	Die temperature, TJ	150	170	185	°C
T _{HYS} ⁽¹⁾	Thermal hysteresis		Die temperature, TJ		20		°C
BUCK REGUL	ATOR SUPPLY (VIN)						
I _{nSHDN}	Shutdown supply cu	ırrent	$V_{nSHDN} = 0 V$		1	3	μA
lq	Operating quiescen	t current	V _{VIN} = 12 V, no load; not switching		28		μA
M	VIN undervoltage lo	ckout	VIN Rising			4	
V _{VIN_UVLO}	threshold		VIN Falling	3			V
BUCK REGUL	ATOR SHUTDOWN (n	SHDN)	·				
$V_{\text{nSHDN}_{\text{TH}}}$	Rising nSHDN thres	hold		1.05	1.25	1.38	V
1	Input ourrent		$V_{nSHDN} = 2.3 V$		-4.2		
InSHDN	Input current		$V_{nSHDN} = 0.9 V$		-1		μA
I _{nSHDN_HYS}	Hysteresis current				-3		μA
BUCK REGUL	ATOR HIGH-SIDE MO	SFET					
R _{DS_ON}	MOSFET on resista	nce	V_{VIN} = 12 V, V_{CB} to V_{SW} = 5.8 V, T_A = 25°C		900		mΩ
BUCK REGUL	ATOR VOLTAGE REFI	ERENCE (FB)					
V _{FB}	Feedbackvoltage			0.747	0.765	0.782	V
BUCK REGUL	ATOR CURRENT LIMI	Т					
	De ek eumentlineit		V _{VIN} = 12 V, T _A = 25°C		1200		
ILIMIT Peak current lim						1700	mA
BUCK REGUL	ATOR SWITCHING (SV	V)	•				
f _{sw}	Switching frequency	1		595	700	805	kHz
D _{MAX}	Maximum duty cycl	Э			96%		
BUCK REGUL	ATOR THERMAL SHU	TDOWN	•	4			
T _{SHDN} ⁽¹⁾	Thermal shutdown t	hreshold			170		°C
T _{HYS} ⁽¹⁾	Thermal shutdown	nysteresis			10		°C

SLVSDJ3D -FEBRUARY 2017-REVISED MARCH 2022



www.ti.com

7.6 SPI Timing Requirements⁽¹⁾

at $T_A = -40^{\circ}$ C to +125°C, $V_{VM} = 6$ to 60 V (unless otherwise noted)

			MIN	NOM	MAX	UNIT
SPI (nSCS, S	SCLK, SDI, SDO)					
t _{READY}	SPI ready after enable	VM > UVLO, ENABLE = 3.3 V			1	ms
t _{CLK}	SCLK minimum period		100			ns
t _{CLKH}	SCLK minimum hightime		50			ns
t _{CLKL}	SCLK minimum low time	50			ns	
t _{SU_SDI}	SDI input data setup time	SDI input data setup time				ns
t _{H_SDI}	SDI input data hold time		30			ns
t _{D_SDO}	SDO output data delay time	SCLK high to SDO valid			30	ns
t _{SU_nSCS}	nSCS input setup time		50			ns
t _{H_nSCS}	nSCS input hold time	nSCS input hold time				ns
t _{HI_nSCS}	nSCS minimum hightime before	nSCS minimum high time before active low				ns
t _{DIS_nSCS}	nSCS disable time	nSCS high to SDO high impedance		10		ns

(1) Specified by design and characterization data





Figure 1. SPI Slave Mode Timing Diagram



7.7 Typical Characteristics




DRV8320, DRV8320R DRV8323, DRV8323R SLVSDJ3D –FEBRUARY 2017–REVISED MARCH 2022

INSTRUMENTS

Texas

Typical Characteristics (continued)



www.ti.com



8 Detailed Description

8.1 Overview

The DRV832x family of devices is an integrated 6 to 60-V gate driver for three-phase motor drive applications. These devices decrease system component count, cost, and complexity by integrating three independent halfbridge gate drivers, charge pump, and linear regulator for the supply voltages of the high-side and low-side gate drivers. The device also integrates optional triple current shunt (or current sense) amplifiers and an optional 600-mA buck regulator. A standard serial peripheral interface (SPI) provides a simple method for configuring the various device settings and reading fault diagnostic information through an external controller. Alternatively, a hardware interface (H/W) option allows for configuring the most common settings through fixed external resistors.

The gate drivers support external N-channel high-side and low-side power MOSFETs and can drive up to 1-A source, 2-A sink peak currents with a 25-mA average output current. A doubler charge pump generates the supply voltage of the high-side gate drive. This charge pump architecture regulates the VCP output to V_{VM} + 11 V. The supply voltage of the low-side gate driver is generated using a linear regulator from the VM power supply that regulates to 11 V. A Smart Gate Drive architecture provides the ability to dynamically adjust the strength of the gate drive output current which lets the gate drive resistors and diodes, reducing the component count in the bill of materials (BOM), cost, and area of the printed circuit board (PCB). The architecture also uses an internal state machine to protect against short-circuit events in the gate driver, control the half-bridge dead time, and protect against dV/dt parasitic turnon of the external power MOSFET.

The DRV8323 and DRV8323R devices integrate three bidirectional current sense amplifiers for monitoring the current level through each of the external half-bridges using a low-side shunt resistor. The gain setting of the current sense amplifier can be adjusted through the SPI or hardware interface. The SPI method provides additional flexibility to adjust the output bias point.

The DRV8320R and DRV8323R devices integrate a 600-mA buck regulator that can be used to power an external controller or other logic circuits. The buck regulator is implemented as a separate internal die that can use either the same or a different power supply than the gate driver.

In addition to the high level of device integration, the DRV832x family of devices provides a wide range of integrated protection features. These features include power supply undervoltage lockout (UVLO), charge pump undervoltage lockout (CPUV), V_{DS} overcurrent monitoring (OCP), gate driver short-circuit detection (GDF), and overtemperature shutdown (OTW and OTSD). Fault events are indicated by the nFAULT pin with detailed information available in the SPI registers on the SPI device version.


The DRV832x family of devices are available in 0.5-mm pin pitch, QFN surface-mount packages. The QFN sizes are 5 × 5 mm for the 32-pin package, 6 × 6 mm for the 40-pin package, and 7 × 7 mm for the 48-pin package.

DRV8320, DRV8320R DRV8323, DRV8323R SLVSDJ3D –FEBRUARY 2017–REVISED MARCH 2022



www.ti.com

8.2 Functional Block Diagram



Copy right © 2017, Texas Instruments Incorporated

Figure 10. Block Diagram for DRV8320H

Copy right © 2017-2022, Texas Instruments Incorporated

Product Folder Links: DRV8320 DRV8320R DRV8323 DRV8323R







Figure 11. Block Diagram for DRV8320S

TEXAS INSTRUMENTS

www.ti.com

Functional Block Diagram (continued)




Copy right © 2017, Texas Instruments Incorporated

Figure 12. Block Diagram for DRV8320RH



Functional Block Diagram (continued)



Copy right © 2017, Texas Instruments Incorporated

Figure 13. Block Diagram for DRV8320RS

TEXAS INSTRUMENTS

www.ti.com






Figure 14. Block Diagram for DRV8323H






















8.3 Feature Description

Table 1 lists the recommended values of the external components for the gate driver and the buck regulator.

COMPONENTS	PIN 1	PIN 2	RECOMMENDED
GATE DRIVER AND SE		1 111 2	
C _{VM1}	VM	PGND	X5R or X7R, 0.1-µF, VM-rated capacitor
C _{VM2}	VM	PGND	≥ 10 µF, VM-rated capacitor
C _{VCP}	VCP	VM	X5R or X7R, 16-V, 1-µF capacitor
C _{SW}	CPH	CPL	X5R or X7R, 47-nF, VM-rated capacitor
C _{DVDD}	DVDD	AGND	X5R or X7R, 1-µF, 6.3-V capacitor
R _{nFAULT}	VCC ⁽¹⁾	nFAULT	Pullup resistor
R _{SDO}	VCC ⁽¹⁾	SDO	Pullup resistor
R _{IDRIVE}	IDRIVE	AGND or DVDD	DRV832x hardware interface
R _{VDS}	VDS	AGND or DVDD	DRV832x hardware interface
R _{MODE}	MODE	AGND or DVDD	DRV832x hardware interface
R _{GAIN}	GAIN	AGND or DVDD	DRV832x hardware interface
C _{VREF}	VREF	AGND or DGND	X5R or X7R, 0.1-µF, VREF-rated capacitor
R _{ASENSE}	SPA	SNA and PGND	Sense shunt resistor
R _{BSENSE}	SPB	SNB and PGND	Sense shunt resistor
R _{CSENSE}	SPC	SNC and PGND	Sense shunt resistor
BUCK REGULATOR			
C _{VIN}	VIN	BGND	X5R or X7R, 1 to 10 µF, VM-rated capacitor
C _{BOOT}	SW	СВ	X5R or X7R, 0.1-µF, 16-V capacitor
D _{SW}	SW	BGND	Schottky diode
L _{SW}	SW	OUT ⁽²⁾	Output inductor
C _{OUT}	OUT ⁽²⁾	BGND	X5R or X7R, OUT rated capacitor
R _{FB1}	OUT ⁽²⁾	FB	Pagistar dividante est huek eutrus veltare
R _{FB2}	FB	BGND	Resistor divider to set buck output voltage

Table 1. DRV832x External Components

(1) The VCC pin is not a pin on the DRV832x family of devices, but a VCC supply voltage pullup is required for the open-drain outputs, nFAULT and SDO. These pins can also be pulled up to DVDD.

(2) The OUT pin is not a pin on the DRV8320R and DRV8323R devices, but is the regulated output voltage of the buck regulator after the output inductor.

8.3.1 Three Phase Smart Gate Drivers

The DRV832x family of devices integrates three, half-bridge gate drivers, each capable of driving high-side and low-side N-channel power MOSFETs. A doubler charge pump provides the correct gate bias voltage to the high-side MOSFET across a wide operating voltage range in addition to providing 100% support of the duty cycle. An internal linear regulator provides the gate bias voltage for the low-side MOSFETs. The half-bridge gate drivers can be used in combination to drive a three-phase motor or separately to drive other types of loads.

The DRV832x family of devices implements a Smart Gate Drive architecture which allows the user to dynamically adjust the gate drive current without requiring external resistors to limit the gate current. Additionally, this architecture provides a variety of protection features for the external MOSFETs including automatic dead time insertion, prevent of parasitic dV/dt gate turnon, and gate fault detection.

8.3.1.1 PWM Control Modes

The DRV832x family of devices provides four different PWM control modes to support various commutation and control methods. Texas Instruments does not recommend changing the MODE pin or PWM_MODE register during operation of the power MOSFETs. Set all INHx and INLx pins to logic low before changing the MODE pin or PWM_MODE register.

30 Submit Documentation Feedback

8.3.1.1.1 6x PWM Mode (PWM_MODE = 00b or MODE Pin Tied to AGND)

In 6x PWM mode, each half-bridge supports three output states: low, high, or high-impedance (Hi-Z). The corresponding INHx and INLx signals control the output state as listed in Table 2.

INLx	INHx	GLx	GHx	SHx
0	0	L	L	Hi-Z
0	1	L	Н	Н
1	0	Н	L	L
1	1	L	L	Hi-Z

Table 2. 6x PWM Mode Truth Table

8.3.1.1.2 3x PWM Mode (PWM_MODE = 01b or MODE Pin = 47 k Ω to AGND)

In 3x PWM mode, the INHx pin controls each half-bridge and supports two output states: low or high. The INLx pin is used to put the half bridge in the Hi-Z state. If the Hi-Z state is not required, tie all INLx pins to logic high. The corresponding INHx and INLx signals control the output state as listed in Table 3.

INLx	INHx	GLx	GHx	SHx
0	Х	L	L	Hi-Z
1	0	Н	L	L
1	1	L	Н	Н

Table 3. 3x PWM Mode Truth Table

8.3.1.1.3 1x PWM Mode (PWM MODE = 10b or MODE Pin = Hi-Z)

In 1x PWM mode, the DRV832x family of devices uses 6-step block commutation tables that are stored internally. This feature allows for a three-phase BLDC motor to be controlled using one PWM sourced from a simple controller. The PWM is applied on the INHA pin and determines the output frequency and duty cycle of the half-bridges.

The half-bridge output states are managed by the INLA, INHB, and INLB pins which are used as state logic inputs. The state inputs can be controlled by an external controller or connected directly to the digital outputs of the Hall effect sensor from the motor (INLA = HALL_A, INHB = HALL_B, INLB = HALL_C). The 1x PWM mode usually operates with synchronous rectification (low-side MOSFET recirculation); however, the mode can be configured to use asynchronous rectification (MOSFET body diode freewheeling) on SPI devices. This configuration is set using the 1PWM_COM bit in the SPI registers.

The INHC input controls the direction through the 6-step commutation table which is used to change the direction of the motor when Hall effect sensors are directly controlling the state of the INLA, INHB, and INLB inputs. Tie the INHC pin low if this feature is not required.

The INLC input brakes the motor by turning off all high-side MOSFETs and turning on all low-side MOSFETs when the INLC pin is pulled low. This brake is independent of the state of the other input pins. Tie the INLC pin high if this feature is not required.

LOGIC AND HALL INPUTS									GATE DRIVE OUTPUTS ⁽¹⁾				
STATE		INHC = 0			INHC = 1		PHA	SE A	PHA	SE B	PHASE C		DESCRIPTION
STATE	INLA	INHB	INLB	INLA	INHB	INLB	GHA	GLA	GHB	GLB	GHC	GLC	DESCRIPTION
Stop	0	0	0	0	0	0	L	L	L	L	L	L	Stop
Align	1	1	1	1	1	1	PWM	!PWM	L	Н	L	Н	Align
1	1	1	0	0	0	1	L	L	PWM	!PWM	L	Н	$B\toC$
2	1	0	0	0	1	1	PWM	!PWM	L	L	L	Н	$A \to C$
3	1	0	1	0	1	0	PWM	!PWM	L	Н	L	L	$A \to B$
4	0	0	1	1	1	0	L	L	L	Н	PWM	!PWM	$C\toB$
5	0	1	1	1	0	0	L	Н	L	L	PWM	!PWM	$C\toA$
6	0	1	0	1	0	1	L	Н	PWM	!PWM	L	L	$B\toA$

Table 4. Synchronous 1x PWM Mode

(1) *!PWM* is the inverse of the PWM signal.

Copy right © 2017-2022, Texas Instruments Incorporated



Table 5. Asynchronous 1x PWM Mode 1PWM_COM = 1 (SPI Only)

	LOGIC AND HALL INPUTS								GATE DRIVE OUTPUTS					
STATE		INHC = 0			INHC = 1		PHA	SE A	PHA	SE B	PHA	SE C	DESCRIPTION	
STATE	INLA	INHB	INLB	INLA	INHB	INLB	GHA	GLA	GHB	GLB	GHC	GLC	DESCRIPTION	
Stop	0	0	0	0	0	0	L	L	L	L	L	L	Stop	
Align	1	1	1	1	1	1	PWM	L	L	Н	L	Н	Align	
1	1	1	0	0	0	1	L	L	PWM	L	L	Н	$B\toC$	
2	1	0	0	0	1	1	PWM	L	L	L	L	Н	$A \to C$	
3	1	0	1	0	1	0	PWM	L	L	Н	L	L	$A \to B$	
4	0	0	1	1	1	0	L	L	L	Н	PWM	L	$C\toB$	
5	0	1	1	1	0	0	L	Н	L	L	PWM	L	$C\toA$	
6	0	1	0	1	0	1	L	Н	PWM	L	L	L	$B\toA$	

Figure 18 and Figure 19 show the different possible configurations in 1x PWM mode.




Figure 18. 1x PWM—Simple Controller

Figure 19. 1x PWM—Hall Effect Sensor

8.3.1.1.4 Independent PWM Mode (PWM_MODE = 11b or MODE Pin Tied to DVDD)

In independent PWM mode, the corresponding input pin independently controls each high-side and low-side gate driver. This control mode lets the DRV832x family of devices drive separate high-side and low-side loads with each half-bridge. These types of loads include unidirectional brushed DC motors, solenoids, and low-side and high-side switches. In this mode, if the system is configured in a half-bridge configuration, turning on both the high-side and low-side MOSFETs at the same time causes shoot-through.

INLx	INHx	GLx	GHx
0	0	L	L
0	1	L	Н
1	0	Н	L
1	1	Н	Н

Table 6. Independent PWM Mode Truth Table



Because the high-side and low-side V_{DS} overcurrent monitors share the SHx sense line, using the monitors when both the high-side and low-side gate drivers of one half-bridge are split and being used is not possible. In this case, connect the SHx pin to the high-side driver and disable the V_{DS} overcurrent monitors as shown in Figure 20.




Figure 20. Independent PWM High-Side and Low-Side Drivers

If the half-bridge is used to implement only a high-side or low-side driver, using the V_{DS} overcurrent monitors is still possible. Connect the SHx pin as shown in Figure 21 or Figure 22. The unused gate driver and the corresponding input can stay disconnected.




Figure 21. One High-Side Driver



8.3.1.2 Device Interface Modes

The DRV832x family of devices supports two different interface modes (SPI and hardware) to let the end application design for either flexibility or simplicity. The two interface modes share the same four pins, allowing the different versions to be pin-to-pin compatible. This compatibility lets application designers evaluate with one interface version and potentially switch to another with minimal modifications to their design.

Copy right © 2017-2022, Texas Instruments Incorporated

DRV8320, DRV8320R DRV8323, DRV8323R SLVSDJ3D – FEBRUARY 2017 – REVISED MARCH 2022



8.3.1.2.1 Serial Peripheral Interface (SPI)

The SPI devices support a serial communication bus that lets an external controller send and receive data with the DRV832x. This support lets the external controller configure device settings and read detailed fault information. The interface is a four wire interface using the SCLK, SDI, SDO, and nSCS pins which are described as follows:

- The SCLK pin is an input that accepts a clock signal to determine when data is captured and propagated on the SDI and SDO pins.
- The SDI pin is the data input.
- The SDO pin is the data output. The SDO pin uses an open-drain structure and requires an external pullup resistor.
- The nSCS pin is the chip select input. A logic low signal on this pin enables SPI communication with the DRV832x.


For more information on the SPI, see the SPI Communication section.

8.3.1.2.2 Hardware Interface

Hardware interface devices convert the four SPI pins into four resistor-configurable inputs which are GAIN, IDRIVE, MODE, and VDS. This conversion lets the application designer configure the most common device settings by tying the pin logic high or logic low, or with a simple pullup or pulldown resistor. This removes the requirement for an SPI bus from the external controller. General fault information can still be obtained through the nFAULT pin.

- The GAIN pin configures the gain of the current sense amplifier.
- The IDRIVE pin configures the gate drive current strength.
- The MODE pin configures the PWM control mode.
- The VDS pin configures the voltage threshold of the V_{DS} overcurrent monitors.

For more information on the hardware interface, see the *Pin Diagrams* section.








Figure 24. Hardware Interface

8.3.1.3 Gate Driver Voltage Supplies

The voltage supply for the high-side gate driver is created using a doubler charge pump that operates from the VM voltage supply input. The charge pump lets the gate driver correctly bias the high-side MOSFET gate with respect to the source across a wide input supply voltage range. The charge pump is regulated to keep a fixed output voltage of V_{VM} + 11 V and supports an average output current of 25 mA. When V_{VM} is less than 12 V, the charge pump operates in full doubler mode and generates V_{VCP} = 2 × V_{VM} – 1.5 V when unloaded. The charge pump is continuously monitored for undervoltage events to prevent under-driven MOSFET conditions. The charge pump requires a X5R or X7R, 1-µF, 16-V ceramic capacitor between the VM and VCP pins to act as the storage capacitor. Additionally, a X5R or X7R, 47-nF, VM-rated ceramic capacitor is required between the CPH and CPL pins to act as the flying capacitor.






Figure 25. Charge Pump Architecture

The voltage supply of the low-side gate driver is created using a linear regulator that operates from the VM voltage supply input. The linear regulator lets the gate driver correctly bias the low-side MOSFET gate with respect to ground. The linear regulator output is fixed at 11 V and supports an output current of 25 mA.

8.3.1.4 Smart Gate Drive Architecture

The DRV832x gate drivers use an adjustable, complimentary, push-pull topology for both the high-side and low-side drivers. This topology allows for both a strong pullup and pulldown of the external MOSFET gates.

Additionally, the gate drivers use a Smart Gate Drive architecture to provide additional control of the external power MOSFETs, additional steps to protect the MOSFETs, and optimal tradeoffs between efficiency and robustness. This architecture is implemented through two components called IDRIVE and TDRIVE which are described in the *IDRIVE: MOSFET Slew-Rate Control* section and *TDRIVE: MOSFET Gate Drive Control* section. Figure 26 shows the high-level functional block diagram of the gate driver.

The IDRIVE gate drive current and TDRIVE gate drive time should be initially selected based on the parameters of the external power MOSFET used in the system and the desired rise and fall times (see the *Application and Implementation* section).

The high-side gate driver also implements a Zener clamp diode to help protect the external MOSFET gate from overvoltage conditions in the case of external short-circuit events on the MOSFET.






Figure 26. Gate Driver Block Diagram

8.3.1.4.1 IDRIVE: MOSFET Slew-Rate Control

The IDRIVE component implements adjustable gate drive current to control the MOSFET V_{DS} slew rates. The MOSFET V_{DS} slew rates are a critical factor for optimizing radiated emissions, energy, and duration of diode recovery spikes, dV/dt gate turnon resulting in shoot-through, and switching voltage transients related to parasitics in the external half-bridge. The IDRIVE component operates on the principal that the MOSFET V_{DS} slew rates are predominately determined by the rate of gate charge (or gate current) delivered during the MOSFET Q_{GD} or Miller charging region. By letting the gate driver adjust the gate current, the gate driver can effectively control the slew rate of the external power MOSFETs.

The IDRIVE component lets the DRV832x family of devices dynamically switch between gate drive currents either through a register setting on SPI devices or the IDRIVE pin on hardware interface devices. The SPI devices provide 16 I_{DRIVE} settings ranging from 10-mA to 1-A source and 20-mA to 2-A sink. Hardware interface devices provide 7 I_{DRIVE} settings within the same ranges. The setting of the gate drive current is delivered to the gate during the turnon and turnoff of the external power MOSFET for the t_{DRIVE} duration. After the MOSFET turnon or turnoff, the gate driver switches to a smaller hold I_{HOLD} current to improve the gate driver efficiency. For additional details on the IDRIVE settings, see the *Register Maps* section for the SPI devices and the *Pin Diagrams* section for the hardware interface devices.

8.3.1.4.2 TDRIVE: MOSFET Gate Drive Control

The TDRIVE component is an integrated gate drive state machine that provides automatic dead time insertion through handshaking between the high-side and low-side gate drivers, parasitic dV/dt gate turnon prevention, and MOSFET gate fault detection.

The first component of the TDRIVE state machine is automatic dead time insertion. Dead time is period of time between the switching of the external high-side and low-side MOSFETs to make sure that they do not cross conduct and cause shoot-through. The DRV832x family of devices uses V_{GS} voltage monitors to measure the MOSFET gate-to-source voltage and determine the correct time to switch instead of relying on a fixed time value. This feature lets the dead time of the gate driver adjust for variation in the system such as temperature drift and variation in the MOSFET parameters. An additional digital dead time (t_{DEAD}) can be inserted and is adjustable through the registers on SPI devices.



The second component of the TDRIVE state machine is parasitic dV/dt gate turnon prevention. To implement this component, the TDRIVE state machine enables a strong pulldown current (I_{STRONG}) on the opposite MOSFET gate whenever a MOSFET is switching. The strong pulldown occurs for the TDRIVE duration. This feature helps remove parasitic charge that couples into the MOSFET gate when the voltage half-bridge switch node slews rapidly.

The third component of the TDRIVE state machine implements a scheme for gate fault detection to detect pin-topin solder defects, a MOSFET gate failure, or stuck-high or stuck-low voltage condition on a MOSFET gate. This implementation occurs with a pair of V_{GS} gate-to-source voltage monitors for each half-bridge gate driver. When the gate driver receives a command to change the state of the half-bridge, it starts to monitor the gate voltage of the external MOSFET. If the V_{GS} voltage has not reached the correct threshold at the end of the t_{DRIVE} period,, the gate driver reports a fault. To make sure that a false fault is not detected, a t_{DRIVE} time should be selected that is longer than the time required to charge or discharge the MOSFET gate. The t_{DRIVE} time does not increase the PWM time and will terminate if another PWM command is received while active. For additional details on the TDRIVE settings, see the *Register Maps* section for SPI devices. The hardware interface devices have a fixed t_{DRIVE} of 4 µs.

VINHX VINLx V_{GHx} t_{DEAD} t_{DEAD} HOLD **I**DRIVE HOLD ISTRONG HOLD ISTRONG HOLD IGHX **I**DRIVE HOLD t_{DRIVE} ^tDRIVE V_{GLx} t_{DEAD} t_{DEAD} ISTRONG HOLD **I**DRIVE HOLD HOLD HOLD ISTRONG $I_{GLx} =$ HOLD **I**DRIVE t_{DRIVE} **t**DRIVE Figure 27. TDRIVE State Machine

Figure 27 shows an example of the TDRIVE state machine in operation.

8.3.1.4.3 Propagation Delay

The propagation delay time (t_{pd}) is measured as the time between an input logic edge to a detected output change. This time has three parts consisting of the digital input deglitcher delay, the digital propagation delay, and the delay through the analog gate drivers.

The input deglitcher prevents high-frequency noise on the input pins from affecting the output state of the gate drivers. To support multiple control modes and dead time insertion, a small digital delay is added as the input command propagates through the device. Lastly, the analog gate drivers have a small delay that contributes to the overall propagation delay of the device.

8.3.1.4.4 MOSFET V_{DS} Monitors

The gate drivers implement adjustable V_{DS} voltage monitors to detect overcurrent or short-circuit conditions on the external power MOSFETs. When the monitored voltage is greater than the V_{DS} trip point (V_{VDS_OCP}) for longer than the deglitch time (t_{OCP}), an overcurrent condition is detected and action is taken according to the device V_{DS} fault mode.

Copy right © 2017-2022, Texas Instruments Incorporated

DRV8320, DRV8320R DRV8323, DRV8323R SLVSDJ3D – FEBRUARY 2017 – REVISED MARCH 2022



The high-side V_{DS} monitors measure the voltage between the VDRAIN and SHx pins. In devices with three current sense amplifiers (DRV8323 and DRV8323R), the low-side V_{DS} monitors measure the voltage between the SHx and SPx pins. If the current sense amplifier is unused, tie the SP pins to the common ground point of the external half-bridges. On device options without the current sense amplifiers (DRV8320 and DRV8320R) the low-side V_{DS} monitor measures between the SHx and SLX pins.

For the SPI devices, the reference point of the low-side V_{DS} monitor can be changed between the SPx and SNx pins if desired with the LS_REF register setting.

The V_{VDS_OCP} threshold is programmable from 0.06 V to 1.88 V. For additional information on the V_{DS} monitor levels, see the *Register Maps* section for SPI devices and in the *Pin Diagrams* section hardware interface device.




Figure 28. DRV8320 and DRV8320R V_{DS} Monitors




Figure 29. DRV8323 and DRV8323R V_{DS} Monitors

8.3.1.4.5 VDRAIN Sense Pin

The DRV832x family of devices provides a separate sense pin for the common point of the high-side MOSFET drain. This pin is called VDRAIN. This pin lets the sense line for the overcurrent monitors (VDRAIN) and the power supply (VM) stay separate and prevent noise on the VDRAIN sense line. This separation also lets implementation of a small filter on the gate driver supply (VM) or insertion of a boost converter to support lower voltage operation if desired. Care must still be used when designing the filter or separate supply because VM is still the reference point for the VCP charge pump that supplies the high-side gate drive voltage (V_{GSH}). The VM supply must not drift too far from the VDRAIN supply to avoid violating the V_{GS} voltage specification of the external power MOSFETs.

8.3.2 DVDD Linear Voltage Regulator

A 3.3-V, 30-mA linear regulator is integrated into the DRV832x family of devices and is available for use by external circuitry. This regulator can provide the supply voltage for a low-power MCU or other circuitry supporting low current. The output of the DVDD regulator should be bypassed near the DVDD pin with a X5R or X7R, $1-\mu$ F, 6.3-V ceramic capacitor routed directly back to the adjacent AGND ground pin.

The DVDD nominal, no-load output voltage is 3.3 V. When the DVDD load current exceeds 30 mA, the regulator functions like a constant-current source. The output voltage drops significantly with a current load greater than 30 mA.

Copy right © 2017-2022, Texas Instruments Incorporated



(1)

(2)




Figure 30. DVDD Linear Regulator Block Diagram

Use Equation 1 to calculate the power dissipated in the device by the DVDD linear regulator.

 $\mathsf{P} = \left(\mathsf{V}_{\mathsf{VM}} - \mathsf{V}_{\mathsf{DVDD}}\right) \times \mathsf{I}_{\mathsf{DVDD}}$

For example, at a V_{VM} of 24 V, drawing 20 mA out of DVDD results in a power dissipation as shown in Equation 2.

$$P = (24 V - 3.3 V) \times 20 mA = 414 mW$$

8.3.3 Pin Diagrams

Figure 31 shows the input structure for the logic level pins, INHx, INLx, CAL, ENABLE, nSCS, SCLK, and SDI. The input can be driven with a voltage or external resistor.




Figure 31. Logic-Level Input Pin Structure

Figure 32 shows the structure of the four level input pins, MODE and GAIN, on hardware interface devices. The input can be set with an external resistor.




Figure 32. Four Level Input Pin Structure

Figure 33 shows the structure of the seven level input pins, IDRIVE and VDS, on hardware interface devices. The input can be set with an external resistor.








Figure 34 shows the structure of the open-drain output pins, nFAULT and SDO. The open-drain output requires an external pullup resistor to function correctly.




Figure 34. Open-Drain Output Pin Structure


8.3.4 Low-Side Current Sense Amplifiers (DRV8323 and DRV8323R Only)

The DRV8323 and DRV8323R integrate three, high-performance low-side current sense amplifiers for current measurements using low-side shunt resistors in the external half-bridges. Low-side current measurements are commonly used to implement overcurrent protection, external torque control, or brushless DC commutation with the external controller. All three amplifiers can be used to sense the current in each of the half-bridge legs or one amplifier can be used to sense the sum of the half-bridge legs. The current sense amplifiers include features such as programmable gain, offset calibration, unidirectional and bidirectional support, and a voltage reference pin (VREF). If any of the three current sense amplifiers are not being used, they can be tied off by shorting the SNx pin to the SPx pin and leaving the SOx pin unconnected. Remember to connect the SPx or SNx pin to the low-side FET source, so that the overcurrent VDS monitor is still functional

8.3.4.1 Bidirectional Current Sense Operation


The SOx pin on the DRV8323 and DRV8323R outputs an analog voltage equal to the voltage across the SPx and SNx pins multiplied by the gain setting (G_{CSA}). The gain setting is adjustable between four different levels (5 V/V, 10 V/V, 20 V/V, and 40 V/V). Use Equation 3 to calculate the current through the shunt resistor.

$$I = \frac{\frac{V_{VREF}}{2} - V_{SOx}}{G_{CSA} \times R_{SENSE}}$$
















Figure 37. Bidirectional Current Sense Regions



8.3.4.2 Unidirectional Current Sense Operation (SPI only)


On the DRV8323 and DRV8323R SPI devices, use the VREF_DIV bit to remove the VREF divider. In this case the current sense amplifier operates unidirectionally and the SOx pin outputs an analog voltage equal to the voltage across the SPx and SNx pins multiplied by the gain setting (G_{CSA}). Use Equation 4 to calculate the current through the shunt resistor.













8.3.4.3 Auto Offset Calibration

To minimize DC offset, the DRV8323 and DRV8323R devices can perform an automatic offset calibration through the SPI registers (CSA_CAL_X) or CAL pin. When the calibration is enabled, the inputs to the amplifier are shorted, the load is disconnected, and the gain (G_{CSA}) of the amplifier is changed to the 40 V/V setting. The amplifier then goes through an automatic trim routine to minimize the input offset. The automatic trim routine requires 100 µs to complete after the calibration is enabled. After this time, the inputs of the amplifier stay shorted, the load stays disconnected, and the gain stays at 40 V/V if further offset calibration is desired to be done by the external controller. To complete the offset calibration, the CSA_CAL_X registers or CAL pin should be taken back low. The gain is returned to the original gain setting after the device completes calibration. For the best results, perform offset calibration when the external MOSFETS are not switching to decrease the potential noise impact to the amplifier. When the current sense amplifiers go into a calibration mode, the VREF pin is set to bidirectional mode if the device is configured in unidirectional mode. The setting of the VREF pin affects the channels all three current sense amplifier, even if the CSA_CAL_X register is not set for the all channels.

8.3.4.4 MOSFET VDs Sense Mode (SPI Only)

The current sense amplifiers on the DRV8323 and DRV8323R SPI devices can be configured to amplify the voltage across the external low-side MOSFET V_{DS} . This configuration lets the external controller measure the voltage drop across the MOSFET $R_{DS(on)}$ without the shunt resistor and then calculate the half-bridge current level.

To enable this mode set the CSA_FET bit to 1. The positive input of the amplifier is then internally connected to the SHx pin with an internal clamp to prevent high voltage on the SHx pin from damaging the sense amplifier inputs. During this mode of operation, the SPx pins should stay disconnected. When the CSA_FET bit is set to 1, the negative reference for the low-side V_{DS} monitor is automatically set to the SNx pin, regardless of the state of the state of the LS_REF bit. This setting is implemented to prevent disabling of the low-side V_{DS} monitor.

If the system operates in MOSFET V_{DS} current sense mode, route the SHx and SNx pins with Kelvin connections across the drain and source of the external low-side MOSFETs.

Copy right © 2017-2022, Texas Instruments Incorporated



DRV8320, DRV8320R DRV8323, DRV8323R

SLVSDJ3D - FEBRUARY 2017-REVISED MARCH 2022

www.ti.com






Figure 42. V_{DS} Current Sense Mode

When operating in MOSFET V_{DS} current sense mode, the amplifier is enabled at the end of the t_{DRIVE} time. At this time, the amplifier input is connected to the SHx pin, and the SOx output is valid. When the low-side MOSFET receives a signal to turn off, the amplifier inputs, SPx and SNx, are shorted together internally.

8.3.5 Step-Down Buck Regulator

The DRV8320R and DRV8323R have an integrated buck regulator (LMR16006) to supply power for an external controller or system voltage rail. The LMR16006 device is a 60-V, 600-mA, buck (step-down) regulator.

The buck regulator has a very-low quiescent current during light loads to prolong battery life. The LMR16006 device improves performance during line and load transients by implementing a constant-frequency current-mode control scheme which requires less output capacitance and simplifies frequency compensation design. The LMR16006 is the LMR16006X device version that uses a 0.7-MHz switching frequency.

The LMR16006 device decreases the external component count by integrating the bootstrap recharge diode. The bias voltage for the integrated high-side MOSFET is supplied by a capacitor on the CB to SW pin. The bootstrap capacitor voltage is monitored by a UVLO circuit and turns off the high-side MOSFET when the boot voltage falls lower than a preset threshold.

The LMR16006 device can operate at high duty cycles because of the boot UVLO and then refreshes the wimp MOSFET. The output voltage can be stepped down to as low as the 0.8-V reference. The internal soft-start feature minimizes inrush currents.

For additional details, a block diagram showing the wimp MOSFET, and design information refer to the *LMR16006 SIMPLE SWITCHER*® 60 V 0.6 A Buck Regulators With High Efficiency Eco-mode data sheet.

TEXAS INSTRUMENTS

www.ti.com

(5)

8.3.5.1 Fixed Frequency PWM Control

The LMR16006 device has a fixed switching frequency and implements peak current-mode control. The output voltage is compared through external resistors on the FB pin to an internal voltage reference by an error amplifier which drives the internal COMP node. An internal oscillator initiates the turnon of the high-side power switch. The error amplifier output is compared to the high-side power switch current. When the power switch current reaches the level set by the internal COMP voltage, the power switch turns off. The internal COMP node voltage increases and decreases as the output current increases and decreases. The device implements a current limit by clamping the COMP node voltage to a maximum level.

8.3.5.2 Bootstrap Voltage (CB)

The LMR16006 device has an integrated bootstrap regulator, and requires a small ceramic capacitor between the CB and SW pins to provide the gate drive voltage for the high-side MOSFET. The CB capacitor is refreshed when the high-side MOSFET is off and the low-side diode conducts. To improve dropout, the LMR16006 device is designed to operate at 100% duty cycle as long as the CB to SW pin voltage is greater than 3 V. When the voltage from the CB to SW pin drops to less than 3 V, the high-side MOSFET turns off using a UVLO circuit which lets the low-side diode conduct and refresh the charge on the CB capacitor. Because the supply current sourced from the CB capacitor is low, the high-side MOSFET can stay on for more switching cycles than are required to refresh the capacitor. Therefore, the effective duty cycle of the switching regulator is high. Attention must be given in maximum duty-cycle applications with a light load. To make sure the SW pin can be pulled to ground to refresh the CB capacitor, an internal circuit charges the CB capacitor when the load is light or the device is working in dropout condition.

8.3.5.3 Output Voltage Setting

The output voltage is set using the feedback pin (FB) and a resistor divider connected to the output as shown in Figure 53. The voltage of the feedback pin is 0.765 V, so the ratio of the feedback resistors sets the output voltage according to $\frac{1}{5}$ quation 5.

$$V_{O} = 0.765 \text{ V} \times \left(1 + \left[\frac{\text{R1}}{\text{R2}}\right]\right)$$

Typically the starting value of R2 is from 1 k Ω to 100 k Ω . Use Equation 6 to calculate the value of R1.

$R1 = R2 \times \left(\left[\frac{V_0}{0.765 \text{ V}} \right] - 1 \right]$) (6)

8.3.5.4 Enable nSHDN and VIN Undervoltage Lockout

The nSHDN pin of the LMR16006 device is an input that is tolerant of high voltages with an internal pullup circuit. The device can be enabled even if the nSHDN pin is floating. The regulator can also be turned on using 1.23-V or higher logic signals. If the use of a higher voltage is desired because of system or other constraints, a 100-k Ω or larger value resistor is recommended between the applied voltage and the nSHDN pin to help protect the device. When the nSHDN pin is pulled down to 0 V, the device turns off and goes to the lowest shutdown current mode. In shutdown mode the supply current decreases to approximately 1 μ A. If the shutdown function is unused, the nSHDN pin can be tied to the VIN pin with a 100-k Ω resistor. The maximum voltage to the nSHDN pin should not exceed 60 V. The LMR16006 device has an internal UVLO circuit to shut down the output if the input voltage falls lower than an UVLO threshold level that is internally fixed. Shutting down the output in this way makes sure the regulator is not latched into an unknown state during low input voltage conditions. The regulator powers up when the input voltage exceeds the voltage level. If the UVLO voltage must be higher, use the nSHDN pin to adjust the system UVLO by using external resistors.

8.3.5.5 Current Limit

The LMR16006 device implements current-mode control which uses the internal COMP voltage to turn off the high-side MOSFET on a cycle-by-cycle basis. Each cycle, the switch current and internal COMP voltage are compared. When the peak switch current intersects the COMP voltage, the high-side switch turns off. During overcurrent conditions that pull the output voltage low, the error amplifier responds by driving the COMP node high, increasing the switch current. The error amplifier output is clamped internally causing it to function as a switch current limit.

46 Submit Documentation Feedback



8.3.5.6 Overvoltage Transient Protection

The LMR16006 device incorporates an overvoltage transient protection (OVTP) circuit to minimize voltage overshoot when recovering from output fault conditions or strong unloaded transients on power supply designs with low-value output capacitance. For example, when the power supply output is overloaded, the error amplifier compares the actual output voltage to the internal reference voltage. If the voltage of the FB pin is lower than the internal reference voltage for a considerable time, the output of the error amplifier responds by clamping the error amplifier output to a high voltage, therefore requesting the maximum output current. When the condition clears, the regulator output rises and the error amplifier output transitions to the steady-state duty cycle. In some applications, the output voltage of the power supply can respond faster than the error amplifier output capacitor by implementing a circuit to compare the FB pin voltage to the OVTP threshold which is 108% of the internal voltage reference. If the FB pin voltage is greater than the OVTP threshold, the high-side MOSFET is disabled preventing current from flowing to the output and minimizing output overshoot. When the FB voltage drops lower than the OVTP threshold, the high-side MOSFET can turn on at the next clock cycle.

8.3.5.7 Thermal Shutdown

The device implements an internal thermal shutdown to help protect the device if the junction temperature exceeds 170°C (typical). The thermal shutdown forces the device to stop switching when the junction temperature exceeds the thermal trip threshold. When the junction temperature decreases to less than 160°C (typical), the device reinitiates the power-up sequence.

8.3.6 Gate Driver Protective Circuits

The DRV832x family of devices is protected against VM undervoltage, charge pump undervoltage, MOSFET V_{DS} overcurrent, gate driver shorts, and overtemperature events.

FAULT	CONDITION	CONFIGURATION	REPORT	GATE DRIVER	LOGIC	RECOVERY
VM undervoltage (UVLO)	V _{VM} < V _{UVLO}	—	nFAULT	Hi-Z	Disabled	Automatic: V _{VM} > V _{UVLO}
Charge pump		DIS_CPUV = 0b	nFAULT	Hi-Z	Active	Automatic:
undervoltage (CPUV)	$V_{VCP} < V_{CPUV}$	DIS_CPUV = 1b	None	Active	Active	$V_{VCP} > V_{CPUV}$
		OCP_MODE = 00b	nFAULT	Hi-Z	Active	Latched: CLR_FLT, ENABLE Pulse
V _{DS} overcurrent (VDS_OCP)	$V_{DS} > V_{VDS_OCP}$	OCP_MODE = 01b	nFAULT	Hi-Z	Active	Retry. t _{RETRY}
		OCP_MODE = 10b	nFAULT	Active	Active	No action
		OCP_MODE = 11b	None	Active	Active	No action
		OCP_MODE = 00b	nFAULT	Hi-Z	Active	Latched: CLR_FLT, ENABLE Pulse
V _{SENSE} overcurrent	$V_{SP} > V_{SEN_OCP}$	OCP_MODE = 01b	nFAULT	Hi-Z	Active	Retry. t _{RETRY}
(SEN_OCP)		OCP_MODE = 10b	nFAULT	Active	Active	No action
		OCP_MODE = 11b or DIS_SEN = 1b	None	Active	Active	No action
Gate driver fault (GDF)	Gate voltage stuck > t _{DRME}	DIS_GDF = 0b	nFAULT	Hi-Z	Active	Latched: CLR_FLT, ENABLE Pulse
(GDF)		DIS_GDF = 1b	None	Active	Active	No action
Thermal		OTW_REP = 0b	None	Active	Active	No action
warning (OTW)	T _J > T _{OTW}	OTW_REP = 1b	nFAULT	Active	Active	Automatic: T _J < T _{OTW} – T _{HYS}
Thermal shutdown (OTSD)	T _J > T _{OTSD}	_	nFAULT	Hi-Z	Active	Automatic: T _J < T _{OTSD} – T _{HYS}

Table 7. Fault Action and Response (SPI Devices)



8.3.6.1 VM Supply Undervoltage Lockout (UVLO)

If at any time the input supply voltage on the VM pin falls lower than the V_{UVLO} threshold, all of the external MOSFETs are disabled, the charge pump is disabled, and the nFAULT pin is driven low. The FAULT and VM_UVLO bits are also latched high in the registers on SPI devices. Normal operation starts again (gate driver operation and the nFAULT pin is released) when the VM undervoltage condition clears. The VM_UVLO bit stays set until cleared through the CLR_FLT bit or an ENABLE pin reset pulse (t_{RST}).

8.3.6.2 VCP Charge Pump Undervoltage Lockout (CPUV)

If at any time the voltage on the VCP pin (charge pump) falls lower than the V_{CPUV} threshold voltage of the charge pump, all of the external MOSFETs are disabled and the nFAULT pin is driven low. The FAULT and CPUV bits are also latched high in the registers on SPI devices. Normal operation starts again (gate driver operation and the nFAULT pin is released) when the VCP undervoltage condition clears. The CPUV bit stays set until cleared through the CLR_FLT bit or an ENABLE pin reset pulse (t_{RST}). Setting the DIS_CPUV bit high on the SPI devices disables this protection feature. On hardware interface devices, the CPUV protection is always enabled.

8.3.6.3 MOSFET VDS Overcurrent Protection (VDS_OCP)

A MOSFET overcurrent event is sensed by monitoring the V_{DS} voltage drop across the external MOSFET R_{DS(on)}. If the voltage across an enabled MOSFET exceeds the V_{VDS_OCP} threshold for longer than the t_{OCP_DEG} deglitch time, a VDS_OCP event is recognized and action is done according to the OCP_MODE bit. On hardware interface devices, the V_{VDS_OCP} threshold is set with the VDS pin, the t_{OCP_DEG} is fixed at 4 μ s, and the OCP_MODE bit is configured for 4-ms automatic retry but can be disabled by tying the VDS pin to DVDD. On SPI devices, the V_{VDS_OCP} threshold is set through the VDS_LVL SPI register, the t_{OCP_DEG} is set through the OCP_DEG SPI register, and the OCP_MODE bit can operate in four different modes: V_{DS} latched shutdown, V_{DS} automatic retry, V_{DS} report only, and V_{DS} disabled.

8.3.6.3.1 V_{DS} Latched Shutdown (OCP_MODE = 00b)

After a VDS_OCP event in this mode, all external MOSFETs are disabled and the nFAULT pin is driven low. When the external MOSFETs are disabled in this way, the driver automatically uses a lower setting for the gate drive current instead of the programmed IDRIVE setting. This setting lets any large current that may be present to be switched off slowly to minimize any inductive kickback caused by parasitic capacitance in the system. The FAULT, VDS_OCP, and corresponding MOSFET OCP bits are latched high in the SPI registers. Normal operation starts again (gate driver operation and the nFAULT pin is released) when the VDS_OCP condition clears and a clear faults command is issued either through the CLR_FLT bit or an ENABLE reset pulse (t_{RST}).

8.3.6.3.2 V_{DS} Automatic Retry (OCP_MODE = 01b)

After a VDS_OCP event in this mode, all the external MOSFETs are disabled and the nFAULT pin is driven low. When the external MOSFETs are disabled in this way, the driver automatically uses a lower setting for the gate drive current instead of the programmed IDRIVE setting. This setting lets any large current that may be present to be switched off slowly to minimize any inductive kickback caused by parasitic capacitance in the system. The FAULT, VDS_OCP, and corresponding MOSFET OCP bits are latched high in the SPI registers. Normal operation starts again automatically (gate driver operation and the nFAULT pin is released) after the t_{RETRY} time elapses. The FAULT, VDS_OCP, and MOSFET OCP bits stay latched until the t_{RETRY} period expires.

8.3.6.3.3 V_{DS} Report Only (OCP_MODE = 10b)

No protective action occurs after a VDS_OCP event in this mode. The overcurrent event is reported by driving the nFAULT pin low and latching the FAULT, VDS_OCP, and corresponding MOSFET OCP bits high in the SPI registers. The gate drivers continue to operate as usual. The external controller manages the overcurrent condition by acting appropriately. The reporting clears (nFAULT pin is released) when the VDS_OCP condition clears and a clear faults command is issued either through the CLR_FLT bit or an ENABLE reset pulse (t_{RST}).

8.3.6.3.4 V_{DS} Disabled (OCP_MODE = 11b)

No action occurs after a VDS_OCP event in this mode.



8.3.6.4 VSENSE Overcurrent Protection (SEN_OCP)

Half-bridge overcurrent is also monitored by sensing the voltage drop across the external current sense resistor with the SP pin. If at any time the voltage on the SP input of the CSA exceeds the V_{SEN_OCP} threshold for longer than the t_{OCP_DEG} deglitch time, a SEN_OCP event is recognized and action is done according to the OCP_MODE bit. On hardware interface devices, the V_{SENSE} threshold is fixed at 1 V, t_{OCP_DEG} is fixed at 4 μ s, and the OCP_MODE for V_{SENSE} is fixed for 4-ms automatic retry. On SPI devices, the V_{SENSE} threshold is set through the SEN_LVL SPI register, the t_{OCP_DEG} is set through the OCP_DEG SPI register, and the OCP_MODE bit can operate in four different modes: V_{SENSE} latched shutdown, V_{SENSE} automatic retry, V_{SENSE} report only, and V_{SENSE} disabled.

8.3.6.4.1 V_{SENSE} Latched Shutdown (OCP_MODE = 00b)

After a SEN_OCP event in this mode, all the external MOSFETs are disabled and the nFAULT pin is driven low. The FAULT and SEN_OCP bits are latched high in the SPI registers. Normal operation starts again (gate driver operation and the nFAULT pin is released) when the SEN_OCP condition clears and a clear faults command is issued either through the CLR_FLT bit or an ENABLE reset pulse (t_{RST}).

8.3.6.4.2 V_{SENSE} Automatic Retry (OCP_MODE = 01b)

After a SEN_OCP event in this mode, all the external MOSFETs are disabled and the nFAULT pin is driven low. The FAULT, SEN_OCP, and corresponding sense OCP bits are latched high in the SPI registers. Normal operation starts again automatically (gate driver operation and the nFAULT pin is released) after the t_{RETRY} time elapses. The FAULT, SEN_OCP, and sense OCP bits stay latched until the t_{RETRY} period expires.

8.3.6.4.3 V_{SENSE} Report Only (OCP_MODE = 10b)

No protective action occurs after a SEN_OCP event in this mode. The overcurrent event is reported by driving the nFAULT pin low and latching the FAULT and SEN_OCP bits high in the SPI registers. The gate drivers continue to operate. The external controller manages the overcurrent condition by acting appropriately. The reporting clears (nFAULT released) when the SEN_OCP condition clears and a clear faults command is issued either through the CLR_FLT bit or an ENABLE reset pulse (t_{RST}).

8.3.6.4.4 V_{SENSE} Disabled (OCP_MODE = 11b or DIS_SEN = 1b)

No action occurs after a SEN_OCP event in this mode. The SEN_OCP bit can be disabled independently of the VDS_OCP bit by using the DIS_SEN SPI register.

8.3.6.5 Gate Driver Fault (GDF)

The GHx and GLx pins are monitored such that if the voltage on the external MOSFET gate does not increase or decrease after the t_{DRIVE} time, a gate driver fault is detected. This fault may be encountered if the GHx or GLx pins are shorted to the PGND, SHx, or VM pins. Additionally, a gate driver fault may be encountered if the selected I_{DRIVE} setting is not sufficient to turn on the external MOSFET within the t_{DRIVE} period. After a gate drive fault is detected, all external MOSFETs are disabled and the nFAULT pin driven low. In addition, the FAULT, GDF, and corresponding VGS bits are latched high in the SPI registers. Normal operation starts again (gate driver operation and the nFAULT pin is released) when the gate driver fault condition clears and a clear faults command is issued either through the CLR_FLT bit or an ENABLE reset pulse (t_{RST}). On SPI devices, setting the DIS_GDF bit high disables this protection feature.

Gate driver faults can indicate that the selected I_{DRIVE} or t_{DRIVE} settings are too low to slew the external MOSFET in the desired time. Increasing either the I_{DRIVE} or t_{DRIVE} setting can resolve gate driver faults in these cases. Alternatively, if a gate-to-source short occurs on the external MOSFET, a gate driver fault is reported because of the MOSFET gate not turning on.

8.3.6.6 Thermal Warning (OTW)

If the die temperature exceeds the trip point of the thermal warning (T_{OTW}), the OTW bit is set in the registers of SPI devices. The device performs no additional action and continues to function. When the die temperature falls lower than the hysteresis point of the thermal warning, the OTW bit clears automatically. The OTW bit can also be configured to report on the nFAULT pin by setting the OTW_REP bit to 1 through the SPI registers.

Copy right © 2017–2022, Texas Instruments Incorporated

TEXAS INSTRUMENTS

www.ti.com

8.3.6.7 Thermal Shutdown (OTSD)

If the die temperature exceeds the trip point of the thermal shutdown limit (T_{OTSD}), all the external MOSFETs are disabled, the charge pump is shut down, and the nFAULT pin is driven low. In addition, the FAULT and TSD bits are latched high. Normal operation starts again (gate driver operation and the nFAULT pin is released) when the overtemperature condition clears. The TSD bit stays latched high indicating that a thermal event occurred until a clear fault command is issued either through the CLR_FLT bit or an ENABLE reset pulse (t_{RST}). This protection feature cannot be disabled.

8.4 Device Functional Modes

8.4.1 Gate Driver Functional Modes


8.4.1.1 Sleep Mode

The ENABLE pin manages the state of the DRV832x family of devices. When the ENABLE pin is low, the device goes to a low-power sleep mode. In sleep mode, all gate drivers are disabled, sense amplifiers (if present) are disabled, all external MOSFETs are disabled, the charge pump is disabled, the DVDD regulator is disabled, and the SPI bus is disabled. The LMR16006X buck regulator (if present) is not controlled by the ENABLE pin and can be operated independently of the gate driver. The t_{SLEEP} time must elapse after a falling edge on the ENABLE pin before the device goes into sleep mode.

NOTE

The INHx and INLx pins should be low before t_{RST} (max 40 µs) after ENABLE goes low to prevent the GHx and GLx outputs from entering into Hi-Z state while any of the gates are high.

Figure 43 shows the behavior of the device after ENABLE goes low when the INHx and INLx pins are low prior to the time when the driver outputs ignore the inputs 50 μ s after ENABLE goes low. The GHx and GLx pins will remain low as the device begins the process to enter sleep mode. Figure 44 shows the behavior of the device if the input PWMs are not pulled low prior to the driver outputs ignoring the inputs. The GHx and GLx pins will follow the inputs for 50 μ s after ENABLE goes low, then will become Hi-Z until nFAULT goes low up to 400 μ s after ENABLE is low. To avoid this behavior, the INHx and INLx pins should be low before t_{RST} (max 40 μ s) after ENABLE goes low as shown in Figure 43 to avoid the GHx and GLx outputs going into Hi-Z state while any of the gate outputs are high.



The device comes out of sleep mode automatically if the ENABLE pin is pulled high. The t_{WAKE} time must elapse before the device is ready for inputs.



51

In sleep mode and when $V_{VM} < V_{UVLO}$, all external MOSFETs are disabled. The high-side gate pins, GHx, are pulled to the SHx pin by an internal resistor and the low-side gate pins, GLx, are pulled to the PGND pin by an internal resistor.

NOTE

During power up and power down of the device through the ENABLE pin, the nFAULT pin is held low as the internal regulators enable or disable. After the regulators have enabled or disabled, the nFAULT pin is automatically released. The duration that the nFAULT pin is low does not exceed the t_{SLEEP} or t_{WAKE} time.

8.4.1.2 Operating Mode

When the ENABLE pin is high and the V_{VM} voltage is greater than the V_{UVLO} voltage, the device goes to operating mode. The t_{WAKE} time must elapse before the device is ready for inputs. In this mode the charge pump, low-side gate regulator, DVDD regulator, and SPI bus are active

8.4.1.3 Fault Reset (CLR_FLT or ENABLE Reset Pulse)

In the case of device latched faults, the DRV832x family of devices goes to a partial shutdown state to help protect the external power MOSFETs and system.

When the fault condition clears, the device can go to the operating state again by either setting the CLR_FLTSPI bit on SPI devices or issuing a reset pulse to the ENABLE pin on either interface variant. The ENABLE reset pulse (t_{RST}) consists of a high-to-low-to-high transition on the ENABLE pin. The low period of the sequence should fall with the t_{RST} time window or else the device will start the complete shutdown sequence. The reset pulse has no effect on any of the regulators, device settings, or other functional blocks



Device Functional Modes (continued)

8.4.2 Buck Regulator Functional Modes

8.4.2.1 Continuous Conduction Mode (CCM)

conduction mode (when the inductor current never reaches zero at CCM), the buck regulator operates in two cycles. The power switch is connected between the VIN and SW pins. During the first cycle of operation, the transistor is closed and the diode is reverse biased. Energy is collected in the inductor and the load current is supplied by the C_{OUT} capacitor and the rising current through the inductor. During the second cycle of operation, the transistor is open and the diode is forward biased because the inductor current cannot instantaneously change direction. The energy stored in the inductor is transferred to the load and output capacitor. The ratio of these two cycles determines the output voltage. Equation 7 and Equation 8 define the approximate output voltage.

$$D = \frac{V_0}{V_{VIN}}$$

where

• D is the duty cycle of the switch (7)

$$D' = (1-D)$$
(8)

The value of D and D' is required for design calculations.

8.4.2.2 Eco-mode[™] Control Scheme

The LMR16006 device operates with the Eco-mode control scheme at light-load currents to improve efficiency by reducing switching and gate drive losses. The LMR16006 device is designed so that if the output voltage is within regulation and the peak switch current at the end of any switching cycle is less than the sleep-current threshold, $I_{INDUCTOR} \le 80$ mA, the device goes to Eco-mode. For Eco-mode operation, the LMR16006 device senses peak current, not average or load current, so the load current when the device goes to Eco-mode is dependent on the input voltage, the output voltage, and the value of the output inductor. When the load current is low and the output voltage is within regulation, the device goes to Eco-mode and draws only 28-µA input quiescent current.

8.5 Programming

This section applies only to the DRV832x SPI devices.

8.5.1 SPI Communication

8.5.1.1 SPI

On DRV832x SPI devices, an SPI bus is used to set device configurations, operating parameters, and read out diagnostic information. The SPI operates in slave mode and connects to a master controller. The SPI input data (SDI) word consists of a 16-bit word, with a 5-bit command and 11 bits of data. The SPI output data (SDO) word consists of 11-bit register data. The first 5 bits are don't care bits.

A valid frame must meet the following conditions:

- The SCLK pin should be low when the nSCS pin transitions from high to low and from low to high.
- The nSCS pin should be pulled high for at least 400 ns between words.
- When the nSCS pin is pulled high, any signals at the SCLK and SDI pins are ignored and the SDO pin is placed in the Hi-Z state.
- Data is captured on the falling edge of the SCLK pin and data is propagated on the rising edge of the SCLK pin.
- The most significant bit (MSB) is shifted in and out first.
- A full 16 SCLK cycles must occur for transaction to be valid.
- If the data word sent to the SDI pin is less than or more than 16 bits, a frame error occurs and the data word is ignored.
- For a write command, the existing data in the register being written to is shifted out on the SDO pin following



Programming (continued)

the 5-bit command data.

The SPI registers are reset to the default settings on power up, when the device is enters sleep mode, and when a UVLO fault occurs.

8.5.1.1.1 SPI Format

The SDI input data word is 16 bits long and consists of the following format:

- 1 read or write bit, W (bit B15)
- 4 address bits, A (bits B14 through B11)
- 11 data bits, D (bits B11 through B0)

The SDO output data word is 16 bits long and the first 5 bits are don't care bits. The data word is the content of the register being accessed.

For a write command (W0 = 0), the response word on the SDO pin is the data currently in the register being written to.

For a read command (W0 = 1), the response word is the data currently in the register being read.

Table 8. SDI Input Data Word Format

R/W		ADD	RESS		DATA										
B15	B14	B13	B12	B11	B10	B10 B9 B8 B7 B6 B5 B4 B3 B2 B						B1	B0		
W0	A3	A2	A1	A0	D10	D9	D8	D7	D6	D5	D4	D3	D2	D1	D0

Table 9. SDO Output Data Word Format

	DON'T CARE BITS									DATA					
B15	B14	B13	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1	B0
Х	Х	Х	Х	Х	D10	D9	D8	D7	D6	D5	D4	D3	D2	D1	D0




Figure 45. SPI Slave Timing Diagram



This section applies only to the DRV832x SPI devices.

NOTE

Do not modify reserved registers or addresses not listed in the register map (Table 10). Writing to these registers may have unintended effects. For all reserved bits, the default value is 0. To help prevent erroneous SPI writes from the master controller, set the LOCK bits to lock the SPI registers.

Name	10	9	8	7	6	5	4	3	2	1	0	Туре	Address
					DF	RV8320S and DR	V8320RS						
Fault Status 1	FAULT	VDS_OCP	GDF	UVLO	OTSD	VDS_HA	VDS_LA	VDS_HB	VDS_LB	VDS_HC	VDS_LC	R	0h
VGS Status 2	SA_OC	SB_OC	SC_OC	OTW	CPUV	VGS_HA	VGS_LA	VGS_HB	VGS_LB	VGS_HC	VGS_LC	R	1h
Driver Control	Reserved	DIS_CPUV	DIS_GDF	OTW_REP	DTW_REP PWM_MODE 1PWM_COM 1PWM_DIR COAST BRAKE CLR_FLT I						RW	2h	
Gate Drive HS		LOCK			IDRIV	EP_HS			IDRIV	EN_HS		RW	3h
Gate Drive LS	CBC	CBC TDRIVE IDRIVEP_LS IDRIVEN_LS										RW	4h
OCP Control	TRETRY	DEAD	AD_TIME OCP_MODE OCP_DEG VDS_LVL								RW	5h	
Reserved		Reserved										RW	6h
Reserved						Reserved						RW	7h
					DF	RV8323S and DR	V8323RS						
Fault Status 1	FAULT	VDS_OCP	GDF	UVLO	OTSD	VDS_HA	VDS_LA	VDS_HB	VDS_LB	VDS_HC	VDS_LC	R	0h
VGS Status 2	SA_OC	SB_OC	SC_OC	OTW	CPUV	VGS_HA	VGS_LA	VGS_HB	VGS_LB	VGS_HC	VGS_LC	R	1h
Driver Control	Reserved	DIS_CPUV	DIS_GDF	OTW_REP	PWM	MODE	1PWM_COM	1PWM_DIR	COAST	BRAKE	CLR_FLT	RW	2h
Gate Drive HS		LOCK			IDRIV	EP_HS			IDRIV	EN_HS		RW	3h
Gate Drive LS	CBC	TDI	RIVE		IDRIV	'EP_LS			IDRIV	'EN_LS		RW	4h
OCP Control	TRETRY	DEAD	_TIME	OCP_MODE OCP_DEG VDS_LVL						RW	5h		
CSA Control	CSA_FET	VREF_DIV	LS_REF	CSA	GAIN	DIS_SEN	CSA_CAL_A	CSA_CAL_B	CSA_CAL_C	SEN	I_LVL	RW	6h
Reserved						Reserved						RW	7h

Table 10. DRV832xS and DRV832xRS Register Map



8.6.1 Status Registers

The status registers are used to reporting warning and fault conditions. The status registers are read-only registers

Complex bit access types are encoded to fit into small table cells. Table 11 shows the codes that are used for access types in this section.

		<u> </u>
Access Type	Code	Description
Read Type		
R	R	Read
Reset or Defaul	t Value	
-n		Value after reset or the default value

Table 11. Status Registers Access Type Codes

8.6.1.1 Fault Status Register 1 (address = 0x00)

The fault status register 1 is shown in Figure 46 and described in Table 12.

Register access type: Read only

Figure 46. Fault Status Register 1

10	9	8	7	6	5	4	3	2	1	0
FAULT	VDS_OCP	GDF	UVLO	OTSD	VDS_HA	VDS_LA	VDS_HB	VDS_LB	VDS_HC	VDS_LC
R-0b	R-0b	R-0b	R-0b	R-0b	R-0b	R-0b	R-0b	R-0b	R-0b	R-0b

Table 12. Fault Status Register 1 Field Descriptions

Bit	Field	Туре	Default	Description
10	FAULT	R	0b	Logic OR of FAULT status registers. Mirrors nFAULT pin.
9	VDS_OCP	R	0b	Indicates VDS monitor overcurrent fault condition
8	GDF	R	0b	Indicatesgate drive fault condition
7	UVLO	R	0b	Indicates undervoltage lockout fault condition
6	OTSD	R	0b	Indicates overtemperature shutdown
5	VDS_HA	R	0b	Indicates VDS overcurrent fault on the A high-side MOSFET
4	VDS_LA	R	0b	Indicates VDS overcurrent fault on the A low-side MOSFET
3	VDS_HB	R	0b	Indicates VDS overcurrent fault on the B high-side MOSFET
2	VDS_LB	R	0b	Indicates VDS overcurrent fault on the B low-side MOSFET
1	VDS_HC	R	0b	Indicates VDS overcurrent fault on the C high-side MOSFET
0	VDS_LC	R	0b	Indicates VDS overcurrent fault on the Clow-side MOSFET



55

www.ti.com

8.6.1.2 Fault Status Register 2 (address = 0x01)

The fault status register 2 is shown in Figure 47 and described in Table 13.

Register access type: Read only

Figure 47. Fault Status Register 2

10	9	8	7	6	5	4	3	2	1	0
SA_OC	SB_OC	SC_OC	OTW	CPUV	VGS_HA	VGS_LA	VGS_HB	VGS_LB	VGS_HC	VGS_LC
R-0b	R-0b	R-0b	R-0b	R-0b	R-0b	R-0b	R-0b	R-0b	R-0b	R-0b

Table 13. Fault Status Register 2 Field Descriptions

Bit	Field	Туре	Default	Description
10	SA_OC	R	0b	Indicates overcurrent on phase A sense amplifier (DRV8323xS)
9	SB_OC	R	0b	Indicates overcurrent on phase B sense amplifier (DRV8323xS)
8	SC_OC	R	0b	Indicates overcurrent on phase C sense amplifier (DRV8323xS)
7	OTW	R	0b	Indicates overtemperature warning
6	CPUV	R	0b	Indicates charge pump undervoltage fault condition
5	VGS_HA	R	0b	Indicates gate drive fault on the A high-side MOSFET
4	VGS_LA	R	0b	Indicatesgate drive fault on the A low-side MOSFET
3	VGS_HB	R	0b	Indicates gate drive fault on the B high-side MOSFET
2	VGS_LB	R	0b	Indicatesgate drive fault on the B low-side MOSFET
1	VGS_HC	R	0b	Indicatesgate drive fault on the Chigh-side MOSFET
0	VGS_LC	R	0b	Indicatesgate drive fault on the Clow-side MOSFET



8.6.2 Control Registers

The control registers are used to configure the device. The control registers are read and write capable

Complex bit access types are encoded to fit into small table cells. Table 14 shows the codes that are used for access types in this section.

Access Type	Code	Description
Read Type		
R	R	Read
Write Type		
W	W	Write
Reset or Defaul	t Value	
-n		Value after reset or the default value

Table 14. Control Registers Access Type Codes

8.6.2.1 Driver Control Register (address = 0x02)

The driver control register is shown in Figure 48 and described in Table 15.

Register access type: Read/Write

Figure 48. Driver Control Register

10	9	8	7	6	5	4	3	2	1	0
Reserved	DIS _CPUV	DIS _GDF	OTW _REP	PWM_	MODE	1PWM _COM	1PWM _DIR	COAST	BRAKE	CLR _FLT
R/W-0b	R/W-0b	R/W-0b	R/W-0b	R/W-	-00b	R/W-0b	R/W-0b	R/W-0b	R/W-0b	R/W-0b

Table 15. Driver Control Field Descriptions

Bit	Field	Time	Default	Description
		Туре		Description
10	Reserved	R/W	0b	Reserved
9	DIS_CPUV	R/W	0b	0b = Charge pump UVLO fault is enabled
				1b = Charge pump UVLO fault is disabled
8	DIS_GDF	R/W	0b	0b = Gate drive fault is enabled
				1b = Gate drive fault is disabled
7	OTW_REP	R/W	0b	0b = OTW is not reported on nFAULT or the FAULT bit
				1b = OTW is reported on nFAULT and the FAULT bit
6-5	PWM_MODE	R/W	00b	00b = 6x PWM Mode
				01b = 3x PWM mode
				10b = 1x PWM mode
			-	11b = Independent PWM mode
4	1PWM_COM	R/W	0b	0b = 1x PWM mode uses synchronous rectification
				1b = 1x PWM mode uses asynchronous rectification (diode
				freewheeling)
3	1PWM_DIR	R/W	0b	In 1x PWM mode this bit is ORed with the INHC (DIR) input
2	COAST	R/W	0b	Write a 1 to this bit to put all MOSFETs in the Hi-Z state
1	BRAKE	R/W	0b	Write a 1 to this bit to turn on all three low-side MOSFETs in 1x
				PWM mode.
				Thisbit is ORed with the INLC (BRAKE) input.
0	CLR_FLT	R/W	0b	Write a 1 to this bit to clear latched fault bits.
				This bit automatically resets after being written.



8.6.2.2 Gate Drive HS Register (address = 0x03)

The gate drive HS register is shown in Figure 49 and described in Table 16.

Register access type: Read/Write

Figure 49. Gate Drive HS Register

10	9	8	7	6	5	4	3	2	1	0	
	LOCK			IDRIVEP_HS				IDRIVEN_HS			
	R/W-011b			R/W-	1111b			R/W-	1111b		

	Table 16. Gate Drive HS Field Descriptions					
Bit	Field	Туре	Default	Description		
10-8	LOCK	R/W	011b	Write 110b to lock the settings by ignoring further register writes except to these bits and address 0x02 bits0-2. Writing any sequence other than 110b has no effect when unlocked. Write 011b to this register to unlock all registers. Writing any sequence other than 011b has no effect when locked.		
7-4	IDRIVEP_HS	R/W	1111Ь	0000b = 10 mA 0001b = 30 mA 0010b = 60 mA 0011b = 80 mA 0100b = 120 mA 0100b = 120 mA 0101b = 140 mA 0110b = 170 mA 0111b = 190 mA 1000b = 260 mA 1001b = 330 mA 1010b = 370 mA 1011b = 440 mA 1110b = 570 mA 1110b = 820 mA 1111b = 1000 mA		
3-0	IDRIVEN_HS	R/W	1111b	0000b = 20 mA 0001b = 60 mA 0010b = 120 mA 0011b = 160 mA 0100b = 240 mA 0100b = 240 mA 0110b = 340 mA 0110b = 340 mA 1010b = 520 mA 1000b = 520 mA 1001b = 660 mA 1010b = 740 mA 1011b = 880 mA 1100b = 1140 mA 1110b = 1640 mA 1111b = 2000 mA		

Table 16. Gate Drive HS Field Descriptions



8.6.2.3 Gate Drive LS Register (address = 0x04)

The gate drive LS register is shown in Figure 50 and described in Table 17.

Register access type: Read/Write

Figure 50. Gate Drive LS Register

10	9	8	7	6	5	4	3	2	1	0	
CBC	TDR	IVE		IDRIVEP_LS				IDRIVEN_LS			
R/W-1b	R/W-	-11b		R/W-	1111b			R/W-	1111b		

Bit	Field	Туре	Default	Description
10	CBC	R/W	1b	Cycle-by cycle operation. In retry OCP_MODE, for both VDS_OCP and SEN_OCP, the fault is automatically cleared when a PWM input isgiven
9-8	TDRIVE	R/W	11b	00b = 500-nspeak gate-current drive time 01b = 1000-nspeak gate-current drive time 10b = 2000-nspeak gate-current drive time 11b = 4000-ns peak gate-current drive time
7-4	IDRIVEP_LS	R/W	1111Ь	0000b = 10 mA 0001b = 30 mA 0010b = 60 mA 0011b = 80 mA 0100b = 120 mA 0101b = 140 mA 0110b = 170 mA 0111b = 190 mA 1000b = 260 mA 1001b = 330 mA 1010b = 370 mA 1011b = 440 mA 1100b = 570 mA 1101b = 680 mA 1110b = 820 mA 1111b = 1000 mA
3-0	IDRIVEN_LS	R/W	1111Ь	0000b = 20 mA 0001b = 60 mA 0010b = 120 mA 0011b = 160 mA 0100b = 240 mA 0100b = 240 mA 0101b = 280 mA 0110b = 340 mA 0111b = 380 mA 1000b = 520 mA 1001b = 660 mA 1010b = 740 mA 1011b = 880 mA 1100b = 1140 mA 1101b = 1360 mA 1110b = 1640 mA

Submit Documentation Feedback Copy right © 2017–2022, Texas Instruments Incorporated

58



8.6.2.4 OCP Control Register (address = 0x05)

The OCP control register is shown in Figure 51 and described in Table 18.

Register access type: Read/Write

Figure 51. OCP Control Register

10	9	8	7	6	5	4	3	2	1	0
TRETRY	DEAD	_TIME	OCP_	MODE	OCP_	_DEG		VDS	5_LVL	
R/W-0b	R/W	-01b	R/V	 R/W-01b		/-01b	R/W-1001b			

	Table 18. OCP Control Field Descriptions							
Bit	Field	Туре	Default	Description				
10	TRETRY	R/W	0b	0b = VDS_OCP and SEN_OCP retry time is 4 ms 1b = VDS_OCP and SEN_OCP retry time is 50 μs				
9-8	DEAD_TIME	R/W	01b	00b = 50-ns dead time 01b = 100-ns dead time 10b = 200-ns dead time 11b = 400-ns dead time				
7-6	OCP_MODE	R/W	01b	00b = Overcurrent causes a latched fault 01b = Overcurrent causes an automatic retrying fault 10b = Overcurrent is report only but no action is taken 11b = Overcurrent is not reported and no action is taken				
5-4	OCP_DEG	R/W	01b	00b = Overcurrent deglitch time of 2 μs 01b = Overcurrent deglitch time of 4 μs 10b = Overcurrent deglitch time of 6 μs 11b = Overcurrent deglitch time of 8 μs				
3-0	VDS_LVL	R/W	1001b	$\begin{array}{l} 0000b = 0.06 \ V \\ 0001b = 0.13 \ V \\ 0010b = 0.2 \ V \\ 0011b = 0.26 \ V \\ 0100b = 0.31 \ V \\ 0100b = 0.31 \ V \\ 0110b = 0.45 \ V \\ 0110b = 0.53 \ V \\ 0111b = 0.6 \ V \\ 1000b = 0.68 \ V \\ 1000b = 0.68 \ V \\ 1001b = 0.75 \ V \\ 1010b = 0.94 \ V \\ 1011b = 1.13 \ V \\ 1100b = 1.3 \ V \\ 1110b = 1.5 \ V \\ 1110b = 1.7 \ V \end{array}$				

Copy right © 2017–2022, Texas Instruments Incorporated

Submit Documentation Feedback 59



8.6.2.5 CSA Control Register (DRV8323x Only) (address = 0x06)

The CSA control register is shown in Figure 52 and described in Table 19.

Register access type: Read/Write

This register is only available with the DRV8323x family of devices.

Figure 52. CSA Control Register

10	9	8	7	6	5	4	3	2	1	0
CSA _FET	VREF _DIV	LS _REF	CS _GA	SA AIN	DIS _SEN	CSA _CAL_A	CSA _CAL_B	CSA _CAL_C	SEN _LVL	
R/W-0b	R/W-1b	R/W-0b	R/W-	-10b	R/W-0b	R/W-0b	R/W-0b	R/W-0b	R/W-11	b

Bit	Field	Туре	Default	Description
10	CSA_FET	R/W	0b	0b = Current sense amplifier positive input is SPx 1b = Current sense amplifier positive input is SHx (also automatically sets the LS REF bit to 1)
9	VREF_DIV	R/W	1b	0b = Current sense amplifier reference voltage is VREF (unidirectional mode) 1b = Current sense amplifier reference voltage is VREF divided by 2
8	LS_REF	R/W	Ob	0b = VDS_OCP for the low-side MOSFET is measured across SHx to SPx 1b = VDS_OCP for the low-side MOSFET is measured across SHx to SNx
7-6	CSA_GAIN	R/W	10b	00b = 5-V/V current sense amplifier gain 01b = 10-V/V current sense amplifier gain 10b = 20-V/V current sense amplifier gain 11b = 40-V/V current sense amplifier gain
5	DIS_SEN	R/W	0b	0b = Sense ov ercurrent fault is enabled 1b = Sense overcurrent fault is disabled
4	CSA_CAL_A	R/W	0b	0b = Normal current sense amplifier A operation 1b = Short inputs to current sense amplifier A for offset calibration
3	CSA_CAL_B	R/W	Ob	0b = Normal current sense amplifier B operation 1b = Short inputs to current sense amplifier B for offset calibration
2	CSA_CAL_C	R/W	Ob	0b = Normal current sense amplifier C operation 1b = Short inputs to current sense amplifier C for offset calibration
1-0	SEN_LVL	R/W	11b	00b = Sense OCP 0.25 V 01b = Sense OCP 0.5 V 10b = Sense OCP 0.75 V 11b = Sense OCP 1 V

Table 19. CSA Control Field Descriptions

Copy right © 2017-2022, Texas Instruments Incorporated



DRV8320, DRV8320F DRV8323, DRV8323F SLVSDJ3D – FEBRUARY 2017 – REVISED MARCH 2022

61

9 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

9.1 Application Information

The DRV832x family of devices is primarily used in applications for three-phase brushless DC motor control. The design procedures in the *Typical Application* section highlight how to use and configure the DRV832x family of devices.

9.2 Typical Application

9.2.1 Primary Application

The DRV8323R SPI device is used in this application example.



Typical Application (continued)




Figure 53. Primary Application Schematic



Typical Application (continued)

9.2.1.1 Design Requirements

Table 20 lists the example input parameters for the system design.

EXAMPLE DESIGN PARAMETER	REFERENCE	EXAMPLE VALUE
Nominal supply voltage		24 V
Supply voltage range		8 V to 45 V
MOSFET part number		CSD18536KCS
MOSFET total gate charge	Qg	83 nC (typical) at V _{VGS} = 10 V
MOSFET gate to drain charge	Q _{gd}	14 nC (typical)
Target output rise time	tr	100 to 300 ns
Target output fall time	t _f	50 to 150 ns
PWM Frequency	<i>f</i> pwm	45 kHz
Buckregulatoroutputvoltage	V _{VCC}	3.3 V
Maximum motor current	I _{max}	100 A
ADC reference voltage	V _{VREF}	3.3 V
Winding sense current range	I _{SENSE}	-40 A to +40 A
Motor RMS current	I _{RMS}	28.3 A
Sense resistor power rating	P _{SENSE}	2 W
System ambient temperature	T _A	–20°C to +105°C

Table 20. Design Parameters

9.2.1.2 Detailed Design Procedure

9.2.1.2.1 External MOSFET Support

The DRV832x MOSFET support is based on the capacity of the charge pump and PWM switching frequency of the output. For a quick calculation of MOSFET driving capacity, use Equation 9 and Equation 10 for three phase BLDC motor applications.

Trapezoidal 120° Commutation: $I_{VCP} > Q_q \times f_{PWM}$

where

- f_{PWM} is the maximum desired PWM switching frequency.
 - IvcP is the charge pump capacity, which depends on the VM pin voltage.
- The multiplier based on the commutation control method, may vary based on implementation. (9)

Sinusoidal 180° Commutation: IvcP > 3 × Qq × fPWM

9.2.1.2.1.1 Example

If a system with a V_{VM} voltage of 8 V (I_{VCP} = 15 mA) uses a maximum PWM switching frequency of 45 kHz, then the charge pump can support MOSFETs using trapezoidal commutation with a Q_a less than 333 nC, and MOSFETs using sinusoidal commutation with a Q_q less than 111 nC.

9.2.1.2.2 IDRIVE Configuration

The strength of the gate drive current, I_{DRIVE}, is selected based on the gate-to-drain charge of the external MOSFETs and the target rise and fall times at the outputs. If I_{DRIVE} is selected to be too low for a given MOSFET, then the MOSFET may not turn on completely within the t_{DRIVE} time and a gate drive fault may be asserted. Additionally, slow rise and fall times result in higher switching power losses. The commends adjusting these values in the system with the required external MOSFETs and motor to determine the best possible setting for any application.

The IDRIVEP and IDRIVEN current for both the low-side and high-side MOSFETs are independently adjustable on SPI devices through the SPI registers. On hardware interface devices, both source and sink settings are selected at the same time on the IDRIVE pin.

(10)

Copyright © 2017-2022, Texas Instruments Incorporated

Copy right © 2017-2022, Texas Instruments Incorporated

For MOSFETs with a known gate-to-drain charge Q_{ad} , desired rise time (t_r), and a desired fall time (t_f), use Equation 11 and Equation 12 to calculate the value of I_{DRIVEP} and I_{DRIVEP} (respectively).

$$I_{\text{DRIVEP}} > \frac{Q_{\text{gd}}}{t_{\text{r}}}$$

$$I_{\text{DRIVEN}} > \frac{Q_{\text{gd}}}{t_{\text{r}}}$$
(11)
(12)

9.2.1.2.2.1 Example

tf

Use Equation 13 and Equation 14 to calculate the value of IDRIVEP1 and IDRIVEP2 (respectively) for a gate-to-drain charge of 14 nC and a rise time from 100 to 300 ns.

$$I_{DRIVEP1} = \frac{14 \text{ nC}}{100 \text{ ns}} = 140 \text{ mA}$$
(13)
$$I_{DRIVEP2} = \frac{14 \text{ nC}}{300 \text{ ns}} = 47 \text{ mA}$$
(14)

Select a value for I_{DRIVEP} that is between 47 mA and 140 mA. For this example, the value of I_{DRIVEP} was selected as 120-mA source.

Use Equation 15 and Equation 16 to calculate the value of IDRIVEN1 and IDRIVEN2 (respectively) for a gate-to-drain charge of 14 nC and a fall time from 50 to 150 ns.

$$I_{DRIVEN1} = \frac{14 \text{ nC}}{50 \text{ ns}} = 280 \text{ mA}$$

$$I_{DRIVEN2} = \frac{14 \text{ nC}}{150 \text{ ns}} = 93 \text{ mA}$$
(15)
(16)

Select a value for I_{DRIVEN} that is between 93 mA and 280 mA. For this example, the value of I_{DRIVEN} was selected as 240-mA sink.

9.2.1.2.3 V_{DS} Overcurrent Monitor Configuration

The V_{DS} monitors are configured based on the worst-case motor current and the R_{DS(on)} of the external MOSFETs as shown in Equation 17.

$$V_{DS_{OCP}} > I_{max} \times R_{DS(on)max}$$
 (17)

9.2.1.2.3.1 Example

The goal of this example is to set the V_{DS} monitor to trip at a current greater than 100 A. According to the CSD18536KCS 60 V N-Channel NexFET™ Power MOSFET data sheet, the R_{DS(on)} value is 1.8 times higher at 175°C, and the maximum $R_{DS(on)}$ value at a V_{GS} of 10 V is 1.6 m Ω . From these values, the approximate worstcase value of $R_{DS(on)}$ is 1.8 × 1.6 m Ω = 2.88 m Ω .

Using Equation 17 with a value of 2.88 m Ω for R_{DS(on)} and a worst-case motor current of 100 A, Equation 18 shows the calculated the value of the V_{DS} monitors.

$$V_{DS_{OCP}} > 100 \text{ A x } 2.88 \text{ m}\Omega$$

$$V_{DS_{OCP}} > 0.288 \text{ V}$$
For this example, the value of V_{DS_{OCP}} was selected as 0.31 \text{ V}. (18)

The SPI devices allow for adjustment of the deglitch time for the V_{DS} overcurrent monitor. The deglitch time can be set to $2 \mu s$, $4 \mu s$, $6 \mu s$, or $8 \mu s$.

9.2.1.2.4 Sense Amplifier Bidirectional Configuration (DRV 8323 and DRV 8323R)

The sense amplifier gain on the DRV8323, DRV8323R devices and sense resistor value are selected based on the target current range, VREF voltage supply, power rating of the sense resistor, and operating temperature range. In bidirectional operation of the sense amplifier, the dynamic range at the output is approximately calculated as shown in Equation 19.



(19)

$$V_{O} = (V_{VREF} - 0.25 V) - \frac{V_{VREF}}{2}$$

Use Equation 20 to calculate the approximate value of the selected sense resistor with V_0 calculated using Equation 19,

$$R = \frac{V_0}{A_V \times I} \qquad P_{SENSE} > I_{RMS}^2 \times R$$
(20)

From Equation 19 and Equation 20, select a target gain setting based on the power rating of the target sense resistor.

9.2.1.2.4.1 Example

In this system example, the value of the VREF voltage is 3.3 V with a sense current from –40 to +40 A. The linear range of the SOx output is 0.25 V to V_{VREF} – 0.25 V (from the V_{LINEAR} specification). The differential range of the sense amplifier input is –0.3 to +0.3 V (V_{DIFF}).

$$V_{O} = (3.3 \text{ V} - 0.25 \text{ V}) - \frac{3.3 \text{ V}}{2} = 1.4 \text{ V}$$
(21)


$$R = \frac{1.4 \text{ V}}{\text{A}_{\text{V}} \times 40 \text{ A}} \qquad 2 \text{ W} > 28.3^2 \times \text{R} \rightarrow \text{R} < 2.5 \text{ m}\Omega$$
(22)

$$2.5 \text{ m}\Omega > \frac{1.4 \text{ V}}{\text{A}_{\text{V}} \times 40 \text{ A}} \rightarrow \text{A}_{\text{V}} > 14$$
(23)

Therefore, the gain setting must be selected as 20 V/V or 40 V/V and the value of the sense resistor must be less than 2.5 m Ω to meet the power rating for the sense resistor. For this example, the gain setting was selected as 20 V/V. The value of the resistor and worst case current can be verified that R < 2.5 m Ω and I_{max} = 40 A does not violate the differential range specification of the sense amplifier input (V_{SPxD}).

9.2.1.2.5 Buck Regulator Configuration (DRV8320R and DRV8323R)

For a detailed design procedure and information on selecting the correct buck regulator external components, refer to the *LMR16006 SIMPLE SWITCHER*® 60 V 0.6 A Buck Regulators With High Efficiency Eco-mode data sheet.




9.2.1.3 Application Curves

DRV8320, DRV8320R DRV8323, DRV8323R

NSTRUMENTS www.ti.com

Texas

SLVSDJ3D -FEBRUARY 2017-REVISED MARCH 2022




Copy right © 2017-2022, Texas Instruments Incorporated



DRV8320, DRV8320R DRV8323, DRV8323R

67


SLVSDJ3D - FEBRUARY 2017-REVISED MARCH 2022





9.2.2 Alternative Application

In this application, one sense amplifier is used in unidirectional mode for a summing current sense scheme often used in trapezoidal or hall-based BLDC commutation control.





Copy right © 2017-2022, Texas Instruments Incorporated



9.2.2.1 Design Requirements

Table 21 lists the example design input parameters for system design.

Table 2'	1. Design	Parameters
----------	-----------	------------

EXAMPLE DESIGN PARAMETER	REFERENCE	EXAMPLE VALUE
ADC reference voltage	V _{VREF}	3.3 V
Sensed current	I _{SENSE}	0 to 40 A
Motor RMS current	I _{RMS}	28.3 A
Sense-resistor power rating	P _{SENSE}	3 W
System ambient temperature	T _A	–20°C to +105°C

9.2.2.2 Detailed Design Procedure

9.2.2.2.1 Sense Amplifier Unidirectional Configuration

The sense amplifiers are configured to be unidirectional through the registers on SPI devices by writing a 0 to the VREF_DIV bit.

The sense amplifier gain and sense resistor values are selected based on the target current range, VREF, power rating of the sense resistor, and operating temperature range. In unidirectional operation of the sense amplifier, use Equation 24 to calculate the approximate value of the dynamic range at the output.

$$V_{O} = (V_{VREF} - 0.25 V) - 0.25 V = V_{VREF} - 0.5 V$$
(24)

Use Equation 25 to calculate the approximate value of the selected sense resistor.

$$R = \frac{V_0}{A_V \times I} \qquad P_{SENSE} > I_{RMS}^2 \times R$$

where

$$V_{O} = V_{VREF} - 0.5 V \tag{25}$$

From Equation 24 and Equation 25, select a target gain setting based on the power rating of a target sense resistor.

9.2.2.2.1.1 Example

In this system example, the value of the VREF voltage is 3.3 V with a sense current from 0 to 40 A. The linear range of the SOx output for the DRV8323x device is 0.25 V to $V_{VREF} - 0.25$ V (from the V_{LINEAR} specification). The differential range of the sense-amplifier input is -0.3 to +0.3 V (V_{DIFF}).

$$V_{\rm O} = 3.3 \text{ V} - 0.5 \text{ V} = 2.8 \text{ V}$$
 (26)

$$\mathsf{R} = \frac{2.8 \text{ V}}{\mathsf{A}_{\mathsf{V}} \times 40 \text{ A}} \qquad 3 \text{ W} > 28.3^2 \times \mathsf{R} \to \mathsf{R} < 3.75 \text{ m}\Omega$$
⁽²⁷⁾

$$3.75 \text{ m}\Omega > \frac{2.8 \text{ V}}{\text{A}_{\text{V}} \times 40 \text{ A}} \rightarrow \text{A}_{\text{V}} > 18.7 \tag{28}$$

Therefore, the gain setting must be selected as 20 V/V or 40 V/V and the value of the sense resistor must be less than 3.75 m Ω to meet the power rating for the sense resistor. For this example, the gain setting was selected as 20 V/V. The value of the resistor and worst-case current can be verified that R < 3.75 m Ω and I_{max} = 40 A does not violate the differential range specification of the sense amplifier input (V_{SPxD}).



10 Power Supply Recommendations

The DRV832x family of devices is designed to operate from an input voltage supply (VM) range from 6 V to 60 V. A 0.1- μ F ceramic capacitor rated for VM must be placed as close to the device as possible. In addition, a bulk capacitor must be included on the VM pin but can be shared with the bulk bypass capacitance for the external power MOSFETs. Additional bulk capacitance is required to bypass the external half-bridge MOSFETs and should be sized according to the application requirements.

10.1 Bulk Capacitance Sizing

Having appropriate local bulk capacitance is an important factor in motor drive system design. It is generally beneficial to have more bulk capacitance, while the disadvantages are increased cost and physical size. The amount of local capacitance depends on a variety of factors including:

- The highest current required by the motor system
- The power supply's type, capacitance, and ability to source current
- The amount of parasitic inductance between the power supply and motor system
- · The acceptable supply voltage ripple
- Type of motor (brushed DC, brushless DC, stepper)
- · The motor startup and braking methods

The inductance between the power supply and motor drive system will limit the rate current can change from the power supply. If the local bulk capacitance is too small, the system will respond to excessive current demands or dumps from the motor with a change in voltage. When adequate bulk capacitance is used, the motor voltage remains stable and high current can be quickly supplied.

The data sheet provides a recommended minimum value, but system level testing is required to determine the appropriate sized bulk capacitor.




Figure 65. Motor Drive Supply Parasitics Example



11 Layout

11.1 Layout Guidelines

Bypass the VM pin to the PGND pin using a low-ESR ceramic bypass capacitor with a recommended value of 0.1 μ F. Place this capacitor as close to the VM pin as possible with a thick trace or ground plane connected to the PGND pin. Additionally, bypass the VM pin using a bulk capacitor rated for VM. This component can be electrolytic. This capacitance must be at least 10 μ F.

Additional bulk capacitance is required to bypass the high current path on the external MOSFETs. This bulk capacitance should be placed such that it minimizes the length of any high current paths through the external MOSFETs. The connecting metal traces should be as wide as possible, with numerous vias connecting PCB layers. These practices minimize inductance and let the bulk capacitor deliver high current.

Place a low-ESR ceramic capacitor between the CPL and CPH pins. This capacitor should be 47 nF, rated for VM, and be of type X5R or X7R. Additionally, place a low-ESR ceramic capacitor between the VCP and VM pins. This capacitor should be 1 µF, rated for 16 V, and be of type X5R or X7R.

Bypass the DVDD pin to the AGND pin with a 1- μ F low-ESR ceramic capacitor rated for 6.3 V and of type X5R or X7R. Place this capacitor as close to the pin as possible and minimize the path from the capacitor to the AGND pin.

The VDRAIN pin can be shorted directly to the VM pin. However, if a significant distance is between the device and the external MOSFETs, use a dedicated trace to connect to the common point of the drains of the high-side external MOSFETs. Do not connect the SLx pins directly to PGND. Instead, use dedicated traces to connect these pins to the sources of the low-side external MOSFETs. These recommendations offer more accurate V_{DS} sensing of the external MOSFETs for overcurrent detection.

Minimize the loop length for the high-side and low-side gate drivers. The high-side loop is from the GHx pin of the device to the high-side power MOSFET gate, then follows the high-side MOSFET source back to the SHx pin. The low-side loop is from the GLx pin of the device to the low-side power MOSFET gate, then follows the low-side MOSFET gate, then follows the low-side MOSFET gate, then follows the low-side MOSFET source back to the PGND pin.

For additional layout guidelines and examples see the *Layout Guide for the DRV832x Family of Three-Phase Smart Gate Drivers* application report.

11.1.1 Buck-Regulator Layout Guidelines

Layout is a critical portion of good power supply design. The following guidelines help users design a PCB with the best power conversion performance, thermal performance, and minimized generation of unwanted electromagnetic interference (EMI):

- Place the feedback network resistors close to the FB pin and away from the inductor to minimize coupling noise into the feedback pin.
- Place the input bypass capacitor close to the VIN pin to decrease copper trace resistance which effects the input voltage ripple of the device.
- Place the inductor close to the SW pin to decrease magnetic and electrostatic noise.
- Place the output capacitor close to the junction of the inductor and the diode. The inductor, diode, and C_{OUT} trace should be as short as possible to decrease conducted and radiated noise and increase overall efficiency.
- Make the ground connection for the diode, C_{VIN}, and C_{OUT} as small as possible and tie it to the system ground plane in only one spot (preferably at the C_{OUT} ground point) to minimize conducted noise in the system ground plane.

For more detail on switching power supply layout considerations refer to the AN-1149 Layout Guidelines for Switching Power Supplies application report.

DRV8320, DRV8320R DRV8323, DRV8323R

SLVSDJ3D -FEBRUARY 2017-REVISED MARCH 2022



www.ti.com

11.2 Layout Example




Figure 66. Layout Example

Product Folder Links: DRV8320 DRV8320R DRV8323 DRV8323R




12 Device and Documentation Support

12.1 Device Support

12.1.1 Device Nomenclature

The following figure shows a legend for interpreting the complete device name:



12.2 Documentation Support

12.2.1 Related Documentation

- Texas Instruments, Architecture for Brushless-DC Gate Drive Systems application report
- Texas Instruments, LMR16006 SIMPLE SWITCHER® 60 V 0.6 A Buck Regulators With High Efficiency Ecomode data sheet
- Texas Instruments, Layout Guide for the DRV832x Family of Three-Phase Smart Gate Drivers application report
- Texas Instruments, AN-1149 Layout Guidelines for Switching Power Supplies application report
- Texas Instruments, Understanding IDRIVE and TDRIVE In TI Motor Gate Drivers application report
- Texas Instruments, Reduce Motor Drive BOM and PCB Area with TI Smart Gate Drive TI TechNote
- Texas Instruments, Reducing EMI Radiated Emissions with TI Smart Gate Drive TI TechNote
- Texas Instruments, Motor Drive Protection With TI Smart Gate Drive TI TechNote
- Texas Instruments, QFN/SON PCB Attachment application report
- Texas Instruments, Cut-Off Switch in High-Current Motor-Drive Applications application report
- Texas Instruments, Hardware Design Considerations for an Efficient Vacuum Cleaner using BLDC Motor application report
- Texas Instruments, Hardware Design Considerations for an Electric Bicycle using BLDC Motor application report
- Texas Instruments, Sensored 3-Phase BLDC Motor Control Using MSP430™ application report

12.3 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to order now.

PARTS	PRODUCT FOLDER	ORDER NOW	TECHNICAL DOCUMENTS	TOOLS & SOFTWARE	SUPPORT & COMMUNITY
DRV8320	Clickhere	Click here	Clickhere	Clickhere	Clickhere
DRV8320R	Clickhere	Click here	Click here	Click here	Clickhere

Table 22. Related Links

Copy right © 2017-2022, Texas Instruments Incorporated



Related Links (continued)

PARTS	PRODUCT FOLDER	ORDER NOW	TECHNICAL DOCUMENTS	TOOLS & SOFTWARE	SUPPORT & COMMUNITY
DRV8323	Clickhere	Click here	Click here	Click here	Click here
DRV8323R	Clickhere	Click here	Click here	Clickhere	Clickhere

Table 22. Related Links (continued)

12.4 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

12.5 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E[™] Online Community TI's Engineer-to-Engineer (E2E) Community. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support TI's Design Support Quickly find helpful E2E forums along with design support tools and contact information for technical support.

12.6 Trademarks

Eco-mode, NexFET, MSP430, E2E are trademarks of Texas Instruments. SIMPLE SWITCHER is a registered trademark of Texas Instruments. All other trademarks are the property of their respective owners.

12.7 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

12.8 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Copy right © 2017-2022, Texas Instruments Incorporated



10-Dec-2020

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
DRV8320HRTVR	ACTIVE	WQFN	RTV	32	3000	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8320H	Samples
DRV8320HRTVT	ACTIVE	WQFN	RTV	32	250	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8320H	Samples
DRV8320RHRHAR	ACTIVE	VQFN	RHA	40	2500	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV 8320RH	Samples
DRV8320RHRHAT	ACTIVE	VQFN	RHA	40	250	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV 8320RH	Samples
DRV8320RSRHAR	ACTIVE	VQFN	RHA	40	2500	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV 8320RS	Samples
DRV8320RSRHAT	ACTIVE	VQFN	RHA	40	250	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV 8320RS	Samples
DRV8320SRTVR	ACTIVE	WQFN	RTV	32	3000	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8320S	Samples
DRV8320SRTVT	ACTIVE	WQFN	RTV	32	250	RoHS & Green	Call TI NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8320S	Samples
DRV8323HRTAR	ACTIVE	WQFN	RTA	40	2500	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8323H	Samples
DRV8323HRTAT	ACTIVE	WQFN	RTA	40	250	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8323H	Samples
DRV8323RHRGZR	ACTIVE	VQFN	RGZ	48	2500	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8323RH	Samples
DRV8323RHRGZT	ACTIVE	VQFN	RGZ	48	250	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8323RH	Samples
DRV8323RSRGZR	ACTIVE	VQFN	RGZ	48	2500	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8323RS	Samples
DRV8323RSRGZT	ACTIVE	VQFN	RGZ	48	250	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8323RS	Samples
DRV8323SRTAR	ACTIVE	WQFN	RTA	40	2500	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8323S	Samples
DRV8323SRTAT	ACTIVE	WQFN	RTA	40	250	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8323S	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

 $\textbf{LIFEBUY:} \ \textbf{TI} has announced that the device will be discontinued, and a lifetime-buy period is in effect.$

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.



10-Dec-2020

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <= 1000ppm threshold. Antimony trioxide based flame retardants must also meet the <= 1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁶⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


PACKAGE MATERIALS INFORMATION

www.ti.com


Texas Instruments

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE




Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
DRV8320HRTVR	WQFN	RTV	32	3000	330.0	12.4	5.3	5.3	1.1	8.0	12.0	Q2
DRV8320HRTVT	WQFN	RTV	32	250	180.0	12.4	5.3	5.3	1.1	8.0	12.0	Q2
DRV8320RHRHAR	VQFN	RHA	40	2500	330.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2
DRV8320RHRHAT	VQFN	RHA	40	250	180.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2
DRV8320RSRHAR	VQFN	RHA	40	2500	330.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2
DRV8320RSRHAT	VQFN	RHA	40	250	180.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2
DRV8320SRTVR	WQFN	RTV	32	3000	330.0	12.4	5.3	5.3	1.1	8.0	12.0	Q2
DRV8320SRTVT	WQFN	RTV	32	250	180.0	12.4	5.3	5.3	1.1	8.0	12.0	Q2
DRV8323HRTAR	WQFN	RTA	40	2500	330.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2
DRV8323HRTAT	WQFN	RTA	40	250	180.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2
DRV8323RHRGZR	VQFN	RGZ	48	2500	330.0	16.4	7.3	7.3	1.1	12.0	16.0	Q2
DRV8323RHRGZT	VQFN	RGZ	48	250	180.0	16.4	7.3	7.3	1.1	12.0	16.0	Q2
DRV8323RSRGZR	VQFN	RGZ	48	2500	330.0	16.4	7.3	7.3	1.1	12.0	16.0	Q2
DRV8323RSRGZT	VQFN	RGZ	48	250	180.0	16.4	7.3	7.3	1.1	12.0	16.0	Q2
DRV8323SRTAR	WQFN	RTA	40	2500	330.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2
DRV8323SRTAT	WQFN	RTA	40	250	180.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2

TEXAS INSTRUMENTS

www.ti.com

PACKAGE MATERIALS INFORMATION

22-Aug-2018



All dimensions are nominal Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
DRV8320HRTVR	WQFN	RTV	32	3000	367.0	367.0	35.0
DRV8320HRTVT	WQFN	RTV	32	250	210.0	185.0	35.0
DRV8320RHRHAR	VQFN	RHA	40	2500	367.0	367.0	38.0
DRV8320RHRHAT	VQFN	RHA	40	250	210.0	185.0	35.0
DRV8320RSRHAR	VQFN	RHA	40	2500	367.0	367.0	38.0
DRV8320RSRHAT	VQFN	RHA	40	250	210.0	185.0	35.0
DRV8320SRTVR	WQFN	RTV	32	3000	367.0	367.0	35.0
DRV8320SRTVT	WQFN	RTV	32	250	210.0	185.0	35.0
DRV8323HRTAR	WQFN	RTA	40	2500	367.0	367.0	38.0
DRV8323HRTAT	WQFN	RTA	40	250	210.0	185.0	35.0
DRV8323RHRGZR	VQFN	RGZ	48	2500	367.0	367.0	38.0
DRV8323RHRGZT	VQFN	RGZ	48	250	210.0	185.0	35.0
DRV8323RSRGZR	VQFN	RGZ	48	2500	367.0	367.0	38.0
DRV8323RSRGZT	VQFN	RGZ	48	250	210.0	185.0	35.0
DRV8323SRTAR	WQFN	RTA	40	2500	367.0	367.0	38.0
DRV8323SRTAT	WQFN	RTA	40	250	210.0	185.0	35.0

RHA 40


6 x 6, 0.5 mm pitch

GENERIC PACKAGE VIEW

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.






RHA0040B



PACKAGE OUTLINE

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.




RHA0040B

EXAMPLE BOARD LAYOUT

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).




RHA0040B

EXAMPLE STENCIL DESIGN

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD




NOTES. (continued)

5.Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



MECHANICAL DATA



- D. The package thermal pad must be soldered to the board for thermal and mechanical performance.
- E. See the additional figure in the Product Data Sheet for details regarding the exposed thermal pad features and dimensions. F. Falls within JEDEC M0-220.






PACKAGE OUTLINE

WQFN - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES:


- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.2. This drawing is subject to change without notice.3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



EXAMPLE BOARD LAYOUT

WQFN - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature


number SLUA271 (www.ti.com/lit/slua271). 5. Viasare optional depending on application, refer to device data sheet. If any viasare implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



EXAMPLE STENCIL DESIGN

WQFN - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

6.Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.




RGZ 48

7 x 7, 0.5 mm pitch

GENERIC PACKAGE VIEW

VQFN - 1 mm max height

PLASTIC QUADFLAT PACK-NO LEAD




Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.



PACKAGE OUTLINE VQFN - 1 mm max height

PLASTIC QUADFLAT PACK- NO LEAD



NOTES:


- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for optimal thermal and mechanical performance.



EXAMPLE BOARD LAYOUT

VQFN - 1 mm max height

PLASTIC QUADFLAT PACK- NO LEAD



NOTES: (continued)


- 4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- 5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



EXAMPLE STENCIL DESIGN

VQFN - 1 mm max height


PLASTIC QUADFLAT PACK- NO LEAD



6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



MECHANICAL DATA



See the Product Data Sheet for details regarding the exposed thermal pad dimensions.




RTA0040B

PACKAGE OUTLINE

WQFN - 0.8 mm max height

PLASTIC QUAD FLATPACK- NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for optimal thermal and mechanical performance.




RTA0040B

EXAMPLE BOARD LAYOUT

WQFN - 0.8 mm max height

PLASTIC QUAD FLATPACK- NO LEAD



NOTES: (continued)

- 4. Thispackage is designed to be soldered to a thermal pad on the board. For more information, see TexasInstrumentsIiterature number SLUA271 (www.ti.com/lit/slua271).
- 5. Viasare optional depending on application, refer to device data sheet. If any viasare implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.




RTA0040B

EXAMPLE STENCIL DESIGN

WQFN - 0.8 mm max height

PLASTIC QUAD FLATPACK- NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.





PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
DRV8320HRTVR	ACTIVE	WQFN	RTV	32	3000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	DRV8320H	Samples
DRV8320HRTVT	ACTIVE	WQFN	RTV	32	250	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	DRV8320H	Samples
DRV8320RHRHAR	ACTIVE	VQFN	RHA	40	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	DRV 8320RH	Samples
DRV8320RHRHAT	ACTIVE	VQFN	RHA	40	250	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	DRV 8320RH	Samples
DRV8320RSRHAR	ACTIVE	VQFN	RHA	40	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	DRV 8320RS	Samples
DRV8320RSRHAT	ACTIVE	VQFN	RHA	40	250	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	DRV 8320RS	Samples
DRV8320SRTVR	ACTIVE	WQFN	RTV	32	3000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	DRV8320S	Samples
DRV8320SRTVT	ACTIVE	WQFN	RTV	32	250	RoHS & Green	Call TI NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8320S	Samples
DRV8323HRTAR	ACTIVE	WQFN	RTA	40	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	DRV8323H	Samples
DRV8323HRTAT	ACTIVE	WQFN	RTA	40	250	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	DRV8323H	Samples
DRV8323RHRGZR	ACTIVE	VQFN	RGZ	48	2500	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8323RH	Samples
DRV8323RHRGZT	ACTIVE	VQFN	RGZ	48	250	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8323RH	Samples
DRV8323RSRGZR	ACTIVE	VQFN	RGZ	48	2500	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8323RS	Samples
DRV8323RSRGZT	ACTIVE	VQFN	RGZ	48	250	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV8323RS	Samples
DRV8323SRTAR	ACTIVE	WQFN	RTA	40	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	DRV8323S	Samples
DRV8323SRTAT	ACTIVE	WQFN	RTA	40	250	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	DRV8323S	Samples

⁽¹⁾ The marketing status values are defined as follows: **ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect. NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design. PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.



⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

Texas

STRUMENTS

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE




Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter	Reel Width	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
		Ŭ			(mm)	W1 (mm)	· · /	, ,	. ,	` ´	l` í	
DRV8320HRTVR	WQFN	RTV	32	3000	330.0	12.4	5.3	5.3	1.1	8.0	12.0	Q2
DRV8320HRTVT	WQFN	RTV	32	250	180.0	12.4	5.3	5.3	1.1	8.0	12.0	Q2
DRV8320RHRHAR	VQFN	RHA	40	2500	330.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2
DRV8320RHRHAT	VQFN	RHA	40	250	180.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2
DRV8320RSRHAR	VQFN	RHA	40	2500	330.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2
DRV8320RSRHAT	VQFN	RHA	40	250	180.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2
DRV8320SRTVR	WQFN	RTV	32	3000	330.0	12.4	5.3	5.3	1.1	8.0	12.0	Q2
DRV8320SRTVT	WQFN	RTV	32	250	180.0	12.4	5.3	5.3	1.1	8.0	12.0	Q2
DRV8323HRTAR	WQFN	RTA	40	2500	330.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2
DRV8323HRTAT	WQFN	RTA	40	250	180.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2
DRV8323RHRGZR	VQFN	RGZ	48	2500	330.0	16.4	7.3	7.3	1.1	12.0	16.0	Q2
DRV8323RHRGZT	VQFN	RGZ	48	250	180.0	16.4	7.3	7.3	1.1	12.0	16.0	Q2
DRV8323RSRGZR	VQFN	RGZ	48	2500	330.0	16.4	7.3	7.3	1.1	12.0	16.0	Q2
DRV8323RSRGZT	VQFN	RGZ	48	250	180.0	16.4	7.3	7.3	1.1	12.0	16.0	Q2
DRV8323SRTAR	WQFN	RTA	40	2500	330.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2
DRV8323SRTAT	WQFN	RTA	40	250	180.0	16.4	6.3	6.3	1.1	12.0	16.0	Q2



PACKAGE MATERIALS INFORMATION

19-Dec-2023



Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
DRV8320HRTVR	WQFN	RTV	32	3000	346.0	346.0	33.0
DRV8320HRTVT	WQFN	RTV	32	250	182.0	182.0	20.0
DRV8320RHRHAR	VQFN	RHA	40	2500	367.0	367.0	38.0
DRV8320RHRHAT	VQFN	RHA	40	250	182.0	182.0	20.0
DRV8320RSRHAR	VQFN	RHA	40	2500	367.0	367.0	38.0
DRV8320RSRHAT	VQFN	RHA	40	250	182.0	182.0	20.0
DRV8320SRTVR	WQFN	RTV	32	3000	346.0	346.0	33.0
DRV8320SRTVT	WQFN	RTV	32	250	210.0	185.0	35.0
DRV8323HRTAR	WQFN	RTA	40	2500	367.0	367.0	38.0
DRV8323HRTAT	WQFN	RTA	40	250	182.0	182.0	20.0
DRV8323RHRGZR	VQFN	RGZ	48	2500	367.0	367.0	38.0
DRV8323RHRGZT	VQFN	RGZ	48	250	210.0	185.0	35.0
DRV8323RSRGZR	VQFN	RGZ	48	2500	367.0	367.0	38.0
DRV8323RSRGZT	VQFN	RGZ	48	250	210.0	185.0	35.0
DRV8323SRTAR	WQFN	RTA	40	2500	367.0	367.0	38.0
DRV8323SRTAT	WQFN	RTA	40	250	182.0	182.0	20.0

RHA 40


6 x 6, 0.5 mm pitch

GENERIC PACKAGE VIEW

VQFN - 1 mm max height


PLASTIC QUAD FLATPACK - NO LEAD

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.





MECHANICAL DATA



- D. The package thermal pad must be soldered to the board for thermal and mechanical performance.
- D. The package thermal pad must be soldered to the board for thermal and mechanical performance.
 E. See the additional figure in the Product Data Sheet for details regarding the exposed thermal pad features and dimensions.
- F. Falls within JEDEC MO-220.






PACKAGE OUTLINE

WQFN - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES:


- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



EXAMPLE BOARD LAYOUT

WQFN - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).


5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



EXAMPLE STENCIL DESIGN

WQFN - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



RGZ 48

7 x 7, 0.5 mm pitch

GENERIC PACKAGE VIEW

VQFN - 1 mm max height

PLASTIC QUADFLAT PACK- NO LEAD




Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.



PACKAGE OUTLINE VQFN - 1 mm max height

VQ: IT I IIII IIIAX Holgit

PLASTIC QUADFLAT PACK- NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for optimal thermal and mechanical performance.



EXAMPLE BOARD LAYOUT

VQFN - 1 mm max height

PLASTIC QUADFLAT PACK- NO LEAD



NOTES: (continued)

- 4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- 5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



EXAMPLE STENCIL DESIGN

VQFN - 1 mm max height


PLASTIC QUADFLAT PACK- NO LEAD



6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



MECHANICAL DATA



NOTES: A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.

- B. This drawing is subject to change without notice.
- C. QFN (Quad Flatpack No-Lead) Package configuration.
- The package thermal pad must be soldered to the board for thermal and mechanical performance. See the Product Data Sheet for details regarding the exposed thermal pad dimensions.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated