

SCLS394J-APRIL 1999-REVISED FEBRUARY 2015

# SNx4LV132A Quadruple Positive-NAND Gates With Schmitt-Trigger Inputs

Technical

Documents

Sample &

Buv


## 1 Features

- 2-V to 5.5-V V<sub>CC</sub> Operation
- Max t<sub>pd</sub> of 9 ns at 5 V
- Typical V<sub>OLP</sub> (Output Ground Bounce) <0.8 V at V<sub>CC</sub> = 3.3 V, T<sub>A</sub> = 25°C
- Typical V<sub>OHV</sub> (Output V<sub>OH</sub> Undershoot) >2.3 V at V<sub>CC</sub> = 3.3 V, T<sub>A</sub> = 25°C
- Support Mixed-Mode Voltage Operation on All Ports
- Latch-Up Performance Exceeds 250 mA per JESD 17
- I<sub>off</sub> Supports Live Insertion, Partial Power-Down Mode, and Back Drive Protection
- ESD Protection Exceeds JESD 22
  - 2000-V Human-Body Model (A114-A)
  - 200-V Machine Model (A115-A)
  - 1000-V Charged-Device Model (C101)

## 2 Applications

- Industrial PC: Rugged PC and Laptop
- Access Control and Security: Camera Surveillance IP Network
- Vending, Payment and Change Machines
- Patient Monitoring STB / DVR / Streaming Media (Withdraw)
- Other Motor Drives (Such as Switch Reluctance)

## 4 Logic Diagram (Positive Logic)



## 3 Description

Tools &

Software

The 'LV132A devices are quadruple positive-NAND gates designed for 2-V to 5.5-V  $V_{CC}$  operation.

Support &

Community

20

The <u>'LV132A</u> devices perform the Boolean function Y =  $\overline{A \cdot B}$  or Y =  $\overline{A + B}$  in positive logic.

Each circuit functions as a NAND gate, but because of the Schmitt trigger, it has different input threshold levels for positive- and negative-going signals.

These circuits are temperature compensated and can be triggered from the slowest of input ramps and still give clean jitter-free output signals.

PART NUMBER	PACKAGE	BODY SIZE (NOM)					
	SOIC (14)	8.65 mm × 3.91 mm					
	SOP (14)	10.30 mm × 5.30 mm					
LV132A	SSOP (14)	6.20 mm × 5.30 mm					
	TSSOP (14)	5.00 mm × 4.40 mm					
	TVSOP (14)	3.60 mm × 4.40 mm					

Device Information<sup>(1)</sup>

(1) For all available packages, see the orderable addendum at the end of the data sheet.

2

# **Table of Contents**

9

1	Feat	ures 1
2	App	lications 1
3	Desc	cription 1
4	Logi	c Diagram (Positive Logic) 1
5	Revi	sion History 2
6	Pin (	Configuration and Functions
7	Spee	cifications 4
	7.1	Absolute Maximum Ratings 4
	7.2	ESD Ratings 4
	7.3	Recommended Operating Conditions 4
	7.4	Thermal Information 5
	7.5	Electrical Characteristics5
	7.6	Switching Characteristics
	7.7	Switching Characteristics
	7.8	Switching Characteristics
	7.9	Noise Characteristics for SN74LV132A 6
	7.10	Operating Characteristics6
	7.11	Typical Characteristics 7
8	Para	meter Measurement Information

# 5 Revision History

Changes from Revision I (June 2010) to Revision J

	9.1	Overview	9
	9.2	Functional Block Diagram	9
	9.3	Feature Description	9
	9.4	Device Functional Modes	9
10	Арр	lication and Implementation	10
	10.1	Application Information	. 10
	10.2	Typical Application	. 10
11	Pow	ver Supply Recommendations	11
12	Lay	out	11
	12.1	Layout Guidelines	. 11
	12.2	Layout Example	. 11
13	Dev	ice and Documentation Support	12
	13.1	Related Links	. 12
	13.2	Trademarks	. 12
	13.3	Electrostatic Discharge Caution	. 12
	13.4	Glossary	. 12
14	Mec	hanical, Packaging, and Orderable	
		rmation	12

Copyright © 1999–2015, Texas Instruments Incorporated

•	Added ESD Ratings table, Feature Description section, Device Functional Modes, Application and Implementation	
	section, Power Supply Recommendations section, Layout section, Device and Documentation Support section, and	
	Mechanical, Packaging, and Orderable Information section	1




#### www.ti.com

### Page




# 6 Pin Configuration and Functions



1A   1B   1Y   2A   2B   2Y		12 13 12 11 10 9	3	V <sub>CC</sub> 4B 4A 4A 4Y 3B 3A
2Y 🛛	6	9	- H-	
gnd [	7	8	3	3Y

SN54LV132A: FK Package (Top View) 3 2 1 20 19 Π4 5



A. NC - No internal connection

#### **Pin Functions**

Р	IN		DECODIDION
NO.	NAME	I/O	DESCRIPTION
1	1A	I	1A input
2	1B	I	1B
3	1Y	0	1Y
4	2A	I	2A
5	2B	I	2B
6	2Y	0	2Y
7	GND	—	GND
8	ЗҮ	0	3Y
9	3A	I	3A
10	3B	I	3В
11	4Y	0	4Y
12	4A	I	4A
13	4B	I	4B
14	V <sub>CC</sub>		V <sub>CC</sub>

## SN54LV132A, SN74LV132A

SCLS394J-APRIL 1999-REVISED FEBRUARY 2015

## TEXAS INSTRUMENTS

www.ti.com

## 7 Specifications

## 7.1 Absolute Maximum Ratings<sup>(1)</sup>

over operating free-air temperature (unless otherwise noted)

			MIN	MAX	UNIT
$V_{CC}$	Supply voltage		-0.5	7	V
VI	Input voltage <sup>(2)</sup>		-0.5	7	V
Vo	Voltage applied to any output in the h	igh-impedance or power-off state <sup>(2)</sup>	-0.5	7	V
Vo	Output voltage <sup>(2) (3)</sup>		-0.5	V <sub>CC</sub> + 0.5	V
I <sub>IK</sub>	Input clamp current	V <sub>1</sub> < 0		-20	mA
I <sub>OK</sub>	Output clamp current	V <sub>O</sub> < 0		-50	mA
I <sub>O</sub>	Continuous output current	$V_{O} = 0$ to $V_{CC}$	-25	25	mA
	Continuous current through V <sub>CC</sub> or GND		-50	50	mA
T <sub>stg</sub>	Storage temperature		-65	150	°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) The input and output negative-voltage ratings may be exceeded if the input and output current ratings are observed.

(3) The value is limited to 5.5-V maximum.

# 7.2 ESD Ratings

			VALUE	UNIT
		Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>	±2000	
V <sub>(ESD)</sub>	Electrostatic discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup>	±1000	V
	aloonargo	Machine model (A115-A)	200	

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

# 7.3 Recommended Operating Conditions

See (1)(2)

			MIN	MAX	UNIT
V <sub>CC</sub>	Supply voltage		2	5.5	V
VI	Input voltage			5.5	V
Vo	Output voltage		0	V <sub>CC</sub>	V
		$V_{CC} = 2 V$		-50	μA
I <sub>OH</sub>	High lovel output ourrent	$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$		-2	
	High-level output current	$V_{CC} = 3 V$ to 3.6 V		-6	mA
		$V_{CC}$ = 4.5 V to 5.5 V		-12	
		$V_{CC} = 2 V$		50	μA
	Low lovel output ourrent	$V_{CC}$ = 2.3 V to 2.7 V		2	
I <sub>OL</sub>	Low-level output current	$V_{CC} = 3 V$ to 3.6 V		6	mA
		$V_{CC}$ = 4.5 V to 5.5 V		12	
-	T <sub>A</sub> Operating free-air temperature	SN54LV132A	-55	125	°C
IA		SN74LV132A	-40	125	

 All unused inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. See the TI application report, Implications of Slow or Floating CMOS Inputs, SCBA004.

(2) SN54LV132A is in product preview



## 7.4 Thermal Information

over operating free-air temperature range (unless otherwise noted)

		D	DB	DGV	NS	PW	
			14 PINS				
$R_{\theta JA}$	Junction-to-ambient thermal resistance	90.6	107.1	129.0	90.7	122.6	
R <sub>0JC(top)</sub>	Junction-to-case (top) thermal resistance	50.9	59.6	52.1	48.3	51.4	
$R_{\theta J B}$	Junction-to-board thermal resistance	44.8	54.4	62.0	49.4	64.4	°C/W
$\Psi_{JT}$	Junction-to-top characterization parameter	14.7	20.5	6.5	14.6	6.7	
$\Psi_{JB}$	Junction-to-board characterization parameter	44.5	53.8	61.3	49.1	63.8	

(1) For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report, SPRA953.

# 7.5 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

				SN54L	.V132A <sup>(1)</sup>	SN74		
	PARAMETER	TEST CONDITIONS	V <sub>cc</sub>	MIN	TYP MAX	MIN	TYP MAX	UNIT
			2.5 V	1	1.75	1	1.75	
$V_{T+}$	Positive-going input threshold voltage		3.3 V	1.31	2.31	1.31	2.31	V
	threahold voltage		5 V	1.95	3.5	1.95	3.5	
			2.5 V	0.75	1.5	0.75	1.5	
$V_{T-}$	Negative-going input threshold voltage		3.3 V	0.99	2.07	0.99	2.07	V
	anoonola voltago		5 V	1.5	3.05	1.5	3.05	
			2.5 V	0.25	1	0.25	1	
$\Delta V_{\rm T}$	Hysteresis (V <sub>T+</sub> – V <sub>T-</sub> )		3.3 V	0.33	1.32	0.33	1.32	V
	(v + v -)		5 V	0.5	2	0.5	2	
		I <sub>OH</sub> = -50 μA	2 to 5.5 V	V <sub>CC</sub> – 0.1		V <sub>CC</sub> – 0.1		
V		$I_{OH} = -2 \text{ mA}$	2.3 V	2		2		v
V <sub>OH</sub>		I <sub>OH</sub> = -6 mA	3 V	2.48		2.48		v
		$I_{OH} = -12 \text{ mA}$	4.5 V	3.8		3.8		
		$I_{OL} = 50 \ \mu A$	2 to 5.5 V		0.1		0.1	
V		$I_{OL} = 2 \text{ mA}$	2.3 V		0.4		0.4	V
V <sub>OL</sub>		$I_{OL} = 6 \text{ mA}$	3 V		0.44		0.44	v
		I <sub>OL</sub> = 12 mA	4.5 V		0.55		0.55	
կ		$V_I = 5.5 V \text{ or GND}$	0 to 5.5 V		±1		±1	μA
I <sub>CC</sub>		$V_{I} = V_{CC} \text{ or GND, } I_{O}$ = 0	5.5 V		20		20	μA
I <sub>off</sub>		$V_{I}$ or $V_{O}$ = 0 to 5.5 V	0 V		5		5	μA
Ci		$V_I = V_{CC}$ or GND	3.3 V		1.9		1.9	pF

(1) SN54LV132A is in product preview

#### SN54LV132A, SN74LV132A

SCLS394J-APRIL 1999-REVISED FEBRUARY 2015

www.ti.com

### 7.6 Switching Characteristics

over recommended operating free-air temperature range, V<sub>CC</sub> = 2.5 V ±0.2 V (unless otherwise noted) (see Figure 3)

	DADAMETER			LOAD	т	<sub>A</sub> = 25°C		SN54LV	132A <sup>(1)</sup>	SN74LV	/132A	UNIT
PARAMETER	FROM (INPUT)	TO (OUTPUT)	CAPACITANCE	MIN	TYP	MAX	MIN	MAX	MIN	MAX	UNIT	
		A or D	V	C <sub>L</sub> = 15 pF		7.9 <sup>(2)</sup>	16.5 <sup>(2)</sup>	1 <sup>(2)</sup>	18.5 <sup>(2)</sup>	1	18.5	22
	<sup>L</sup> pd	A or B	T	C <sub>L</sub> = 50 pF		10.8	20.2	1	23	1	23	ns

(1) SN54LV132A is in product preview

(2) On products compliant to MIL-PRF-38535, this parameter is not production tested.

## 7.7 Switching Characteristics

over recommended operating free-air temperature range, V<sub>CC</sub> = 3.3 V ±0.3 V (unless otherwise noted) (see Figure 3)

PARAMETER	FROM (INPUT)		LOAD	т	<sub>A</sub> = 25°C		SN54LV1	132A <sup>(1)</sup>	SN74LV	132A	UNIT
PARAMETER	AMETER FROM (INPUT) TO (OUTPUT)	10 (001901)	CAPACITANCE	MIN	TYP	MAX	MIN	MAX	MIN	MAX	UNIT
	A or P	X	C <sub>L</sub> = 15 pF		5.6 <sup>(2)</sup>	11.9 <sup>(2)</sup>	1 <sup>(2)</sup>	14 <sup>(2)</sup>	1	14	20
<sup>L</sup> pd	A or B	ř	C <sub>L</sub> = 50 pF		7.6	15.4	1	17.5	1	17.5	ns

(1) SN54LV132A is in product preview

(2) On products compliant to MIL-PRF-38535, this parameter is not production tested.

## 7.8 Switching Characteristics

over recommended operating free-air temperature range,  $V_{CC} = 5 V \pm 0.5 V$  (unless otherwise noted) (see Figure 3)

PARAMETER	FROM	то	LOAD	T,	<sub>A</sub> = 25°C		SN54LV1	132A <sup>(1)</sup>	SN74LV	/132A	UNIT
PARAMETER	(INPUT)	(OUTPUT)	CAPACITANCE	MIN	TYP	MAX	MIN	MAX	MIN	MAX	
	A or B	X	C <sub>L</sub> = 15 pF		3.9 <sup>(2)</sup>	7.7 <sup>(2)</sup>	1 (2)	9(2)	1	9	20
<sup>L</sup> pd	AUB	Ť	C <sub>L</sub> = 50 pF		5.3	9.7	1	11	1	11	ns

(1) SN54LV132A is in product preview

(2) On products compliant to MIL-PRF-38535, this parameter is not production tested.

## 7.9 Noise Characteristics for SN74LV132A

 $V_{CC}$  = 3.3 V,  $C_L$  = 50 pF,  $T_A$  = 25°C<sup>(1)</sup>

	PARAMETER	MIN	TYP	MAX	UNIT
V <sub>OL(P)</sub>	Quiet output, maximum dynamic V <sub>OL</sub>		0.21	0.8	
V <sub>OL(V)</sub>	Quiet output, minimum dynamic V <sub>OL</sub>		-0.09	-0.8	
V <sub>OH(V)</sub>	Quiet output, minimum dynamic V <sub>OH</sub>		3.12		V
V <sub>IH(D)</sub>	High-level dynamic input voltage	2.31			
V <sub>IL(D)</sub>	Low-level dynamic input voltage			0.99	

(1) Characteristics are for surface-mount packages only.


## 7.10 Operating Characteristics

 $T_A = 25^{\circ}C$ 

	PARAMETER	TEST CONDITIONS	V <sub>cc</sub>	TYP	UNIT
<u> </u>	Dawar dissinction consoltance		3.3 V	7.5	~ [
C <sub>pd</sub>	Power dissipation capacitance	C <sub>L</sub> = 50 pF, f = 10 MHz	5 V	11.2	pF




# 7.11 Typical Characteristics



SN54LV132A, SN74LV132A SCLS394J – APRIL 1999 – REVISED FEBRUARY 2015 TEXAS INSTRUMENTS

www.ti.com

## 8 Parameter Measurement Information



- A. C<sub>L</sub> includes probe and jig capacitance.
- B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  1 MHz, Z<sub>O</sub> = 50  $\Omega$ , t<sub>r</sub>  $\leq$  3 ns, t<sub>f</sub>  $\leq$  3 ns.
- D. The outputs are measured one at a time, with one input transition per measurement.
- E.  $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
- F. t<sub>PZL</sub> and tPZH are the same as t<sub>en</sub>.
- G.  $t_{PHL}$  and  $t_{PLH}$  are the same as  $t_{pd}$ .
- H. All parameters and waveforms are not applicable to all devices.

#### Figure 3. Load Circuit and Voltage Waveforms

8



## 9 Detailed Description

#### 9.1 Overview

The SN74LV132A Is a quadruple 2-input positive NAND gate with low drive that produces slow rise and fall times. This reduces ringing on the output signal. Each circuit functions as a NAND gate, but because of the Schmitt trigger, it has different input threshold levels for positive- and negative-going signals. These circuits are temperature compensated and can be triggered from the slowest of input ramps and still give clean jitter-free output signals.

## 9.2 Functional Block Diagram




Figure 4. Logic Diagram (Positive Logic)

#### 9.3 Feature Description

- Wide operating voltage range, operates from 2 to 5.5 V
- Allows down voltage translation, inputs accept voltages to 5.5 V

## 9.4 Device Functional Modes

#### **Table 1. Function Table**

INP	INPUTS						
Α	A B						
Н	Н	L					
L	Х	Н					
Х	L	Н					

Copyright © 1999–2015, Texas Instruments Incorporated



## **10** Application and Implementation

#### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

### **10.1** Application Information

The SN74LV132A is a low-drive CMOS device that can be used for a multitude of bus interface type applications where output ringing is a concern. The low drive and slow edge rates will minimize overshoot and undershoot on the outputs. The inputs can accept voltages to 5.5 V at any valid  $V_{CC}$  making it Ideal for down translation.

## **10.2 Typical Application**




Figure 5. Typical Application Schematic

#### 10.2.1 Design Requirements

This device uses CMOS technology and has balanced output drive. Care should be taken to avoid bus contention because it can drive currents that would exceed maximum limits. The high drive will also create fast edges into light loads so routing and load conditions should be considered to prevent ringing. The Schmitt trigger inputs allow for slow or noisy inputs while producing clean outputs.

## 10.2.2 Detailed Design Procedure

- 1. Recommended input conditions
  - Specified high and low levels. See (V<sub>IH</sub> and V<sub>IL</sub>) in *Recommended Operating Conditions*.
  - Inputs are overvoltage tolerant allowing them to go as high as 5.5 V at any valid V<sub>CC</sub>
- 2. Recommend output conditions
  - Load currents should not exceed 25 mA per output and 50 mA total for the part
  - Outputs should not be pulled above V<sub>CC</sub>



#### SN54LV132A, SN74LV132A SCLS394J – APRIL 1999 – REVISED FEBRUARY 2015

www.ti.com

## **Typical Application (continued)**

### 10.2.3 Application Curve




Figure 6. Switching Characteristics Comparison

## **11 Power Supply Recommendations**

The power supply can be any voltage between the min and max supply voltage rating located in *Recommended Operating Conditions*.


Each V<sub>CC</sub> terminal should have a good bypass capacitor to prevent power disturbance. For devices with a single supply, TI recommends 0.1  $\mu$ F and if there are multiple V<sub>CC</sub> terminals then TI recommends .01  $\mu$ F or .022  $\mu$ F for each power terminal. It is okay to parallel multiple bypass caps to reject different frequencies of noise. A 0.1  $\mu$ F and 1  $\mu$ F are commonly used in parallel. The bypass capacitor should be installed as close to the power terminal as possible for best results.

## 12 Layout

## 12.1 Layout Guidelines

When using multiple bit logic devices inputs should not ever float. In many cases, functions or parts of functions of digital logic devices are unused, for example, when only two inputs of a triple-input AND gate are used or only 3 of the 4 buffer gates are used. Such input pins should not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. Specified below are the rules that must be observed under all circumstances. All unused inputs of digital logic devices must be connected to a high or low bias to prevent them from floating. The logic level that should be applied to any particular unused input depends on the function of the device. Generally they will be tied to GND or  $V_{CC}$  whichever make more sense or is more convenient. It is generally okay to float outputs unless the part is a transceiver. If the transceiver has an output enable pin it will disable the outputs section of the part when asserted. This will not disable the input section of the IOs so they also cannot float when disabled.

## 12.2 Layout Example





# 13 Device and Documentation Support

#### 13.1 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

PARTS	PRODUCT FOLDER	SAMPLE & BUY	TECHNICAL DOCUMENTS	TOOLS & SOFTWARE	SUPPORT & COMMUNITY
SN54LV132A	Click here	Click here	Click here	Click here	Click here
SN74LV132A	Click here	Click here	Click here	Click here	Click here

#### Table 2. Related Links

#### 13.2 Trademarks

All trademarks are the property of their respective owners.

## **13.3 Electrostatic Discharge Caution**



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

## 13.4 Glossary

#### SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

## 14 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Copyright © 1999–2015, Texas Instruments Incorporated





## PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
	(.)		0			(=)	(6)	(0)		()	
SN74LV132ADBR	ACTIVE	SSOP	DB	14	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	LV132A	Samples
SN74LV132ADGVR	ACTIVE	TVSOP	DGV	14	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	LV132A	Samples
SN74LV132ADR	ACTIVE	SOIC	D	14	2500	RoHS & Green	NIPDAU   SN	Level-1-260C-UNLIM	-40 to 125	LV132A	Samples
SN74LV132ANSR	ACTIVE	SO	NS	14	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	74LV132A	Samples
SN74LV132APWR	ACTIVE	TSSOP	PW	14	2000	RoHS & Green	NIPDAU   SN	Level-1-260C-UNLIM	-40 to 125	(LV132, LV132A)	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.



# PACKAGE OPTION ADDENDUM

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



Texas

STRUMENTS

## TAPE AND REEL INFORMATION





#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74LV132ADBR	SSOP	DB	14	2000	330.0	16.4	8.35	6.6	2.4	12.0	16.0	Q1
SN74LV132ADGVR	TVSOP	DGV	14	2000	330.0	12.4	6.8	4.0	1.6	8.0	12.0	Q1
SN74LV132ADR	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
SN74LV132ANSR	SO	NS	14	2000	330.0	16.4	8.2	10.5	2.5	12.0	16.0	Q1
SN74LV132APWR	TSSOP	PW	14	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
SN74LV132APWR	TSSOP	PW	14	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
SN74LV132APWR	TSSOP	PW	14	2000	330.0	12.4	6.85	5.45	1.6	8.0	12.0	Q1



# PACKAGE MATERIALS INFORMATION

26-Jan-2024



Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74LV132ADBR	SSOP	DB	14	2000	356.0	356.0	35.0
SN74LV132ADGVR	TVSOP	DGV	14	2000	356.0	356.0	35.0
SN74LV132ADR	SOIC	D	14	2500	356.0	356.0	35.0
SN74LV132ANSR	SO	NS	14	2000	356.0	356.0	35.0
SN74LV132APWR	TSSOP	PW	14	2000	356.0	356.0	35.0
SN74LV132APWR	TSSOP	PW	14	2000	356.0	356.0	35.0
SN74LV132APWR	TSSOP	PW	14	2000	366.0	364.0	50.0

# MECHANICAL DATA

## PLASTIC SMALL-OUTLINE PACKAGE

#### 0,51 0,35 ⊕0,25⊛ 1,27 8 14 0,15 NOM 5,60 8,20 5,00 7,40 $\bigcirc$ Gage Plane ₽ 0,25 7 1 1,05 0,55 0-10 Δ 0,15 0,05 Seating Plane — 2,00 MAX 0,10PINS \*\* 14 16 20 24 DIM 10,50 10,50 12,90 15,30 A MAX A MIN 9,90 9,90 12,30 14,70 4040062/C 03/03

NOTES: A. All linear dimensions are in millimeters.

NS (R-PDSO-G\*\*)

**14-PINS SHOWN** 

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



# **MECHANICAL DATA**

PLASTIC SMALL-OUTLINE

MPDS006C - FEBRUARY 1996 - REVISED AUGUST 2000

## DGV (R-PDSO-G\*\*)

24 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15 per side.
- D. Falls within JEDEC: 24/48 Pins MO-153

14/16/20/56 Pins – MO-194



D (R-PDSO-G14)

PLASTIC SMALL OUTLINE



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AB.





NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
  E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



PW (R-PDSO-G14)

PLASTIC SMALL OUTLINE



A. An integration of the information o

Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0,15 each side.

Body width does not include interlead flash. Interlead flash shall not exceed 0,25 each side.

E. Falls within JEDEC MO-153



# **MECHANICAL DATA**

MSSO002E - JANUARY 1995 - REVISED DECEMBER 2001

# DB (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE

28 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.
- D. Falls within JEDEC MO-150



## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated