

SBOS056F - JANUARY 2002 - JULY 2005


High-Voltage, High-Current OPERATIONAL AMPLIFIER

FEATURES

- WIDE SUPPLY RANGE Single Supply: +8V to +60V Dual Supply: ±4V to ±30V
- HIGH OUTPUT CURRENT:
 500mA Continuous
- WIDE OUTPUT VOLTAGE SWING
- FULLY PROTECTED: Thermal Shutdown Adjustable Current Limit
- OUTPUT DISABLE CONTROL
- THERMAL SHUTDOWN INDICATOR
- HIGH SLEW RATE: 6V/μs
- LOW QUIESCENT CURRENT
- PACKAGES:
 7-Lead TO-220, Zip and Straight Leads
 7-Lead DDPAK Surface-Mount

APPLICATIONS

- VALVE, ACTUATOR DRIVERS
- SYNCHRO, SERVO DRIVERS
- POWER SUPPLIES
- TEST EQUIPMENT
- TRANSDUCER EXCITATION
- AUDIO AMPLIFIERS



DESCRIPTION

The OPA547 is a low-cost, high-voltage/high-current operational amplifier ideal for driving a wide variety of loads. A laser-trimmed monolithic integrated circuit provides excellent low-level signal accuracy and high output voltage and current

The OPA547 operates from either single or dual supplies for design flexibility. In single-supply operation, the input common-mode range extends below ground.

The OPA547 is internally protected against over-temperature conditions and current overloads. In addition, the OPA547 was designed to provide an accurate, user-selected current limit. Unlike other designs which use a "power" resistor in series with the output current path, the OPA547 senses the load indirectly. This allows the current limit to be adjusted from 0mA to 750mA with a 0 to 150 μ A control signal. This is easily done with a resistor/potentiometer or controlled digitally with a voltage-out or current-out DAC.

The Enable/Status (E/S) pin provides two functions. An input on the pin not only disables the output stage to effectively disconnect the load, but also reduces the quiescent current to conserve power. The E/S pin output can be monitored to determine if the OPA547 is in thermal shutdown.

The OPA547 is available in an industry-standard 7-lead staggered and straight lead TO-220 package, and a 7-lead DDPAK surface-mount plastic power package. The copper tab allows easy mounting to a heat sink or circuit board for excellent thermal performance. It is specified for operation over the extended industrial temperature range, -40°C to +85°C.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



ABSOLUTE MAXIMUM RATINGS(1)

Output Current	See SOA Curve
Supply Voltage, V+ to V	60V
Input Voltage	
Input Shutdown Voltage	V+
Operating Temperature	40°C to +125°C
Storage Temperature	55°C to +125°C
Junction Temperature	150°C
Lead Temperature (soldering 10s)(2)	300°C

NOTES: (1) Stresses above these ratings may cause permanent damage. (2) Vapor-phase or IR reflow techniques are recommended for soldering the OPA547F surface-mount package. Wave soldering is not recommended due to excessive thermal shock and "shadowing" of nearby devices.




This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

PACKAGE/ORDERING INFORMATION

For the most current package and ordering information, see the Package Ordering Addendum at the end of this document, or see the TI website at www.ti.com.

PIN CONFIGURATIONS



ELECTRICAL CHARACTERISTICS


At $T_{CASE} = +25$ °C, $V_S = \pm 30$ V and E/S pin open, unless otherwise noted.


			ı			
PARAMETER	CONDITION	MIN	TYP	MAX	UNITS	
OFFSET VOLTAGE						
Input Offset Voltage	$V_{CM} = 0, I_{O} = 0$		±1	±5	mV	
vs Temperature	$T_A = -40^{\circ}C \text{ to } +85^{\circ}C$		±25		μV/°C	
vs Power Supply	$V_S = \pm 4V \text{ to } \pm 30V$		10	100	μV/V	
INPUT BIAS CURRENT(1)						
Input Bias Current(2)	$V_{CM} = 0V$		-100	-500	nA	
vs Temperature			±0.5		nA/°C	
Input Offset Current	$V_{CM} = 0V$		±5	±50	nA	
NOISE						
Input Voltage Noise Density, f = 1kHz			90		nV/√ Hz	
Current Noise Density, f = 1kHz			200		fA/√Hz	
INPUT VOLTAGE RANGE						
Common-Mode Voltage Range: Positive	Linear Operation	(V+) -3	(V+) -2.3		V	
Negative	Linear Operation	(V-) -0.1	(V-) -0.2		V	
Common-Mode Rejection	$V_{CM} = (V-) -0.1V \text{ to } (V+) -3V$	80	95		dB	
INPUT IMPEDANCE						
Differential			10 ⁷ 6		Ω pF	
Common-Mode			10 ⁹ 4		Ω pF	
OPEN-LOOP GAIN						
Open-Loop Voltage Gain, f = 10Hz	$V_O = \pm 25V$, $R_L = 1k\Omega$	100	115		dB	
	$V_0 = \pm 25V, R_L = 50\Omega$		110		dB	
FREQUENCY RESPONSE						
Gain-Bandwidth Product	$R_L = 50\Omega$		1		MHz	
Slew Rate	$G = 1,50V_{PP}, R_{L} = 50\Omega$		6		V/μs	
Full-Power Bandwidth	0 40 50 / 0 /		See Typical Curve		kHz	
Settling Time: ±0.1%	G = -10, 50V Step		18 0.004 ⁽³⁾		μs	
Total Harmonic Distortion + Noise, f = 1kHz	$R_L = 50\Omega$, $G = +3V$, 1W Power		0.004(0)		%	
OUTPUT	1 0.54	()(.) 0.0	()(.) 40		.,	
Voltage Output, Positive	$I_{O} = 0.5A$ $I_{O} = -0.5A$	(V+) -2.2	(V+) -1.9		V V	
Negative Positive	$I_0 = -0.5A$ $I_0 = 0.1A$	(V–) +1.6 (V+) –1.8	(V-) +1.3 (V+) -1.5		ľ	
Negative	$I_0 = 0.1A$ $I_0 = -0.1A$	(V+) -1.8 (V-) +1.2	(V+) =1.3 (V-) +0.8		ľ	
Maximum Continuous Current Output: dc	10 = -0.1A	±500	(V-) +0.0		mA	
ac		500			mArms	
Leakage Current, Output Disabled, dc			See Typical Curve			
Output Current Limit						
Current Limit Range			0 to ±750		mA	
Current Limit Equation		$I_{LIM} = ($	5000)(4.75)/(316000		A	
Current Limit Tolerance ⁽¹⁾	$R_{CL} = 31.6k\Omega (I_{LIM} = \pm 375mA),$		±10	±30	mA	
Consoitive Lond Drive	$R_L = 50\Omega$		 See Typical Curve ⁽⁴)		
Capacitive Load Drive			The Typical Curve	,		
OUTPUT ENABLE /STATUS (E/S) PIN Shutdown Input Mode						
V _{E/S} HIGH (output enabled)	E/S Pin Open or Forced HIGH	(V-) +2.4			V	
$V_{E/S}$ LOW (output enabled)	E/S Pin Forced LOW	(v=) +2.4		(V-) +0.8	ľ	
I _{E/S} HIGH (output enabled)	E/S Pin HIGH		-60	(. ,	μA	
I _{E/S} LOW (output disabled)	E/S Pin LOW		–65		μΑ	
Output Disable Time			1		μs	
Output Enable Time			3		μs	
Thermal Shutdown Status Output						
Normal Operation	Sourcing 20μA	(V-) +2.4	(V-) +3.5		V	
Thermally Shutdown	Sinking 5μA, T _J > 160°C		(V-) +0.35	(V-) +0.8	V	
Junction Temperature, Shutdown			+160		°C	
Reset from Shutdown			+140		°C	
POWER SUPPLY						
Specified Voltage		1.4	±30	100	V	
Operating Voltage Range	Connected to V C	±4	140	±30	V m^	
Quiescent Current Quiescent Current, Shutdown Mode	I _{LIM} Connected to V-, I _O = 0 I _{LIM} Connected to V-		±10 ±4	±15	mA mA	
TEMPERATURE RANGE	I _{LIM} Solificoted to V=		<u></u>		111/5	
TEMPERATURE RANGE Specified Range		-40		+85	°C	
Operating Range		-40 -40		+125	.c	
Storage Range		-55		+125	.c	
Thermal Resistance, θ_{IC}		30		20	l	
7-Lead DDPAK, 7-Lead TO-220	f > 50Hz		2		°C/W	
7-Lead DDPAK, 7-Lead TO-220	dc		3		°C/W	
Thermal Resistance, θ_{JA}						
7-Lead DDPAK, 7-Lead TO-220	No Heat Sink		65		°C/W	


NOTES: (1) High-speed test at $T_J = +25^{\circ}$ C. (2) Positive conventional current flows into the input terminals. (3) See *Total Harmonic Distortion+Noise* in the Typical Characteristics section for additional power levels. (4) See *Small-Signal Overshoot vs Load Capacitance* in the Typical Characteristics section.


TYPICAL CHARACTERISTICS


At T_{CASE} = +25°C, V_{S} = ± 30 V, and E/S pin open, unless otherwise noted.




















TYPICAL CHARACTERISTICS (Cont.)


At T_{CASE} = +25°C, V_S = ±30V, and E/S pin open, unless otherwise noted.






















TYPICAL CHARACTERISTICS (Cont.)


At T_{CASE} = +25°C, V_{S} = ±30V, and E/S pin open, unless otherwise noted.



















TYPICAL CHARACTERISTICS (Cont.)

At T_{CASE} = +25°C, V_S = ± 35 V, and E/S pin open, unless otherwise noted.





LARGE SIGNAL STEP RESPONSE $G=3,\,C_L=100pF,\,R_L=50\Omega$







APPLICATIONS INFORMATION

Figure 1 shows the OPA547 connected as a basic noninverting amplifier. The OPA547 can be used in virtually any op amp configuration.

Power-supply terminals should be bypassed with low series impedance capacitors. The technique shown, using a ceramic and tantalum type in parallel, is recommended. Powersupply wiring should have low series impedance.




FIGURE 1. Basic Circuit Connections.

POWER SUPPLIES

The OPA547 operates from single (+8V to +60V) or dual (±4V to ±30V) supplies with excellent performance. Most behavior remains unchanged throughout the full operating voltage range. Parameters which vary significantly with operating voltage are shown in the typical characteristic curves.

Some applications do not require equal positive and negative output voltage swing. Power-supply voltages do not need to be equal. The OPA547 can operate with as little as 8V between the supplies and with up to 60V between the supplies. For example, the positive supply could be set to 55V with the negative supply at -5V, or vice-versa.

ADJUSTABLE CURRENT LIMIT

The OPA547 features an accurate, user-selected current limit. Current limit is set from 0mA to 750mA by controlling the input to the I_{LIM} pin. Unlike other designs which use a power resistor in series with the output current path, the OPA547 senses the load indirectly. This allows the current limit to be set with a 0μA to 150μA control signal. In contrast, other designs require a limiting resistor to handle the full output current (750mA in this case).

With the OPA547, the simplest method for adjusting the current limit uses a resistor or potentiometer connected between the I_{LIM} pin and V- according to the Equation 1:

$$R_{CL} = \frac{(5000)(4.75)}{I_{LIM}} - 31.6k\Omega \tag{1}$$

The low-level control signal (0μA to 150μA) also allows the current limit to be digitally controlled with a current-out or voltage-out DAC reference to V- according to the equations given in Figure 3.

Figure 3 shows a simplified schematic of the internal circuitry used to set the current limit. Leaving the IIIM pin open programs the output current to zero, while connecting IIIM directly to V- programs the maximum output current limit, typically 750mA.

SAFE OPERATING AREA

Stress on the output transistors is determined both by the output current and by the output voltage across the conducting output transistor, V_S - V_O. The power dissipated by the output transistor is equal to the product of the output current and the voltage across the conducting transistor, $V_S - V_O$. The Safe Operating Area (SOA curve, Figure 2) shows the permissible range of voltage and current.




FIGURE 2. Safe Operating Area.

The safe output current decreases as $V_S - V_O$ increases. Output short-circuits are a very demanding case for SOA. A short-circuit to ground forces the full power-supply voltage (V+ or V–) across the conducting transistor. With $T_C = 25$ °C the maximum output current of 500mA can be achieved under most conditions. Increasing the case temperature reduces the safe output current that can be tolerated without activating the thermal shutdown circuit of the OPA547. For further insight on SOA, consult Application Bulletin SBOA022.

POWER DISSIPATION

Power dissipation depends on power supply, signal, and load conditions. For dc signals, power dissipation is equal to the product of output current times the voltage across the con-



ducting output transistor. Power dissipation can be minimized by using the lowest possible power-supply voltage necessary to assure the required output voltage swing.

For resistive loads, the maximum power dissipation occurs at a dc output voltage of one-half the power-supply voltage. Dissipation with ac signals is lower. Application Bulletin SBOA022 explains how to calculate or measure power dissipation with unusual signals and loads.

HEAT SINKING

Most applications require a heat sink to assure that the maximum junction temperature (150°C) is not exceeded. The heat sink required depends on the power dissipated and on

ambient conditions. Consult Application Bulletin SBOA021 for information on determining heat sink requirements. The internal protection circuitry was designed to protect against overload conditions. It does not activate until the junction temperature reaches approximately 160°C and was not intended to replace proper heat sinking. Continuously running the OPA547 into thermal shutdown will degrade reliability.

The tab of the DDPAK surface-mount version should be soldered to a circuit board copper area for good heat dissipation. Figure 4 shows typical thermal resistance from junction to ambient as a function of the copper area.




FIGURE 3. Adjustable Current Limit.




FIGURE 4. Thermal Resistance versus Circuit Board Copper Area.





THERMAL PROTECTION

The OPA547 has thermal shutdown that protects the amplifier from damage. Activation of the thermal shutdown circuit during normal operation is an indication of excessive power dissipation or an inadequate heat sink. Depending on load and signal conditions, the thermal protection circuit may cycle on and off. This limits the dissipation of the amplifier but may have an undesirable effect on the load.

The thermal protection activates at a junction temperature of approximately 160°C. However, for reliable operation, junction temperature should be limited to 150°C. To estimate the margin of safety in a complete design (including heat sink), increase the ambient temperature until the thermal protection is activated. Use worst-case load and signal conditions. For good reliability, the thermal protection should trigger more than 35°C above the maximum expected ambient condition of the application. This produces a junction temperature of 125°C at the maximum expected ambient condition.

ENABLE/STATUS (E/S) PIN

The Enable/Status pin provides two functions: forcing this pin low disables the output stage, or E/S can be monitored to determine if the OPA547 is in thermal shutdown. One or both of these functions can be utilized on the same device using single or dual supplies. For normal operation (output enabled), the E/S pin can be left open or pulled high (at least +2.4V above the negative rail).

Output Disable

A unique feature of the OPA547 is its output disable capability. This function not only conserves power during idle periods (quiescent current drops to approximately 4mA), but also allows multiplexing in low frequency (f<10kHz), multichannel applications. Signals that are greater than 10kHz may cause leakage current to increase in devices that are shutdown. Figure 15 shows the two OPA547s in a switched amplifier configuration. The on/off state of the two amplifiers is controlled by the voltage on the E/S pin.

To disable the output, the E/S pin is pulled low, no greater than 0.8V above the negative rail. Typically the output is shutdown in 1 μ s. Figure 5 provides an example of how to implement this function using a single supply. Figure 6 gives a circuit for dual-supply applications. To return the output to an enabled state, the E/S pin should be disconnected (open) or pulled to at least (V–) + 2.4V. It should be noted that pulling the E/S pin high (output enabled) does not disable internal thermal shutdown.




FIGURE 5. Output Disable with a Single Supply.




FIGURE 6. Output Disable with Dual Supplies.

Thermal Shutdown Status

Internal thermal shutdown circuitry shuts down the output when the die temperature reaches approximately 160°C, resetting when the die has cooled to 140°C. The E/S pin can be monitored to determine if shutdown has occurred. During normal operation the voltage on the E/S pin is typically 3.5V above the negative rail. Once shutdown has occurred this voltage drops to approximately 350mV above the negative rail.

Figure 7 gives an example of monitoring shutdown in a single-supply application. Figure 8 provides a circuit for dual supplies. External logic circuitry or an LED could be used to indicate if the output has been thermally shutdown, see Figure 13.




FIGURE 7. Thermal Shutdown Status with a Single Supply.




FIGURE 8. Thermal Shutdown Status with Dual Supplies.



Output Disable and Thermal Shutdown Status

As mentioned earlier, the OPA547's output can be disabled and the disable status can be monitored simultaneously. Figures 9 and 10 provide examples using a single supply and dual supplies, respectively.




FIGURE 9. Output Disable and Thermal Shutdown Status with a Single Supply.

OUTPUT STAGE COMPENSATION

The complex load impedances common in power op amp applications can cause output stage instability. For normal operation output compensation circuitry is not typically required. However, if the OPA547 is intended to be driven into current limit, a R/C network may be required. Figure 11 shows an output series R/C compensation (snubber) network (3 Ω in series with 0.01 μF) which generally provides excellent stability. Some variations in circuit values may be required with certain loads.

OUTPUT PROTECTION

Reactive and EMF-generating loads can return load current to the amplifier, causing the output voltage to exceed the power-supply voltage. This damaging condition can be avoided with clamp diodes from the output terminal to the power supplies, as shown in Figure 11. Schottkey rectifier diodes with a 1A or greater continuous rating are recommended.




FIGURE 11. Motor Drive Circuit.




FIGURE 10. Output Disable and Thermal Shutdown Status with Dual Supplies.





VOLTAGE SOURCE APPLICATION

Figure 12 illustrates how to use the OPA547 to provide an accurate voltage source with only three external resistors. First, the current limit resistor, R_{CL} , is chosen according to the desired output current. The resulting voltage at the I_{LIM} pin is constant and stable over temperature. This voltage, V_{CL} , is connected to the noninverting input of the op amp and used as a voltage reference, thus eliminating the need for an external reference. The feedback resistors are selected to gain V_{CL} to the desired output voltage level.

PROGRAMMABLE POWER SUPPLY

A programmable power supply can easily be built using the OPA547. Both the output voltage and output current are user-controlled. Figure 13 shows a circuit using potentiometers to adjust the output voltage and current while Figure 14 uses DACs. An LED tied to the E/S pin through a logic gate indicates if the OPA547 is in thermal shutdown.




FIGURE 12. Voltage Source.




FIGURE 13. Resistor-Controlled Programmable Power Supply.






FIGURE 14. Digitally-Controlled Programmable Power Supply.




FIGURE 15. Swap Amplifier.




FIGURE 16. Multiple Current Limit Values.

www.ti.com 27-Feb-2024

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing		Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
OPA547F/500	ACTIVE	DDPAK/ TO-263	KTW	7	500	RoHS & Green	Call TI SN	Level-2-260C-1 YEAR	-40 to 85	OPA547F	Samples
OPA547FKTWT	ACTIVE	DDPAK/ TO-263	KTW	7	250	RoHS & Green	Call TI SN	Level-2-260C-1 YEAR	-40 to 85	OPA547F	Samples
OPA547T	ACTIVE	TO-220	KVT	7	50	RoHS & Green	Call TI SN	N / A for Pkg Type	-40 to 85	OPA547T	Samples
OPA547T-1	ACTIVE	TO-220	KC	7	50	RoHS & Green	Call TI SN	N / A for Pkg Type	-40 to 85	OPA547T	Samples
OPA547TG3	ACTIVE	TO-220	KVT	7	50	TBD	Call TI	Call TI	-40 to 85		Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.



PACKAGE OPTION ADDENDUM

www.ti.com 27-Feb-2024


Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 2-Nov-2023

TUBE




*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
OPA547T	KVT	TO-220	7	50	532.13	34.54	13340	NA
OPA547T-1	KC	TO-220	7	50	532.13	34.54	13340	NA

KTW (R-PSFM-G7)

PLASTIC FLANGE-MOUNT



NOTES: A. All linear dimensions are in inches (millimeters).

B. This drawing is subject to change without notice.

Lead width and height dimensions apply to the plated lead.


- D. Leads are not allowed above the Datum B.
- E. Stand-off height is measured from lead tip with reference to Datum B.

Lead width dimension does not include dambar protrusion. Allowable dambar protrusion shall not cause the lead width to exceed the maximum dimension by more than 0.003".

G. Cross-hatch indicates exposed metal surface.

Falls within JEDEC MO–169 with the exception of the dimensions indicated.






NOTES: A. All linear dimensions are in inches (millimeters).

B. This drawing is subject to change without notice.

1

KC (R-PSFM-T7)

PLASTIC FLANGE-MOUNT PACKAGE



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- C. Lead dimensions are not controlled within this area.
- D. All lead dimensions apply before solder dip.
- E. The center lead is in electrical contact with the mounting tab.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated