











**TRF37B73** 

SLASE41 - MAY 2014

# TRF37B73 1-6000 MHz RF Gain Block

#### **Features**

1 MHz - 6000 MHz

Gain: 14.5 dB

Noise Figure: 4 dB

Output P1dB: 15 dBm at 2000 MHz Output IP3: 27 dBm at 2000 MHz

Power Down Mode Single Supply: 3.3 V

Stabilized Performance Over Temperature

Unconditionally Stable

Robust ESD: >1 kV HBM; >1 kV CDM

# **Applications**

- General Purpose RF Gain Block
- Consumer
- Industrial
- **Utility Meters**
- Low-cost Radios
- Cellular Base Station
- Wireless Infrastructure
- RF Backhaul
- Radar
- **Electronic Warfare**
- Software-defined Radio
- **Test and Measurement**
- Point-to-Point/Multipoint Microwave
- Software Defined Radios
- **RF** Repeaters
- Distributed Antenna Systems
- LO and PA Driver Amplifier
- Wireless Data, Satellite, DBS, CATV
- IF Amplifier

## 3 Description

The TRF37B73 is packaged in a 2.00mm x 2.00mm WSON with a power down pin feature making it ideal for applications where space and low power modes are critical.


The TRF37B73 is designed for ease of use. For maximum flexibility, this family of parts uses a common 3.3 V supply and consumes 52 mA. In addition, this family was designed with an active bias circuit that provides a stable and predictable bias current over process, temperature and voltage variations. For gain and linearity budgets the device was designed to provide a flat gain response and excellent OIP3 out to 6000 MHz. For space constrained applications, this family is internally matched to 50  $\Omega$ , which simplifies ease of use and minimizes needed PCB area.

#### Device Information<sup>(1)</sup>

PART NUMBER	PACKAGE	BODY SIZE (NOM)		
TRF37B73	WSON (32)	2.00mm x 2.00mm		

(1) For all available packages, see the orderable addendum at the end of the datasheet.

## Simplified Schematic



SLASE41 –MAY 2014 www.ti.com



# **Table of Contents**

1	Features 1		7.2 Functional Block Diagram	8
2	Applications 1		7.3 Feature Description	8
3	Description 1		7.4 Device Functional Modes	8
4	Revision History2	8	Applications and Implementation	9
5	Pin Configuration and Functions3		8.1 Application Information	9
6	Specifications4		8.2 Typical Application	9
U	6.1 Absolute Maximum Ratings	9	Power Supply Recommendations	10
	6.2 Handling Ratings	10	Layout	11
	6.3 Recommended Operating Conditions		10.1 Layout Guidelines	11
	6.4 Thermal Information		10.2 Layout Example	11
	6.5 Electrical Characteristics	11	Device and Documentation Support	12
	6.6 Timing Requirements		11.1 Trademarks	12
	6.7 Typical Characteristics		11.2 Electrostatic Discharge Caution	12
7	Detailed Description 8		11.3 Glossary	12
-	7.1 Overview 8	12	Mechanical, Packaging, and Orderable Information	12

# 4 Revision History


DATE	REVISION	NOTES
May 2014	*	Initial release.



www.ti.com

# **5 Pin Configuration and Functions**

### DSG PACKAGE (TOP VIEW)



### **Pin Functions**

	PIN	DESCRIPTION
NAME	NO.	DESCRIPTION
VCC	1	DC Bias.
RFIN	2	RF input. Connect to an RF source through a DC-blocking capacitor. Internally matched to 50 $\Omega$ .
NC	3, 4, 6, 8	No electrical connection. Connect pad to GND for board level reliability integrity.
PWDN	5	When high the device is in power down state. When LOW or NC the device is in active state. Internal pulldown resistor to GND.
RFOUT	7	RF Output and DC Bias ( $V_{CC}$ ). Connect to DC supply through an RF choke inductor. Connect to output load through a DC-blocking capacitor. Internally matched to 50 $\Omega$ .
GND	PowerPAD™	RF and DC GND. Connect to PCB ground plane.

SLASE41 – MAY 2014 www.ti.com

# TEXAS INSTRUMENTS

### 6 Specifications

#### 6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) (1)

	MIN	MAX	UNIT
Supply Input voltage	-0.3	3.6	V
Input Power		10	dBm
Operating virtual junction temperature range	-40	150	°C

<sup>(1)</sup> Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

## 6.2 Handling Ratings

			MIN	MAX	UNIT
T <sub>STG</sub>	Storage temperature range		-65	150	°C
V <sub>ESD</sub>	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins <sup>(1)</sup>	-1	1	kV
		Charged device model (CDM), per JEDEC specification JESD22-C101, all pins (2)	-1	1	kV

<sup>(1)</sup> JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

## 6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

	MIN	NOM	MAX	UNIT
Supply Voltage, V <sub>CC</sub>	3	3.3	3.45	V
Operating junction temperature, T <sub>J</sub>	-40		125	°C

#### 6.4 Thermal Information

	THERMAL METRIC <sup>(1)</sup>	DSG	LIAUT
	THERMAL METRIC***	8 PINS	UNIT
$R_{\theta JA}$	Junction-to-ambient thermal resistance	79.3	
R <sub>0JCtop</sub>	Junction-to-case (top) thermal resistance	110	
$R_{\theta JB}$	Junction-to-board thermal resistance	49	9000
ΨЈТ	Junction-to-top characterization parameter	6	°C/W
ΨЈВ	Junction-to-board characterization parameter	49.4	
R <sub>0JCbot</sub>	Junction-to-case (bottom) thermal resistance	19.2	

(1) For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report, SPRA953.

<sup>(2)</sup> JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.



www.ti.com

## 6.5 Electrical Characteristics

 $V_{CC} = 3V3, \, T_A = 25^{\circ}C, \, PWDN = Low, \, L_{OUT} = 100 \, \, nH, \, C1 = C2 = 1000 \, \, pF, \, Z_S = Z_L = 50 \, \, \Omega \, \, (unless \, \, otherwise \, \, noted)$ 


	PARAMETER	TEST CONDITIONS	MIN TYP	MAX	UNIT
DC PRA	METERS				
	Total supply current		52	2 65	mA
I <sub>CC</sub>	Power down current	PWDN = High	125	5	μA
P <sub>diss</sub>	Power dissipation		0.172	2	W
	QUENCY RANGE				
	Frequency range		1	6000	MHz
		f <sub>RF</sub> = 400 MHz	15.5	5	dB
		f <sub>RF</sub> = 2000 MHz	14.5	5	dB
G	O constitution of social	f <sub>RF</sub> = 3000 MHz	14.5	5	dB
	Small signal gain	f <sub>RF</sub> = 4000 MHz	14	ļ	dB
		f <sub>RF</sub> = 5000 MHz	13	3	dB
		f <sub>RF</sub> = 6000 MHz	11.5	5	dB
OP1dB	Output 1dB compression point	At 2000 MHz	15	5	dBm
OIP3	Output 3rd order intercept point	At 2000 MHz, 2-tone 10 MHz apart	27	7	dBm
NF	Noise figure	At 2000 MHz	4	ļ	dB
R <sub>(LI)</sub>	Input return loss	At 2000 MHz	20	)	dB
R <sub>(LO)</sub>	Output return loss	At 2000 MHz	16	3	dB
PWDN P	PIN				
V <sub>IH</sub>	High level input level		2		V
$V_{IL}$	Low level input level			0.8	V
I <sub>IH</sub>	High level input current		30	)	μA
I <sub>IL</sub>	Low level input current				μA

# 6.6 Timing Requirements

			MIN	TYP	MAX	UNIT
<b>PWDN PIN</b>				·		
t <sub>ON</sub>	Turn-on Time	50% TTL to 90% P <sub>OUT</sub>		0.6		μs
t <sub>OFF</sub>	Turn-off Time	50% TTL to 10% P <sub>OUT</sub>		1.4		μs

# TEXAS INSTRUMENTS


### 6.7 Typical Characteristics





www.ti.com

**Typical Characteristics (continued)** 



SLASE41 – MAY 2014 www.ti.com


# TEXAS INSTRUMENTS

### 7 Detailed Description

#### 7.1 Overview

The device is a 3.3 V general purpose RF gain block. It is a SiGe Darlington amplifier with integrated 50  $\Omega$  input and output matching. The device contains an active bias circuit to maintain performance over a wide temperature and voltage range. The included power down function allows the amplifier to shut down saving power when the amplifier is not needed. Fast shut down and start up enable the amplifier to be used in a host of time division duplex applications.

#### 7.2 Functional Block Diagram



## 7.3 Feature Description

The TRF37B73 is a fixed gain RF amplifier. It is internally matched to 50  $\Omega$  on both the input and output. It is a fully cascadable general purpose amplifier. The included active bias circuitry ensures the amplifier performance is optimized over the full operating temperature and voltage ranges.

#### 7.4 Device Functional Modes

#### 7.4.1 Power Down

The TRF37B73 PWDN pin can be left unconnected for normal operation or a logic-high for disable mode operation. For applications that use the power down mode, normal 5 V TLL levels are supported.



# 8 Applications and Implementation

### 8.1 Application Information

The TRF37B73 is a wideband, high performance, general purpose RF amplifier. To maximize its performance, good RF layout and grounding techniques should be employed.

## 8.2 Typical Application

The TRF37B73 device is typically placed in a system as illustrated in Figure 13.




Figure 13. Typical Application Schematic for TRF37B73

#### 8.2.1 Design Requirements

**Table 1. Design Parameters** 

PARAMETERS	EXAMPLE VALUES
Input power range	< 3 dBm
Output power	< 18 dBm
Operating frequency range	1 — 6000 MHz

SLASE41 – MAY 2014 www.ti.com

# TEXAS INSTRUMENTS

#### 8.2.2 Detailed Design Procedure

The TRF37B73 is a simple to use internally matched and cascadable RF amplifier. Following the recommended RF layout with good quality RF components and local DC bypass capacitors will ensure optimal performance is achieved. TI provides various support materials including S-Parameter and ADS models to allow the design to be optimized to the user's particular performance needs.

#### 8.2.3 Application Curve




Figure 14. OP1dB and NF vs Frequency

# 9 Power Supply Recommendations

All supplies may be generated from a common nominal 3.3 V source but should be isolated through decoupling capacitors placed close to the device. The typical application schematic in Figure 13 is an excellent example. Select capacitors with self-resonant frequency near the application frequency. When multiple capacitors are used in parallel to create a broadband decoupling network, place the capacitor with the higher self-resonant frequency closer to the device. Expensive tantalum capacitors are not needed for optimal performance.



# 10 Layout


www.ti.com

#### 10.1 Layout Guidelines

Good layout practice helps to enable excellent linearity and isolation performance. An example of good layout is shown in Figure 15. In the example, only the top signal layer and its adjacent ground reference plane are shown.

- Excellent electrical connection from the PowerPAD™ to the board ground is essential. Use the recommended footprint, solder the pad to the board, and do not include solder mask under the pad.
- Connect pad ground to device terminal ground on the top board layer.
- Verify that the return DC and RF current path have a low impedance ground plane directly under the package and RF signal traces into and out of the amplifier.
- Ensure that ground planes on the top and any internal layers are well stitched with vias.
- Do not route RF signal lines over breaks in the reference ground plane.
- · Avoid routing clocks and digital control lines near RF signal lines.
- Do not route RF or DC signal lines over noisy power planes. Ground is the best reference, although clean power planes can serve where necessary.
- · Place supply decoupling close to the device.

## 10.2 Layout Example



Note: Ensure all components are connected to a common RF/DC ground plane with plenty of vias

Figure 15. Layout

SLASE41 – MAY 2014 www.ti.com



## 11 Device and Documentation Support

#### 11.1 Trademarks

PowerPAD is a trademark of Texas Instruments.

### 11.2 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

## 11.3 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms and definitions.

# 12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical packaging and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

www.ti.com 11-Aug-2022

#### PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
TRF37B73IDSGR	ACTIVE	WSON	DSG	8	3000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	B73I	Samples
TRF37B73IDSGT	ACTIVE	WSON	DSG	8	250	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	B73I	Samples

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



# **PACKAGE OPTION ADDENDUM**

www.ti.com 11-Aug-2022

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 9-Aug-2022

### TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TRF37B73IDSGR	WSON	DSG	8	3000	180.0	8.4	2.3	2.3	1.15	4.0	8.0	Q2
TRF37B73IDSGT	WSON	DSG	8	250	180.0	8.4	2.3	2.3	1.15	4.0	8.0	Q2

www.ti.com 9-Aug-2022



#### \*All dimensions are nominal

Ì	Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
	TRF37B73IDSGR	WSON	DSG	8	3000	182.0	182.0	20.0
İ	TRF37B73IDSGT	WSON	DSG	8	250	182.0	182.0	20.0

2 x 2, 0.5 mm pitch


PLASTIC SMALL OUTLINE - NO LEAD

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.





PLASTIC SMALL OUTLINE - NO LEAD




#### NOTES:

- All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



PLASTIC SMALL OUTLINE - NO LEAD




NOTES: (continued)

- 4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



PLASTIC SMALL OUTLINE - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



### **IMPORTANT NOTICE AND DISCLAIMER**

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated