

Sample &

Buy







SN74AHCT16244

SCLS334J-MARCH 1996-REVISED OCTOBER 2014

SN74AHCT16244 16-Bit Buffers/Drivers With 3-State Outputs

1 Features

- Members of the Texas Instruments Widebus™ Family
- EPIC[™] (Enhanced-Performance Implanted CMOS) Process
- Inputs are TTL-Voltage Compatible
- Distributed V_{CC} and GND Pins Minimize • High-Speed Switching Noise
- Flow-Through Architecture Optimizes PCB Layout
- Latch-Up Performance Exceeds 250 mA • Per JESD 17
- ESD Protection Exceeds 2000 V Per . MIL-STD-883, Method 3015
- Package Options Include:

Simplified Schematic

4

- _ Plastic Shrink Small Outline (DL) Package
- Thin Shrink Small Outline (DGG) Package
- Thin Very Small Outline (DGV) Package
- _ 380-mil Fine-Pitch Ceramic Flat (WD) Package Using 25-mil Center-to-Center Spacings

Applications 2

• **Telecom Infrastructure**

Tools &

Software

- Wireless Infrastructure
- Electronic Points of Sale
- Health and Fitness
- **Printers and Other Peripherals** •
- Motor Drives


3 Description


The SN74AHCT16244 device is a 16-bit buffer and line driver specifically designed to improve the performance and density of 3-state memory address drivers, clock drivers, and bus-oriented receivers and transmitters.


Device	Informa	ation ⁽¹⁾
--------	---------	----------------------

PART NUMBER	PACKAGE	BODY SIZE (NOM)	
SN74AHCT16244	TSSOP (48)	12.50 mm x 6.10 mm	
	TVSOP (48)	9.70 mm x 4.40 mm	
	SSOP (48)	15.80 mm x 7.50 mm	

(1) For all available packages, see the orderable addendum at the end of the data sheet.







An IMPORTANT NOTICE at the end of this data sheet addresses availability, warranty, changes, use in safety-critical applications, 63 intellectual property matters and other important disclaimers. PRODUCTION DATA.

Table of Contents

1	Feat	ures 1
2	Арр	lications 1
3	Dese	cription 1
4	Sim	plified Schematic 1
5	Revi	sion History 2
6	Pin	Configuration and Functions 3
7	Spee	cifications5
	7.1	Absolute Maximum Ratings 5
	7.2	Handling Ratings5
	7.3	Recommended Operating Conditions 5
	7.4	Thermal Information 6
	7.5	Electrical Characteristics
	7.6	Switching Characteristics, $V_{CC} = 5 V \pm 0.5 V$
	7.7	Noise Characteristics 7
	7.8	Operating Characteristics7
	7.9	Typical Characteristics 7
8	Para	meter Measurement Information

9	Deta	iled Description	9
	9.1	Overview	9
	9.2	Functional Block Diagram	9
	9.3	Feature Description	9
	9.4	Device Functional Modes	9
10	Арр	lication and Implementation	10
	10.1	Application Information	10
	10.2	Typical Application	
11	Pow	ver Supply Recommendations	11
12	Laye	out	11
	12.1	Layout Guidelines	11
	12.2	Layout Example	11
13	Dev	ice and Documentation Support	12
	13.1	Trademarks	12
	13.2	Electrostatic Discharge Caution	12
	13.3	Glossary	12
14	Mec	hanical, Packaging, and Orderable	
	Infor	mation	12

Copyright © 1996–2014, Texas Instruments Incorporated

5 Revision History

Changes from Revision I (January 2000) to Revision J

•	Updated document to new TI data sheet format	1
•	Deleted Ordering Information table.	. 1
•	Deleted SN54AHCT16244 device from data sheet	1
•	Added Applications.	. 1
•	Added Pin Functions table	. 3
•	Added Handling Ratings table	. 5
•	Changed MAX operating temperature to 125°C in Recommended Operating Conditions table.	5
•	Added Thermal Information table.	. 6
•	Added –40°C to 125°C range for SN74AHCT16244 in Electrical Characteristics table.	6
•	Added $T_A = -40^{\circ}$ C to 125°C for SN74AHCT16244 in the Switching Characteristics table	6
•	Added Typical Characteristics.	. 7
•	Added Detailed Description section	. 9
•	Added Application and Implementation section	10
•	Added Power Supply Recommendations and Layout sections	11



www.ti.com



6 Pin Configuration and Functions

SN74AHCT16244 DGG, DGV, OR DL PACKAGE (TOP VIEW)					
10E 1Y1 1Y2 GND 1Y3 1Y4 V _{CC} 2Y1 2Y2 GND 2Y3 2Y4 3Y1 3Y2 GND 3Y3 3Y4 V _{CC} 4Y1 4Y2 GND	1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23	48 20E 47 1A1 46 1A2 45 GND 44 1A3 43 1A4 42 V _{CC} 41 2A1 40 2A2 39 GND 38 2A3 37 2A4 36 3A1 35 3A2 34 GND 33 3A3 32 3A4 31 V _{CC} 30 4A1 29 4A2 28 GND 27 4A3 26 4A4			
4 0E L	24	25 30E			

Pin Functions

PIN		1/0	DESCRIPTION
NO.	NAME	I/O	DESCRIPTION
1	1 <mark>OE</mark>	I	Output Enable 1
2	1Y1	0	1Y1 Output
3	1Y2	0	1Y2 Output
4	GND	—	Ground Pin
5	1Y3	0	1Y3 Output
6	1Y4	0	1Y4 Output
7	V _{CC}	—	Power Pin
8	2Y1	0	2Y1 Output
9	2Y2	0	2Y2 Output
10	GND	—	Ground Pin
11	2Y3	0	2Y3 Output
12	2Y4	0	2Y4 Output
13	3Y1	0	3Y1 Output
14	3Y2	0	3Y2 Output
15	GND	_	Ground Pin
16	3Y3	0	3Y3 Output
17	3Y4	0	3Y4 Output
18	V _{CC}	—	Power Pin

Copyright © 1996–2014, Texas Instruments Incorporated



PIN			DECODIDITION
NO. NAME		- I/O	DESCRIPTION
19	4Y1	0	4Y1 Output
20	4Y2	0	4Y2 Output
21	GND		Ground Pin
22	4Y3	0	4Y3 Output
23	4Y4	0	4Y4 Output
24	4 0E	I	Output Enable 4
25	3 0E	I	Output Enable 3
26	4A4	I	4A4 Input
27	4A3	I	4A3 Input
28	GND		Ground Pin
29	4A2	I	4A2 Input
30	4A1	I	4A1 Input
31	V _{CC}		Power Pin
32	3A4	I	3A4 Input
33	3A3	I	3A3 Input
34	GND		Ground Pin
35	3A2	I	3A2 Input
36	3A1	I	3A1 Input
37	2A4	I	2A4 Input
38	2A3	I	2A3 Input
39	GND	_	Ground Pin
40	2A2	I	2A2 Input
41	2A1	I	2A1 Input
42	V _{CC}	_	Power Pin
43	1A4	I	1A4 Input
44	1A3	I	1A3 Input
45	GND	_	Ground Pin
46	1A2	I	1A2 Input
47	1A1	I	1A1 Input
48	2OE	I	Output Enable 2

Pin Functions (continued)



7 Specifications

7.1 Absolute Maximum Ratings⁽¹⁾

over operating free-air temperature range (unless otherwise noted)

			MIN	MAX	UNIT
V_{CC}	Supply voltage range		-0.5	7	V
VI	Input voltage range ⁽²⁾		-0.5	7	V
Vo	Output voltage range ⁽²⁾		-0.5	V _{CC} + 0.5	V
I _{IK}	Input clamp current	V ₁ < 0		-20	mA
I _{OK}	Output clamp current	$V_O < 0$ or $V_O > V_{CC}$		±20	mA
Ι _Ο	Continuous output current	$V_{O} = 0$ to V_{CC}		±25	mA
	Continuous current through V_{CC} or GND			±75	mA

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

7.2 Handling Ratings

			MIN	MAX	UNIT
T _{stg}	Storage temperature rang	Storage temperature range			°C
V _(ESD)	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins ⁽¹⁾	0	2000	V
		Charged device model (CDM), per JEDEC specification JESD22-C101, all pins ⁽²⁾	0	2000	

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

7.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

		SN74AHCT	SN74AHCT16244		
		MIN MAX		UNIT	
V _{CC}	Supply voltage	4.5	5.5	V	
VIH	High-level input voltage	2		V	
VIL	Low-level input voltage		0.8	V	
VI	Input voltage	0	5.5	V	
Vo	Output voltage	0	V _{CC}	V	
I _{OH}	High-level output current		8	mA	
I _{OL}	Low-level output current		8	mA	
$\Delta t / \Delta v$	Input transition rise or fall rate		20	ns/V	
T _A	Operating free-air temperature	-40	125	°C	

 All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs (SCBA004).

7.4 Thermal Information

			SN74AHCT16244			
	THERMAL METRIC ⁽¹⁾	DGG	DGV	DL	UNIT	
		48 PINS	48 PINS	48 PINS		
$R_{\theta JA}$	Junction-to-ambient thermal resistance	72.5	83.5	64.6		
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	26.8	35.7	34.5		
$R_{\theta J B}$	Junction-to-board thermal resistance	39.4	46.6	36.4	°C/W	
Ψ_{JT}	Junction-to-top characterization parameter	2.6	4.3	11.1		
Ψ _{JB}	Junction-to-board characterization parameter	39.1	46.0	36.1		

(1) For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report (SPRA953).

7.5 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	V _{cc}	T _A = 25°C			SN74AHCT16244		-40°C to 125°C SN74AHCT16244		UNIT
			MIN	TYP	MAX	MIN	MAX	MIN	MAX	
V	I _{OH} = -50 μA	4.5 V	4.4	4.5		4.4		4.4		V
V _{OH}	I _{OH} = -8 mA	4.5 V	3.94			3.8		3.8		v
V	I _{OL} = 50 μA	4.5 V			0.1		0.1		0.1	V
V _{OL}	$I_{OL} = 8 \text{ mA}$	4.5 V			0.36		0.44		0.44	v
lı	$V_{I} = V_{CC}$ or GND	0 V to 5.5 V			±0.1		±1		±1	μΑ
I _{OZ}	$V_0 = V_{CC}$ or GND	5.5 V			±0.25		±2.5		±2.5	μA
I _{CC}	$V_{I} = V_{CC}$ or GND, $I_{O} = 0$	5.5 V			4		40		40	μA
$\Delta I_{CC}^{(1)}$	One input at 3.4 V, Other inputs at V_{CC} or GND	5.5 V			1.35		1.5		1.5	mA
C _i	$V_{I} = V_{CC}$ or GND	5 V		2.5	10		10		10	pF
C _o	$V_0 = V_{CC}$ or GND	5 V		3						pF

(1) This is the increase in supply current for each input at one of the specified TTL voltage levels rather than 0 V or V_{CC}.

7.6 Switching Characteristics, $V_{cc} = 5 V \pm 0.5 V$

over recommended operating free-air temperature range (unless otherwise noted) (see Figure 2)

PARAMETER	FROM (INPUT)	TO (OUTPUT)		T _A = 25°C		SN74AHCT16244		T _A = −40°C to 125°C SN74AHCT16244		UNIT		
	(INFOT)	(001901)	CAPACITANCE	TYP	MAX	MIN	MAX	MIN	MAX			
t _{PLH}	А	Y	0 45 - 5	5.4 ⁽¹⁾	8.5 ⁽¹⁾	1	9.5	1	10.5	ns		
t _{PHL}	A	ř	G _L = 15 pF	C _L = 15 pF	5.4 ⁽¹⁾	8.5 ⁽¹⁾	1	9.5	1	10.5	ns	
t _{PZH}	OE	Y	0 45 - 5	7.7 ⁽¹⁾	10.4 ⁽¹⁾	1	12	1	13			
t _{PZL}	0E	ř	C _L = 15 pF	7.7 ⁽¹⁾	10.4(1)	1	12	1	13	ns		
t _{PHZ}	OE	Y	C ₁ = 15 pF	5 ⁽¹⁾	10.4(1)	1	12	1	13	ns		
t _{PLZ}	UE	ř	0 _L = 15 pr	0L = 15 pF	5 ⁽¹⁾	10.4(1)	1	12	1	13	113	
t _{PLH}	А	Y	0 50 - 5	7	9.5	1	10.5	1	11.5	ns		
t _{PHL}	A	ř	$C_{L} = 50 \text{ pF}$	$G_L = 50 \text{ pm}$	C _L = 50 pF	5.9	9.5	1	10.5	1	11.5	ns
t _{PZH}	OE	Y	0 50 - 5	8.2	11.4	1	13	1	14.5			
t _{PZL}	0E	ř	C _L = 50 pF	8.2	11.4	1	13	1	14.5	ns		
t _{PHZ}	OE	Y	C = 50 pF	8.8	11.4	1	13	1	14	ns		
t _{PLZ}		Ť	C _L = 50 pF	8.8	11.4	1	13	1	14	115		
t _{sk(o)}			C _L = 50 pF		1 ⁽²⁾		1		1	ns		

On products compliant to MIL-PRF-38535, this parameter is not production tested.
 On products compliant to MIL-PRF-38535, this parameter does not apply.



7.7 Noise Characteristics

 $V_{CC} = 5 \text{ V}, \text{ C}_{I} = 50 \text{ pF}, \text{ T}_{A} = 25^{\circ}\text{C}^{(1)}$

	PARAMETER	SN74	UNIT		
	PARAMETER	MIN	TYP	MAX	UNIT
V _{OL(P)}	Quiet output, maximum dynamic V _{OL}		0.7		V
V _{OL(V)}	Quiet output, minimum dynamic V _{OL}		-0.7		V
V _{OH(V)}	Quiet output, minimum dynamic V _{OH}		4.8		V
V _{IH(D)}	High-level dynamic input voltage	2			V
V _{IL(D)}	Low-level dynamic input voltage			0.8	V


(1) Characteristics are for surface-mount packages only.

7.8 Operating Characteristics

 $V_{CC} = 5 \text{ V}, \text{ } \text{T}_{A} = 25^{\circ}\text{C}$

	PARAMETER	TEST C	ONDITIONS	ТҮР	UNIT
C _{pd}	Power dissipation capacitance	No load,	f = 1 MHz	8.2	pF

7.9 Typical Characteristics




SN74AHCT16244

SCLS334J-MARCH 1996-REVISED OCTOBER 2014

www.ti.com

8 Parameter Measurement Information



NOTES: A. CL includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 1 MHz, Z_O = 50 Ω , t_f \leq 3 ns, t_f \leq 3 ns.
- D. The outputs are measured one at a time with one input transition per measurement.

Figure 2. Load Circuit and Voltage Waveforms




Detailed Description 9

Overview 9.1

The SN74AHCT16244 device is a 16-bit buffer and line driver specifically designed to improve the performance and density of 3-state memory address drivers, clock drivers, and bus-oriented receivers and transmitters. This device can be used as a four 4-bit buffers, two 8-bit buffers, or one 16-bit buffer. It provides true outputs and symmetrical active-low output-enable (OE) inputs. To ensure the high-impedance state during power up or power down, OE should be tied to V_{CC} through a pullup resistor. The minimum value of the resistor is determined by the current-sinking capability of the driver. The SN74AHCT16244 is characterized for operation from -40°C to 125°C.

9.2 Functional Block Diagram



This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

Figure 3.

9.3 Feature Description

- V_{CC} is optimized at 5 V
- Allows up voltage translation from 3.3 V to 5 V •
 - Inputs accept V_{IH} levels of 2 V
- Slow edge rates minimize output ringing
- Inputs are TTL-voltage compatible

9.4 Device Functional Modes

	(Each 4-bit Buffer/Driver)									
1	NPUTS	OUTPUT								
OE	Α	Y								
L	Н	Н								
L	L	L								

Х

Ζ

Table 1 Eurotion Table

Copyright © 1996–2014, Texas Instruments Incorporated

н



10 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

10.1 Application Information

The SN74HCT16244 is a low-drive CMOS device that can be used for a multitude of bus interface type applications where output ringing is a concern. The low drive and slow edge rates will minimize overshoot and undershoot on the outputs. The input switching levels have been lowered to accommodate TTL inputs of 0.8-V V_{IL} and 2-V V_{IH} . This feature makes it ideal for translating up from 3.3 V to 5 V. The figure below shows this type of translation

10.2 Typical Application




Figure 4. Typical Application Schematic

10.2.1 Design Requirements

This device uses CMOS technology and has balanced output drive. Care should be taken to avoid bus contention because it can drive currents that would exceed maximum limits. The high drive will also create fast edges into light loads, so routing and load conditions should be considered to prevent ringing.


10.2.2 Detailed Design Procedure

- 1. Recommended Input Conditions:
 - For rise time and fall time specifications, see $\Delta t/\Delta V$ in the *Recommended Operating Conditions* table.
 - For specified high and low levels, see V_{IH} and V_{IL} in the *Recommended Operating Conditions* table.
 - Inputs are overvoltage tolerant allowing them to go as high as 5.5 V at any valid V_{CC} .
- 2. Recommended Output Conditions:
 - Load currents should not exceed 25 mA per output and 75 mA total for the part.
 - Outputs should not be pulled above V_{CC}.



Typical Application (continued)

10.2.3 Application Curves



11 Power Supply Recommendations

The power supply can be any voltage between the MIN and MAX supply voltage rating located in the *Recommended Operating Conditions*. Each V_{CC} terminal should have a good bypass capacitor to prevent power disturbance. For devices with a single supply, 0.1 μ F is recommended. If there are multiple V_{CC} terminals then 0.01 μ F or 0.022 μ F is recommended for each power terminal. It is acceptable to parallel multiple bypass capacitor reject different frequencies of noise. A 0.1 μ F and 1 μ F are commonly used in parallel. The bypass capacitor should be installed as close to the power terminal as possible for best results.


12 Layout

12.1 Layout Guidelines

When using multiple bit logic devices, inputs should not float. In many cases, functions or parts of functions of digital logic devices are unused. Some examples are when only two inputs of a triple-input AND gate are used, or when only 3 of the 4-buffer gates are used. Such input pins should not be left unconnected because the undefined voltages at the outside connections result in undefined operational states.

Specified in Figure 6 are rules that must be observed under all circumstances. All unused inputs of digital logic devices must be connected to a high or low bias to prevent them from floating. The logic level that should be applied to any particular unused input depends on the function of the device. Generally they will be tied to GND or V_{CC} , whichever makes more sense or is more convenient. It is acceptable to float outputs unless the part is a transceiver. If the transceiver has an output enable pin, it will disable the outputs section of the part when asserted. This will not disable the input section of the I/Os so they also cannot float when disabled.

12.2 Layout Example





12

Product Folder Links: SN74AHCT16244

Copyright © 1996–2014, Texas Instruments Incorporated

13.2 Electrostatic Discharge Caution

13 Device and Documentation Support



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

13.3 Glossary

13.1 Trademarks

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

14 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



PACKAGING INFORMATION

Orderable Device	Status	Package Type	•	Pins	Package	Eco Plan	Lead finish/	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	Ball material	(3)		(4/5)	
							(6)				
74AHCT16244DGGRE4	ACTIVE	TSSOP	DGG	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	AHCT16244	Samples
SN74AHCT16244DGGR	ACTIVE	TSSOP	DGG	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	AHCT16244	Samples
SN74AHCT16244DGVR	ACTIVE	TVSOP	DGV	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	HF244	Samples
SN74AHCT16244DL	LIFEBUY	SSOP	DL	48	25	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	AHCT16244	
SN74AHCT16244DLR	ACTIVE	SSOP	DL	48	1000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	AHCT16244	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



Texas

STRUMENTS

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74AHCT16244DGGR	TSSOP	DGG	48	2000	330.0	24.4	8.6	13.0	1.8	12.0	24.0	Q1
SN74AHCT16244DGVR	TVSOP	DGV	48	2000	330.0	16.4	7.1	10.2	1.6	12.0	16.0	Q1
SN74AHCT16244DLR	SSOP	DL	48	1000	330.0	32.4	11.35	16.2	3.1	16.0	32.0	Q1



PACKAGE MATERIALS INFORMATION

9-Aug-2022



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74AHCT16244DGGR	TSSOP	DGG	48	2000	367.0	367.0	45.0
SN74AHCT16244DGVR	TVSOP	DGV	48	2000	356.0	356.0	35.0
SN74AHCT16244DLR	SSOP	DL	48	1000	367.0	367.0	55.0

TEXAS INSTRUMENTS

www.ti.com

9-Aug-2022

TUBE



- B - Alignment groove width

*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	Τ (μm)	B (mm)
SN74AHCT16244DL	DL	SSOP	48	25	473.7	14.24	5110	7.87

DL (R-PDSO-G48)

PLASTIC SMALL-OUTLINE PACKAGE



- A. All linear dimensions are in inches (millimeters).B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).
- D. Falls within JEDEC MO-118

PowerPAD is a trademark of Texas Instruments.



MECHANICAL DATA

PLASTIC SMALL-OUTLINE

MPDS006C - FEBRUARY 1996 - REVISED AUGUST 2000

DGV (R-PDSO-G**)

24 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15 per side.
- D. Falls within JEDEC: 24/48 Pins MO-153

14/16/20/56 Pins – MO-194



PACKAGE OUTLINE

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 This drawing is subject to change without notice.
 This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not

- exceed 0.15 mm per side. 4. Reference JEDEC registration MO-153.




DGG0048A

DGG0048A

EXAMPLE BOARD LAYOUT

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



DGG0048A

EXAMPLE STENCIL DESIGN

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate

design recommendations. 8. Board assembly site may have different recommendations for stencil design.



MECHANICAL DATA

MTSS003D - JANUARY 1995 - REVISED JANUARY 1998

DGG (R-PDSO-G**)

PLASTIC SMALL-OUTLINE PACKAGE

48 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold protrusion not to exceed 0,15.
- D. Falls within JEDEC MO-153



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated