





Top Layer




Bottom Layer









Top Overlay



Top Paste



Top Solder



Bottom Solder

•


:::

Bottom Paste


ms

Bottom Overlay

Keep-Out Layer




M1 Board Outline



M2 Board Dimensions

M4 3D STEP Bottom



COMPONENTS MARKED 'DNP' SHOULD NOT BE POPULATED. ASSEMBLY VARIANT: [No Variations]

PCB VIEWED FROM TOP SIDE	BOARD #: TIDA-01330 REU: E1 SUN REU: Not In VersionContro			
PLOT NAME = TIDA-01330.GM5	GENERATED : 1/6/2017 10:44:2	7 AM TEXAS INSTRUMENTS		

řt.

В

8

## COMPONENTS MARKED 'DNP' SHOULD NOT BE POPULATED. ASSEMBLY VARIANT: [NO Variations]

Not In VersionControl	REV: E1	IDA-01330	80ARD #: T]	PCB VIEWED FROM BOTTOM SIDE	
			IDA-01330	TID #: TI	
TEXAS INSTRUMENTS	MA	10:44:28	: 1/6/2017	GENERATED	PLOT NAME = TIDA-01330.6M6

- 1			0	7			- 1
		M9 Title Sheet			or any information contained therein. If and/or its licensors do not warrant that this design uil meet the specifications, uill be suitable for your application or fit for any particular purpose, or uill operate in an implementation. If and/or its licensors do not warrant that the design is production worthy. You should completely validate and test your design implementation to confirm the system functionality for your application.	Clark Kinnaird	
	D				Texas Instruments (TI) and/or its licensors do not warrant the accuracy or completeness of this specification	DESCRED FOR PUBLIC Release FLE NAME: TIDH-01330, PcbDoc ENGREER LAYOUT BY:	D
						PROJECT TITLE: Automotive 2-Axis Power Seat Driver	
	С						С
	В						В
	A						A


M10 Fab Notes

	DESIGN INFORMATION
RE	MIN. TRACK WIDTH: 8 MIL MIN. CLEARANCE: 0.2 mm MIN. VIA PAD SIZE: 24 MIL NIMUM ANNULAR RING 0.05mm (ZML) EXTERNAL PER PC-D-275 CLASS 2 LEVEL C EGSTRATION TOLERANCES: METAL + /- 5 MIL, HOLES + /- 3 MI DLE SIZE TOLERANCE (UNLESS OTHERWISE SPECIFIED): +/- 3 MI
	FR-408 X FR-4 High Tg OTHER
	HICKNESS: X 62 MIL (1.6mm) +/-10% OTHER  DLERANCE: X ANSI PC-6012 TYPE 3 CLASS 2  OTHER +/-
В	DW & TWIST: X ANSI PC-6012 TYPE 3 CLASS 2 OTHER +/-
RE	LING: EFERENCE: X AS SHOWN X NC_DRILL FILES ITH COPPER THICKNESS: X 20-30 um OTHER
	ARD FINISH: SILKSCREEN: X TOP X BOTTOM SILKSCREEN COLOR: X WHITE OTHER
	SOLDER RESIST COLOR: X GREEN OTHER  X MATTE SEMI-GLOSS
SUR	Face Finish: X Immersion gold (Enig) Enepig  MM. Tin/silver or Equiv Other
	RAY/PANEL: CUT AND TRM PER M1 BOARD OUTLINE N.C. ROUTE X V. SCORE
CER	TIFICATION: MATERIALS AND WORKMANSHIP FOR ALL PCBS TO MEET OR EXCEED THE REQUIREMENTS OF:  X ANSI IPC-A-600F CLASS -> 1 X 2 3
	X Rohs OTHER PER ORDER BOARDS MUST MEET OR EXCEED UL94-VO REQUIREMENTS. B MUST BEAR THE UL94V-O UL REGISTERED MATERIAL ID NUMBE
MI	OTTONAL REQUIREMENTS: CROSECTION:YES ARE BOARD ELEC. TEST:NONE _X_REQUIREDPER ORDEI

ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: TIDA-01330 REV: E1	SUN REV: Not In VersionControl
LAYER NAME =	TID #: TIDA-01330	
PLOT NAME = TIDA-01330.GM11	GENERATED : 1/6/2017 10:44:2	8 AM TEXAS INSTRUMENTS

M12 Stackup


Layer	Name	Material	Thickness	Constant	Board Layer Stack
1	Top Overlay				
2	Top Solder	Solder Resist	0.40m1l	3.5	
3	Top Layer	Copper	1.40mıl		
4	Dielectric1	FR-4	59.20m1l	4.8	
5	Bottom Layer	Copper	1.40mıl		
6	Bottom Solder	Solder Resist	0.40m1l	3.5	
7	Bottom Overlay				



M13 Component Bodies Top

000

M14 Component Bodies Bottom



M15 Courtyards Top

H

₽ ₽ ₽

M16 Courtyards Bottom

M17 Embedded Cavity

M18 Embedded Assembly

M19 Embedded Keepout

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products <a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation modules, and samples (<a href="http://www.ti.com/sc/docs/sampterms.htm">http://www.ti.com/sc/docs/sampterms.htm</a>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2018, Texas Instruments Incorporated