Using the TPS92001EVM-628

User's Guide



Literature Number: SLUU897 March 2012



Dimmable LED Lighting Driver Controller

1 Introduction

The TPS92001EVM-628 evaluation module is a constant-current, dimmable LED driver. It is designed to drive 9 LEDs at 330 mA and is rated for an AC input of 105 V_{RMS} to 135 V_{RMS} .

2 Description

The TPS92001/2 family of general LED lighting PWM controllers contains control and drive circuitry required for off-line isolated or non-isolated LED lighting applications. The TPS92001EVM-628 evaluation module uses the TPS92001 as a non-isolated buck controller; more specifically it is an inverting buck topology. The controller operates in fixed-frequency, current-mode switching with minimal external parts count. In LED illumination applications there is typically no need for the LED load to be referenced to ground. This utilizes the inverted buck which moves the controller and FET to the low side of the circuit, referenced to the lowest voltage, while the LED load is floated (referenced to the highest voltage). With an appropriately designed bias regulator for the controller, we can now use a much lower voltage controller which is more economical.

2.1 Typical Applications

Commercial/Household LED Lighting

2.2 Features

- Dimmable, Non-Isolated LED Driver with Minimum External Part Count
- Wide-Duty Cycle Range for Wide-Input Voltage
- Convenient 5-V Reference Output
- Test Points for Output Voltage/Current


3 Electrical Performance Specifications

Table 1. TPS92001EVM-628 EVM-001 Electrical Performance Specifications

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNITS
Input Characteristics				ļ	
Voltage range		105	120	135	V
Maximum input current			115		mA
Output Characteristics		ŀ			
Output voltage, V _{OUT}		26	30	34	V
Output load current, I _{OUT}		280	330	380	mA
Output current ripple	VIN = 120 VAC		280		mA_{pp}
Output over voltage			36		V
Systems Characteristics					
Switching frequency			133		kHz
Full load efficiency	VIN = 120 VAC		85%		
Power factor			0.90		



4 Schematic





Schematic

5 Test Setup

WARNING

High voltages that may cause injury exist on this evaluation module (EVM). Please ensure all safety procedures are followed when working on this EVM. Never leave a powered EVM unattended. The use of isolated equipment is highly recommended.

5.1 Test Equipment

Voltage Source: 105 V_{RMS} to 135 V_{RMS} isolated AC source capable of at least 20 W.

Multimeters: Two voltmeters for measuring up to 35 V_{DC} each and two ammeters for up to 1 A each.

Output Load: 9 LEDs in series (VF = 3.4 V at 330 mA per LED)

Oscilloscope: 4 channel 100 MHz with high-voltage probe rated for at least 600 V.

Recommended Wire Gauge: 18 AWG not more than two feet long.

5.2 TPS92001EVM-645 Recommended Test Setup




Figure 2. Recommended Test Set Up

5.3 List of Test Points

Table 2. Test Point Functions	5
-------------------------------	---

TEST POINTS	NAME	DESCRIPTION	
TP1	LED +	LED output	
TP2	LED ¬-	LED return point	
TP3	CS	Feedback pin of TPS92001	
TP4	СТ	Clock signal	
TP5	SW	Buck switch node	
TP6	Bulk-	Rectified AC negative input	
TP7	Bulk +	Rectified AC positive input	
TP8	Line	AC line input	
TP9	Neutral	AC neutral input	

4 Dimmable LED Lighting Driver Controller



6 Test Procedure

All tests should use the set up described in Section 5 of this user guide.

WARNING

High voltage levels are present on this evaluation module whenever it is energized. Proper precautions must be observed whenever working with this module. Serious injury can occur if proper safety procedures are not followed.

6.1 Line/Load Regulation and Efficiency Measurement Procedure

- 1. Connect EVM per Figure 2 above. An external LED load must be used to start up the EVM.
- 2. Prior to turning on the AC source, set the voltage to 105 V_{RMS} .
- 3. Turn on the AC source.
- 4. Record the output voltage and current readings from voltmeter 2 and output current reading from ammeter 2 and input voltage reading from voltmeter 1 and ammeter 1.
- 5. Increase output voltage by 5 V_{RMS}
- 6. Repeat steps 4 and 5 until you reach 135 V_{RMS}
- 7. Refer to Section 6.2 for shutdown procedure.

6.2 Equipment Shutdown

- 1. Turn off the AC source.
- 2. Make sure that output capacitors are fully discharged.

7 Performance Data and Typical Characteristic Curves


Figure 3 through Figure 28 present typical performance curves for TPS92001EVM-628.

Unless otherwise specified the following test conditions are required:

- 1. Use LED load module PR916 set for 9 LED load.
- 2. Figure 6 through Figure 28 input set to 120 V_{AC} nominal.
- 3. Triac dimmer used is Leviton Cat No 6684 or equivalent.


7.1 Efficiency

Efficiency vs Line Voltage



7.2 Input Voltage vs. Power Factor


Input voltage vs. PF



Dimmable LED Lighting Driver Controller



7.3 Input Voltage vs. Output Current



Input voltage vs. Output current

(with respect to input voltage phase)



Performance Data and Typical Characteristic Curves

7.4 Output Ripple




Figure 7. Output Ripple (Ch1-LED current Ch2- rectified line voltage Ch3- Q2 drain)

7.5 Input Waveforms




Figure 8. Input Waveform (Ch1- line current Ch2-rectified line voltage Ch3-Q4 source voltage)



7.6 Current Fdbk Signal and Switch Node Voltage






Figure 9. Current Sense and Switching Node Waveform (peak line) (Ch1- LED current Ch2- Q2 current sense Ch3- Q2 drain voltage)

7.7 Current Sense








Performance Data and Typical Characteristic Curves

www.ti.com

7.8 Triac Dimmer Waveforms



NOTE: LED current highly filtered.




Figure 12. Dummy Load Conduction Time (Ch1- LED current Ch2- Q4 collector voltage Ch3- bulk voltage)






Figure 13. Triac Holding Current (2.5-ms Triac on time) (Ch1- LED current Ch2- bulk voltage Ch3- Q4 source voltage)




Figure 14. Triac Holding Current(3-ms Triac on time) (Ch1- LED current Ch2- bulk voltage Ch3- Q4 source voltage)



7.9 Triac Phase Waveforms




Figure 15. Dummy Load Conduction Time vs. Dimmer Setting (Ch1- Line current Ch2- bulk voltage Ch3- Q4 source voltage)




Figure 16. Dummy Load Conduction Time vs. Dimmer Setting (Ch1- line current Ch2- bulk voltage Ch3- Q4 source voltage)






Figure 17. Dummy Load Conduction Time vs. Dimmer Setting (Ch1- line current Ch2- bulk voltage Ch3- Q4 source voltage)




Figure 18. Dummy Load Conduction Time vs. Dimmer Setting (Ch1- line current Ch2- bulk voltage Ch3- Q4 source voltage)



Performance Data and Typical Characteristic Curves




Figure 19. Dummy Load Conduction Time vs. Dimmer Setting (Ch1- line current Ch2- bulk voltage Ch3- Q4 source voltage)






Figure 20. Dummy Load Conduction Time vs. Dimmer Setting (Ch1- line current Ch2- bulk voltage Ch3- Q4 source voltage)







NOTE: U2-1 is Q2 averaged current feedback.











Figure 23. LED Current vs. Triac Conduction Time (Ch1- LED current Ch2- bulk voltage Ch3- U2-1 voltage waveform)

NOTE: U2-1 is Q2 averaged current feedback.











Figure 25. LED Current vs. Triac Conduction Time (Ch1- LED current Ch2- bulk voltage Ch3- U2-1 voltage waveform)

NOTE: U2-1 is Q2 averaged current feedback.



(Ch1- LED current Ch2- bulk voltage Ch3- U2-1 voltage waveform)





Performance Data and Typical Characteristic Curves




Figure 27. LED Current vs. Triac Conduction Time (Ch1- LED current Ch2- bulk voltage Ch3- U2-1 voltage waveform)

NOTE: U2-1 is Q2 averaged current feedback.




Figure 28. LED Current vs. Triac Conduction Time (Ch1- LED current Ch2- bulk voltage Ch3- U2-1 voltage waveform)





8 TPS92001EVM-628 Assembly Drawing and PCB layout

The following figures (Figure 29 through Figure 32) show the design of the TPS92001EVM-628 printed circuit board.




Figure 29. Assembly Drawing (top view)




Figure 30. Assembly Drawing (bottom view)






Figure 31. Top Copper (top view)




Figure 32. Bottom Copper (top view)



9 List of Materials

The TPS92001EVM-628 component's list according to the schematic shown in Figure 1.

QTY	REF DES	DESCRIPTION	PART NUMBER	MFR
2	C1,C12	Capacitor, leaded, metalized film, 400 VDC, 125°C, 20 ±%, 0.1 $\mu\text{F},$ 0.310 inch x 0.310 inch	B32529D6104J or B32559C6104K001	Epcos
1	C10	Capacitor, ceramic, 25 V, X7R, 10%, 1.0 µF, 0805	Std	Std
1	C11	Capacitor, ceramic, 10 V, X7R, 10%, 0.47 µF, 0603	Std	Std
1	C2	Capacitor, poly film, 200 VAC, ±20%, 0.1 µF, 6.00 mm x 13.00 mm	B32521C6104J	Epcos
1	C3	Capacitor, ceramic, 100 V, X7R, 10%, 0.1 µF, 0805	std	Std
1	C4	CAP, aluminum elec, 220 µF, 50 V, radial, 5000 hrs at 105°C, 850-mA ripple, 10 mm x 16 mm	UPW1H221MPD	Rubycon/Nichicon
1	C5	Capacitor, ceramic, 250 V, X7R, 20%, 1.0 µF, 2220	"C5750X7R2E105M orGRM55DR72E105K W01L"	"TDK or Murata"
1	C6	Capacitor, ceramic, 50 V, X7R, 10%, 180 pF, 0603	Std	Std
2	C7, C9	Capacitor, ceramic, 25 V, X7R, 10%, 0.01 µF, 0603	Std	Std
2	C15,C16	Capacitor, ceramic, 25 V, X7R, 10%, 0.01 µF, 0603	Std	Std
1	C8	Capacitor, ceramic, 50 V, X7R, 10%, 680 pF, 0603	Std	Std
1	C14	Capacitor, ceramic, 25 V, X7R, 10%, 0.22uF, 0805	Std	Std
1	C13	Capacitor, ceramic, 25 V, X7R, 10%, 1.0uF, 1206	Std	Std
1	D1	Diode, bridge, 2.0 A, 400 V, 4 EDIP	DF204-G	Comchip
3	D2,D6,D7	Diode, high-speed switching, 250 mA, 200 V, SOD-323	BAS21-03W	Infineon
1	D3	Diode, Zener, 12 V, 20 mA, 225 mW, 5%, 12 V, SOT23	MMBZ5242BLT1	Motorola
1	D4	Rectifier, ultrafast power, 200 V, 1 A, 403D	MURA120T3G	On Semi
2	D5,D8	Diode, Zener, 15 V, 20 mA, 225 mW, 5%, 15 V, SOT23	MMBZ5245BLT1	Motorola
1	F1	1-A fuse, subminiature fast acting, 0.125 diameter	MCRW1A	Bussmann
1	JP1	Jumper, 0.200 inch length, PVC insulation, AWG 22, 0.035 inch diameter Jumper, 0.300 inch length	923345-02-C	
2	L1,L3	Inductor, radial, 470 μH, 310 mA, 10%, 70°C, 470 μH, 0.315 inch diameter	22R474C	Murata
1	L2	Inductor toroid 470 $\mu H,$ 15%, horizontal, 470 $\mu H,$ 0.860 inch x 0.450 inch	2100LL-471-H-RC	Bourns
1	Q3	Bipolar, PNP, 40 V, 200 mA, 350 mW, SOT23, 3906		
	Std	Std		
1	Q4	Mosfet, N-channel, 600 V, 200 mA, 1.5 Ω, 2.1 W	FQT1N60CTF_WS	Fairchild
1	Q1	Transistor, power bipolar PNP, 350 V, 4 A, TO-220	MJE15035G	On Semi
1	Q2	Transistor, NFET, 250 V, 2.1 A, 2 Ω, TO-220	IRFI614GPBF	Vishay

Table 3. TPS92001EVM-628 List of Materials

QTY	REF DES	DESCRIPTION	PART NUMBER	MFR
1	R1	Resistor, 1/4 W, ±5%, 1.0 kΩ, 1206	Std	Std
1	R10	Resistor, chip, 1/16 W, 1%, 4.32 kΩ, 0603	Std	Std
1	R2	Resistor, 1/4 W, ±5%, 604 kΩ, 1206	Std	Std
1	R3	Resistor, chip, 1/16 W, 1%, 5.11 kΩ, 0603	Std	Std
1	R4	Resistor, chip, 1/16 W, 1%, 10 Ω, 0603	Std	Std
1	R5	Resistor, SM, 3/4 W, 1%, 2.7 Ω, 2010	Std	Std
1	R7	Resistor, chip, 1/16 W, 1%, 4.12 kΩ, 0603	Std	Std
1	R8	Resistor, chip, 1/16 W, 1%, 20.0 kΩ, 0603	Std	Std
2	R9,R22	Resistor, chip, 1/16 W, 1%, 10.0 kΩ, 0603	Std	Std
1	R21	Resistor, chip, 1/16 W, 1%, 3.92 kΩ, 0603	Std	Std
1	R16	Resistor, chip, 1/16 W, 1%, 5.49 kΩ, 0603	Std	Std
2	R20,R6	Resistor, chip, 1/16 W, 1%, 100 kΩ, 0603	Std	Std
1	R17	Resistor, chip, 1/16 W, 1%, 118 kΩ, 0603	Std	Std
1	R15	Resistor, chip, 1/16 W, 1%, 221 kΩ, 0603	Std	Std
1	R12	Resistor, MF, 1/4 W, 5%, 249 Ω, 1206	Std	Std
1	R19	Resistor, MF, 1/4 W, 5%, 300 Ω, 1206	Std	Std
1	R13	Resistor, MF, 1/4 W, 5%, 499 Ω, 1206	Std	Std
1	R14	Resistor, MF, 1/4 W, 5%, 909 kΩ, 1206	Std	Std
1	R18	Resistor power metal oxide, 1 kΩ, 2 W, 5%	ERG-2SJ102	Panasonic
1	R11	Resistor power metal oxide, 33 Ω, 1 W, 5%	ERG-1SJ330	Panasonic
1	U1	G.P LED Lighting PWM Controller, MSOP-8	TPS92001DGK	TI
1	U2	Comparator, Differential, Single	TL331KDBV	TI
1		PCB, 4 inch x 4 inch x 0.062 inch	HPA628	Any

Table 3. TPS92001EVM-628 List of Materials (continued)

Evaluation Board/Kit Important Notice

Texas Instruments (TI) provides the enclosed product(s) under the following conditions:

This evaluation board/kit is intended for use for **ENGINEERING DEVELOPMENT, DEMONSTRATION, OR EVALUATION PURPOSES ONLY** and is not considered by TI to be a finished end-product fit for general consumer use. Persons handling the product(s) must have electronics training and observe good engineering practice standards. As such, the goods being provided are not intended to be complete in terms of required design-, marketing-, and/or manufacturing-related protective considerations, including product safety and environmental measures typically found in end products that incorporate such semiconductor components or circuit boards. This evaluation board/kit does not fall within the scope of the European Union directives regarding electromagnetic compatibility, restricted substances (RoHS), recycling (WEEE), FCC, CE or UL, and therefore may not meet the technical requirements of these directives or other related directives.

Should this evaluation board/kit not meet the specifications indicated in the User's Guide, the board/kit may be returned within 30 days from the date of delivery for a full refund. THE FOREGOING WARRANTY IS THE EXCLUSIVE WARRANTY MADE BY SELLER TO BUYER AND IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESSED, IMPLIED, OR STATUTORY, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE.

The user assumes all responsibility and liability for proper and safe handling of the goods. Further, the user indemnifies TI from all claims arising from the handling or use of the goods. Due to the open construction of the product, it is the user's responsibility to take any and all appropriate precautions with regard to electrostatic discharge.

EXCEPT TO THE EXTENT OF THE INDEMNITY SET FORTH ABOVE, NEITHER PARTY SHALL BE LIABLE TO THE OTHER FOR ANY INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES.

TI currently deals with a variety of customers for products, and therefore our arrangement with the user is not exclusive.

TI assumes no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein.

Please read the User's Guide and, specifically, the Warnings and Restrictions notice in the User's Guide prior to handling the product. This notice contains important safety information about temperatures and voltages. For additional information on TI's environmental and/or safety programs, please contact the TI application engineer or visit www.ti.com/esh.

No license is granted under any patent right or other intellectual property right of TI covering or relating to any machine, process, or combination in which such TI products or services might be or are used.

FCC Warning

This evaluation board/kit is intended for use for **ENGINEERING DEVELOPMENT, DEMONSTRATION, OR EVALUATION PURPOSES ONLY** and is not considered by TI to be a finished end-product fit for general consumer use. It generates, uses, and can radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC rules, which are designed to provide reasonable protection against radio frequency interference. Operation of this equipment in other environments may cause interference with radio communications, in which case the user at his own expense will be required to take whatever measures may be required to correct this interference.

EVM Warnings and Restrictions

It is important to operate this EVM within the input voltage range of 105 V to 135 V and the output voltage range of 26 V to 34 V.

Exceeding the specified input range may cause unexpected operation and/or irreversible damage to the EVM. If there are questions concerning the input range, please contact a TI field representative prior to connecting the input power.

Applying loads outside of the specified output range may result in unintended operation and/or possible permanent damage to the EVM. Please consult the EVM User's Guide prior to connecting any load to the EVM output. If there is uncertainty as to the load specification, please contact a TI field representative.

During normal operation, some circuit components may have case temperatures greater than 50°C. The EVM is designed to operate properly with certain components above 50°C as long as the input and output ranges are maintained. These components include but are not limited to linear regulators, switching transistors, pass transistors, and current sense resistors. These types of devices can be identified using the EVM schematic located in the EVM User's Guide. When placing measurement probes near these devices during operation, please be aware that these devices may be very warm to the touch.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2012, Texas Instruments Incorporated

EVALUATION BOARD/KIT/MODULE (EVM) ADDITIONAL TERMS

Texas Instruments (TI) provides the enclosed Evaluation Board/Kit/Module (EVM) under the following conditions:

The user assumes all responsibility and liability for proper and safe handling of the goods. Further, the user indemnifies TI from all claims arising from the handling or use of the goods.

Should this evaluation board/kit not meet the specifications indicated in the User's Guide, the board/kit may be returned within 30 days from the date of delivery for a full refund. THE FOREGOING LIMITED WARRANTY IS THE EXCLUSIVE WARRANTY MADE BY SELLER TO BUYER AND IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESSED, IMPLIED, OR STATUTORY, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE. EXCEPT TO THE EXTENT OF THE INDEMNITY SET FORTH ABOVE, NEITHER PARTY SHALL BE LIABLE TO THE OTHER FOR ANY INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES.

Please read the User's Guide and, specifically, the Warnings and Restrictions notice in the User's Guide prior to handling the product. This notice contains important safety information about temperatures and voltages. For additional information on TI's environmental and/or safety programs, please visit www.ti.com/esh or contact TI.

No license is granted under any patent right or other intellectual property right of TI covering or relating to any machine, process, or combination in which such TI products or services might be or are used. TI currently deals with a variety of customers for products, and therefore our arrangement with the user is not exclusive. TI assumes no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein.

REGULATORY COMPLIANCE INFORMATION

As noted in the EVM User's Guide and/or EVM itself, this EVM and/or accompanying hardware may or may not be subject to the Federal Communications Commission (FCC) and Industry Canada (IC) rules.

For EVMs **not** subject to the above rules, this evaluation board/kit/module is intended for use for ENGINEERING DEVELOPMENT, DEMONSTRATION OR EVALUATION PURPOSES ONLY and is not considered by TI to be a finished end product fit for general consumer use. It generates, uses, and can radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC or ICES-003 rules, which are designed to provide reasonable protection against radio frequency interference. Operation of the equipment may cause interference with radio communications, in which case the user at his own expense will be required to take whatever measures may be required to correct this interference.

General Statement for EVMs including a radio

User Power/Frequency Use Obligations: This radio is intended for development/professional use only in legally allocated frequency and power limits. Any use of radio frequencies and/or power availability of this EVM and its development application(s) must comply with local laws governing radio spectrum allocation and power limits for this evaluation module. It is the user's sole responsibility to only operate this radio in legally acceptable frequency space and within legally mandated power limitations. Any exceptions to this are strictly prohibited and unauthorized by Texas Instruments unless user has obtained appropriate experimental/development licenses from local regulatory authorities, which is responsibility of user including its acceptable authorization.

For EVMs annotated as FCC – FEDERAL COMMUNICATIONS COMMISSION Part 15 Compliant

Caution

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

FCC Interference Statement for Class A EVM devices

This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his own expense.

FCC Interference Statement for Class B EVM devices

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- · Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

For EVMs annotated as IC – INDUSTRY CANADA Compliant

This Class A or B digital apparatus complies with Canadian ICES-003.

Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

Concerning EVMs including radio transmitters

This device complies with Industry Canada licence-exempt RSS standard(s). Operation is subject to the following two conditions: (1) this device may not cause interference, and (2) this device must accept any interference, including interference that may cause undesired operation of the device.

Concerning EVMs including detachable antennas

Under Industry Canada regulations, this radio transmitter may only operate using an antenna of a type and maximum (or lesser) gain approved for the transmitter by Industry Canada. To reduce potential radio interference to other users, the antenna type and its gain should be so chosen that the equivalent isotropically radiated power (e.i.r.p.) is not more than that necessary for successful communication.

This radio transmitter has been approved by Industry Canada to operate with the antenna types listed in the user guide with the maximum permissible gain and required antenna impedance for each antenna type indicated. Antenna types not included in this list, having a gain greater than the maximum gain indicated for that type, are strictly prohibited for use with this device.

Cet appareil numérique de la classe A ou B est conforme à la norme NMB-003 du Canada.

Les changements ou les modifications pas expressément approuvés par la partie responsable de la conformité ont pu vider l'autorité de l'utilisateur pour actionner l'équipement.

Concernant les EVMs avec appareils radio

Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes : (1) l'appareil ne doit pas produire de brouillage, et (2) l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

Concernant les EVMs avec antennes détachables

Conformément à la réglementation d'Industrie Canada, le présent émetteur radio peut fonctionner avec une antenne d'un type et d'un gain maximal (ou inférieur) approuvé pour l'émetteur par Industrie Canada. Dans le but de réduire les risques de brouillage radioélectrique à l'intention des autres utilisateurs, il faut choisir le type d'antenne et son gain de sorte que la puissance isotrope rayonnée équivalente (p.i.r.e.) ne dépasse pas l'intensité nécessaire à l'établissement d'une communication satisfaisante.

Le présent émetteur radio a été approuvé par Industrie Canada pour fonctionner avec les types d'antenne énumérés dans le manuel d'usage et ayant un gain admissible maximal et l'impédance requise pour chaque type d'antenne. Les types d'antenne non inclus dans cette liste, ou dont le gain est supérieur au gain maximal indiqué, sont strictement interdits pour l'exploitation de l'émetteur.

[Important Notice for Users of this Product in Japan]

This development kit is NOT certified as Confirming to Technical Regulations of Radio Law of Japan

If you use this product in Japan, you are required by Radio Law of Japan to follow the instructions below with respect to this product:

- Use this product in a shielded room or any other test facility as defined in the notification #173 issued by Ministry of Internal Affairs and Communications on March 28, 2006, based on Sub-section 1.1 of Article 6 of the Ministry's Rule for Enforcement of Radio Law of Japan,
- 2. Use this product only after you obtained the license of Test Radio Station as provided in Radio Law of Japan with respect to this product, or
- 3. Use of this product only after you obtained the Technical Regulations Conformity Certification as provided in Radio Law of Japan with respect to this product. Also, please do not transfer this product, unless you give the same notice above to the transferee. Please note that if you could not follow the instructions above, you will be subject to penalties of Radio Law of Japan.

Texas Instruments Japan Limited (address) 24-1, Nishi-Shinjuku 6 chome, Shinjuku-ku, Tokyo, Japan

http://www.tij.co.jp

【ご使用にあたっての注】

本開発キットは技術基準適合証明を受けておりません。

本製品のご使用に際しては、電波法遵守のため、以下のいずれかの措置を取っていただく必要がありますのでご注意ください。

- 1. 電波法施行規則第6条第1項第1号に基づく平成18年3月28日総務省告示第173号で定められた電波暗室等の試験設備でご使用いただく。
- 2. 実験局の免許を取得後ご使用いただく。
- 3. 技術基準適合証明を取得後ご使用いただく。

なお、本製品は、上記の「ご使用にあたっての注意」を譲渡先、移転先に通知しない限り、譲渡、移転できないものとします。

上記を遵守頂けない場合は、電波法の罰則が適用される可能性があることをご留意ください。

日本テキサス・インスツルメンツ株式会社 東京都新宿区西新宿6丁目24番1号 西新宿三井ビル http://www.tij.co.jp

EVALUATION BOARD/KIT/MODULE (EVM) WARNINGS, RESTRICTIONS AND DISCLAIMERS

For Feasibility Evaluation Only, in Laboratory/Development Environments. Unless otherwise indicated, this EVM is not a finished electrical equipment and not intended for consumer use. It is intended solely for use for preliminary feasibility evaluation in laboratory/development environments by technically qualified electronics experts who are familiar with the dangers and application risks associated with handling electrical mechanical components, systems and subsystems. It should not be used as all or part of a finished end product.

Your Sole Responsibility and Risk. You acknowledge, represent and agree that:

- 1. You have unique knowledge concerning Federal, State and local regulatory requirements (including but not limited to Food and Drug Administration regulations, if applicable) which relate to your products and which relate to your use (and/or that of your employees, affiliates, contractors or designees) of the EVM for evaluation, testing and other purposes.
- 2. You have full and exclusive responsibility to assure the safety and compliance of your products with all such laws and other applicable regulatory requirements, and also to assure the safety of any activities to be conducted by you and/or your employees, affiliates, contractors or designees, using the EVM. Further, you are responsible to assure that any interfaces (electronic and/or mechanical) between the EVM and any human body are designed with suitable isolation and means to safely limit accessible leakage currents to minimize the risk of electrical shock hazard.
- 3. You will employ reasonable safeguards to ensure that your use of the EVM will not result in any property damage, injury or death, even if the EVM should fail to perform as described or expected.
- 4. You will take care of proper disposal and recycling of the EVM's electronic components and packing materials.

Certain Instructions. It is important to operate this EVM within TI's recommended specifications and environmental considerations per the user guidelines. Exceeding the specified EVM ratings (including but not limited to input and output voltage, current, power, and environmental ranges) may cause property damage, personal injury or death. If there are questions concerning these ratings please contact a TI field representative prior to connecting interface electronics including input power and intended loads. Any loads applied outside of the specified output range may result in unintended and/or inaccurate operation and/or possible permanent damage to the EVM and/or interface electronics. Please consult the EVM User's Guide prior to connecting any load to the EVM output. If there is uncertainty as to the load specification, please contact a TI field representative. During normal operation, some circuit components may have case temperatures greater than 60°C as long as the input and output are maintained at a normal ambient operating temperature. These components include but are not limited to linear regulators, switching transistors, pass transistors, and current sense resistors which can be identified using the EVM schematic located in the EVM User's Guide. When placing measurement probes near these devices during normal operation, please be aware that these devices may be very warm to the touch. As with all electronic evaluation tools, only qualified personnel knowledgeable in electronic measurement and diagnostics normally found in development environments should use these EVMs.

Agreement to Defend, Indemnify and Hold Harmless. You agree to defend, indemnify and hold TI, its licensors and their representatives harmless from and against any and all claims, damages, losses, expenses, costs and liabilities (collectively, "Claims") arising out of or in connection with any use of the EVM that is not in accordance with the terms of the agreement. This obligation shall apply whether Claims arise under law of tort or contract or any other legal theory, and even if the EVM fails to perform as described or expected.

Safety-Critical or Life-Critical Applications. If you intend to evaluate the components for possible use in safety critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, such as devices which are classified as FDA Class III or similar classification, then you must specifically notify TI of such intent and enter into a separate Assurance and Indemnity Agreement.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2012, Texas Instruments Incorporated

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components which meet ISO/TS16949 requirements, mainly for automotive use. Components which have not been so designated are neither designed nor intended for automotive use; and TI will not be responsible for any failure of such components to meet such requirements.

Products		Applications	
Audio	www.ti.com/audio	Automotive and Transportation	www.ti.com/automotive
Amplifiers	amplifier.ti.com	Communications and Telecom	www.ti.com/communications
Data Converters	dataconverter.ti.com	Computers and Peripherals	www.ti.com/computers
DLP® Products	www.dlp.com	Consumer Electronics	www.ti.com/consumer-apps
DSP	dsp.ti.com	Energy and Lighting	www.ti.com/energy
Clocks and Timers	www.ti.com/clocks	Industrial	www.ti.com/industrial
Interface	interface.ti.com	Medical	www.ti.com/medical
Logic	logic.ti.com	Security	www.ti.com/security
Power Mgmt	power.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video
RFID	www.ti-rfid.com		
OMAP Applications Processors	www.ti.com/omap	TI E2E Community	e2e.ti.com
Wireless Connectivity	www.ti.com/wirelessconne	ctivity	

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2012, Texas Instruments Incorporated