

WL1271 ini File Description and Parameters User's Guide



Literature Number: SPRUGT8

January 2010

Contents	2
Revision History.....	4
Reference Documents.....	4
About This Document	4
Chapter 1	6
Introduction	6
1.1 Synopsis.....	7
Chapter 2	8
Ini File Parameters.....	8
2.1 Short Description.....	9
2.2 Detailed Description	10
2.2.1 SmeConnectMode.....	10
2.2.2 WME_Enable	10
2.2.3 dot11NetworkType	10
2.2.4 SmeScanGChannelList	10
2.2.5 SmeScanAChannelList	10
2.2.6 BeaconListenInterval	11
2.2.7 DtimListenInterval.....	11
2.2.8 dot11PowerMode	11
2.2.9 PowerMgmtHangOverPeriod.....	11
2.2.10 AutoPowerModeDozeMode.....	11
2.2.11 AutoPowerModeActiveTh.....	11
2.2.12 AutoPowerModeDozeTh	12
2.2.13 defaultPowerLevel.....	12
2.2.14 PowerSavePowerLevel	12
2.2.15 TxPower	12
2.2.16 dot11FragmentationThreshold	12
2.2.17 dot11RTSThreshold	12
2.2.18 WPAMixedMode.....	13
2.2.19 RSNPreAuthentication	13
2.2.20 AllowedChannelsTable24.....	13
2.2.21 AllowedChannelsTable5.....	13
2.2.22 SpectrumManagement	14
2.2.23 RxBroadcastInPs.....	14
2.2.24 RatePolicyUserShortRetryLimit.....	14
2.2.25 RatePolicyUserLongRetryLimit.....	14
2.2.26 BeaconReceiveTime	14

2.2.27	desiredPsMode	14
2.2.28	QOS_wmePsModeBE	15
2.2.29	QOS_wmePsModeBK	15
2.2.30	QOS_wmePsModeVI.....	15
2.2.31	QOS_wmePsModeVO	15
2.2.32	Clsfr_Type	15
2.2.33	NumOfDstIPPortClassifiers	15
2.2.34	IPPortClassifier00_IPAddress	16
2.2.35	IPPortClassifier00_Port	16
2.2.36	IPPortClassifier00_DTag	16
2.2.37	NumOfCodePoints.....	16
2.2.38	DSCPClassifier00_CodePoint	16
2.2.39	DSCPClassifier00_DTag	17
2.2.40	STRdot11MaxReceiveLifetime	17

List of Tables

Table 1: Ini File Parameters	9
------------------------------------	---



Revision History

Version	Date	Description
1.0	January 2010	Release

Reference Documents

The documents listed below provide complementary specifications and information for the device:

- NONE

About This Document

This document describes the WiLink 6.1 *.ini file and its parameters.

The document contains the following chapters:

- **Chapter 1, Overview**, page 6, introduces the WiLink ini file.
- **Chapter 2, Ini File Parameters**, page 8, provides a summary and a detailed table describing each parameter.

This page was intentionally left blank.

Introduction

The *.ini file configures driver behavior and is loaded upon driver initialization, in order to customize its behavior to best meet customer needs.

Parameters in the *.ini file may be changed by editing the *.ini file entries using a text editor.
Parameter changes take effect during the following driver load.

The *.ini file is located under the /WiLink/platforms/ps/linux directory.

Topic	Page
1.1 Synopsis	
2.1 Short Description	
2.2 Detailed Description.....	

1.1 Synopsis

Each *.ini line item adheres to the following convention:

Param = Value

Ini File Parameters

Unless otherwise noted, parameters are referenced to the Front End Module's (FEM's) single-ended RFANT port (without the band-pass filter at the FEM output).

Topic	Page
1.1 Synopsis	
2.1 Short Description	
2.2 Detailed Description.....	

2.1 Short Description

Table 1: Ini File Parameters

Parameter	Description	Detailed Description
SmeConnectMode	Connection scan initiator	2.2.1
WME_Enable	QoS support	2.2.2
dot11NetworkType	802.11 mode	2.2.3
SmeScanGChannelList	Channel list to be scanned when working in G band	2.2.4
SmeScanAChannelList	Channel list to be scanned when working in A band	2.2.5
BeaconListenInterval	Number of N-beacons to wake up	2.2.6
DtimListenInterval	Number of N-DTMs to wake up	2.2.7
dot11PowerMode	Default Power mode profile of the station	2.2.8
PowerMgmtHangOverPeriod	Station awake time after sending a frame to the AP	2.2.9
AutoPowerModeDozeMode	Default Doze mode	2.2.10
AutoPowerModeActiveTh	Number of frames per second for moving from Doze mode to Active mode	2.2.11
AutoPowerModeDozeTh	Number of frames per seconds for moving from Active mode to Doze mode	2.2.12
defaultPowerLevel	Default power level when station not connected	2.2.13
PowerSavePowerLevel	Default power level when station connected	2.2.14
TxPower	Default transmission power	2.2.15
dot11FragmentationThreshold	Minimum frame size for fragmentation	2.2.16
dot11RTSThreshold	Frame size to send Request To Send frame	2.2.17
WPAMixedMode	WPA and the WPA2 support	2.2.18
RSNPreAuthentication	Preattentiation support	2.2.19
AllowedChannelsTable24	Allowed channels in 2.4 GHz radio band	2.2.20
AllowedChannelsTable5	Allowed channels in 5.0 GHz radio band	2.2.21
SpectrumManagement	802.11h standard support	2.2.22
RxBroadcastInPs	Reception of broadcast frames while in PS support	2.2.23
RatePolicyUserShortRetryLimit	Number of transmission retries for short frames	2.2.24
RatePolicyUserLongRetryLimit	Number of transmission retries for long frames	2.2.25
BeaconReceiveTime	Time to wait for the beacon	2.2.26
desiredPsMode	Global power-save delivery protocol support	2.2.27
QOS_wmePsModeBE	Power-save delivery protocol for Best Effort access	2.2.28
QOS_wmePsModeBK	Power-save delivery protocol for Background access	2.2.29
QOS_wmePsModeVI	Power-save delivery protocol for Video access	2.2.30
QOS_wmePsModeVO	Power-save delivery protocol for Voice access	2.2.31
Clsfr_Type	Packet classification type	2.2.32
NumOfDstIPPortClassifiers	Number of classifiers	2.2.33
IPPortClassifier00_IPAddress	IP address and IP port for mapping to user priority	2.2.34
IPPortClassifier00_Port	IP port for mapping to user priority	2.2.35
IPPortClassifier00_DTag	IP port classifier for mapping to user priority	2.2.36

Parameter	Description	Detailed Description
NumOfCodePoints	Number of classifiers	2.2.37
DSCPClassifier00_CodePoint	Code point for mapping to user priority	2.2.38
DSCPClassifier00_DTag	Classifier for mapping to user priority	2.2.39
STRdot11MaxReceiveLifetime	Time to maintain a frame fragment before dropping it	2.2.40

2.2 Detailed Description

2.2.1 *SmeConnectMode*

If set to AUTO, the driver initiates a SCAN automatically, based on the configuration, and selects an appropriate BSSID. If set to MANUAL, the driver does not initiate a SCAN operation and does not select a BSSID. Instead, the application initiates the scan.

Values: 0: AUTO
 1: Manual

Default: 1

2.2.2 *WME_Enable*

This parameter defines whether or not quality of service is supported.

Values: 0: Disabled
 1: Enabled

Default: 1

2.2.3 *dot11NetworkType*

This parameter defines the 802.11 mode.

Values: 1: B mode
 2: A mode
 3: G mode
 4: A/G Dual mode

Default: 3

2.2.4 *SmeScanGChannelList*

This parameter provides the list of channels to be scanned when working in G band.

Values: List of channels in G band, from 1 to 14
Default: 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14

2.2.5 *SmeScanAChannelList*

This parameter provides the list of channels to be scanned when working in A band.

Values: List of channels in A band, from 36 to 64
Default: 36, 40, 44, 48, 52, 56, 60, 64

2.2.6 *BeaconListenInterval*

This parameter defines the number of N-beacons to wake up. It is used when working in Short Doze mode.

Values: 1 - 50

Default: 1

2.2.7 *DtimListenInterval*

This parameter defines the number of N-DTMs to wake up. It is used when working in Long Doze mode.

Values: 1 - 50

Default: 1

2.2.8 *dot11PowerMode*

This parameter defines the default Power mode profile of the station.

Values: 0: Auto. The Power mode toggles between Active mode and the defined Doze mode.

1: Always active.

2: Short doze.

3: Long doze.

Default: 0

2.2.9 *PowerMgmtHangOverPeriod*

This parameter defines the time, in milliseconds, during which the station will remain awake after sending a frame to the AP, indicating that the station is going into Power Save.

Values: 5 - 255

Default: 10

2.2.10 *AutoPowerModeDozeMode*

This parameter defines the default Doze mode (short or long) that Auto mode uses when toggling between doze and active.

Values: 2: Short doze

3: Long doze

Default: 2

2.2.11 *AutoPowerModeActiveTh*

This parameter specifies the number of frames per seconds for moving from Doze mode to Active mode, if Power mode is set to Auto.

Values: 2 - 30,000

Default: 15

2.2.12 *AutoPowerModeDozeTh*

This parameter specifies the number of frames per seconds for moving from Active mode to Doze mode, if Power mode is set to Auto.

Values: 1 - 30,000

Default: 8

2.2.13 *defaultPowerLevel*

This parameter specifies the default power level to be used when the station is not connected.

Values:
0: ELP
1: Power down
2: Awake

Default: 0

2.2.14 *PowerSavePowerLevel*

This parameter specifies the default power level to be used when the station is connected.

Values:
0: ELP
1: Power down
2: Awake

Default: 0

2.2.15 *TxPower*

This parameter specifies the default transmission power, in dBm * 10.

Values: 0 - 250

Default: 205

2.2.16 *dot11FragmentationThreshold*

This parameter specifies the minimum frame size, in bytes, used for fragmentation.

Values: 256 - 4,096 (must be a multiple of 256)

Default: 4,096

2.2.17 *dot11RTSThreshold*

This parameter specifies the threshold of the frame size, in bytes, to send Request To Send frame.

Values: 0 - 4,096

Default: 4,096

2.2.18 **WPAMixedMode**

This parameter defines whether both the WPA and the WPA2 are supported.

- Values:** **0:** Only the WPA is supported.
 1: Both the WPA and WPA2 are supported.

Default: 1

2.2.19 **RSNPreAuthentication**

This parameter defines if Preauthentication is supported.

- Values:** **0:** Not supported
 1: Supported

Default: 1

2.2.20 **AllowedChannelsTable24**

When working in 2.4 GHz radio band, this parameter defines the following for each channel:

- **Bit 7:** Whether it is allowed to be scanned
- **Bit 6:** Whether it is allowed to be scanned in Active mode
- **Bits 0-4:** The maximum Tx power allowed when scanning

Each byte correlates to one channel in sequential order.

Values: 00-FF for each channel

Default: FFFFFFFFFFFFFFF

2.2.21 **AllowedChannelsTable5**

When working in 5.0 GHz radio band, this parameter defines the following for each channel:

- **Bit 7:** Whether it is allowed to be scanned
- **Bit 6:** Whether it is allowed to be scanned in Active mode
- **Bits 0-4:** The maximum Tx power allowed when scanning

Each byte correlates to one channel in sequential order.

Values: 00-FF for each channel

Default: FF000000FF000000FF000000FF000000FF000000FF000000
 FF000000FF00
 000
 FF000000FF000000FF000000FF000000FF000000FF000000
 FF000000FF000000FF00
 00FF000000FF000000FF00

2.2.22 SpectrumManagement

This parameter defines if the 802.11h standard is supported.

Values: 0: Not supported
 1: Supported

Default: 0

2.2.23 RxBroadcastInPs

This parameter defines whether or not the reception of broadcast frames while in PS is enabled.

Values: 0: Disabled
 1: Enabled
Default: 1

2.2.24 RatePolicyUserShortRetryLimit

This parameter specifies the number of transmission retries for short frames (less than or equal to dot11RTSThreshold).

Values: 1 - 255
Default: 10

2.2.25 RatePolicyUserLongRetryLimit

This parameter specifies the number of transmission retries for long frames (greater than dot11RTSThreshold).

Values: 1 - 255
Default: 10

2.2.26 BeaconReceiveTime

This parameter defines how much time, in milliseconds (msecs), to wait for the beacon, before going back into power save.

Values: 10 - 1,000 msecs
Default: 50 msecs

2.2.27 desiredPsMode

This parameter defines the global power-save delivery protocol.

Values: **0 – Standard PS:** The station sends a PsPoll frame in order to retrieve the data buffered at the AP. As a result, the AP sends only one frame to the station.
1 – UPSD: The station sends a data frame in order to retrieve the data buffered at the AP. As a result, the AP sends data frames according to the service period indicated by the station.
Default: 1

2.2.28 QOS_wmePsModeBE

This parameter defines the power-save delivery protocol for the Best Effort access category.

Values: 0 - 1 (For exact values, refer to the desiredPsMode field.)

Default: 0

2.2.29 QOS_wmePsModeBK

This parameter defines the power-save delivery protocol for the Background access category.

Values: 0 - 1 (For exact values, refer to the desiredPsMode field.)

Default: 0

2.2.30 QOS_wmePsModeVI

This parameter defines the power-save delivery protocol for the Video access category.

Values: 0 - 1 (For exact values, refer to the desiredPsMode field.)

Default: 0

2.2.31 QOS_wmePsModeVO

This parameter defines the power-save delivery protocol for the Voice access category.

Values: 0 - 1 (For exact values, refer to the desiredPsMode field.)

Default: 1

2.2.32 Clsfr_Type

This parameter defines the packet classification type. The classified packet is mapped to one of the QoS user priorities and is transmitted over the WLAN using the corresponding access category.

Values: **0:** Classification according to 802.1d tag

1: Classification according to Diffserv control service point

2: Classification according to IP port

3: Classification according to IP port and IP address

Default: 3

2.2.33 NumOfDstIPPortClassifiers

This parameter defines the number of classifiers when the classification type is based on the IP port and IP address.

Values: 0 - 16

Default: 0

2.2.34 IPPortClassifier00_IPAddress

Frames destined to this IP address and to the IP port defined in IPPortClassifier00_Port are mapped to the user priority defined in IPPortClassifier00_DTag and are transmitted over the WLAN using the corresponding access category.

Values: 0 0 0 0 – 0xFF 0xFF 0xFF 0xFF

Default: 0a 03 01 C9 (IP address 10.3.1.201)

2.2.35 IPPortClassifier00_Port

Refer to *Section 2.2.34, IPPortClassifier00_IPAddress*, for more information.

Values: 1 - 65,535

Default: 5,004

2.2.36 IPPortClassifier00_DTag

Refer to *Section 2.2.34, IPPortClassifier00_IPAddress*, for more information.

Values: 0 - 7

Default: 0

There are 16 IP address and IP port classifiers:

- IPPortClassifier00_IPAddress – IPPortClassifier15_IPAddress
- IPPortClassifier00_Port – IPPortClassifier15_Port
- IPPortClassifier00_DTag – IPPortClassifier15_DTag

2.2.37 NumOfCodePoints

This parameter defines the number of classifiers when the classification type is based on the Diffserv control service point.

Values: 0 - 16

Default: 0

2.2.38 DSCPClassifier00_CodePoint

Frames with this code point are mapped to the user priority defined in DSCPClassifier00_DTag and are transmitted over the WLAN using the corresponding access category.

Values: 0 - 63

Default: 0

2.2.39 DSCPClassifier00_DTag

Refer to *Section 2.2.38, DSCPClassifier00_CodePoint*, for more information.

Values: 0 - 7

Default: 0

There are 16 DSCP classifiers:

- DSCPClassifier00_CodePoint – DSCPClassifier00_CodePoint
- DSCPClassifier15_DTag – DSCPClassifier15_DTag

2.2.40 STRdot11MaxReceiveLifetime

This parameter specifies the maximum time to keep a fragment of a frame that was not reassembled yet, before deciding to drop it.

Values: 0 - 0xFFFFFFFF

Default: 512 msecs

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DLP® Products	www.dlp.com	Communications and Telecom	www.ti.com/communications
DSP	dsp.ti.com	Computers and Peripherals	www.ti.com/computers
Clocks and Timers	www.ti.com/clocks	Consumer Electronics	www.ti.com/consumer-apps
Interface	interface.ti.com	Energy	www.ti.com/energy
Logic	logic.ti.com	Industrial	www.ti.com/industrial
Power Mgmt	power.ti.com	Medical	www.ti.com/medical
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
RFID	www.ti-rfid.com	Space, Avionics & Defense	www.ti.com/space-avionics-defense
RF/IF and ZigBee® Solutions	www.ti.com/lprf	Video and Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless-apps