

TPS54610EVM

6-Amp Externally Compensated SWIFT™ Regulator Evaluation Module

User's Guide

August 2001 PMP PD & PS

IMPORTANT NOTICE

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgment, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

Customers are responsible for their applications using TI components.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, license, warranty or endorsement thereof.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations and notices. Representation or reproduction of this information with alteration voids all warranties provided for an associated TI product or service, is an unfair and deceptive business practice, and TI is not responsible nor liable for any such use.

Resale of TI's products or services with <u>statements different from or beyond the parameters</u> stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service, is an unfair and deceptive business practice, and TI is not responsible nor liable for any such use.

Also see: Standard Terms and Conditions of Sale for Semiconductor Products, www.ti.com/sc/docs/stdterms.htm

Mailing Address:

Texas Instruments
Post Office Box 655303
Dallas, Texas 75265

EVM IMPORTANT NOTICE

Texas Instruments (TI) provides the enclosed product(s) under the following conditions:

This evaluation kit being sold by TI is intended for use for **ENGINEERING DEVELOPMENT OR EVALUATION PURPOSES ONLY** and is not considered by TI to be fit for commercial use. As such, the goods being provided may not be complete in terms of required design-, marketing-, and/or manufacturing-related protective considerations, including product safety measures typically found in the end product incorporating the goods. As a prototype, this product does not fall within the scope of the European Union directive on electromagnetic compatibility and therefore may not meet the technical requirements of the directive.

Should this evaluation kit not meet the specifications indicated in the EVM User's Guide, the kit may be returned within 30 days from the date of delivery for a full refund. THE FOREGOING WARRANTY IS THE EXCLUSIVE WARRANTY MADE BY SELLER TO BUYER AND IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESSED, IMPLIED, OR STATUTORY, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE.

The user assumes all responsibility and liability for proper and safe handling of the goods. Further, the user indemnifies TI from all claims arising from the handling or use of the goods. Please be aware that the products received may not be regulatory compliant or agency certified (FCC, UL, CE, etc.). Due to the open construction of the product, it is the user's responsibility to take any and all appropriate precautions with regard to electrostatic discharge.

EXCEPT TO THE EXTENT OF THE INDEMNITY SET FORTH ABOVE, NEITHER PARTY SHALL BE LIABLE TO THE OTHER FOR ANY INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES.

TI currently deals with a variety of customers for products, and therefore our arrangement with the user **is not exclusive**.

TI assumes no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein.

Please read the EVM User's Guide and, specifically, the EVM Warnings and Restrictions notice in the EVM User's Guide prior to handling the product. This notice contains important safety information about temperatures and voltages. For further safety concerns, please contact the TI application engineer.

Persons handling the product must have electronics training and observe good laboratory practice standards.

No license is granted under any patent right or other intellectual property right of TI covering or relating to any machine, process, or combination in which such TI products or services might be or are used.

Mailing Address:

Texas Instruments Post Office Box 655303 Dallas, Texas 75265

EVM WARNINGS AND RESTRICTIONS

It is important to operate this EVM within the specified input and output ranges described in the EVM User's Guide.

Exceeding the specified input range may cause unexpected operation and/or irreversible damage to the EVM. If there are questions concerning the input range, please contact a TI field representative prior to connecting the input power.

Applying loads outside of the specified output range may result in unintended operation and/or possible permanent damage to the EVM. Please consult the EVM User's Guide prior to connecting any load to the EVM output. If there is uncertainty as to the load specification, please contact a TI field representative.

During normal operation, some circuit components may have case temperatures greater than 60°C . The EVM is designed to operate properly with certain components above 60°C as long as the input and output ranges are maintained. These components include but are not limited to linear regulators, switching transistors, pass transistors, and current sense resistors. These types of devices can be identified using the EVM schematic located in the EVM User's Guide. When placing measurement probes near these devices during operation, please be aware that these devices may be very warm to the touch.

Mailing Address:

Texas Instruments Post Office Box 655303 Dallas, Texas 75265

Copyright © 2001, Texas Instruments Incorporated

Preface

Read This First

About This Manual

This user's guide describes the characteristics, operation, and use of the TPS54610 6-amp externally compensated SWIFT™ regulator evaluation module (EVM). The user's guide includes a schematic diagram and bill of materials.

How to Use This Manual

Thi	s document contains the following chapters:
	Chapter 1—Introduction
	Chapter 2—Test Setup and Results
	Chapter 3—Board Layout
	Chapter 4—Schematic and Bill of Materials

FCC Warning

This equipment is intended for use in a laboratory test environment only. It generates, uses, and can radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to subpart J of part 15 of FCC rules, which are designed to provide reasonable protection against radio frequency interference. Operation of this equipment in other environments may cause interference with radio communications, in which case the user at his own expense will be required to take whatever measures may be required to correct this interference.

Trademarks

SWIFT™ is a trademark of Texas Instruments.

Contents

1	Intro	duction	1-1
	1.1	Background	
	1.2	Performance Specification Summary	
	1.3	Modifications	
2	Test :	Setup and Results	2-1
	2.1	Input/Output Connections	
	2.2	Loop Characterization Setup	2-3
	2.3	Efficiency	
	2.4	Thermal Performance	2-4
	2.5	Output Voltage Regulation	
	2.6	Load Transients	
	2.7	Loop Characteristics	
	2.8	Output Voltage Ripple	
	2.9	Input Ripple Voltage	2-9
	2.10	Start-Up	
3	Boar	d Layout	3-1
	3.1	Layout	
4	Sche	matic and Bill of Materials	4-1
	4.1	Schematic	
	42	Bill of Materials	4-3

Figures

1–1	Frequency Trimming Resistor Selection Graph	1-4
2–1	Connection Diagram	
2-2	Measured Efficiency	
2-3	Measured Board Losses	2-4
2–4	Measured Junction Temperature at 25°C Ambient	2-4
2–5	Measured Case Temperature at 25°C Ambient	2-5
2–6	Measured Load Regulation	2-5
2-7	Measured Line Regulation	2-6
2-8	Measured Load Transient Response	2-6
2-9	Measured Loop Gain	2-7
2-10	Measured Loop Phase	2-7
2-11	Measured Output Voltage Ripple at 350-kHz Operation	2-8
2-12	Measured Output Voltage Ripple at 550-kHz Operation	2-8
2-13	Measured Input Voltage Ripple at 350-kHz Operation	2-9
2-14	Measured Input Voltage Ripple at 550-kHz Operation	2-9
2-15	Measured Start-Up Waveforms	2-10
3–1	Top-Side Assembly	3-2
3–2	Top-Side Layout	3-3
3-3	Internal Layers	3-4
3–4	Bottom-Side Layer	3-5
4–1	TPS54610 EVM Schematic	4-2

Tables

1–1	Performance Specification Summary	1-2
	Output Voltage Programming	
4–1	TPS54610 EVM Bill of Materials	4-3

Chapter 1

Introduction

This chapter contains background information for the TPS54610 and support documentation for the TPS54610 evaluation module. The EVM performance specifications are also given.

Topi	c Pag	E
1.1	Background1-	2
1.2	Performance Specification Summary 1-	2
1.3	Modifications 1-	3

1.1 Background

The TPS54610 evaluation module (EVM) uses the TPS54610 synchronous buck regulator to provide a 3.3-V output over an input range of 4.0 V to 6.0 V and over a load range of 0 A to 6 A. The EVM is designed to be easily modified. Additional pads support multiple input and output capacitors, and the inductor pads are large to accommodate different inductors. A jumper is provided to allow the switching frequency to be easily changed from 350 kHz to 550 kHz.

The MOSFETs of the TPS54610 are incorporated inside the TPS54610 package. This eliminates the need for external MOSFETs and their associated drivers. The low drain-to-source on resistance of the MOSFETs gives the TPS54610 high efficiency and helps to keep the junction temperature low at high output currents. The compensation components, external to the IC, allow for an adjustable output voltage and a customizable loop response.

1.2 Performance Specification Summary

Table 1–1 provides a summary of the TPS54610 EVM performance specifications. All specifications are given for an ambient temperature of 25°C, unless otherwise noted.

Table 1–1. Performance Specification Summary

Specification	Test Conditions	Min	Тур	Max	Units
Input voltage range		4	5	6	V
Output voltage set point			3.3		V
Output current range	V _{IN} = 5 V	0		6	Α
Line regulation	I _O = 6 A	-5		+5	mV
Load regulation	V _{IN} = 5 V	-5		+5	mV
	1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1		-50		mV_{PK}
L d to- o - i - o t	$I_O = 1 \text{ A to 5 A}, t_{(rise)} = 10 \mu\text{s}$		100		μs
Load transient response	L 5 A 42 4 A 4 A 40 W2		50		mV_{PK}
	$I_O = 5 \text{ A to 1 A}, t_{(fall)} = 10 \mu\text{s}$		150		μs
Loop bandwidth	V _{IN} = 5 V, I _O = 6 A		25		kHz
Phase margin	V _{IN} = 5 V, I _O = 6 A		75		0
Input ripple voltage				250	mV_{PP}
Output ripple voltage				18	mV_{PP}
Output rise time		4.7	8.4	15	ms
On a series of the series of	V _{SYNCH} = 0 V	280	350	420	1.1.1-
Operating frequency	V _{SYNCH} = V _{IN}	440	550	660	kHz
Efficiency	V _{IN} = 5 V, I _O = 1.5 A		94%		

1.3 Modifications

The TPS54610 EVM is designed to support numerous types of input capacitors, output capacitors, and inductors (see Top-Side Layout Figure 3–1, and EVM schematic Figure 4–1). C3 provides pads for a surface mount input capacitor, while the holes of C1 can be used for through-hole input capacitors. Similarly, C10 and C11 provide pads for surface-mount output capacitors, while the holes of C12 can be used for through-hole output capacitors. The pads of L1, which are intentionally large, can accommodate a variety of power inductors. When changing the output filter, the compensation values must also be changed to ensure stability. The SWIFT Designer software tool or Texas Instruments Application Note SLVA104 - Designing With Externally Compensated SWIFT Regulators can be used to assist in the calculation of compensation components. Both SWIFT Designer software and application note SLVA104 are available for download at the Texas Instruments web site.

The TPS54610 EVM can be easily configured to switch at either 350 kHz or 550 kHz by changing the location of jumper JP1. Alternatively, by using RT (R3), the switching frequency can be trimmed to any value between 280 kHz and 700 kHz. A plot of the value of RT versus the switching frequency is given in Figure 1–1.

The output voltage of the TPS54610 EVM can be adjusted to any value down to 0.9 V by changing only one component value (R2). The value of R2 for a specific output voltage can be calculated by using Equation 1–1. Table 1–2 lists the value of R2 for some common bus voltages.


Equation 1–1.

$$R_2 = 10 \text{ k}\Omega \times \frac{0.891 \text{ V}}{\text{V}_0 - 0.891 \text{ V}}$$

Changing the value of C2 can modify the slow start time of the TPS54610 EVM. Use Equation 1–2 to calculate the value of C2 for a specific slow start time. With C2 left open, the slow start time is typically 3.6 ms. The slow start time can not be made faster than 3.6 ms.

Equation 1-2.

$$C_2 = \frac{T_{SS} \times 5 \,\mu A}{0.891 \,V}$$






Table 1–2. Output Voltage Programming

Output Voltage (V)	R2 (kΩ)
0.9	1000
1.2	28.7
1.5	14.7
1.8	9.76
2.5	5.49
3.3	3.74

Chapter 2

Test Setup and Results


This chapter describes how to properly connect, setup, and use the TPS54610 EVM. It also presents the test results and covers efficiency, output voltage regulation, load transients, loop response, output ripple, input ripple, and start-up.

Topic	С	Page
2.1	Input/Output Connections	. 2-2
2.2	Loop Characterization Setup	2-3
2.3	Efficiency	2-3
2.4	Thermal Performance	. 2-4
2.5	Output Voltage Regulation	. 2-5
2.6	Load Transients	. 2-6
2.7	Loop Characteristics	2-7
2.8	Output Voltage Ripple	. 2-8
2.9	Input Ripple Voltage	. 2-9
2.10	Start-Up	2-10

2.1 Input/Output Connections

The TPS54610 EVM has the following input/output connections: J1 (V_{in} and GND) and J3 (V_{out} and GND). A diagram showing the connection points is shown in Figure 2–1. Connect a power supply capable of supplying 6 A to J1 through a pair of 20 AWG wires. Connect the load to J3 through a pair of 16 AWG wires. Minimize wire lengths to reduce losses in the wires. Test point TP5 provides easy connection for an oscilloscope voltage probe to monitor the output voltage.

Figure 2-1. Connection Diagram



2.2 Loop Characterization Setup

The TPS54610 EVM contains a 49.9- Ω resistor (R6) in the feedback path for use in measuring the loop response. Test points on either side of R6 (TP4 and TP3) provide connection points for network analyzer signals. By injecting a small AC signal across R6, the loop gain and phase can be measured from one side of R6 to the other. Because the value of R6 is small in relation to the value of R4, it does not affect the output voltage set point of the regulator.

2.3 Efficiency

The TPS54610 EVM efficiency peaks at around 1.5 A of load current. At full load this drops to around 89%. Figure 2–2 shows the typical efficiency for a 5-V input and an ambient temperature of 25°C. The efficiency is lower at higher ambient temperatures, due to temperature variation in the drain-to-source resistance of the MOSFETs. The efficiency is slightly higher at 350 kHz than at 550 kHz due to the gate and switching losses in the MOSFETs. The total board losses are shown in Figure 2–3.

Figure 2–2. Measured Efficiency






Figure 2-3. Measured Board Losses



2.4 Thermal Performance

The junction temperature is plotted versus the load current with a 5-V input voltage and a 25°C ambient temperature in Figure 2–4. The case temperature is plotted in Figure 2–5. The low junction-to-case thermal resistance of the PWP package, along with a good board layout, helps to keep the junction temperature low at high output currents. With a 5-V input source and a 6-A load, the junction temperature is approximately 60°C, while the case temperature is approximately 55°C.

Figure 2-4. Measured Junction Temperature at 25°C Ambient







Figure 2-5. Measured Case Temperature at 25°C Ambient

2.5 Output Voltage Regulation

The output voltage load regulation with a 5-V input and a 25°C ambient temperature is shown in Figure 2–6. The output voltage line regulation is shown in Figure 2–7. Over the input voltage range of 4.0 V to 6.0 and the load range of 0 A to 6 A, the output voltage varies less than 0.3%.








Figure 2-7. Measured Line Regulation



2.6 Load Transients

The TPS54610 EVM response to load transients is shown in Figure 2–8.The load transient in Figure 2–8 transitions from 1 A to 5 A in 10 μ s. The output voltage deviates approximately 50 mV from its average value as a result of these transients.

Figure 2-8. Measured Load Transient Response



2.7 Loop Characteristics

The loop gain and phase for a 5.0-V input and a 6.0-A load are shown in Figure 2–9 and Figure 2–10. The loop crossover frequency is approximately 25 kHz, and the phase margin is approximately 75°.

Figure 2-9. Measured Loop Gain





Figure 2-10. Measured Loop Phase



2.8 Output Voltage Ripple

The output ripple voltage is plotted in Figure 2–11 for a switching frequency of 350 kHz and in Figure 2–12 for a switching frequency of 550 kHz. The SLVP192 has a typical output voltage ripple of less than 18 mV $_{pp}$.

Figure 2-11. Measured Output Voltage Ripple at 350-kHz Operation





Figure 2-12. Measured Output Voltage Ripple at 550-kHz Operation



2.9 Input Ripple Voltage

The input ripple voltage for a 6-A load is shown in Figure 2–13 with a switching frequency of 350 kHz and in Figure 2–14 with a switching frequency of 550 kHz. With a switching frequency of 550 kHz, the input ripple is approximately 200 mV $_{pp}$. The input ripple voltage can be made lower by adding capacitance to the input.

Figure 2–13. Measured Input Voltage Ripple at 350-kHz Operation






Figure 2–14. Measured Input Voltage Ripple at 550-kHz Operation



2.10 Start-up

The start-up voltage waveform of the TPS54610 EVM is shown in Figure 2–15. There is approximately a 12.8-ms delay after the input voltage rises above the 3.0-V start-up voltage threshold before the TPS54610 EVM output begins to rise. The output voltage then ramps to 3.3 V in 7.2 ms. The change of slope in the output voltage rising edge occurs at the point where control of the TPS54610 EVM internal reference voltage changes from the internally controlled slow start to the externally controlled slow start. Decreasing the value of C2 can decrease the start-up delay time and slow start time. To program a specific slow start time, see Chapter 1, Section 1.3, *Modifications*. If C2 is left unpopulated, the start-up delay time is eliminated, and the slow start time is typically 3.6 ms.

Figure 2-15. Measured Start-Up Waveforms



Chapter 3

Board Layout

This chapter provides a description of the TPS 54610 EVM board layout and layer illustrations.

Topi	С																								P	а	g	е	
3.1	Layout																					 			 	3	3-2	2	

3.1 Layout

The top-side (component) layer for the TPS54610 EVM is shown in Figure 3–1. The input decoupling capacitor (C9), bias decoupling capacitor (C4), and bootstrap capacitor (C8) are all located as close to the IC as possible. In addition, the compensation components are also kept close to the IC. The compensation circuit ties to the output voltage at the point of regulation (TP4).

All layers are shown on the following pages and resemble a layer stack-up encountered in a typical application. The top and bottom layers are 1.5 oz. copper, while the two internal layers are 0.5 oz. copper. The two internal layers are identical and are used as *quiet* ground planes. The power ground plane is routed on the top layer, and is tied to the *quiet* (analog) ground planes at the output sense point (test point TP8). A wide power ground plane is used to keep the input ground current from injecting noise between the analog and power grounds. A total of 16 vias are used to tie the thermal land area under the TPS54610 device to the internal ground planes and to the thermal plane on the backside of the board.

Figure 3-1. Top-Side Assembly




Figure 3–2. Top-Side Layout




Figure 3–3. Internal Layers





Figure 3-4. Bottom-Side Layer



Chapter 4


Schematic and Bill of Materials

The EVM schematic and bill of materials are presented in this chapter.

Горіс	Pag	е
4.1	Schematic	2
4.2	Bill of Materials 4-3	3

4.1 Schematic

Figure 4–1. TPS54610 EVM Schematic



4.2 Bill of Materials

Table 4–1. TPS54610 EVM Bill of Materials

Count	Ref Des	Description	Size	MFR	Part Number
_	C1, C12	Open	0.394		
2	C10, C11	Capacitor, POSCAP, 470 μF, 4 V, 40 mΩ, 20%	7343 (D)	Sanyo	4TPB470M
1	C13	Capacitor, ceramic, 1000 pF, 25 V, X7R, 10%	603	Murata	GRM39X7R102K25
	C14	Open	603		
2	C2, C8	Capacitor, ceramic, 0.047 μF, 25 V, X7R, 10%	603	Murata	GRM39X7R473K25
1	C3	Capacitor, POSCAP, 220 μ F, 10 V, 40 m Ω , 20%	7343 (D)	Sanyo	10TPB220M
1	C4	Capacitor, ceramic, 0.1 μF, 25 V, X7R, 10%	603	Murata	GRM39X7R104K25
1	C5	Capacitor, ceramic, 68 pF, 50 V, C0G, 5%	603	Murata	GRM39C0G680J50
1	C6	Capacitor, ceramic, 6800 pF, 25 V, X7R, 10%	603	Murata	GRM39X7R682K25
1	C7	Capacitor, ceramic, 0.012 μF, 50 V, X7R, 10%	603	Murata	GRM39X7R123K50
1	C9	Capacitor, ceramic, 10 μF, 10 V, X5R, 20%	1210	Panasonic	ECJ-4YB1A106K
1	J1	Terminal block, 2 pin, 6 A, 3,5 mm	0.27 x 0.25	OST	ED1514
1	J2	Header, 4 pin, 100 mil spacing, (361-pin strip)	0.100 x 4	Sullins	PTC36SAAN
1	J3	Terminal block, 2 pin, 15 A, 5,1 mm	0.40×0.35	OST	ED1609
1	JP1	Header, 3 pin, 100 mil spacing, (36-pin strip)	0.100 x 3	Sullins	PTC36SAAN
1	L1	Inductor, SMT, 4.7 μ H, 7.7 A, 12 m Ω	0.76 x 0.52	Coiltronics	UP3B-4R7
1	R1	Resistor, chip, 9.76 kΩ, 1/16 W, 1%	603	Std	Std
1	R2	Resistor, chip, 3.74 kΩ, 1/16 W, 0.1%	603	Std	Std
	R3	Open	603		
1	R4	Resistor, chip, 10 kΩ, 1/16 W, 0.1%	603	Std	Std
1	R5	Resistor, chip, 1.18 kΩ, 1/16 W, 1%	603	Std	Std
1	R6	Resistor, chip, 49.9 Ω, 1/16 W, 1%	603	Std	Std
1	R7	Resistor, chip, 10 kΩ, 1/16 W, 1%	603	Std	Std
_	R8	Open	805		
5	TP1-TP4, TP6	Test point, red, 1 mm	0.038	Farnell	240-345
1	TP5	Adapter, 3.5-mm probe clip (or 131-5031-00)	0.2	Tektronix	131-4244-00
2	TP7, TP8	Test point, black, 1 mm	0.038	Farnell	240-333
1	U1	IC, SWIFT™ power controller, adjustable-V, 6 A	PWP28	TI	TPS54610PWP
1	_	PCB, 3 ln × 3 ln × 0.062 ln		Any	SLVP192
2	_	Shunt, 100 mil, black	0.100	3M	929950-00