

ISO7821LLS 高性能 8000 V_{PK} 增强型隔离式双 LVDS 缓冲器

1 特性

- 符合 TIA/EIA-644-A LVDS 标准
- 信号传输速率: 50Mbps 至 150Mbps
- 针对直流均衡数据进行了优化
- 宽电源电压范围: 3V 至 5.5V
- 宽温度范围: -55°C 至 125°C
- 低功耗: 电流典型值为 10.3mA/通道 (150Mbps 时)
- 低传播延迟: 17ns (典型值)
- 行业领先的 CMTI (最小值): $\pm 100\text{kV}/\mu\text{s}$
- 优异的电磁兼容性 (EMC)
- 系统级静电放电 (ESD)、瞬态放电 (EFT) 以及抗浪涌保护
- 低辐射
- 隔离栅寿命: > 40 年
- SOIC-16 宽体 (DW) 和超宽体 (DWW) 封装选项
- 可承受的隔离浪涌电压高达 12800 V_{PK}
- 安全相关认证:
 - 符合 DIN V VDE V 0884-10 (VDE V 0884-10): 2006-12 标准的 8000 V_{PK} 增强型隔离
 - 符合 UL 1577 标准且长达 1 分钟的 5700 V_{RMS} 隔离
 - CSA 组件验收通知 5A, IEC 60950-1 和 IEC 60601-1 终端设备标准
 - 符合 EN 61010-1 和 EN 60950-1 标准的 TUV 认证
 - 符合 GB4943.1-2011 标准的 CQC 认证
 - 已通过所有认证

2 应用

- 电机控制
- 测试和测量
- 工业自动化
- 医疗设备
- 通信系统

3 说明

ISO7821LLS 器件是一款高性能、隔离式双 LVDS 缓冲器，隔离电压为 8000 V_{PK}。在隔离 LVDS 总线信号时，该器件可提供高电磁抗扰度，辐射较低，并且具有低功耗特性。各隔离通道具有一个 LVDS 接收和传输缓冲器。ISO7821LLS 器件的定时性能针对与通信系统结合使用进行了优化。通信采用通过内部失真校正方案实现的直流均衡数据流。

ISO7821LLS 器件有一条正向通道和一条反向通道。

凭借创新的芯片设计和布线技术，ISO7821LLS 器件的电磁兼容性得到了显著增强，从而可确保提供系统级 ESD、EFT 和浪涌保护并符合辐射标准。


ISO7821LLS 器件采用 16 引脚小外形尺寸集成电路 (SOIC) 宽体 (DW) 和超宽体 (DWW) 封装。

器件信息⁽¹⁾

器件型号	封装	封装尺寸 (标称值)
ISO7821LLS	DW (16)	10.30mm x 7.50mm
	DWW (16)	10.30mm x 14.00mm

(1) 要了解所有可用封装，请参见数据表末尾的可订购产品附录。

简化电路原理图



Copyright © 2016, Texas Instruments Incorporated

V_{CCI} 和 GNDI 分别是输入通道的电源和接地连接。

V_{CCO} 和 GNDI 分别是输出通道的电源和接地连接。



An IMPORTANT NOTICE at the end of this data sheet addresses availability, warranty, changes, use in safety-critical applications, intellectual property matters and other important disclaimers. PRODUCTION DATA.

English Data Sheet: SLLSETS5

目 录

1	特性	1
2	应用	1
3	说明	1
4	修订历史记录	2
5	Pin Configuration and Functions	3
6	Specifications	4
6.1	Absolute Maximum Ratings	4
6.2	ESD Ratings	4
6.3	Recommended Operating Conditions	4
6.4	Thermal Information	5
6.5	Power Ratings	5
6.6	Insulation Specifications	6
6.7	Safety-Related Certifications	7
6.8	Safety Limiting Values	7
6.9	DC Electrical Characteristics	8
6.10	DC Supply Current Characteristics	9
6.11	Timing Requirements for Distortion Correction Scheme	9
6.12	Switching Characteristics	10
6.13	Insulation Characteristics Curves	11
6.14	Typical Characteristics	12
7	Parameter Measurement Information	14
8	Detailed Description	17
8.1	Overview	17
8.2	Functional Block Diagram	17
8.3	Feature Description	18
8.4	Device Functional Modes	19
9	Application and Implementation	20
9.1	Application Information	20
9.2	Typical Application	20
10	Power Supply Recommendations	23
11	Layout	24
11.1	Layout Guidelines	24
11.2	Layout Example	24
12	器件和文档支持	25
12.1	文档支持	25
12.2	接收文档更新通知	25
12.3	社区资源	25
12.4	商标	25
12.5	静电放电警告	25
12.6	Glossary	25
13	机械、封装和可订购信息	25

4 修订历史记录


注：之前版本的页码可能与当前版本有所不同。

Changes from Original (March 2016) to Revision A

Page

• 已更改 器件状态“产品预览”至“量产数据”并且已发布完整版本数据表	1
---	---

5 Pin Configuration and Functions



Pin Functions

PIN		I/O	DESCRIPTION
NAME	NO.		
EN1	7	I	Output enable 1. Output pins on side 1 are enabled when EN1 is high or open and in high impedance state when EN1 is low.
EN2	10	I	Output enable 2. Output pins on side 2 are enabled when EN2 is high or open and in high impedance state when EN2 is low.
GND1	2	—	Ground connection for V _{CC1}
	8		
GND2	9	—	Ground connection for V _{CC2}
	15		
INA+	3	I	Positive differential input, channel A
INA-	4	I	Negative differential input, channel A
INB+	11	I	Positive differential input, channel B
INB-	12	I	Negative differential input, channel B
OUTA+	14	O	Positive differential output, channel A
OUTA-	13	O	Negative differential output, channel A
OUTB+	6	O	Positive differential output, channel B
OUTB-	5	O	Negative differential output, channel B
V _{CC1}	1	—	Power supply, side 1, V _{CC1}
V _{CC2}	16	—	Power supply, side 2, V _{CC2}

6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

			MIN	MAX	UNIT
V_{CCx}	Supply voltage ⁽²⁾	V_{CC1}, V_{CC2}	-0.5	6	V
V	Voltage on input, output, and enable pins	OUTx, INx, ENx	-0.5	$V_{CCx} + 0.5$ ⁽³⁾	V
I_O	Maximum current through OUTx pins		-20	20	mA
T_J	Junction temperature		-55	150	°C
T_{stg}	Storage temperature		-65	150	°C

(1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) All voltage values except differential I/O bus voltages are with respect to the local ground pin (GND1 or GND2) and are peak voltage values.

(3) Maximum voltage must not exceed 6 V.

6.2 ESD Ratings

			VALUE	UNIT
$V_{(ESD)}$	Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	± 4500	V
		Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾	± 1500	

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

6.3 Recommended Operating Conditions

		MIN	NOM	MAX	UNIT
V_{CC1}, V_{CC2}	Supply voltage	3	3.3	5.5	V
$ V_{ID} $	Magnitude of RX input differential voltage	Driven with voltage sources on RX pins	100	600	mV
V_{IC}	RX input common-mode voltage	$V_{CC1}, V_{CC2} \geq 3$ V	$0.5 V_{ID} $	$2.4 - 0.5 V_{ID} $	V
R_L	TX far-end differential termination		100		Ω
DR	Signaling rate	50		150	Mbps
T_A	Ambient temperature	-55	25	125	°C

6.4 Thermal Information

THERMAL METRIC ⁽¹⁾	ISO7821LLS		UNIT
	DW (SOIC)	DWW (SOIC)	
	16 PINS	16 PINS	
R _{θJA} Junction-to-ambient thermal resistance	82	84.6	°C/W
R _{θJC(top)} Junction-to-case(top) thermal resistance	44.6	46.4	°C/W
R _{θJB} Junction-to-board thermal resistance	46.6	55.3	°C/W
Ψ _{JT} Junction-to-top characterization parameter	17.8	18.7	°C/W
Ψ _{JB} Junction-to-board characterization parameter	46.1	54.5	°C/W
R _{θJC(bottom)} Junction-to-case(bottom) thermal resistance	—	—	°C/W

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

6.5 Power Ratings

V_{CC1} = V_{CC2} = 5.5 V, T_J = 150°C, C_L = 5 pF, R_L = 100-Ω differential, input a 75-MHz 50% duty-cycle square wave, EN1 = EN2 = 5.5 V

PARAMETER	TEST CONDITIONS	MAX	TYP	MAX	UNIT
P _D Maximum power dissipation (both sides)				180	mW
P _{D1} Maximum power dissipation (side 1)				90	mW
P _{D2} Maximum power dissipation (side 2)				90	mW

6.6 Insulation Specifications

over operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	SPECIFICATION		UNIT		
		DW	DWW			
GENERAL						
CLR	External clearance ⁽¹⁾	>8	>14.5	mm		
CPG	External creepage ⁽¹⁾	>8	>14.5	mm		
DTI	Distance through the insulation	>21	>21	μm		
CTI	Tracking resistance (comparative tracking index)	DIN EN 60112 (VDE 0303–11); IEC 60112; UL 746A	>600	>600	V	
	Material group	According to IEC 60664-1	I	I		
Overvoltage category per IEC 60664-1	Rated mains voltage ≤ 600 V _{RMS}	I–IV	I–IV			
	Rated mains voltage ≤ 1000 V _{RMS}	I–III	I–IV			
DIN V VDE V 0884–10 (VDE V 0884–10):2006–12⁽²⁾						
V _{IORM}	Maximum repetitive peak isolation voltage	AC voltage (bipolar)	2121	2828	V _{PK}	
V _{IOWM}	Maximum isolation working voltage	AC voltage (sine wave); time dependent dielectric breakdown (TDDB) test; see Figure 1 and Figure 2	1500	2000	V _{RMS}	
		DC voltage	2121	2828	V _{DC}	
V _{IOTM}	Maximum transient isolation voltage	V _{TEST} = V _{IOTM} , t = 60 s (qualification) t = 1 s (100% production)	8000	8000	V _{PK}	
V _{IOSM}	Maximum surge isolation voltage ⁽³⁾	Test method per IEC 60065, 1.2/50 μs waveform, V _{TEST} = 1.6 × V _{IOSM} = 12800 V _{PK} (qualification)	8000	8000	V _{PK}	
q _{pd}	Apparent charge ⁽⁴⁾	Method a: After I/O safety test subgroup 2/3, V _{ini} = V _{IOTM} , t _{ini} = 60 s; V _{pd(m)} = 1.2 × V _{IORM} = 2545 V _{PK} (DW) and 3394 V _{PK} (DWW), t _m = 10 s	≤5	≤5	pC	
		Method a: After environmental tests subgroup 1, V _{ini} = V _{IOTM} , t _{ini} = 60 s; V _{pd(m)} = 1.6 × V _{IORM} = 3394 V _{PK} (DW) and 4525 V _{PK} (DWW), t _m = 10 s	≤5	≤5		
		Method b1: At routine test (100% production) and preconditioning (type test) V _{ini} = V _{IORM} , t _{ini} = 1 s; V _{pd(m)} = 1.875 × V _{IORM} = 3977 V _{PK} (DW) and 5303 V _{PK} (DWW), t _m = 1 s	≤5	≤5		
C _{IO}	Barrier capacitance, input to output ⁽⁵⁾	V _{IO} = 0.4 × sin (2πft), f = 1 MHz	~0.7	~0.7	pF	
R _{IO}	Isolation resistance, input to output ⁽⁵⁾	V _{IO} = 500 V, T _A = 25°C	>10 ¹²	>10 ¹²	Ω	
		V _{IO} = 500 V, 100°C ≤ T _A ≤ 125°C	>10 ¹¹	>10 ¹¹		
		V _{IO} = 500 V at T _S = 150°C	>10 ⁹	>10 ⁹		
Pollution degree			2	2		
Climatic category			55/125/21	55/125/21		
UL 1577						
V _{ISO}	Withstanding isolation voltage	V _{TEST} = V _{ISO} = 5700 V _{RMS} , t = 60 s (qualification); V _{TEST} = 1.2 × V _{ISO} = 6840 V _{RMS} , t = 1 s (100% production)	5700	5700	V _{RMS}	

- (1) Creepage and clearance requirements should be applied according to the specific equipment isolation standards of an application. Care should be taken to maintain the creepage and clearance distance of a board design to ensure that the mounting pads of the isolator on the printed-circuit board do not reduce this distance. Creepage and clearance on a printed-circuit board become equal in certain cases. Techniques such as inserting grooves and/or ribs on a printed circuit board are used to help increase these specifications.
- (2) This coupler is suitable for safe *electrical insulation* only within the safety ratings. Compliance with the safety ratings shall be ensured by means of suitable protective circuits.
- (3) Testing is carried out in air or oil to determine the intrinsic surge immunity of the isolation barrier.
- (4) Apparent charge is electrical discharge caused by a partial discharge (pd).
- (5) All pins on each side of the barrier tied together creating a two-terminal device.

6.7 Safety-Related Certifications

VDE	CSA	UL	CQC	TUV
Plan to certify according to DIN V VDE V 0884-10 (VDE V 0884-10);2006-12 and DIN EN 60950-1 (VDE 0805 Teil 1):2011-01	Plan to certify under CSA Component Acceptance Notice 5A, IEC 60950-1 and IEC 60601-1	Plan to certify according to UL 1577 Component Recognition Program	Plan to certify according to GB 4943.1-2011	Plan to certify according to EN 61010-1:2010 (3rd Ed) and EN 60950-1:2006/A11:2009/A1:2010/A12:2011/A2:2013
Reinforced insulation Maximum transient isolation voltage, 8000 V_{PK} ; Maximum repetitive peak isolation voltage, 2121 V_{PK} (DW), 2828 V_{PK} (DWW); Maximum surge isolation voltage, 8000 V_{PK}	Reinforced insulation per CSA 60950-1-07+A1+A2 and IEC 60950-1 2nd Ed., 800 V_{RMS} (DW package) and 1450 V_{RMS} (DWW package) max working voltage (pollution degree 2, material group I); 2 MOPP (Means of Patient Protection) per CSA 60601-1:14 and IEC 60601-1 Ed. 3.1, 250 V_{RMS} (354 V_{PK}) max working voltage (DW package)	Single protection, 5700 V_{RMS}	Reinforced Insulation, Altitude \leq 5000 m, Tropical Climate, 250 V_{RMS} maximum working voltage	5700 V_{RMS} Reinforced insulation per EN 61010-1:2010 (3rd Ed) up to working voltage of 600 V_{RMS} (DW package) and 1000 V_{RMS} (DWW package) 5700 V_{RMS} Reinforced insulation per EN 60950-1:2006/A11:2009/A1:2010/A12:2011/A2:2013 up to working voltage of 800 V_{RMS} (DW package) and 1450 V_{RMS} (DWW package)
Certification planned	Certification planned	Certification planned	Certification planned	Certification planned

6.8 Safety Limiting Values

Safety limiting intends to minimize potential damage to the isolation barrier upon failure of input or output circuitry. A failure of the I/O can allow low resistance to ground or the supply and, without current limiting, dissipate sufficient power to overheat the die and damage the isolation barrier potentially leading to secondary system failures.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
DW PACKAGE					
I_S Safety input, output, or supply current	$R_{\theta JA} = 82^\circ\text{C}/\text{W}$, $V_I = 5.5 \text{ V}$, $T_J = 150^\circ\text{C}$, $T_A = 25^\circ\text{C}$, see Figure 3		277		mA
	$R_{\theta JA} = 82^\circ\text{C}/\text{W}$, $V_I = 3.6 \text{ V}$, $T_J = 150^\circ\text{C}$, $T_A = 25^\circ\text{C}$, see Figure 3		423		
P_S Safety input, output, or total power	$R_{\theta JA} = 82^\circ\text{C}/\text{W}$, $T_J = 150^\circ\text{C}$, $T_A = 25^\circ\text{C}$, see Figure 5		1524		mW
T_S Maximum safety temperature			150		°C
DWW PACKAGE					
I_S Safety input, output, or supply current	$R_{\theta JA} = 84.6^\circ\text{C}/\text{W}$, $V_I = 5.5 \text{ V}$, $T_J = 150^\circ\text{C}$, $T_A = 25^\circ\text{C}$, see Figure 4		269		mA
	$R_{\theta JA} = 84.6^\circ\text{C}/\text{W}$, $V_I = 3.6 \text{ V}$, $T_J = 150^\circ\text{C}$, $T_A = 25^\circ\text{C}$, see Figure 4		410		
P_S Safety input, output, or total power	$R_{\theta JA} = 84.6^\circ\text{C}/\text{W}$, $T_J = 150^\circ\text{C}$, $T_A = 25^\circ\text{C}$, see Figure 6		1478		mW
T_S Maximum safety temperature			150		°C

The maximum safety temperature is the maximum junction temperature specified for the device. The power dissipation and junction-to-air thermal impedance of the device installed in the application hardware determines the junction temperature. The assumed junction-to-air thermal resistance in the [Thermal Information](#) is that of a device installed on a High-K test board for leaded surface-mount packages. The power is the recommended maximum input voltage times the current. The junction temperature is then the ambient temperature plus the power times the junction-to-air thermal resistance.

6.9 DC Electrical Characteristics

(over recommended operating conditions unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
GENERAL					
$I_{IN(EN)}$	Leakage Current on ENx pins Internal pullup on ENx pins		13	40	μA
$V_{CC+(UVLO)}$	Positive-going undervoltage-lockout (UVLO) threshold			2.25	V
$V_{CC-(UVLO)}$	Negative-going UVLO threshold		1.7		V
$V_{HYS(UVLO)}$	UVLO threshold hysteresis		0.2		V
$V_{EN(ON)}$	EN pin turn-on threshold			0.7 V_{CCx}	V
$V_{EN(OFF)}$	EN pin turn-off threshold		0.3 V_{CCx}		V
$V_{EN(HYS)}$	EN pin threshold hysteresis		0.1 V_{CCx}		V
CMTI	Common-mode transient immunity $V_I = V_{CC1}^{(1)}$ or 0 V; $V_{CM} = 1000$ V, see Figure 22	100	120		kV/ μs
LVDS TX					
$ V_{OD} $	TX DC output differential voltage $R_L = 100 \Omega$, see Figure 23	250	350	450	mV
ΔV_{OD}	Change in TX DC output differential between logic 1 and 0 states $R_L = 100 \Omega$, see Figure 23	-10	0	10	mV
V_{OC}	TX DC output common-mode voltage $R_L = 100 \Omega$, see Figure 23	1.125	1.2	1.375	V
ΔV_{OC}	TX DC common-mode voltage difference $R_L = 100 \Omega$, see Figure 23	-25	0	25	mV
I_{os}	TX output short circuit current through OUTx OUTx = 0			10	mA
	OUTxP = OUTxM			10	
I_{oz}	TX output current when in high impedance ENx = 0, OUTx from 0 to V_{CCx}	-5		5	μA
C_{OUT}	TX output pad capacitance on OUTx at 1 MHz DW package: ENx = 0, DC offset = $V_{CC} / 2$, Swing = 200 mV, Frequency (f) = 1 MHz		10		pF
			10		
LVDS RX					
V_{IC}	RX input common mode voltage $V_{CCx} \geq 3$ V	0.5 $ V_{ID} $	1.2	2.4 – 0.5 $ V_{ID} $	V
V_{IT1}	Positive going RX input differential threshold Across V_{IC}			50	mV
V_{IT2}	Negative going RX input differential threshold Across V_{IC}	-50			mV
I_{INx}	Input current on INx From 0 to V_{CC} (each input independently)		10	20	μA
$I_{INxP} - I_{INxM}$	Input current balance From 0 to V_{CC}	-6		6	μA
C_{IN}	RX input pad capacitance on INx at 1 MHz DW package: DC offset = 1.2 V, Swing = 200 mV, f = 1 MHz		6.6		pF
			7.5		

(1) V_{CC1} = Input-side V_{CCx} ; V_{CC0} = Output-side V_{CCx} .

6.10 DC Supply Current Characteristics

(over recommended operating conditions unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
I_{CC1} I_{CC2} Supply current side 1 and side 2	3 V < V_{CC1} , $V_{CC2} < 3.6$ V	EN1 = EN2 = 0, OUTx floating, $V_{ID} \geq 50$ mV	2.3	3.6	
		EN1 = EN2 = 0, OUTx floating, $V_{ID} \leq -50$ mV	3.5	5.6	
		EN1 = EN2 = 1, $R_L = 100\Omega$ differential, $V_{ID} \geq 50$ mV	6.2	9.9	
		EN1 = EN2 = 1, $R_L = 100\Omega$ differential, $V_{ID} \leq -50$ mV	7.5	12	
		EN1 = EN2 = 1, $R_L = 100\Omega$ differential, data communication at 50 Mbps	7.6	12.1	
		EN1 = EN2 = 1, $R_L = 100\Omega$ differential, data communication at 125 Mbps	8.5	13.6	
		EN1 = EN2 = 1, $R_L = 100\Omega$ differential, data communication at 150 Mbps	8.9	14.2	
	4.5 V < V_{CC1} , $V_{CC2} < 5.5$ V	EN1 = EN2 = 0, OUTx floating, $V_{ID} \geq 50$ mV	2.3	3.6	
		EN1 = EN2 = 0, OUTx floating, $V_{ID} \leq -50$ mV	3.6	5.7	
		EN1 = EN2 = 1, $R_L = 100\Omega$ differential, $V_{ID} \geq 50$ mV	6.6	10.5	
		EN1 = EN2 = 1, $R_L = 100\Omega$ differential, $V_{ID} \leq -50$ mV	7.9	12.6	
		EN1 = EN2 = 1, $R_L = 100\Omega$ differential, data communication at 50 Mbps	8.3	13.2	
		EN1 = EN2 = 1, $R_L = 100\Omega$ differential, data communication at 125 Mbps	9.7	15.5	
		EN1 = EN2 = 1, $R_L = 100\Omega$ differential, data communication at 150 Mbps	10.3	16.4	

6.11 Timing Requirements for Distortion Correction Scheme

Valid data = 8b10b like data with DC balance and bounded disparity. See [Figure 25](#).

		MIN	NOM	MAX	UNIT
t_{CALIB}	Time to complete internal calibration, after exiting idle state. LVDS TX output is held high during this time. During this time valid data must be presented at the receiver.	250		750	μs
t_{IDLE}	The minimum duration of any idle state that must be maintained between valid data transmissions.	10			μs
t_{IDLE_OUT}	After a channel enters idle state, the internal calibration loses lock after this time, and the LVDS outputs are gated high.	200		600	ns

6.12 Switching Characteristics

(over recommended operating conditions unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
LVDS CHANNEL					
t_{PLH} t_{PHL}	Propagation delay time		17	25	ns
$t_{sk(o)}$	Channel-to-channel output skew time	Opposite directional channels, same voltage and temperature		4.5	ns
$t_{sk(pp)}$	Part-part skew	Same directional channels, same voltage and temperature		4.5	ns
t_{CMset}	Common-mode setting time after EN = 0 to EN = 1 transition	Common-mode capacitive load = 100 pF to 0.5 nF		20	μs
Total eye closure		DC balanced data with maximum run length of 6 at 125 Mbps, RX V_{ID} = 350 mV _{PP} , 1 ns t_{rf} 10%-90%, −40 < T_A < 125°C, 3 V < V_{CC1} , V_{CC2} < 5 V		30%	
		DC balanced data with maximum run length of 6 at 150 Mbps, RX V_{ID} = 350 mV _{PP} , 1 ns t_{rf} 10%-90%, −40 < T_A < 125°C, 3 V < V_{CC1} , V_{CC2} < 5 V		40%	
t_{fs}	Default output delay time from input power loss	Measured from the time V_{CC} goes below 1.7 V, see Figure 21	0.2	9	μs
LVDS TX AND RX					
t_{rf}	TX differential rise and fall times (20% to 80%)	See Figure 19	300	780	1380
$\Delta V_{OC(pp)}$	TX common-mode voltage peak-to-peak at 100 Mbps		0	150	mV _{PP}
t_{PLZ} , t_{PHZ}	TX disable time—valid output to HiZ	See Figure 20	10	20	ns
t_{PZH}	TX enable time—HiZ to valid high output ⁽¹⁾	See Figure 20	10	20	ns
$ V_{ID} $	Magnitude of RX input differential voltage for valid operation	Driven with voltage sources on RX pins, see figures in the Parameter Measurement Information section	100	600	mV
$t_{rf(RX)}$	Allowed RX input differential rise and fall times (20% to 80%)	See Figure 24	1	$0.3 \times UI^{(2)}$	ns

(1) The t_{PLZ} parameter is not defined because of the distortion-correction scheme. See the [Distortion-Correction Scheme](#) section for more information.

(2) UI is the unit interval.

6.13 Insulation Characteristics Curves




Figure 1. Reinforced Isolation Capacitor Lifetime Projection for Devices in DW Package




Figure 2. Reinforced Isolation Capacitor Lifetime Projection for Devices in DWW Package




Figure 3. Thermal Derating Curve for Limiting Current for DW Package




Figure 4. Thermal Derating Curve for Limiting Current for DWW Package




Figure 5. Thermal Derating Curve for Limiting Power for DW Package




Figure 6. Thermal Derating Curve for Limiting Power for DWW Package

6.14 Typical Characteristics




Figure 7. Supply Current vs Data Rate (CH-A)




Figure 8. Supply Current vs Data Rate (CH-B)




Figure 9. Supply Current vs V_{CCx} Output Supply Voltage




Figure 10. Supply Current vs Temperature (CH-A)




Figure 11. Supply Current vs Temperature (CH-B)




Figure 12. Propagation Delay Time vs Temperature

Typical Characteristics (continued)




Figure 13. Propagation Delay Time vs V_{CCx} Output Supply Voltage




Figure 14. Output Voltage vs V_{CCx} Output Supply Voltage




Figure 15. Distortion Correction Scheme Calibration Time (t_{CALIB})




Figure 16. Transition From Valid Data to Idle (t_{IDLE_OUT})




Figure 17. Disable to Enable Time (t_{PZH})




Figure 18. Disable Time (t_{PLZ}, t_{PHZ})

7 Parameter Measurement Information




- A. The input pulse is supplied by a generator having the following characteristics: PRR \leq 50 kHz, 50% duty cycle, $t_r \leq 3$ ns, $t_f \leq 3$ ns, $Z_O = 50 \Omega$.
- B. $C_P = 5 \text{ pF}$ and includes instrumentation and fixture capacitance within $\pm 20\%$.

Figure 19. Switching Characteristics Test Circuit and Voltage Waveforms




- A. The input pulse is supplied by a generator having the following characteristics: PRR \leq 10 kHz, 50% duty cycle, $t_r \leq 3$ ns, $t_f \leq 3$ ns, $Z_O = 50 \Omega$.
- B. $C_L = 5 \text{ pF}$ and includes instrumentation and fixture capacitance within $\pm 20\%$.

Figure 20. Enable and Disable Propagation Delay Time Test Circuit and Waveform

Parameter Measurement Information (continued)


A. $C_L = 5 \text{ pF}$ and includes instrumentation and fixture capacitance within $\pm 20\%$.

Figure 21. Default Output Delay Time Test Circuit and Voltage Waveforms



A. $C_L = 5 \text{ pF}$ and includes instrumentation and fixture capacitance within $\pm 20\%$.

Figure 22. Common-Mode Transient Immunity Test Circuit





Figure 23. Driver Test Circuit

Parameter Measurement Information (continued)

Figure 24. Voltage Definitions and Waveforms

8 Detailed Description

8.1 Overview


The ISO7821LLS device is an isolated LVDS buffer. The differential signal received on the LVDS input pins is first converted to CMOS logic levels. It is then transmitted across a silicon dioxide based capacitive isolation barrier using an On-Off Keying (OOK) modulation scheme. A high frequency carrier transmitted across the barrier represents one logic state and an absence of a carrier represents the other logic state. On the other side of the barrier a demodulator converts the OOK signal back to logic levels, which is then converted to LVDS outputs by a differential driver. This device incorporates advanced circuit techniques to maximize CMTI performance and minimize radiated emissions.

The ISO7821LLS device implements an eye-diagram improvement scheme to correct for signal distortions that are introduced in the LVDS receiver as well as the isolation channel. This enables the device to guarantee an eye closure of less than 30% at 125 Mbps, and less than 40% at 150 Mbps. The distortion correction scheme is optimized for operation with DC balanced data (for example 8b10b or equivalent) with a maximum run length of 6. The minimum data-rate of operation is also constrained to 50 Mbps. For general purpose data communication from 0 to 100 Mbps, the ISO782xLL family of devices should be considered.

The ISO7821LLS device is TIA/EIA-644-A standard compliant. The LVDS transmitter drives a minimum differential-output voltage magnitude of 250 mV into a $100\text{-}\Omega$ load, and the LVDS receiver is capable of detecting differential signal ≥ 50 mV in magnitude. The device consumes 11 mA per channel at 150 Mbps with 5-V supplies.

The *Functional Block Diagram* section shows a conceptual block diagram of one channel of the ISO7821LLS device.

8.2 Functional Block Diagram



Copyright © 2016, Texas Instruments Incorporated

8.3 Feature Description

The ISO7821LLS device is available in a two-channel configuration with a default differential-high output state. [Table 1](#) lists the device features.

Table 1. Device Features


PART NUMBER	CHANNEL DIRECTION	RATED ISOLATION	MAXIMUM DATA RATE	DEFAULT DIFFERENTIAL OUTPUT
ISO7821LLS	1 Forward, 1 Reverse	5700 V _{RMS} / 8000 V _{PK} ⁽¹⁾	150 Mbps	High

(1) See the [Safety-Related Certifications](#) section for detailed isolation ratings.

8.3.1 Distortion-Correction Scheme

The ISO7821LLS device implements a distortion-correction scheme to correct for signal distortions that are introduced in the LVDS receiver as well as the isolation channel. This scheme is optimized for a DC-balanced data-stream with a maximum run length of 6. One example of such a data stream is 8b10b encoded data. The minimum data rate supported by the ISO7821LLS device is 50 Mbps and the maximum is 150 Mbps.

Figure 25 shows the timing requirements associated with the distortion correction scheme (see the [Timing Requirements for Distortion Correction Scheme](#) table for timing parameters). The input to the LVDS channel should be either idle low, idle high, or should have clock or DC-balanced data transitions at 25 MHz / 50 Mbps or higher. Low frequency or DC-unbalanced data is not allowed. The distortion-correction scheme runs an internal calibration each time the LVDS channel transitions from an idle state to a data transmission state. The calibration runs for a period of t_{CALIB} during which the LVDS channel output is held at logic high. This calibration is also run at power up. Lack of activity on the receive inputs for a period greater than t_{IDLE_OUT} takes the channel to an uncalibrated state. If the communication protocol requires the channel to transition to the idle state, the idle-high or idle-low state must be held for at least duration of t_{IDLE} .



- A. Signals shown are differential logic states.
Logic high $\rightarrow V_{IN+} > V_{IN-}$
Logic low $\rightarrow V_{IN-} > V_{IN+}$
- B. The data to ISOLVDS channel should be either idle high, idle low, clock, or valid data.
Valid data = 8b10b like data with DC balance and bounded disparity.
- C. When transitioning from an uncalibrated state to a calibrated state, the ISOLVDS channel output is gated high for up to t_{CALIB} , during which the channel is calibrated.
- D. If the channel finds no transitions in the incoming data for a period of t_{IDLE_OUT} , the channel goes to an uncalibrated state.
- E. Power loss (which implies no data transitions) takes the channel to an uncalibrated state.
- F. If, for some reason, the idle-high or idle-low state must be held on the line, this state must be held for at least t_{IDLE} .

Figure 25. DCD Correction Timing Diagram

8.4 Device Functional Modes

Table 2 lists the functional modes for the ISO7821LLS device.

Table 2. ISO7821LLS Function Table⁽¹⁾

V_{CCI}	V_{CCO}	INPUT ($INx\pm$) ⁽²⁾	OUTPUT ENABLE (ENx)	OUTPUT ($OUTx\pm$) ⁽³⁾	COMMENTS
PU	PU	H	H or open	H	Normal Operation: A channel output assumes the logic state of the input.
		L	H or open	L	
		I	H or open	H or L	
X	PU	X	L	Z	A low-logic state at the output enable causes the outputs to be in high impedance.
PD	PU	X	H or open	H	Default mode: When V_{CCI} is unpowered, a channel output assumes the logic high state. When V_{CCI} transitions from unpowered to powered up, a channel output assumes the logic state of the input. When V_{CCI} transitions from powered up to unpowered, a channel output assumes the selected default high state.
X	PD	X	X	Undetermined	When V_{CCO} is unpowered, a channel output is undetermined. When V_{CCO} transitions from unpowered to powered up, a channel output assumes the logic state of the input

(1) V_{CCI} = Input-side V_{CC} ; V_{CCO} = Output-side V_{CC} ; PU = Powered up ($V_{CCx} \geq 2.25$ V); PD = Powered down ($V_{CCx} \leq 1.7$ V); X = Irrelevant

(2) Input ($INx\pm$): H = high level ($V_{ID} \geq 50$ mV); L = low level ($V_{ID} \leq -50$ mV); I = indeterminate (-50 mV $< V_{ID} < 50$ mV)

(3) Output ($OUTx\pm$): H = high level ($V_{OD} \geq 250$ mV); L = low level ($V_{OD} \leq -250$ mV); Z = high impedance.

8.4.1 Device I/O Schematics




Figure 26. Device I/O Schematics

9 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

9.1 Application Information

The ISO7821LLS device is a high-performance, reinforced isolated dual-LVDS buffer. Isolation can be used to help achieve human and system safety, to overcome ground potential difference (GPD), or to improve noise immunity and system performance.

The LVDS signaling can be used over most interfaces to achieve higher data rates because the LVDS is only a physical layer. LVDS can also be used for a proprietary communication scheme implemented between a host controller and a slave. Example use cases include connecting a high-speed I/O module to a host controller, a subsystem connecting to a backplane, and connection between two high-speed subsystems. Many of these systems operate under harsh environments making them susceptible to electromagnetic interferences, voltage surges, electrical fast transients (EFT), and other disturbances. These systems must also meet strict limits on radiated emissions. Using isolation in combination with a robust low-noise signaling standard such as LVDS, achieves both high immunity to noise and low emissions.

Example end applications that could benefit from the ISO7821LLS device include high-voltage motor control, test and measurement, industrial automation, and medical equipment.


9.2 Typical Application

One application for isolated LVDS buffers is for point-to-point communication between two high-speed capable, application-specific integrated circuits (ASICs) or FPGAs. In a high-voltage motor control application, for example, Node 1 could be a controller on a low-voltage or earth referenced board, and Node 2, could be controller placed on the power board, biased to high voltage. [Figure 27](#) and [Figure 28](#) show the application schematics.

[Figure 28](#) provides further details of using the ISO7821LLS device to isolate the LVDS interface. The LVDS connection to the ISO7821LLS device can be traces on a board (shown as straight lines between Node 1 and the ISO7821LLS device), a twisted pair cable (as shown between Node 2 and the ISO7821LLS device), or any other controlled impedance channel. Differential 100- Ω terminations are placed near each LVDS receiver. The characteristic impedance of the channel should also be 100- Ω differential.


In the example shown in [Figure 27](#) and [Figure 28](#), the ISO7821LLS device provides reinforced or safety isolation between the high-voltage elements of the motor drive and the low-voltage control circuitry. This configuration also ensures reliable communication, regardless of the high conducted and radiated noise present in the system.

Typical Application (continued)



Copyright © 2016, Texas Instruments Incorporated

Figure 27. Isolated LVDS Interface in Motor Control Application



Copyright © 2016, Texas Instruments Incorporated

Figure 28. Isolated LVDS Interface Between Two Nodes (ASIC or FPGA)

Typical Application (continued)

9.2.1 Design Requirements

For the ISO7821LLS device, use the parameters listed in [Table 3](#).

Table 3. Design Parameters

PARAMETER	VALUE
Supply voltage range, V_{CC1} and V_{CC2}	3 V to 5.5 V
Receiver common-mode voltage range	$0.5 V_{ID} $ to $2.4 - 0.5 V_{ID} $
External termination resistance	100Ω
Interconnect differential characteristic impedance	100Ω
Signaling rate	50 to 150 Mbps
Decoupling capacitor from V_{CC1} and GND1	0.1 μ F
Decoupling capacitor from V_{CC2} and GND2	0.1 μ F

9.2.2 Detailed Design Procedure

The ISO7821LLS device has minimum requirements on external components for correct operation. External bypass capacitors (0.1 μ F) are required for both supplies (V_{CC1} and V_{CC2}). A termination resistor with a value of 100Ω is required between each differential input pair ($INx+$ and $INx-$), with the resistors placed as close to the device pins as possible. A differential termination resistor with a value of 100Ω is required on the far end for the LVDS transmitters. [Figure 29](#) shows these connections.




Figure 29. Typical ISO7821LLS Circuit Hook-Up

9.2.2.1 Electromagnetic Compatibility (EMC) Considerations

Many applications in harsh industrial environment are sensitive to disturbances such as electrostatic discharge (ESD), electrical fast transient (EFT), surge and electromagnetic emissions. These electromagnetic disturbances are regulated by international standards such as IEC 61000-4-x and CISPR 22. Although system-level performance and reliability depends, to a large extent, on the application board design and layout, the ISO7821LLS device incorporates many chip-level design improvements for overall system robustness. Some of these improvements include:

- Robust ESD protection cells for input and output signal pins and inter-chip bond pads.
- Low-resistance connectivity of ESD cells to supply and ground pins.
- Enhanced performance of high voltage isolation capacitor for better tolerance of ESD, EFT and surge events.
- Bigger on-chip decoupling capacitors to bypass undesirable high energy signals through a low impedance path.
- PMOS and NMOS devices isolated from each other by using guard rings to avoid triggering of parasitic SCRs.
- Reduced common mode currents across the isolation barrier by ensuring purely differential internal operation.

9.2.3 Application Curve

Figure 30 shows a typical eye diagram of the ISO7821LLS device which indicates low jitter and a wide-open eye at the maximum data rate of 150 Mbps.



Figure 30. Eye Diagram at 150 Mbps PRBS, 3.3 V and 25°C

10 Power Supply Recommendations

To help ensure reliable operation at data rates and supply voltages, a 0.1- μ F bypass capacitor is recommended at the input and output supply pins (V_{CC1} and V_{CC2}). The capacitors should be placed as close to the supply pins as possible. If only a single primary-side power supply is available in an application, isolated power can be generated for the secondary-side with the help of a transformer driver such as Texas Instruments' [SN6501](#) or [SN6505](#). For such applications, detailed power supply design and transformer selection recommendations are available in the following data sheets: [SN6501 Transformer Driver for Isolated Power Supplies](#) (SLLSEA0) and [SN6505 Low-Noise 1-A Transformer Drivers for Isolated Power Supplies](#) (SLLSEP9).

11 Layout

11.1 Layout Guidelines

A minimum of four layers is required to accomplish a low EMI PCB design (see [Figure 31](#)). Layer stacking should be in the following order (top-to-bottom): high-speed signal layer, ground plane, power plane and low-frequency signal layer.

- Routing the high-speed traces on the top layer avoids the use of vias (and the introduction of their inductances) and allows for clean interconnects between the isolator and the transmitter and receiver circuits of the data link.
- Placing a solid ground plane next to the high-speed signal layer establishes controlled impedance for transmission line interconnects and provides an excellent low-inductance path for the return current flow.
- Placing the power plane next to the ground plane creates additional high-frequency bypass capacitance of approximately 100 pF/in^2 .
- Routing the slower speed control signals on the bottom layer allows for greater flexibility as these signal links usually have margin to tolerate discontinuities such as vias.
- While routing differential traces on a board, TI recommends that the distance between two differential pairs be much higher (at least 2x) than the distance between the traces in a differential pair. This distance minimizes crosstalk between the two differential pairs.

If an additional supply voltage plane or signal layer is needed, add a second power or ground plane system to the stack to keep it symmetrical. This makes the stack mechanically stable and prevents it from warping. Also the power and ground plane of each power system can be placed closer together, thus increasing the high-frequency bypass capacitance significantly.

The ISO7821LLS device requires no special layout considerations to mitigate electromagnetic emissions.

For detailed layout recommendations, see the application note, [Digital Isolator Design Guide](#) (SLLA284).

11.1.1 PCB Material

For digital circuit boards operating at less than 150 Mbps (or rise and fall times higher than 1 ns) and trace lengths of up to 10 inches, use standard FR-4 UL94V-0 epoxy-glass as PCB material. This PCB is preferred over cheaper alternatives because of lower dielectric losses at high frequencies, less moisture absorption, greater strength and stiffness, and self-extinguishing flammability-characteristics.

11.2 Layout Example




Figure 31. Layout Example

12 器件和文档支持

12.1 文档支持

12.1.1 相关文档

相关文档如下：

- 《数字隔离器设计指南》（文献编号：SLLA284）
- 《ISO782xLLX 隔离式双 LVDS 缓冲器评估模块》（文献编号：SLLU240）
- 《隔离相关术语》（文献编号：SLLA353）
- 《LVDS 所有者手册》（文献编号：SNLA187）
- 《SN6501 适用于隔离式电源的变压器驱动器》（文献编号：SLLSEA0）
- 《SN6505 适用于隔离式电源的低噪声 1A 变压器驱动器》（文献编号：SLLSEP9）

12.2 接收文档更新通知

要接收文档更新通知，请访问 www.ti.com.cn 您器件对应的产品文件夹。点击右上角的提醒我 (*Alert me*) 注册后，即可每周定期收到已更改的产品信息。有关更改的详细信息，请查阅已修订文档的修订历史记录。

12.3 社区资源

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

TI E2E™ Online Community **TI's Engineer-to-Engineer (E2E) Community.** Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support **TI's Design Support** Quickly find helpful E2E forums along with design support tools and contact information for technical support.

12.4 商标

E2E is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

12.5 静电放电警告

 ESD 可能会损坏该集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理措施和安装程序，可能会损坏集成电路。

 ESD 的损坏小至导致微小的性能降级，大至整个器件故障。精密的集成电路可能更容易受到损坏，这是因为非常细微的参数更改都可能导致器件与其发布的规格不相符。

12.6 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

13 机械、封装和可订购信息

以下页中包括机械、封装和可订购信息。这些信息是针对指定器件可提供的最新数据。这些数据会在无通知且不对本文档进行修订的情况下发生改变。欲获得该数据表的浏览器版本，请查阅左侧的导航栏。

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
ISO7821LLSDW	Active	Production	SOIC (DW) 16	40 TUBE	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7821LLS
ISO7821LLSDW.A	Active	Production	SOIC (DW) 16	40 TUBE	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7821LLS
ISO7821LLSDWR	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7821LLS
ISO7821LLSDWR.A	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7821LLS
ISO7821LLSDWW	Active	Production	SOIC (DWW) 16	45 TUBE	Yes	NIPDAU	Level-3-260C-168 HR	-55 to 125	ISO7821LLS
ISO7821LLSDWW.A	Active	Production	SOIC (DWW) 16	45 TUBE	Yes	NIPDAU	Level-3-260C-168 HR	-55 to 125	ISO7821LLS
ISO7821LLSDWWWR	Active	Production	SOIC (DWW) 16	1000 LARGE T&R	Yes	NIPDAU	Level-3-260C-168 HR	-55 to 125	ISO7821LLS
ISO7821LLSDWWWR.A	Active	Production	SOIC (DWW) 16	1000 LARGE T&R	Yes	NIPDAU	Level-3-260C-168 HR	-55 to 125	ISO7821LLS

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.


⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.


Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION


A0	Dimension designed to accommodate the component width
B0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
ISO7821LLSDWR	SOIC	DW	16	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
ISO7821LLSDWWR	SOIC	DWW	16	1000	330.0	24.4	18.0	10.0	3.0	20.0	24.0	Q1

TAPE AND REEL BOX DIMENSIONS


*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
ISO7821LLSDWR	SOIC	DW	16	2000	350.0	350.0	43.0
ISO7821LLSDWWR	SOIC	DWW	16	1000	350.0	350.0	43.0

TUBE


*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (μ m)	B (mm)
ISO7821LLSDW	DW	SOIC	16	40	506.98	12.7	4826	6.6
ISO7821LLSDW.A	DW	SOIC	16	40	506.98	12.7	4826	6.6
ISO7821LLSDWW	DWW	SOIC	16	45	507	20	5000	9
ISO7821LLSDWW.A	DWW	SOIC	16	45	507	20	5000	9


PACKAGE OUTLINE

DWW0016A



SOIC - 2.65 mm max height

PLASTIC SMALL OUTLINE



NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0,15 mm per side.
4. This dimension does not include interlead flash.

EXAMPLE BOARD LAYOUT

DWW0016A


SOIC - 2.65 mm max height

PLASTIC SMALL OUTLINE




LAND PATTERN EXAMPLE

STANDARD SCALE:3X




LAND PATTERN EXAMPLE
PCB CLEARANCE & CREEPAGE OPTIMIZED
SCALE:3X

OPTION	DIM A	DIM B	DIM C
01	16.375	14.5	1.875
02	16.625	15	1.625
03	16.725	15.2	1.525



SOLDER MASK DETAILS



NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.
6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.


4221501/B 10/2024

EXAMPLE STENCIL DESIGN


DWW0016A

SOIC - 2.65 mm max height

PLASTIC SMALL OUTLINE



SOLDER PASTE EXAMPLE
STANDARD
BASED ON 0.125 mm THICK STENCIL
SCALE:4X



SOLDER PASTE EXAMPLE
PCB CLEARANCE & CREEPAGE OPTIMIZED
BASED ON 0.125 mm THICK STENCIL
SCALE:4X

OPTION	DIM A	DIM B	DIM C
01	16.375	14.5	1.875
02	16.625	15	1.625
03	16.725	15.2	1.525

4221501/B 10/2024

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

GENERIC PACKAGE VIEW


DW 16

SOIC - 2.65 mm max height


7.5 x 10.3, 1.27 mm pitch

SMALL OUTLINE INTEGRATED CIRCUIT

This image is a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.



4224780/A




PACKAGE OUTLINE

DW0016B

SOIC - 2.65 mm max height

SOIC



4221009/B 07/2016

NOTES:


1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.
5. Reference JEDEC registration MS-013.

EXAMPLE BOARD LAYOUT


DW0016B

SOIC - 2.65 mm max height

SOIC



LAND PATTERN EXAMPLE
SCALE:4X



4221009/B 07/2016

NOTES: (continued)


6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

DW0016B

SOIC - 2.65 mm max height

SOIC



4221009/B 07/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做出任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](#) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2026，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月