


# SN74LVT245B 3.3-V ABT OCTAL BUS TRANSCEIVER WITH 3-STATE OUTPUTS


SCES004H – JANUARY 1995 – REVISED SEPTEMBER 2003

- Supports Mixed-Mode Signal Operation (5-V Input and Output Voltages With 3.3-V  $V_{CC}$ )
- Supports Unregulated Battery Operation Down to 2.7 V
- Typical  $V_{OLP}$  (Output Ground Bounce)  $<0.8$  V at  $V_{CC} = 3.3$  V,  $T_A = 25^\circ\text{C}$
- $I_{off}$  and Power-Up 3-State Support Hot Insertion
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Protection Exceeds JESD 22
  - 2000-V Human-Body Model (A114-A)
  - 200-V Machine Model (A115-A)
  - 1000-V Charged-Device Model (C101)

DB, DW, NS, OR PW PACKAGE  
(TOP VIEW)



RGY PACKAGE  
(TOP VIEW)



## description/ordering information

This octal bus transceiver is designed specifically for low-voltage (3.3-V)  $V_{CC}$  operation, but with the capability to provide a TTL interface to a 5-V system environment.

The SN74LVT245B is designed for asynchronous communication between data buses. The device transmits data from the A bus to the B bus or from the B bus to the A bus, depending on the logic level at the direction-control (DIR) input. The output-enable ( $\overline{OE}$ ) input can be used to disable the device so the buses are effectively isolated.

## ORDERING INFORMATION

| $T_A$         | PACKAGE†              |               | ORDERABLE PART NUMBER | TOP-SIDE MARKING |
|---------------|-----------------------|---------------|-----------------------|------------------|
| –40°C to 85°C | QFN – RGY             | Tape and reel | SN74LVT245BRGYR       | LX245B           |
|               | SOIC – DW             | Tube          | SN74LVT245BDW         | LVT245B          |
|               |                       | Tape and reel | SN74LVT245BDWR        |                  |
|               | SOP – NS              | Tape and reel | SN74LVT245BNSR        | LVT245B          |
|               | SSOP – DB             | Tape and reel | SN74LVT245BDBR        | LX245B           |
|               | TSSOP – PW            | Tube          | SN74LVT245BPW         | LX245B           |
|               |                       | Tape and reel | SN74LVT245BPWR        |                  |
|               | VFBGA – GQN           | Tape and reel | SN74LVT245BGQNR       | LX245B           |
|               | VFBGA – ZQN (Pb-free) |               | SN74LVT245BZQNR       |                  |

† Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at [www.ti.com/sc/package](http://www.ti.com/sc/package).



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

**TEXAS  
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 2003, Texas Instruments Incorporated


# SN74LVT245B 3.3-V ABT OCTAL BUS TRANSCEIVER WITH 3-STATE OUTPUTS

SCES004H – JANUARY 1995 – REVISED SEPTEMBER 2003

## description/ordering information (continued)

To ensure the high-impedance state during power up or power down,  $\overline{OE}$  should be tied to  $V_{CC}$  through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

This device is fully specified for hot-insertion applications using  $I_{off}$  and power-up 3-state. The  $I_{off}$  circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down. The power-up 3-state circuitry places the outputs in the high-impedance state during power up and power down, which prevents driver conflict.




## terminal assignments

|   | 1   | 2   | 3        | 4               |
|---|-----|-----|----------|-----------------|
| A | A1  | DIR | $V_{CC}$ | $\overline{OE}$ |
| B | A3  | B2  | A2       | B1              |
| C | A5  | A4  | B4       | B3              |
| D | A7  | B6  | A6       | B5              |
| E | GND | A8  | B8       | B7              |

FUNCTION TABLE

| INPUTS          |     | OPERATION       |
|-----------------|-----|-----------------|
| $\overline{OE}$ | DIR |                 |
| L               | L   | B data to A bus |
| L               | H   | A data to B bus |
| H               | X   | Isolation       |

## logic diagram (positive logic)



Pin numbers shown are for the DB, DW, NS, PW, and RGY packages.

# SN74LVT245B

## 3.3-V ABT OCTAL BUS TRANSCEIVER

### WITH 3-STATE OUTPUTS

SCES004H – JANUARY 1995 – REVISED SEPTEMBER 2003

#### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>†</sup>

|                                                                                                  |                            |
|--------------------------------------------------------------------------------------------------|----------------------------|
| Supply voltage range, $V_{CC}$                                                                   | –0.5 V to 4.6 V            |
| Input voltage range, $V_I$ (see Note 1)                                                          | –0.5 V to 7 V              |
| Voltage range applied to any output in the high-impedance or power-off state, $V_O$ (see Note 1) | –0.5 V to 7 V              |
| Voltage range applied to any output in the high state, $V_O$ (see Note 1)                        | –0.5 V to $V_{CC} + 0.5$ V |
| Current into any output in the low state, $I_O$                                                  | 128 mA                     |
| Current into any output in the high state, $I_O$ (see Note 2)                                    | 64 mA                      |
| Input clamp current, $I_{IK}$ ( $V_I < 0$ )                                                      | –50 mA                     |
| Output clamp current, $I_{OK}$ ( $V_O < 0$ )                                                     | –50 mA                     |
| Package thermal impedance, $\theta_{JA}$ (see Note 3): DB package                                | 70°C/W                     |
| (see Note 3): DW package                                                                         | 58°C/W                     |
| (see Note 3): GQN/ZQN package                                                                    | 78°C/W                     |
| (see Note 3): NS package                                                                         | 60°C/W                     |
| (see Note 3): PW package                                                                         | 83°C/W                     |
| (see Note 4): RGY package                                                                        | 37°C/W                     |
| Storage temperature range, $T_{stg}$                                                             | –65°C to 150°C             |

<sup>†</sup> Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES:
1. The input and output negative-voltage ratings may be exceeded if the input and output clamp-current ratings are observed.
  2. This current flows only when the output is in the high state and  $V_O > V_{CC}$ .
  3. The package thermal impedance is calculated in accordance with JESD 51-7.
  4. The package thermal impedance is calculated in accordance with JESD 51-5.

#### recommended operating conditions (see Note 5)

|                     |                                    |                 | MIN | MAX | UNIT |
|---------------------|------------------------------------|-----------------|-----|-----|------|
| V <sub>CC</sub>     | Supply voltage                     |                 | 2.7 | 3.6 | V    |
| V <sub>IH</sub>     | High-level input voltage           |                 | 2   |     | V    |
| V <sub>IL</sub>     | Low-level input voltage            |                 |     | 0.8 | V    |
| V <sub>I</sub>      | Input voltage                      |                 |     | 5.5 | V    |
| I <sub>OH</sub>     | High-level output current          |                 |     | −32 | mA   |
| I <sub>OL</sub>     | Low-level output current           |                 |     | 64  | mA   |
| Δt/Δv               | Input transition rise or fall rate | Outputs enabled |     | 10  | ns/V |
| Δt/ΔV <sub>CC</sub> | Power-up ramp rate                 |                 | 200 |     | μs/V |
| T <sub>A</sub>      | Operating free-air temperature     |                 | −40 | 85  | °C   |

NOTE 5: All unused inputs of the device must be held at  $V_{CC}$  or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.



# SN74LVT245B

## 3.3-V ABT OCTAL BUS TRANSCEIVER

### WITH 3-STATE OUTPUTS

SCES004H – JANUARY 1995 – REVISED SEPTEMBER 2003

**electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)**

| PARAMETER            |                                                                          | TEST CONDITIONS                                                                                                           | MIN          | TYP† | MAX       | UNIT          |
|----------------------|--------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|--------------|------|-----------|---------------|
| $V_{IK}$             |                                                                          | $V_{CC} = 2.7\text{ V}$ ,<br>$I_I = -18\text{ mA}$                                                                        |              |      | -1.2      | V             |
| $V_{OH}$             |                                                                          | $V_{CC} = 2.7\text{ V to } 3.6\text{ V}$ ,<br>$I_{OH} = -100\text{ }\mu\text{A}$                                          | $V_{CC}-0.2$ |      |           | V             |
|                      |                                                                          | $V_{CC} = 2.7\text{ V}$ ,<br>$I_{OH} = -8\text{ mA}$                                                                      | 2.4          |      |           |               |
|                      |                                                                          | $V_{CC} = 3\text{ V}$ ,<br>$I_{OH} = -32\text{ mA}$                                                                       | 2            |      |           |               |
| $V_{OL}$             | $V_{CC} = 2.7\text{ V}$                                                  | $I_{OL} = 100\text{ }\mu\text{A}$                                                                                         |              |      | 0.2       | V             |
|                      |                                                                          | $I_{OL} = 24\text{ mA}$                                                                                                   |              |      | 0.5       |               |
|                      | $V_{CC} = 3\text{ V}$                                                    | $I_{OL} = 16\text{ mA}$                                                                                                   |              |      | 0.4       |               |
|                      |                                                                          | $I_{OL} = 32\text{ mA}$                                                                                                   |              |      | 0.5       |               |
|                      |                                                                          | $I_{OL} = 64\text{ mA}$                                                                                                   |              |      | 0.55      |               |
| $I_I$                | Control inputs                                                           | $V_{CC} = 3.6\text{ V}$ ,<br>$V_I = V_{CC}\text{ or GND}$                                                                 |              |      | $\pm 1$   | $\mu\text{A}$ |
|                      |                                                                          | $V_{CC} = 0\text{ or } 3.6\text{ V}$ ,<br>$V_I = 5.5\text{ V}$                                                            |              |      | 10        |               |
|                      | A or B ports‡                                                            | $V_{CC} = 3.6\text{ V}$ ,<br>$V_I = 5.5\text{ V}$                                                                         |              |      | 20        |               |
|                      |                                                                          | $V_{CC} = 3.6\text{ V}$ ,<br>$V_I = V_{CC}$                                                                               |              |      | 1         |               |
|                      |                                                                          | $V_{CC} = 3.6\text{ V}$ ,<br>$V_I = 0$                                                                                    |              |      | -5        |               |
| $I_{off}$            |                                                                          | $V_{CC} = 0$ ,<br>$V_I\text{ or } V_O = 0\text{ to } 4.5\text{ V}$                                                        |              |      | $\pm 100$ | $\mu\text{A}$ |
| $I_{OZH}$            |                                                                          | $V_{CC} = 3.6\text{ V}$ ,<br>$V_O = 3\text{ V}$                                                                           |              |      | 5         | $\mu\text{A}$ |
| $I_{OZL}$            |                                                                          | $V_{CC} = 3.6\text{ V}$ ,<br>$V_O = 0.5\text{ V}$                                                                         |              |      | -5        | $\mu\text{A}$ |
| $I_{OZPU}$           |                                                                          | $V_{CC} = 0\text{ to } 1.5\text{ V}$ , $V_O = 0.5\text{ V to } 3\text{ V}$ , $\overline{OE} = \text{don't care}$          |              |      | $\pm 100$ | $\mu\text{A}$ |
| $I_{OZPD}$           |                                                                          | $V_{CC} = 1.5\text{ V to } 0$ , $V_O = 0.5\text{ V to } 3\text{ V}$ , $\overline{OE} = \text{don't care}$                 |              |      | $\pm 100$ | $\mu\text{A}$ |
| $I_{CC}$             | $V_{CC} = 3.6\text{ V}$ ,<br>$I_O = 0$ ,<br>$V_I = V_{CC}\text{ or GND}$ | Outputs high                                                                                                              |              |      | 0.19      | mA            |
|                      |                                                                          | Outputs low                                                                                                               |              |      | 5         |               |
|                      |                                                                          | Outputs disabled                                                                                                          |              |      | 0.19      |               |
| $\Delta I_{CC}^{\S}$ |                                                                          | $V_{CC} = 3\text{ V to } 3.6\text{ V}$ , One input at $V_{CC} - 0.6\text{ V}$ ,<br>Other inputs at $V_{CC}\text{ or GND}$ |              |      | 0.2       | mA            |
| $C_i$                |                                                                          | $V_I = 3\text{ V or } 0$                                                                                                  |              | 4    |           | pF            |
| $C_{io}$             |                                                                          | $V_O = 3\text{ V or } 0$                                                                                                  |              | 9    |           | pF            |

† All typical values are at  $V_{CC} = 3.3\text{ V}$ ,  $T_A = 25^\circ\text{C}$ .

‡ Unused terminals are at  $V_{CC}\text{ or GND}$ .

§ This is the increase in supply current for each input that is at the specified TTL-voltage level, rather than  $V_{CC}\text{ or GND}$ .

**switching characteristics over recommended operating free-air temperature range,  $C_L = 50\text{ pF}$  (unless otherwise noted) (see Figure 1)**

| PARAMETER | FROM (INPUT)    | TO (OUTPUT) | $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$ |      |     | $V_{CC} = 2.7\text{ V}$ |     | UNIT |
|-----------|-----------------|-------------|------------------------------------------|------|-----|-------------------------|-----|------|
|           |                 |             | MIN                                      | TYP† | MAX | MIN                     | MAX |      |
| $t_{PLH}$ | A or B          | B or A      | 1.2                                      | 2.3  | 3.5 | 4                       |     | ns   |
| $t_{PHL}$ |                 |             | 1.2                                      | 2.1  | 3.5 | 4                       |     |      |
| $t_{PZH}$ | $\overline{OE}$ | A or B      | 1.3                                      | 3.2  | 5.5 | 7.1                     |     | ns   |
| $t_{PZL}$ |                 |             | 1.7                                      | 3.4  | 5.5 | 6.5                     |     |      |
| $t_{PHZ}$ | $\overline{OE}$ | A or B      | 2.2                                      | 3.5  | 5.9 | 6.5                     |     | ns   |
| $t_{PLZ}$ |                 |             | 2.2                                      | 3.4  | 5   | 5.1                     |     |      |

† All typical values are at  $V_{CC} = 3.3\text{ V}$ ,  $T_A = 25^\circ\text{C}$ .



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265


# SN74LVT245B

## 3.3-V ABT OCTAL BUS TRANSCEIVER


### WITH 3-STATE OUTPUTS

SCES004H – JANUARY 1995 – REVISED SEPTEMBER 2003


#### PARAMETER MEASUREMENT INFORMATION




LOAD CIRCUIT




VOLTAGE WAVEFORMS  
PULSE DURATION



VOLTAGE WAVEFORMS  
SETUP AND HOLD TIMES



VOLTAGE WAVEFORMS  
PROPAGATION DELAY TIMES  
INVERTING AND NONINVERTING OUTPUTS



VOLTAGE WAVEFORMS  
ENABLE AND DISABLE TIMES  
LOW- AND HIGH-LEVEL ENABLING

- NOTES:
- A.  $C_L$  includes probe and jig capacitance.
  - B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
  - C. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 10 \text{ MHz}$ ,  $Z_O = 50 \Omega$ ,  $t_r \leq 2.5 \text{ ns}$ ,  $t_f \leq 2.5 \text{ ns}$ .
  - D. The outputs are measured one at a time with one transition per measurement.
  - E. All parameters and waveforms are not applicable to all devices.

Figure 1. Load Circuit and Voltage Waveforms

## PACKAGING INFORMATION

| Orderable part number           | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|---------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">SN74LVT245BDBR</a>  | Active        | Production           | SSOP (DB)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LX245B              |
| SN74LVT245BDBR.B                | Active        | Production           | SSOP (DB)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LX245B              |
| SN74LVT245BDBRG4                | Active        | Production           | SSOP (DB)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LX245B              |
| SN74LVT245BDBRG4.B              | Active        | Production           | SSOP (DB)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LX245B              |
| <a href="#">SN74LVT245BDW</a>   | Active        | Production           | SOIC (DW)   20  | 25   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LVT245B             |
| SN74LVT245BDW.B                 | Active        | Production           | SOIC (DW)   20  | 25   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LVT245B             |
| SN74LVT245BDWE4                 | Active        | Production           | SOIC (DW)   20  | 25   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LVT245B             |
| SN74LVT245BDWG4                 | Active        | Production           | SOIC (DW)   20  | 25   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LVT245B             |
| <a href="#">SN74LVT245BDWR</a>  | Active        | Production           | SOIC (DW)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LVT245B             |
| SN74LVT245BDWR.B                | Active        | Production           | SOIC (DW)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LVT245B             |
| SN74LVT245BDWRE4                | Active        | Production           | SOIC (DW)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LVT245B             |
| <a href="#">SN74LVT245BNSR</a>  | Active        | Production           | SOP (NS)   20   | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LVT245B             |
| SN74LVT245BNSR.B                | Active        | Production           | SOP (NS)   20   | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LVT245B             |
| SN74LVT245BNSRG4                | Active        | Production           | SOP (NS)   20   | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LVT245B             |
| SN74LVT245BNSRG4.B              | Active        | Production           | SOP (NS)   20   | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LVT245B             |
| <a href="#">SN74LVT245BPW</a>   | Active        | Production           | TSSOP (PW)   20 | 70   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LX245B              |
| SN74LVT245BPW.B                 | Active        | Production           | TSSOP (PW)   20 | 70   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LX245B              |
| SN74LVT245BPWG4                 | Active        | Production           | TSSOP (PW)   20 | 70   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LX245B              |
| <a href="#">SN74LVT245BPWR</a>  | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LX245B              |
| SN74LVT245BPWR.B                | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LX245B              |
| SN74LVT245BPWRE4                | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LX245B              |
| SN74LVT245BPWRG4                | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LX245B              |
| <a href="#">SN74LVT245BRGYR</a> | Active        | Production           | VQFN (RGY)   20 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | LX245B              |
| SN74LVT245BRGYR.B               | Active        | Production           | VQFN (RGY)   20 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | LX245B              |
| SN74LVT245BRGYRG4               | Active        | Production           | VQFN (RGY)   20 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | LX245B              |
| SN74LVT245BRGYRG4.B             | Active        | Production           | VQFN (RGY)   20 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | LX245B              |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

**(2) Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

**(3) RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

**(4) Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**(5) MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

**(6) Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device            | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74LVT245BDBR    | SSOP         | DB              | 20   | 2000 | 330.0              | 16.4               | 8.2     | 7.5     | 2.5     | 12.0    | 16.0   | Q1            |
| SN74LVT245BDBRG4  | SSOP         | DB              | 20   | 2000 | 330.0              | 16.4               | 8.2     | 7.5     | 2.5     | 12.0    | 16.0   | Q1            |
| SN74LVT245BDWR    | SOIC         | DW              | 20   | 2000 | 330.0              | 24.4               | 10.8    | 13.3    | 2.7     | 12.0    | 24.0   | Q1            |
| SN74LVT245BNSR    | SOP          | NS              | 20   | 2000 | 330.0              | 24.4               | 8.4     | 13.0    | 2.5     | 12.0    | 24.0   | Q1            |
| SN74LVT245BNSRG4  | SOP          | NS              | 20   | 2000 | 330.0              | 24.4               | 8.4     | 13.0    | 2.5     | 12.0    | 24.0   | Q1            |
| SN74LVT245BPWR    | TSSOP        | PW              | 20   | 2000 | 330.0              | 16.4               | 6.95    | 7.0     | 1.4     | 8.0     | 16.0   | Q1            |
| SN74LVT245BRGYR   | VQFN         | RGY             | 20   | 3000 | 330.0              | 12.4               | 3.71    | 4.71    | 1.1     | 8.0     | 12.0   | Q1            |
| SN74LVT245BRGYRG4 | VQFN         | RGY             | 20   | 3000 | 330.0              | 12.4               | 3.71    | 4.71    | 1.1     | 8.0     | 12.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS





\*All dimensions are nominal

| Device            | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74LVT245BDBR    | SSOP         | DB              | 20   | 2000 | 353.0       | 353.0      | 32.0        |
| SN74LVT245BDBRG4  | SSOP         | DB              | 20   | 2000 | 353.0       | 353.0      | 32.0        |
| SN74LVT245BDWR    | SOIC         | DW              | 20   | 2000 | 356.0       | 356.0      | 45.0        |
| SN74LVT245BNSR    | SOP          | NS              | 20   | 2000 | 356.0       | 356.0      | 45.0        |
| SN74LVT245BNSRG4  | SOP          | NS              | 20   | 2000 | 356.0       | 356.0      | 45.0        |
| SN74LVT245BPWR    | TSSOP        | PW              | 20   | 2000 | 353.0       | 353.0      | 32.0        |
| SN74LVT245BRGYR   | VQFN         | RGY             | 20   | 3000 | 353.0       | 353.0      | 32.0        |
| SN74LVT245BRGYRG4 | VQFN         | RGY             | 20   | 3000 | 353.0       | 353.0      | 32.0        |

**TUBE**


\*All dimensions are nominal

| Device          | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-----------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| SN74LVT245BDW   | DW           | SOIC         | 20   | 25  | 507    | 12.83  | 5080   | 6.6    |
| SN74LVT245BDW.B | DW           | SOIC         | 20   | 25  | 507    | 12.83  | 5080   | 6.6    |
| SN74LVT245BDWE4 | DW           | SOIC         | 20   | 25  | 507    | 12.83  | 5080   | 6.6    |
| SN74LVT245BDWG4 | DW           | SOIC         | 20   | 25  | 507    | 12.83  | 5080   | 6.6    |
| SN74LVT245BPW   | PW           | TSSOP        | 20   | 70  | 530    | 10.2   | 3600   | 3.5    |
| SN74LVT245BPW.B | PW           | TSSOP        | 20   | 70  | 530    | 10.2   | 3600   | 3.5    |
| SN74LVT245BPWG4 | PW           | TSSOP        | 20   | 70  | 530    | 10.2   | 3600   | 3.5    |



4214851/B 08/2019

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-150.

# EXAMPLE BOARD LAYOUT



DB0020A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



SOLDER MASK DETAILS

4214851/B 08/2019

NOTES: (continued)


6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

**DB0020A**

### SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4214851/B 08/2019

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

# MECHANICAL DATA

NS (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE PACKAGE

14-PINS SHOWN



- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

## GENERIC PACKAGE VIEW


**RGY 20**


**VQFN - 1 mm max height**

3.5 x 4.5, 0.5 mm pitch

PLASTIC QUAD FGLATPACK - NO LEAD

This image is a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.





4220724/A 05/2016


## NOTES:

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm per side.
5. Reference JEDEC registration MS-013.



**DW0020A**

### SOIC - 2.65 mm max height

SOIC



LAND PATTERN EXAMPLE  
SCALE:6X



## SOLDER MASK DETAILS

4220724/A 05/2016

NOTES: (continued)


6. Publication IPC-7351 may have alternate designs.  
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DW0020A

SOIC - 2.65 mm max height

SOIC



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:6X

4220724/A 05/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.



4220206/A 02/2017

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

# EXAMPLE BOARD LAYOUT


PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



4220206/A 02/2017

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4220206/A 02/2017

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025