



# 具有集成开关的 6A 降压稳压器

查询样品: [TPS53314](#)

## 特性

- 转换输入电压范围: **3 V 至 15 V**
- VDD** 输入电压范围: **4.5 V 至 25 V**
- 输出电压范围: **0.6 V 至 5.5 V**
- 5V LDO** 输出
- 具有 **6A** 连续输出电流的集成型功率 **MOSFET**
- <10 $\mu$ A 停机电流
- 用于提高轻负载效率的 **Auto-Skip Eco-mode<sup>TM</sup>**
- 具有快速瞬态响应的 **D-CAP<sup>TM</sup>** 模式
- 可利用一个外部电阻器在 **250 kHz** 至 **1 MHz** 的范围内选择开关频率
- 内置 **1%、0.6V** 基准
- 0.7-ms、1.4-ms、2.8-ms 和 5.6-ms** 可选内部电压伺服软启动
- 预充电启动能力
- 集成型升压开关
- 可通过外部电阻器来调节过流限值
- 过压/欠压、**UVLO** 和过热保护
- 支持全陶瓷输出电容器
- 漏极开路电源状态良好指示
- 采用 **PowerPAD<sup>TM</sup>** 的 **40 引脚 QFN** 封装

## 应用

- 服务器和台式计算机
- 笔记本电脑
- 电信设备


## 说明

TPS53314 是一款具有集成型 MOSFET 的 D-CAP<sup>TM</sup> 模式、6A 同步开关。该器件专为实现易用性、低外部组件数和小型封装电源系统而设计。

该器件具有单轨输入支持能力、一个 20-m $\Omega$  和一个 7.5-m $\Omega$  集成型 MOSFET、1% 准确度、0.6 V 基准以及集成型升压开关。部分具有竞争力的特性包括: > 96% 的最大效率、3 V 至 15 V 的宽输入电压范围、超低的外部组件数、用于实现超快瞬态响应的 D-CAP<sup>TM</sup> 模式控制、可选的自动跳跃和 PWM 操作方式、内部软启动控制、可调频率且无需补偿。

转换输入电压范围为 3 V 至 15 V，电源电压范围为 4.5 V 至 25 V，而输出电压范围则为 0.6 V 至 5.5 V。

TPS53314 采用 5 mm × 7 mm 40 引脚 QFN 封装，并具有 –40°C 至 85°C 的规定温度范围。



UDG-11138



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

Eco-mode, D-CAP, PowerPAD are trademarks of Texas Instruments.



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

### ORDERING INFORMATION<sup>(1)</sup>

T <sub>A</sub>	PACKAGE	ORDERING NUMBER	PINS	TRANSPORT MEDIA	MINIMUM QUANTITY	ECO PLAN
–40°C to 85°C	Plastic QFN (RGF)	TPS53314RGFR	40	Tape and reel	3000	Green (RoHS and no Pb/Br)
		TPS53314RGFT	40	Mini reel	250	

(1) For the most current package and ordering information, see the *Package Option Addendum* at the end of this document, or see the TI web site at [www.ti.com](http://www.ti.com).

### ABSOLUTE MAXIMUM RATINGS<sup>(1)</sup>

		VALUE	UNIT
Input voltage range	VIN (main supply)	–0.3 to 17	V
	VDD	–0.3 to 28	
	VBST	–0.3 to 24	
	VBST (with respect to LL)	–0.3 to 7	
	EN, TRIP, VFB, RF, MODE	–0.3 to 7	
Output voltage range	LL	DC Pulse < 20 ns, E = 5 μJ	V
	PGOOD, VREG	–1 to 23	
	PGND	–7	
	VBST	–0.3 to 7	
Source/Sink Current		50	mA
Operating free-air temperature, T <sub>A</sub>		–40 to 85	°C
Storage temperature range, T <sub>stg</sub>		–55 to 150	°C
Junction temperature range, T <sub>J</sub>		–40 to 150	°C
Lead temperature 1.6 mm (1/16 inch) from case for 10 seconds		300	°C

(1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

### THERMAL INFORMATION

THERMAL METRIC <sup>(1)</sup>		TPS53314	UNITS
		RGF(40 PINS)	
θ <sub>JA</sub>	Junction-to-ambient thermal resistance	35.8	°C/W
θ <sub>JCtop</sub>	Junction-to-case (top) thermal resistance	23.8	
θ <sub>JB</sub>	Junction-to-board thermal resistance	10.1	
Ψ <sub>JT</sub>	Junction-to-top characterization parameter	0.4	
Ψ <sub>JB</sub>	Junction-to-board characterization parameter	10.0	
θ <sub>JCbot</sub>	Junction-to-case (bottom) thermal resistance	2.8	

(1) For more information about traditional and new thermal metrics, see the *IC Package Thermal Metrics* application report, [SPRA953](http://www.ti.com).

**RECOMMENDED OPERATING CONDITIONS**

		VALUE	UNIT
Input voltage range	VIN (main supply)	3 to 15	V
	VDD	4.5 to 25	
	VBST	4.5 to 21	
	VBST (with respect to LL)	4.5 to 6.5	
Output voltage range	EN, TRIP, VFB, RF, MODE	-0.1 to 6.5	V
	LL	-0.8 to 15	
Source/Sink Current	PGOOD, VREG	-0.1 to 6.5	mA
	VBST	50	
Junction temperature range, $T_J$		-40 to 125	°C

## ELECTRICAL CHARACTERISTICS

Over recommended free-air temperature range, VDD = 12 V (Unless otherwise noted)

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNIT		
<b>SUPPLY VOLTAGE AND SUPPLY CURRENT</b>							
V <sub>VIN</sub>	VIN pin power conversion input voltage	3	15	15	V		
V <sub>DD</sub>	Supply input voltage	4.5	25	25	V		
I <sub>VIN(leak)</sub>	VIN pin leakage current	V <sub>EN</sub> = 0 V		1	μA		
I <sub>VDD</sub>	VDD supply current	VDD current, T <sub>A</sub> = 25°C, No Load, V <sub>EN</sub> = 5 V, V <sub>VFB</sub> = 0.630 V	420	590	μA		
I <sub>VDDSDN</sub>	VDD shutdown current	VDD current, T <sub>A</sub> = 25°C, No Load, V <sub>EN</sub> = 0 V		10	μA		
<b>INTERNAL REFERENCE VOLTAGE</b>							
V <sub>VFB</sub>	VFB voltage, CCM condition <sup>(1)</sup>	0.6000			V		
	T <sub>A</sub> = 25°C	0.597	0.600	0.603	V		
	T <sub>A</sub> = 0°C to 85°C	0.5952	0.600	0.6048			
	T <sub>A</sub> = -40°C to 85°C	0.594	0.600	0.606			
I <sub>VFB</sub>	VFB input current	V <sub>VFB</sub> = 0.630 V, T <sub>A</sub> = 25°C	0.002	0.2	μA		
<b>LDO OUTPUT</b>							
V <sub>VREG</sub>	LDO output voltage	0 mA ≤ I <sub>VREG</sub> ≤ 30 mA	4.77	5.0	5.35	V	
I <sub>VREG</sub>	LDO output current <sup>(1)</sup>	30			mA		
V <sub>DO</sub>	LDO drop out voltage	V <sub>DD</sub> = 4.5 V, I <sub>VREG</sub> = 30 mA		295	mV		
<b>BOOT STRAP SWITCH</b>							
V <sub>FBST</sub>	Forward voltage	V <sub>VREG-VBST</sub> , I <sub>F</sub> = 10 mA, T <sub>A</sub> = 25°C	0.1	0.2	V		
I <sub>VBSTLK</sub>	VBST leakage current	V <sub>VBST</sub> = 23 V, V <sub>LL</sub> = 17 V, T <sub>A</sub> = 25°C	0.01	1.5	μA		
<b>DUTY AND FREQUENCY CONTROL</b>							
t <sub>OFF(min)</sub>	Minimum off time	T <sub>A</sub> = 25°C	150	260	400	ns	
t <sub>ON(min)</sub>	Minimum on time	V <sub>VIN</sub> = 17 V, V <sub>OUT</sub> = 0.6 V, R <sub>RF</sub> = 0 Ω to V <sub>REG</sub> , T <sub>A</sub> = 25°C <sup>(1)</sup>		35			
<b>SOFTSTART</b>							
t <sub>SS</sub>	Internal SS time from V <sub>OUT</sub> = 0 to V <sub>OUT</sub> = 95%	R <sub>MODE</sub> = 39 kΩ	0.7			ms	
		R <sub>MODE</sub> = 100 kΩ	1.4				
		R <sub>MODE</sub> = 200 kΩ	2.8				
		R <sub>MODE</sub> = 470 kΩ	5.6				
<b>POWERGOOD</b>							
V <sub>THPG</sub>	PG threshold	PG in from lower	92.5%	96%	98.5%		
		PG in from higher	107.5%	110%	112.5%		
		PG hysteresis	2.5%	5%	7.8%		
R <sub>PG</sub>	PG transistor on-resistance		15	30	55	Ω	
t <sub>PGDEL</sub>	PG Delay after soft-start		0.8	1	1.2	ms	

(1) Ensured by design. Not production tested.

## ELECTRICAL CHARACTERISTICS


Over recommended free-air temperature range, VDD = 12 V (Unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
<b>LOGIC THRESHOLD AND SETTING CONDITIONS</b>						
V <sub>EN</sub>	EN voltage threshold	Enable	1.8			V
		Disable		0.6		
I <sub>EN</sub>	EN input current	V <sub>EN</sub> = 5 V		1.0		μA
f <sub>sw</sub>	Switching frequency	R <sub>RF</sub> = 0 Ω to GND, T <sub>A</sub> = 25°C <sup>(1)</sup>	200	250	300	kHz
		R <sub>RF</sub> = 187 kΩ to GND, T <sub>A</sub> = 25°C <sup>(1)</sup>	250	300	350	
		R <sub>RF</sub> = 619 kΩ to GND, T <sub>A</sub> = 25°C <sup>(1)</sup>	350	400	450	
		R <sub>RF</sub> = Open, T <sub>A</sub> = 25°C <sup>(1)</sup>	450	500	550	
		R <sub>RF</sub> = 866 kΩ to VREG, T <sub>A</sub> = 25°C <sup>(1)</sup>	580	650	720	
		R <sub>RF</sub> = 309 kΩ to VREG, T <sub>A</sub> = 25°C <sup>(1)</sup>	670	750	820	
		R <sub>RF</sub> = 124 kΩ to VREG, T <sub>A</sub> = 25°C <sup>(1)</sup>	770	850	930	
		R <sub>RF</sub> = 0 Ω to VREG, T <sub>A</sub> = 25°C <sup>(1)</sup>	880	970	1070	
<b>PROTECTION: CURRENT SENSE</b>						
I <sub>TRIP</sub>	TRIP source current	V <sub>TRIP</sub> = 1 V, T <sub>A</sub> = 25°C	9.4	10.0	10.6	μA
T <sub>C</sub> <sub>I</sub> <sub>TRIP</sub>	TRIP current temperature coefficient	On the basis of 25°C <sup>(2)</sup>		4700		ppm/°C
V <sub>TRIP</sub>	Current limit threshold setting range	V <sub>TRIP</sub> -GND voltage	0.2	0.6		V
V <sub>OCL</sub>	Current limit threshold	V <sub>TRIP</sub> = 0.6 V	67	75	83	mV
		V <sub>TRIP</sub> = 0.2	19	26	33	
V <sub>OCLN</sub>	Negative current limit threshold	V <sub>TRIP</sub> = 0.6 V	-83	-75	-67	
		V <sub>TRIP</sub> = 0.2 V	-33	-26	-19	
V <sub>AZCADJ</sub>	Auto zero cross adjustable range	Positive	3	15		mV
		Negative		-15	-3	
<b>PROTECTION: UVP and OVP</b>						
V <sub>OVP</sub>	OVP trip threshold	OVP detect	115%	120%	125%	
t <sub>OVPDEL</sub>	OVP propagation delay time	VFB delay with 50-mV overdrive		1		μs
V <sub>UVP</sub>	Output UVP trip threshold time	UVP detect	65%	70%	75%	
t <sub>UVPDEL</sub>	Output UVP propagation delay time		0.8	1	1.2	ms
t <sub>UVPEN</sub>	Output UVP enable delay time	from EN to UVP workable, R <sub>MODE</sub> = 39 kΩ	2.0	2.6	3.2	ms
<b>UVLO</b>						
V <sub>UVVREG</sub>	VREG UVLO threshold	Wake up	4.00	4.20	4.32	V
		Hysteresis		0.25		
<b>THERMAL SHUTDOWN</b>						
T <sub>SDN</sub>	Thermal shutdown threshold	Shutdown temperature <sup>(2)</sup>		145		°C
		Hysteresis <sup>(2)</sup>		10		

(1) Not production tested. Test condition is V<sub>IN</sub> = 12 V, V<sub>OUT</sub> = 1.1 V, I<sub>OUT</sub> = 5 A using application circuit shown in [图 33](#).

(2) Ensured by design. Not production tested.


## FUNCTIONAL BLOCK DIAGRAM



UDG-11139

## PIN CONFIGURATION

TPS53314  
RGF-40  
(TOP VIEW)



## PIN DESCRIPTIONS

PIN NAME	NO.	I/O/P <sup>(1)</sup>	DESCRIPTION
EN	36	I	Enable pin.
GND1	1	G	GND for controller
GND2	4	G	GND for half-bridge
LL	16 17 18 19 20 21 22 23 24 25 26 27 28	B	Output of converted power. Connect this pin to the output inductor.
MODE	39	I	Soft-start and skip/CCM selection. Connect a resistor to select soft-start time using <a href="#">Table 1</a> . The soft-start time is detected and stored into internal register during start-up.

(1) I=Input, O=Output, B=Bidirectional, P=Supply, G=Ground

## PIN DESCRIPTIONS (接下页)

PIN		I/O/P <sup>(1)</sup>	DESCRIPTION
NAME	NO.		
N/C	29		No connection
	31		
	33		
	34		
PGOOD	32	O	Open drain power good flag. Provides a 1-ms start up delay after the VFB pin voltage falls within specified limits. When the VFB pin voltage goes outside the specified limits, the PGOOD pin goes low after a 2- $\mu$ s delay.
PGND	2	G	Power GND
	5		
	6		
	7		
	8		
	9		
RF	10	I	Switching frequency selection. Connect a resistance to GND or VREG to select switching frequency using <a href="#">表 2</a> . The switching frequency is detected and stored during the startup.
	38		
TRIP	35	I	OCL detection threshold setting pin. 10 $\mu$ A at room temperature, 4700 ppm/ $^{\circ}$ C current is sourced and set the OCL trip voltage as follows. $V_{OCL} = V_{TRIP}/8$ ( $V_{TRIP} \leq 0.6$ V, $V_{OCL} \leq 75$ mV)
VBST	30	P	Supply input for high-side FET gate driver (boost terminal). Connect capacitor from this pin to LL-node. Internally connected to the VREG pin via bootstrap MOSFET switch.
VDD	40	P	Controller power supply input.
VFB	37	I	Output feedback input. Connect this pin to $V_{OUT}$ through a resistor divider.
VIN	11	P	Conversion power input.
	12		
	13		
	14		
	15		
VREG	3	P	5-V LDO output.
Pad	–	–	Package thermal pad. Use proper number of vias to connect to GND plane for heat dissipation.

### TYPICAL CHARACTERISTICS




图 1. VDD Supply Current vs. Temperature




图 2. VDD Shutdown Current vs. Temperature




图 3. OVP/UVP Trip Threshold vs. Temperature




图 4. Trip Pin Current vs. Temperature




图 5. Frequency vs. Temperature ( $f_{SET} = 300$  kHz)




图 6. Frequency vs. Temperature ( $f_{SET} = 500$  kHz)

## TYPICAL CHARACTERISTICS




图 7. Frequency vs. Temperature ( $f_{SET} = 750 \text{ kHz}$ )图 8. Frequency vs. Temperature ( $f_{SET} = 1 \text{ MHz}$ )

图 9. Switching Frequency vs. Output Voltage




图 10. Output Voltage vs. Output Current




图 11. Output Voltage vs. Input Voltage




图 12. Efficiency vs. Output Current


**TYPICAL CHARACTERISTICS**


图 13. Efficiency vs Output Current,  
Inductors: PCMC065T-1R0




图 14. Efficiency vs Output Current,  
Inductors: PCMC065T-1R0




图 15. Efficiency vs Output Current,  
Inductors:  $V_{OUT} \leq 3.3$  V: PCMC065T-1R0,  $V_{OUT} = 5$  V:  
PG0642.222




图 16. Efficiency vs Output Current,  
Inductors:  $V_{OUT} \leq 3.3$  V: PCMC065T-1R0,  $V_{OUT} = 5$  V:  
PG0642.222




图 17. Efficiency vs Output Current,  
Inductor: PCMC065T-1R0




图 18. Efficiency vs Output Current,  
Inductor: PCMC065T-1R0

## TYPICAL CHARACTERISTICS




图 19. Start-Up




图 20. Pre-Bias Start-Up




图 21. Turn-Off




图 22. UVLO Start-Up

### TYPICAL CHARACTERISTICS




图 23. 1.1-V Output FCCM Steady-State Operation




图 24. 1.1-V Output Skip Mode Steady-State Operation




图 25. CCM to DCM Transition




图 26. DCM to CCM Transition

## TYPICAL CHARACTERISTICS




图 27. FCCM Load Transient




图 28. Skip Mode Load Transient




图 29. Overcurrent Protection




图 30. Over-temperature Protection

## TYPICAL CHARACTERISTICS

图 31, shows the thermal signature of the TPS53314 EVM,  $V_{IN} = 12$  V,  $V_{OUT} = 1.1$  V,  $I_{OUT} = 6$  A,  $f_{SW} = 500$  kHz at room temperature with no airflow.

图 32 shows the thermal signature of the TPS53314 EVM,  $V_{IN} = 12$  V,  $V_{OUT} = 3.3$  V,  $I_{OUT} = 6$  A,  $f_{SW} = 650$  kHz at room temperature with no airflow.




图 31. Thermal Signature of TPS53314 EVM,  
 $f_{SW} = 500$  kHz




图 32. Thermal Signature of TPS53314 EVM,  
 $f_{SW} = 650$  kHz

## APPLICATION INFORMATION

## APPLICATION CIRCUIT DIAGRAM




图 33. Typical Application Circuit Diagram




图 34. Typical Application Circuit Diagram with Ceramic Output Capacitors

## General Description

The TPS53314 is a high-efficiency, single channel, synchronous buck converter suitable for low output voltage point-of-load applications in computing and similar digital consumer applications. The device features proprietary D-CAP™ mode control combined with an adaptive on-time architecture. This combination is ideal for building modern low duty ratio, ultra-fast load step response DC-DC converters. The output voltage ranges from 0.6 V to 5.5 V. The conversion input voltage range is from 3 V up to 15 V. The D-CAP™ mode uses the ESR of the output capacitor(s) to sense the device current. One advantage of this control scheme is that it does not require an external phase compensation network. This allows a simple design with a low external component count. Eight preset switching frequency values can be chosen using a resistor connected from the RF pin to ground or the VREG pin. Adaptive on-time control tracks the preset switching frequency over a wide input and output voltage range while allowing the switching frequency to increase at the step-up of the load.

The TPS53314 has a MODE pin to select between auto-skip mode and forced continuous conduction mode (FCCM) for light load conditions. The MODE pin also sets the selectable soft-start time ranging from 0.7 ms to 5.6 ms.

## Enable and Soft Start

When the EN pin voltage rises above the enable threshold voltage (typically 1.2 V), the controller enters its start-up sequence. The internal LDO regulator starts immediately and regulates to 5 V at the VREG pin. The controller then uses the first 250  $\mu$ s to calibrate the switching frequency setting resistance attached to the RF pin and stores the switching frequency code in internal registers. However, switching is inhibited during this phase. In the second phase, an internal DAC starts ramping up the reference voltage from 0 V to 0.6 V. Depending on the MODE pin setting, the ramping up time varies from 0.7 ms to 5.6 ms. Smooth and constant ramp-up of the output voltage is maintained during start-up regardless of load current.

表 1. Soft-Start and MODE

MODE SELECTION	ACTION	SOFT-START TIME (ms)	$R_{MODE}$ (k $\Omega$ )
Auto Skip	Pull down to GND	0.7	39
		1.4	100
		2.8	200
		5.6	475
Forced CCM <sup>(1)</sup>	Connect to PGOOD	0.7	39
		1.4	100
		2.8	200
		5.6	475

(1) The device transitions into FCCM after the PGOOD pin goes high.

## Adaptive On-Time D-CAP™ Control

The TPS53314 does not have a dedicated oscillator to determine switching frequency. However, the device operates with pseudo-constant frequency by feed-forwarding the input and output voltages into the on-time one-shot timer. The adaptive on-time control adjusts the on-time to be inversely proportional to the input voltage

$$t_{ON} \propto \frac{V_{OUT}}{V_{IN}}$$

and proportional to the output voltage


This makes the switching frequency fairly constant in steady state conditions over a wide input voltage range. The switching frequency is selectable from eight preset values by a resistor connected between the RF pin and GND or between the RF pin and the VREG pin as shown in [表 2](#). (Leaving the resistance open sets the switching frequency to 500 kHz.)

**表 2. Resistor and Switching Frequency**


RESISTOR ( $R_{RF}$ ) CONNECTIONS	SWITCHING FREQUENCY (kHz)
0 Ω to GND	250
187 kΩ to GND	300
619 kΩ to GND	400
Open	500
866 kΩ to VREG	600
309 kΩ to VREG	750
124 kΩ to VREG	850
0 Ω to VREG	970

The off-time is modulated by a PWM comparator. The VFB node voltage (the mid-point of resistor divider) is compared to the internal 0.6-V reference voltage added with a ramp signal. When the signal values match, the PWM comparator asserts a set signal to terminate the off-time (turn off the low-side MOSFET and turn on high-side MOSFET). The set signal is valid if the inductor current level is below the OCP threshold, otherwise the off-time is extended until the current level falls below the threshold.

[图 35](#) and [图 36](#) show two on-time control schemes.




**图 35. On-Time Control Without Ramp Compensation**



**图 36. On-Time Control With Ramp Compensation**

## Small Signal Model

From small-signal loop analysis, a buck converter using D-CAP™ mode can be simplified as shown in [图 37](#).



**图 37. Simplified Modulator Model**

The output voltage is compared with the internal reference voltage (ramp signal is ignored here for simplicity). The PWM comparator determines the timing to turn on the high-side MOSFET. The gain and speed of the comparator can be assumed high enough to keep the voltage at the beginning of each on-cycle substantially constant.

$$H(s) = \frac{1}{s \times ESR \times C_{OUT}} \quad (1)$$

For the loop stability, the 0 dB frequency,  $f_0$ , defined in [公式 2](#) must be lower than  $\frac{1}{4}$  of the switching frequency.

$$f_0 = \frac{1}{2\pi \times ESR \times C_{OUT}} \leq \frac{f_{SW}}{4} \quad (2)$$

According to [公式 2](#), the loop stability of D-CAP™ mode modulator is mainly determined by the capacitor chemistry. For example, specialty polymer capacitors (SP-CAP) have  $C_{OUT}$  on the order of several 100  $\mu$ F and ESR in range of 10 m $\Omega$ . These makes  $f_0$  on the order of 100 kHz or less and the loop is stable. However, ceramic capacitors have an  $f_0$  at more than 700 kHz, and need special care when used with this modulator. An application circuit using ceramic capacitors is described in [External Parts Selection](#) section under *All Ceramic Output Capacitors*.

## Ramp Signal

The TPS53314 adds a ramp signal to the 0.6-V reference in order to improve jitter performance. The feedback voltage is compared with the reference information to keep the output voltage in regulation. By adding a small ramp signal to the reference, the signal-to-noise ratio at the onset of a new switching cycle is improved. Therefore the operation becomes less jittery and more stable. The ramp signal is controlled to start with  $-7$  mV at the beginning of an on-cycle and becomes  $0$  mV at the end of an off-cycle in steady state.

## Auto-Skip Eco-mode™ Light Load Operation

While the MODE pin is pulled low via  $R_{MODE}$ , the TPS53314 automatically reduces the switching frequency at light-load conditions to maintain high efficiency. Detailed operation is described as follows. As the output current decreases from heavy load condition, the inductor current is also reduced and eventually comes to the point that its rippled valley touches zero level, which is the boundary between continuous conduction and discontinuous conduction modes. The synchronous MOSFET is turned off when this zero inductor current is detected. As the load current further decreases, the converter runs into discontinuous conduction mode (DCM). The on-time is maintained as it was in the continuous conduction mode so that it takes longer time to discharge the output capacitor with smaller load current to the level of the reference voltage. The transition point to the light-load operation  $I_{OUT(LL)}$  (i.e., the threshold between continuous and discontinuous conduction mode) can be calculated as shown in [公式 3](#).

$$I_{OUT(LL)} = \frac{1}{2 \times L \times f_{SW}} \times \frac{(V_{IN} - V_{OUT}) \times V_{OUT}}{V_{IN}}$$

where

- $f_{SW}$  is the PWM switching frequency (3)

Switching frequency versus output current in the light load condition is a function of  $L$ ,  $V_{IN}$  and  $V_{OUT}$ , but it decreases almost proportionally to the output current from the  $I_{OUT(LL)}$  given in [公式 3](#). For example, it is 60 kHz at  $I_{OUT(LL)}/5$  if the frequency setting is 300 kHz.

## Adaptive Zero Crossing

The TPS53314 has an adaptive zero crossing circuit which performs optimization of the zero inductor current detection at skip mode operation. This function pursues ideal low-side MOSFET turning off timing and compensates inherent offset voltage of the Z-C comparator and delay time of the Z-C detection circuit. It prevents SW-node swing-up caused by postponed detection and minimizes diode conduction period caused by premature detection. As a result, better light-load efficiency is delivered.

## Forced Continuous Conduction Mode

When the MODE pin is tied to PGOOD through a resistor, the controller keeps continuous conduction mode (CCM) during light-load conditions. In this mode, the switching frequency is maintained over the entire load range which is suitable for applications needing tight control of the switching frequency at a cost of lower efficiency.

## Power Good

The TPS53314 has powergood output that indicates high when switcher output is within the target. The powergood function is activated after soft-start has finished. If the output voltage becomes within +10% or -5% of the target value, internal comparators detect the powergood state and the powergood signal becomes high after a 1-ms internal delay. If the output voltage goes outside of +15% or -10% of the target value, the power-good signal becomes low after two microsecond (2-μs) internal delay. The powergood output is an open drain output and must be pulled up externally.

In order for the PGOOD logic to be valid, the VDD input must be higher than 1 V. To avoid invalid PGOOD logic before the TPS53314 is powered up, it is recommended the PGOOD be pull to VREG (either directly or through a resistor divider) because VREG remains low when the device is off.

## Current Sense and Overcurrent Protection

TPS53314 has cycle-by-cycle overcurrent limiting control. The inductor current is monitored during the *OFF* state and the controller maintains the *OFF* state during the period in that the inductor current is larger than the overcurrent trip level. In order to provide both good accuracy and cost effective solution, TPS53314 supports temperature compensated MOSFET  $R_{DS(on)}$  sensing. The TRIP pin should be connected to GND through the trip voltage setting resistor,  $R_{T_{TRIP}}$ . The TRIP pin sources  $I_{T_{TRIP}}$  current, which is 10  $\mu$ A typically at room temperature, and the trip level is set to the OCL trip voltage  $V_{T_{TRIP}}$  as shown in [公式 4](#).

$$V_{T_{TRIP}} (\text{mV}) = R_{T_{TRIP}} (\text{k}\Omega) \times I_{T_{TRIP}} (\mu\text{A}) \quad (4)$$

The inductor current is monitored by the voltage between the GND pin and the LL pin. The GND pin is used as positive current sensing node and the LL pin is used as negative current sensing node. The TRIP pin current,  $I_{T_{TRIP}}$ , has a 4700ppm/ $^{\circ}\text{C}$  temperature slope to compensate the temperature dependency of the  $R_{DS(on)}$ .

As the comparison is done during the *OFF* state,  $V_{T_{TRIP}}$  sets the valley level of the inductor current. Thus, the load current at the overcurrent threshold,  $I_{OCP}$ , can be calculated as shown in [公式 5](#).

$$I_{OCP} = \frac{V_{T_{TRIP}}}{(8 \times R_{DS(on)})} + \frac{I_{IND(\text{ripple})}}{2} = \frac{V_{T_{TRIP}}}{(8 \times R_{DS(on)})} + \frac{1}{2 \times L \times f_{SW}} \times \frac{(V_{IN} - V_{OUT}) \times V_{OUT}}{V_{IN}} \quad (5)$$

In an overcurrent condition, the current to the load exceeds the current to the output capacitor, therefore the output voltage tends to decrease. Eventually, it crosses the undervoltage protection threshold and shuts down. After a hiccup delay (16 ms with 0.7-ms soft-start), the controller restarts. If the overcurrent condition remains, the procedure is repeated and the device enters hiccup mode.

During CCM, the negative current limit (NCL) protects the internal FET from carrying too much current. The NCL detect threshold is set as the same absolute value as positive OCL but negative polarity. Note that the threshold continues to represent the valley value of the inductor current.

## Overvoltage and Undervoltage Protection

The TPS53314 monitors a resistor divided feedback voltage to detect overvoltage and undervoltage. When the feedback voltage becomes lower than 70% of the target voltage, the UVP comparator output goes high and an internal UVP delay counter begins counting. After 1 ms, TPS53314 latches OFF both high-side and low-side MOSFETs drivers. The controller restarts after a hiccup delay (16 ms with 0.7-ms soft-start). This function is enabled 1.5 ms after the soft-start is completed.

When the feedback voltage becomes higher than 120% of the target voltage, the OVP comparator output goes high and the circuit latches OFF the high-side MOSFET driver and latches ON the low-side MOSFET driver. The output voltage decreases. If the output voltage reaches the UV threshold, then both high-side MOSFET and low-side MOSFET driver is OFF and the device restarts after a hiccup delay. If the OV condition remains, both high-side MOSFET and low-side MOSFET driver remains OFF until the OV condition is removed.

## UVLO Protection

The TPS53314 uses VREG undervoltage lockout protection (UVLO). When the VREG voltage is lower than the UVLO threshold voltage, the switch mode power supply shuts off. This is a non-latch protection.

## Thermal Shutdown

TPS53314 includes a temperature monitoring feature. If the temperature exceeds the threshold value (typically 145 $^{\circ}\text{C}$ ), TPS53314 shuts off. When the temperature falls approximately 10 $^{\circ}\text{C}$  below the threshold value, the device turns on again. This is a non-latch protection.

## External Parts Selection

The external components selection is a simple process using D-CAP™ Mode.

### 1. CHOOSE THE INDUCTOR

The inductance value should be determined to give the ripple current of approximately 1/4 to 1/2 of maximum output current. Larger ripple current increases output ripple voltage and improves signal-to-noise ratio and helps stable operation.

$$L = \frac{1}{I_{IND(ripple)} \times f_{SW}} \times \frac{(V_{IN(max)} - V_{OUT}) \times V_{OUT}}{V_{IN(max)}} = \frac{3}{I_{OUT(max)} \times f_{SW}} \times \frac{(V_{IN(max)} - V_{OUT}) \times V_{OUT}}{V_{IN(max)}} \quad (6)$$

The inductor requires a low DCR to achieve good efficiency. It also requires enough room above peak inductor current before saturation. The peak inductor current can be estimated in [公式 7](#).

$$I_{IND(peak)} = \frac{V_{TRIP}}{8 \times R_{DS(on)}} + \frac{1}{L \times f_{SW}} \times \frac{(V_{IN(max)} - V_{OUT}) \times V_{OUT}}{V_{IN(max)}} \quad (7)$$

### 2. CHOOSE THE OUTPUT CAPACITOR(S)

When organic semiconductor capacitor(s) or specialty polymer capacitor(s) are used, for loop stability, capacitance and ESR should satisfy [公式 2](#). For jitter performance, [公式 8](#) is a good starting point to determine ESR.

$$ESR = \frac{V_{OUT} \times 10(mV) \times (1-D)}{0.6(V) \times I_{IND(ripple)}} = \frac{10(mV) \times L \times f_{SW}}{0.6(V)} = \frac{L \times f_{SW}}{60} (\Omega)$$

where

- D is the duty factor
- $t_{sw}$  is the switching period
- the required output ripple slope is approximately 10 mV per  $t_{sw}$  in terms of  $V_{VFB}$

### 3. DETERMINE THE VALUE OF R1 AND R2

The output voltage is programmed by the voltage-divider resistor, R1 and R2 shown in [图 37](#). R1 is connected between VFB pin and the output, and R2 is connected between the VFB pin and GND. Recommended R2 value is from 10kΩ to 20kΩ. Determine R1 using [公式 9](#).

$$R1 = \frac{V_{OUT} - \frac{I_{IND(ripple)} \times ESR}{2} - 0.6}{0.6} \times R2 \quad (9)$$

### 4. CHOOSE THE OVERCURRENT SETTING RESISTOR

The overcurrent setting resistor,  $R_{TRIP}$ , can be determined using [公式 10](#).

$$R_{TRIP}(k\Omega) = \frac{\left( I_{OCP} - \left( \frac{1}{2 \times L \times f_{SW}} \right) \times \frac{(V_{IN} - V_{OUT}) \times V_{OUT}}{V_{IN}} \right) \times 8 \times R_{DS(on)} (m\Omega)}{I_{TRIP} (\mu A)} \quad (10)$$

where

- $I_{TRIP}$  is the TRIP pin sourcing current (10 μA)
- $R_{DS(on)}$  is the on-resistance value of the low-side MOSFET (7.5 mΩ)

## External Component Selection with All Ceramic Output Capacitors

When ceramic output capacitors are used, the stability criteria in [公式 2](#) cannot be satisfied. The ripple injection approach as shown in [图 34](#) is implemented to increase the ripple on the VFB pin and make the system stable. C2 can be fixed at 1 nF. The value of C1 can be selected between 10 nF to 200 nF.

The increased ripple on the VFB pin causes the increase of the VFB DC value. The AC ripple coupled to the VFB pin has two components, one coupled from SW node and the other coupled from  $V_{OUT}$  and they can be calculated using [公式 11](#) and [公式 12](#).

$$V_{INJ\_SW} = \frac{V_{IN} - V_{OUT}}{R7 \times C1} \times \frac{D}{f_{SW}} \quad (11)$$

$$V_{INJ\_OUT} = ESR \times I_{IND(ripple)} + \frac{I_{IND(ripple)}}{8 \times C_{OUT} \times f_{SW}} \quad (12)$$

The DC value of VFB can be calculated by [公式 13](#):

$$V_{VFB} = 0.6 + \frac{V_{INJ\_SW} + V_{INJ\_OUT}}{2} \quad (13)$$

And the resistor divider value can be determined by [公式 14](#):

$$R1 = \frac{V_{OUT} - V_{FB}}{V_{FB}} \times R2 \quad (14)$$

## LAYOUT CONSIDERATIONS

Certain points must be considered before starting a layout work using the TPS53314.

- The power components (including input/output capacitors, inductor and TPS53314) should be placed on one side of the PCB (solder side). Other small signal components should be placed on another side (component side). At least one inner plane should be inserted, connected to ground, in order to shield and isolate the small signal traces from noisy power lines.
- All sensitive analog traces and components such as VFB, PGOOD, TRIP, MODE and RF should be placed away from high-voltage switching nodes such as LL, VBST to avoid coupling. Use internal layer(s) as ground plane(s) and shield feedback trace from power traces and components.
- Place the VIN decoupling capacitors as close to the VIN and PGND pins as possible to minimize the input AC current loop.
- Since the TPS53314 controls output voltage referring to voltage across the  $V_{OUT}$  capacitor, the top-side resistor of the voltage divider should be connected to the positive node of  $V_{OUT}$  capacitor. In a same manner both bottom side resistor and GND pad of the device should be connected to the negative node of  $V_{OUT}$  capacitor. The trace from these resistors to the VFB pin should be short and thin. Place on the component side and avoid via(s) between these resistors and the device.
- Connect the overcurrent setting resistors from TRIP pin to ground and make the connections as close as possible to the device. The trace from TRIP pin to resistor and from resistor to ground should avoid coupling to a high-voltage switching node.
- Connect the frequency setting resistor from RF pin to ground, or to the VREG pin, and make the connections as close as possible to the device. The trace from the RF pin to the resistor and from the resistor to ground should avoid coupling to a high-voltage switching node.
- Connect the MODE setting resistor from MODE pin to ground, or to the PGOOD pin, and make the connections as close as possible to the device. The trace from the MODE pin to the resistor and from the resistor to ground should avoid coupling to a high-voltage switching node.
- The PCB trace defined as switch node, which connects the LL pins and high-voltage side of the inductor, should be as short and wide as possible.
- Connect the ripple injection  $V_{OUT}$  signal ( $V_{OUT}$  side of the C1 capacitor in [图 34](#)) from the terminal of ceramic output capacitor. The AC coupling capacitor (C2 in [图 34](#)) should be placed near the device and R7 and C1 can be placed near the power stage.

**PACKAGING INFORMATION**

Orderable part number	Status (1)	Material type (2)	Package   Pins	Package qty   Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TPS53314RGFR	Active	Production	VQFN (RGF)   40	3000   LARGE T&R	Yes	Call TI   Nipdau	Level-2-260C-1 YEAR	-40 to 85	TPS 53314
TPS53314RGFR.A	Active	Production	VQFN (RGF)   40	3000   LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	TPS 53314
TPS53314RGFT	Active	Production	VQFN (RGF)   40	250   SMALL T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	TPS 53314
TPS53314RGFT.A	Active	Production	VQFN (RGF)   40	250   SMALL T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	TPS 53314
TPS53314RGFTG4	Active	Production	VQFN (RGF)   40	250   SMALL T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	TPS 53314
TPS53314RGFTG4.A	Active	Production	VQFN (RGF)   40	250   SMALL T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	TPS 53314

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

---

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## GENERIC PACKAGE VIEW


**RGF 40**

**VQFN - 1 mm max height**

**5 x 7, 0.5 mm pitch**

**PLASTIC QUAD FLAT PACK- NO LEAD**

This image is a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.




4225115/A

# PACKAGE OUTLINE

## VQFN - 1 mm max height

RGF0040B

PLASTIC QUAD FLAT PACK- NO LEAD



4219019/A 06/2020

### NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for optimal thermal and mechanical performance.

# EXAMPLE BOARD LAYOUT


VQFN - 1 mm max height

RGF0040B

PLASTIC QUAD FLAT PACK- NO LEAD



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 12X



4219019/A 06/2020

NOTES: (continued)


4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 ([www.ti.com/lit/slua271](http://www.ti.com/lit/slua271)).
5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.

# EXAMPLE STENCIL DESIGN

VQFN - 1 mm max height

RGF0040B

PLASTIC QUAD FLAT PACK- NO LEAD



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL

EXPOSED PAD  
74% PRINTED COVERAGE BY AREA  
SCALE: 12X

4219019/A 06/2020

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

## 重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做出任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](#) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2026，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月