

## FEATURES

- Wide Bandwidth (BW = 1100 MHz Typ)
- Low Crosstalk ( $X_{TALK} = -37$  dB Typ)
- Low Bit-to-Bit Skew ( $t_{sk(o)} = 100$  ps Max)
- Low and Flat ON-State Resistance ( $r_{ON} = 4 \Omega$  Typ,  $r_{ON(flat)} = 0.5 \Omega$  Typ)
- Low Input/Output Capacitance ( $C_{ON} = 8$  pF Typ)
- Rail-to-Rail Switching on Data I/O Ports (0 to 5 V)
- $V_{CC}$  Operating Range From 3 V to 3.6 V
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Performance Tested Per JESD 22
  - 2000-V Human-Body Model (A114-B, Class II)
  - 1000-V Charged-Device Model (C101)

## APPLICATIONS

- 10/100/1000 Base-T Signal Switching
- Differential (LVDS, LVPECL) Signal Switching
- Audio/Video Switching
- Hub and Router Signal Switching

## DESCRIPTION/ORDERING INFORMATION

The TS3L4892 is a 16-bit to 8-bit multiplexer/demultiplexer LAN switch with a single select (SEL) input. SEL controls the data path of the multiplexer/demultiplexer. The device provides additional I/Os for switching status indicating LED signals.

The device provides a low and flat ON-state resistance ( $r_{ON}$ ) and an excellent ON-state resistance match. Low input/output capacitance, high bandwidth, low skew, and low crosstalk among channels make this device suitable for various LAN applications, such as 10/100/1000 Base-T.

This device can be used to replace mechanical relays in LAN applications. It also can be used to route signals from a 10/100 Base-T ethernet transceiver to the RJ-45 LAN connectors in laptops or in docking stations.

## ORDERING INFORMATION

| $T_A$         | PACKAGE <sup>(1)(2)</sup> |               | ORDERABLE PART NUMBER | TOP-SIDE MARKING |
|---------------|---------------------------|---------------|-----------------------|------------------|
| –40°C to 85°C | QFN – RHH                 | Tape and reel | TS3L4892RHHR          | TK4892           |


(1) Package drawings, standard packing quantities, and symbolization are available at [www.ti.com/packaging](http://www.ti.com/packaging).

(2) For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI website at [www.ti.com](http://www.ti.com).

## FUNCTION TABLE

| INPUT<br>SEL | INPUT/OUTPUT<br>$A_n$ | FUNCTION                        |
|--------------|-----------------------|---------------------------------|
| L            | $nB_1$                | $A_n = nB_1$ , $LED_x = XLED_1$ |
| H            | $nB_2$                | $A_n = nB_2$ , $LED_x = XLED_2$ |

**RHH PACKAGE  
(TOP VIEW)**



**PIN DESCRIPTION**

| NAME     | DESCRIPTION  |
|----------|--------------|
| $A_n$    | Data I/O     |
| $nB_m$   | Data I/O     |
| SEL      | Select input |
| $LED_x$  | LED I/O port |
| $XLED_m$ | LED I/O port |



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.




# TS3L4892

## 16-BIT TO 8-BIT SPDT GIGABIT LAN SWITCH WITH LED SWITCH

SCDS251–MARCH 2008

### LOGIC DIAGRAM (POSITIVE LOGIC)





## ABSOLUTE MAXIMUM RATINGS<sup>(1)</sup>

over operating free-air temperature range (unless otherwise noted)

|                  |   | MIN                  | MAX  | UNIT   |
|------------------|---|----------------------|------|--------|
| V <sub>CC</sub>  | Supply voltage range                              | –0.5                 | 4.6  | V      |
| V <sub>IN</sub>  | Control input voltage range <sup>(2)(3)</sup>     | –0.5                 | 7    | V      |
| V <sub>I/O</sub> | Switch I/O voltage range <sup>(2)(3)(4)</sup>     | –0.5                 | 7    | V      |
| I <sub>IK</sub>  | Control input clamp current                       | V <sub>IN</sub> < 0  |      | –50 mA |
| I <sub>I/O</sub> | I/O port clamp current                            | V <sub>I/O</sub> < 0 |      | –50 mA |
| I <sub>I/O</sub> | ON-state switch current <sup>(5)</sup>            |                      | ±128 | mA     |
|                  | Continuous current through V <sub>DD</sub> or GND |                      | ±100 | mA     |
| θ <sub>JA</sub>  | Package thermal impedance <sup>(6)</sup>          |                      | 31.8 | °C/W   |
| T <sub>stg</sub> | Storage temperature range                         | –65                  | 150  | °C     |

- (1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) All voltages are with respect to ground, unless otherwise specified.
- (3) The input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.
- (4) V<sub>I</sub> and V<sub>O</sub> are used to denote specific conditions for V<sub>I/O</sub>.
- (5) I<sub>I</sub> and I<sub>O</sub> are used to denote specific conditions for I<sub>I/O</sub>.
- (6) The package thermal impedance is calculated in accordance with JESD 51-7.

## RECOMMENDED OPERATING CONDITIONS<sup>(1)</sup>

|                  |  | MIN | MAX             | UNIT |
|------------------|--|-----|-----------------|------|
| V <sub>CC</sub>  | Supply voltage                         | 3   | 3.6             | V    |
| V <sub>IH</sub>  | High-level control input voltage (SEL) | 2   | 5.5             | V    |
| V <sub>IL</sub>  | Low-level control input voltage (SEL)  | 0   | 0.8             | V    |
| V <sub>I</sub>   | Input voltage (SEL)                    | 0   | 5.5             | V    |
| V <sub>I/O</sub> | Input/output voltage                   | 0   | V <sub>CC</sub> | V    |
| T <sub>A</sub>   | Operating free-air temperature         | –40 | 85              | °C   |

- (1) All unused control inputs of the device must be held at V<sub>DD</sub> or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.



# TS3L4892

## 16-BIT TO 8-BIT SPDT GIGABIT LAN SWITCH WITH LED SWITCH

SCDS251–MARCH 2008

### ELECTRICAL CHARACTERISTICS

for 1000 Base-T Ethernet switching over recommended operating free-air temperature range,  $V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$  (unless otherwise noted)

| PARAMETER                            |        | TEST CONDITIONS <sup>(1)</sup> |  | MIN | TYP <sup>(2)</sup> | MAX     | UNIT          |
|--------------------------------------|--------|--------------------------------|--|-----|--------------------|---------|---------------|
| $V_{IK}$                             | SEL    | $V_{CC} = 3.6 \text{ V}$ ,     | $I_{IN} = -18 \text{ mA}$              |     | -0.7               | -1.2    | V             |
| $I_{IH}$                             | SEL    | $V_{CC} = 3.6 \text{ V}$ ,     | $V_{IN} = V_{CC}$                      |     |                    | $\pm 1$ | $\mu\text{A}$ |
| $I_{IL}$                             | SEL    | $V_{CC} = 3.6 \text{ V}$ ,     | $V_{IN} = \text{GND}$                  |     |                    | $\pm 1$ | $\mu\text{A}$ |
| $I_{CC}$                             |        | $V_{CC} = 3.6 \text{ V}$ ,     | $I_{IO} = 0$ ,                         |     | 250                | 500     | $\mu\text{A}$ |
|                                      |        | Switch ON or OFF               |  |     |                    |         |               |
| $C_{IN}$                             | SEL    | $f = 1 \text{ M Hz}$ ,         | $V_{IN} = 0$                           |     | 2                  | 2.5     | pF            |
| $C_{OFF}$                            | B port | $V_I = 0$ ,                    | $f = 1 \text{ MHz}$ ,                  |     | 2.5                | 4       | pF            |
|                                      |        | Outputs open, Switch OFF       |  |     |                    |         |               |
| $C_{ON}$                             |        | $V_I = 0$ ,                    | $f = 1 \text{ MHz}$ ,                  |     | 8                  | 9       | pF            |
|                                      |        | Outputs open, Switch ON        |  |     |                    |         |               |
| $r_{ON}$                             |        | $V_{CC} = 3 \text{ V}$ ,       | $1.5 \text{ V} \leq V_I \leq V_{CC}$ , |     | 4                  | 6       | $\Omega$      |
|                                      |        | $I_O = -40 \text{ mA}$         |  |     |                    |         |               |
| $r_{ON(\text{flat})}$ <sup>(3)</sup> |        | $V_{CC} = 3 \text{ V}$ ,       | $V_I = 1.5 \text{ V}$ and $V_{CC}$ ,   |     | 0.5                |         | $\Omega$      |
|                                      |        | $I_O = -40 \text{ mA}$         |  |     |                    |         |               |
| $\Delta r_{ON}$ <sup>(4)</sup>       |        | $V_{CC} = 3 \text{ V}$ ,       | $1.5 \text{ V} \leq V_I \leq V_{CC}$ , |     | 0.4                | 1       | $\Omega$      |
|                                      |        | $I_O = -40 \text{ mA}$         |  |     |                    |         |               |

- (1)  $V_I$ ,  $V_O$ ,  $I_I$ , and  $I_O$  refer to I/O pins.  $V_{IN}$  refers to the control inputs.  
(2) All typical values are at  $V_{CC} = 3.3 \text{ V}$  (unless otherwise noted),  $T_A = 25^\circ\text{C}$ .  
(3)  $r_{ON(\text{flat})}$  is the difference of  $r_{ON}$  in a given channel at specified voltages.  
(4)  $\Delta r_{ON}$  is the difference of  $r_{ON}$  from center ( $A_4$ ,  $A_5$ ) ports to any other port.

### ELECTRICAL CHARACTERISTICS

for 10/100 Base-T Ethernet switching over recommended operating free-air temperature range,  $V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$  (unless otherwise noted)

| PARAMETER                            |        | TEST CONDITIONS <sup>(1)</sup>             |   | MIN | TYP <sup>(2)</sup> | MAX     | UNIT          |
|--------------------------------------|--------|--|---|-----|--------------------|---------|---------------|
| $V_{IK}$                             | SEL    | $V_{CC} = 3.6 \text{ V}$ ,                 | $I_{IN} = -18 \text{ mA}$               |     | -0.7               | -1.2    | V             |
| $I_{IH}$                             | SEL    | $V_{CC} = 3.6 \text{ V}$ ,                 | $V_{IN} = V_{CC}$                       |     |                    | $\pm 1$ | $\mu\text{A}$ |
| $I_{IL}$                             | SEL    | $V_{CC} = 3.6 \text{ V}$ ,                 | $V_{IN} = \text{GND}$                   |     |                    | $\pm 1$ | $\mu\text{A}$ |
| $I_{CC}$                             |        | $V_{CC} = 3.6 \text{ V}$ ,                 | $I_{IO} = 0$ ,                          |     | 250                | 500     | $\mu\text{A}$ |
|                                      |        | Switch ON or OFF                           |   |     |                    |         |               |
| $C_{IN}$                             | SEL    | $f = 1 \text{ MHz}$ ,                      | $V_{IN} = 0$                            |     | 2                  | 2.5     | pF            |
| $C_{OFF}$                            | B port | $V_I = 0$ ,                                | $f = 1 \text{ MHz}$ ,                   |     | 2.5                | 4       | pF            |
|                                      |        | Outputs open, Switch OFF                   |   |     |                    |         |               |
| $C_{ON}$                             |        | $V_I = 0$ ,                                | $f = 1 \text{ MHz}$ ,                   |     | 8                  |         | pF            |
|                                      |        | Outputs open, Switch ON                    |   |     |                    |         |               |
| $r_{ON}$                             |        | $V_{CC} = 3 \text{ V}$ ,                   | $1.25 \text{ V} \leq V_I \leq V_{CC}$ , |     | 4                  | 6       | $\Omega$      |
|                                      |        | $I_O = -10 \text{ mA}$ to $-30 \text{ mA}$ |   |     |                    |         |               |
| $r_{ON(\text{flat})}$ <sup>(3)</sup> |        | $V_{CC} = 3 \text{ V}$ ,                   | $V_I = 1.25 \text{ V}$ and $V_{CC}$ ,   |     | 0.5                |         | $\Omega$      |
|                                      |        | $I_O = -10 \text{ mA}$ to $-30 \text{ mA}$ |   |     |                    |         |               |
| $\Delta r_{ON}$ <sup>(4)</sup>       |        | $V_{CC} = 3 \text{ V}$ ,                   | $1.25 \text{ V} \leq V_I \leq V_{CC}$ , |     | 0.4                | 1       | $\Omega$      |
|                                      |        | $I_O = -10 \text{ mA}$ to $-30 \text{ mA}$ |   |     |                    |         |               |

- (1)  $V_I$ ,  $V_O$ ,  $I_I$ , and  $I_O$  refer to I/O pins.  $V_{IN}$  refers to the control inputs.  
(2) All typical values are at  $V_{CC} = 3.3 \text{ V}$  (unless otherwise noted),  $T_A = 25^\circ\text{C}$ .  
(3)  $r_{ON(\text{flat})}$  is the difference of  $r_{ON}$  in a given channel at specified voltages.  
(4)  $\Delta r_{ON}$  is the difference of  $r_{ON}$  from center ( $A_4$ ,  $A_5$ ) ports to any other port.



## SWITCHING CHARACTERISTICS

over recommended operating free-air temperature range,  $V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$ ,  $R_L = 200 \Omega$ ,  $C_L = 10 \text{ pF}$   
(unless otherwise noted) (see Figures 4 and 5)

| PARAMETER             | FROM<br>(INPUT) | TO<br>(OUTPUT) | MIN | TYP <sup>(1)</sup> | MAX | UNIT |
|-----------------------|-----------------|----------------|-----|--------------------|-----|------|
| $t_{pd}^{(2)}$        | A or B          | B or A         |     | 40                 |     | ps   |
| $t_{PZH}$ , $t_{PZL}$ | SEL             | A or B         | 0.5 |                    | 15  | ns   |
| $t_{PHZ}$ , $t_{PLZ}$ | SEL             | A or B         | 0.9 |                    | 9   | ns   |
| $t_{sk(o)}^{(3)}$     | A or B          | B or A         |     | 50                 | 100 | ps   |
| $t_{sk(p)}^{(4)}$     |                 |                |     | 50                 | 150 | ps   |

(1) All typical values are at  $V_{CC} = 3.3 \text{ V}$  (unless otherwise noted),  $T_A = 25^\circ\text{C}$ .

(2) The propagation delay is the calculated RC time constant of the typical ON-state resistance of the switch and the specified load capacitance when driven by an ideal voltage source (zero output impedance).

(3) Output skew between center port ( $A_4$  to  $A_5$ ) to any other port

(4) Skew between opposite transitions of the same output in a given device  $|t_{PHL} - t_{PLH}|$

## DYNAMIC CHARACTERISTICS

over recommended operating free-air temperature range,  $V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$  (unless otherwise noted)

| PARAMETER  | TEST CONDITIONS      |                         |              | TYP <sup>(1)</sup> | UNIT |
|------------|----------------------|-------------------------|--------------|--------------------|------|
| $X_{TALK}$ | $R_L = 100 \Omega$ , | $f = 250 \text{ MHz}$ , | See Figure 8 | –37                | dB   |
| $O_{IRR}$  | $R_L = 100 \Omega$ , | $f = 250 \text{ MHz}$ , | See Figure 9 | –37                | dB   |
| BW         | $R_L = 100 \Omega$ , | See Figure 7            |              | 1100               | MHz  |

(1) All typical values are at  $V_{CC} = 3.3 \text{ V}$  (unless otherwise noted),  $T_A = 25^\circ\text{C}$ .



## OPERATING CHARACTERISTICS




Figure 1. Gain vs Frequency




Figure 2. OFF Isolation vs Frequency




Figure 3. Crosstalk vs Frequency






Figure 4.  $r_{ON}$  ( $\Omega$ ) vs  $V_{com}$  (V)



## PARAMETER MEASUREMENT INFORMATION (Enable and Disable Times)



| TEST                               | V <sub>CC</sub> | S1                  | R <sub>L</sub> | V <sub>I</sub>  | C <sub>L</sub> | V <sub>Δ</sub> |
|------------------------------------|-----------------|---------------------|----------------|-----------------|----------------|----------------|
| t <sub>PLZ</sub> /t <sub>PZL</sub> | 3.3 V ± 0.3 V   | 2 × V <sub>CC</sub> | 200 Ω          | GND             | 10 pF          | 0.3 V          |
| t <sub>PHZ</sub> /t <sub>PZH</sub> | 3.3 V ± 0.3 V   | GND                 | 200 Ω          | V <sub>CC</sub> | 10 pF          | 0.3 V          |




- NOTES: A. C<sub>L</sub> includes probe and jig capacitance.  
 B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.  
 C. All input pulses are supplied by generators having the following characteristics: PRR ≤ 10 MHz, Z<sub>O</sub> = 50 Ω, t<sub>r</sub> ≤ 2.5 ns, t<sub>f</sub> ≤ 2.5 ns.  
 D. The outputs are measured one at a time, with one transition per measurement.  
 E. t<sub>PLZ</sub> and t<sub>PHZ</sub> are the same as t<sub>dis</sub>.  
 F. t<sub>PZL</sub> and t<sub>PZH</sub> are the same as t<sub>en</sub>.



Figure 5. Test Circuit and Voltage Waveforms



# **PARAMETER MEASUREMENT INFORMATION** **(Skew)**



| TEST               | V <sub>CC</sub> | S1   | R <sub>L</sub> | V <sub>in</sub>        | C <sub>L</sub> |
|--------------------|-----------------|------|----------------|------------------------|----------------|
| t <sub>sk(o)</sub> | 3.3 V ± 0.3 V   | Open | 200 Ω          | V <sub>CC</sub> or GND | 10 pF          |
| t <sub>sk(p)</sub> | 3.3 V ± 0.3 V   | Open | 200 Ω          | V <sub>CC</sub> or GND | 10 pF          |




- NOTES: A. C<sub>L</sub> includes probe and jig capacitance.  
B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.  
C. All input pulses are supplied by generators having the following characteristics: PRR ≤ 10 MHz, Z<sub>O</sub> = 50 Ω, t<sub>r</sub> ≤ 2.5 ns, t<sub>f</sub> ≤ 2.5 ns.  
D. The outputs are measured one at a time, with one transition per measurement.

**Figure 6. Test Circuit and Voltage Waveforms**



## PARAMETER MEASUREMENT INFORMATION



A.  $C_L$  includes probe and jig capacitance.

**Figure 7. Test Circuit for Frequency Response (BW)**


Frequency response is measured at the output of the ON channel. For example, when  $V_{SEL} = 0$  and  $A_0$  is the input, the output is measured at  $0B_1$ . All unused analog I/O ports are left open.

### HP8753ES Setup

Average = 4  
RBW = 3 kHz  
 $V_{BIAS} = 0.35$  V  
ST = 2 s  
P1 = 0 dBm



**PARAMETER MEASUREMENT INFORMATION (continued)**



- A.  $C_L$  includes probe and jig capacitance.
- B. A 50- $\Omega$  termination resistor is needed to match the loading of the network analyzer.

**Figure 8. Test Circuit for Crosstalk ( $X_{TALK}$ )**


Crosstalk is measured at the output of the nonadjacent ON channel. For example, when  $V_{SEL} = 0$  and  $A_0$  is the input, the output is measured at  $1B_1$ . All unused analog input (A) ports are connected to GND, and output (B) ports are connected to GND through 50- $\Omega$  pulldown resistors.

**HP8753ES Setup**

Average = 4  
RBW = 3 kHz  
 $V_{BIAS} = 0.35$  V  
ST = 2 s  
P1 = 0 dBm



## PARAMETER MEASUREMENT INFORMATION (continued)



- A.  $C_L$  includes probe and jig capacitance.
- B. A 50- $\Omega$  termination resistor is needed to match the loading of the network analyzer.

**Figure 9. Test Circuit for Off Isolation ( $O_{IRR}$ )**

OFF isolation is measured at the output of the OFF channel. For example, when  $V_{SEL} = V_{CC}$  and  $A_0$  is the input, the output is measured at  $0B_2$ . All unused analog input (A) ports are left open, and output (B) ports are connected to GND through 50- $\Omega$  pulldown resistors.

### HP8753ES Setup

Average = 4  
RBW = 3 kHz  
 $V_{BIAS} = 0.35$  V  
ST = 2 s  
P1 = 0 dBm



## PACKAGING INFORMATION

| Orderable part number        | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TS3L4892RHHR</a> | Active        | Production           | VQFN (RHH)   36 | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-3-260C-168 HR               | -40 to 85    | TK4892              |
| TS3L4892RHHR.B               | Active        | Production           | VQFN (RHH)   36 | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-3-260C-168 HR               | -40 to 85    | TK4892              |
| TS3L4892RHHRG4               | Active        | Production           | VQFN (RHH)   36 | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-3-260C-168 HR               | -40 to 85    | TK4892              |
| TS3L4892RHHRG4.B             | Active        | Production           | VQFN (RHH)   36 | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-3-260C-168 HR               | -40 to 85    | TK4892              |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device         | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TS3L4892RHHR   | VQFN         | RHH             | 36   | 2500 | 330.0              | 16.4               | 6.3     | 6.3     | 1.1     | 12.0    | 16.0   | Q2            |
| TS3L4892RHHRG4 | VQFN         | RHH             | 36   | 2500 | 330.0              | 16.4               | 6.3     | 6.3     | 1.1     | 12.0    | 16.0   | Q2            |



## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device         | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TS3L4892RHHR   | VQFN         | RHH             | 36   | 2500 | 353.0       | 353.0      | 32.0        |
| TS3L4892RHHRG4 | VQFN         | RHH             | 36   | 2500 | 353.0       | 353.0      | 32.0        |



## GENERIC PACKAGE VIEW


**RHH 36**

**VQFN - 1 mm max height**

6 x 6, 0.5 mm pitch

PLASTIC QUAD FLATPACK - NO LEAD

This image is a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.



4225440/A



1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.




# EXAMPLE BOARD LAYOUT


RHH0036B

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 15X



4225414/A 10/2019

NOTES: (continued)

- This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 ([www.ti.com/lit/sluea271](http://www.ti.com/lit/sluea271)).
- Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.




# EXAMPLE STENCIL DESIGN

RHH0036B

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



SOLDER PASTE EXAMPLE  
BASED ON 0.125 MM THICK STENCIL  
SCALE: 15X

EXPOSED PAD 37  
72% PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE

4225414/A 10/2019

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025